

Power Splitter/Combiner

2 Way-0°

SP-ED12593/4

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CA531

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		3200		3600 MHz
Isolation	3200 - 3600 MHz		20	dB
Insertion Loss Above 3.0 dB	3200 - 3600 MHz		0.50	dB
Phase Unbalance	3200 - 3600 MHz		0.092	deg.
Amplitude Unbalance	3200 - 3600 MHz		0.034	dB
VSWR	SUM Port		1.30	(:1)
	OUT Ports		1.25	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Functional Diagram



2 Way-0° Power Splitter/Combiner

SP-ED12593/4

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
500.0	3.63	3.64	0.01	3.89	0.02	500.0	1.91	1.90	1.89
750.0	3.63	3.66	0.03	4.09	0.01	750.0	1.88	1.87	1.87
1000.0	3.62	3.65	0.02	4.38	0.04	1000.0	1.84	1.85	1.84
1125.0	3.60	3.65	0.04	4.55	0.06	1125.0	1.83	1.83	1.83
1250.0	3.59	3.64	0.06	4.75	0.03	1250.0	1.81	1.81	1.81
1375.0	3.59	3.63	0.04	5.02	0.13	1375.0	1.78	1.78	1.78
1500.0	3.58	3.61	0.03	5.33	0.08	1500.0	1.75	1.75	1.74
1750.0	3.54	3.58	0.05	6.06	0.07	1750.0	1.69	1.68	1.66
1875.0	3.53	3.57	0.04	6.57	0.01	1875.0	1.65	1.62	1.61
2000.0	3.53	3.55	0.02	7.16	0.02	2000.0	1.61	1.56	1.55
2125.0	3.52	3.52	0.01	7.82	0.15	2125.0	1.57	1.50	1.49
2250.0	3.49	3.51	0.02	8.63	0.24	2250.0	1.53	1.45	1.43
2500.0	3.44	3.48	0.04	10.75	0.01	2500.0	1.43	1.31	1.29
2750.0	3.43	3.45	0.02	13.96	0.01	2750.0	1.33	1.17	1.17
2875.0	3.41	3.44	0.03	16.20	0.05	2875.0	1.29	1.11	1.11
3000.0	3.40	3.45	0.05	19.14	0.03	3000.0	1.26	1.05	1.06
3050.0	3.39	3.45	0.06	20.65	0.04	3050.0	1.24	1.02	1.04
3075.0	3.40	3.45	0.05	21.51	0.06	3075.0	1.23	1.02	1.03
3100.0	3.40	3.44	0.04	22.44	0.06	3100.0	1.22	1.04	1.04
3200.0	3.42	3.45	0.03	26.76	0.04	3200.0	1.22	1.08	1.06
3300.0	3.44	3.47	0.03	29.16	0.08	3300.0	1.23	1.11	1.11
3400.0	3.46	3.49	0.03	25.39	0.15	3400.0	1.26	1.17	1.16
3425.0	3.47	3.50	0.04	24.28	0.12	3425.0	1.28	1.17	1.17
3500.0	3.50	3.53	0.03	21.54	0.13	3500.0	1.33	1.25	1.21
3525.0	3.50	3.54	0.04	20.73	0.16	3525.0	1.34	1.26	1.22
3575.0	3.52	3.57	0.05	19.32	0.04	3575.0	1.39	1.27	1.25
3600.0	3.54	3.58	0.04	18.70	0.01	3600.0	1.41	1.31	1.26
3650.0	3.57	3.61	0.04	17.52	0.04	3650.0	1.44	1.35	1.29
3675.0	3.58	3.63	0.05	17.01	0.03	3675.0	1.47	1.35	1.31
3700.0	3.60	3.66	0.05	16.52	0.12	3700.0	1.50	1.35	1.32
3725.0	3.63	3.67	0.04	16.05	0.16	3725.0	1.53	1.38	1.34
3750.0	3.66	3.69	0.03	15.6	0.13	3750.0	1.56	1.41	1.36
3800.0	3.71	3.75	0.04	14.77	0.10	3800.0	1.61	1.44	1.38
3850.0	3.78	3.81	0.03	14.03	0.27	3850.0	1.69	1.45	1.42
3875.00	3.82	3.84	0.02	13.69	0.31	3875.00	1.74	1.49	1.44
3900.00	3.86	3.86	0.01	13.35	0.23	3900.00	1.77	1.52	1.45
3950.00	3.92	3.92	0.01	12.70	0.01	3950.00	1.84	1.54	1.49
4000.00	4.05	4.04	0.01	12.10	0.02	4000.00	1.98	1.58	1.54
4050.00	4.09	4.07	0.02	11.56	0.01	4050.00	2.02	1.59	1.56
4100.00	4.20	4.18	0.03	10.99	0.06	4100.00	2.15	1.64	1.60
4150.00	4.31	4.28	0.03	10.52	0.06	4150.00	2.27	1.70	1.64
4200.00	4.43	4.39	0.04	10.04	0.17	4200.00	2.39	1.77	1.68
4250.00	4.54	4.52	0.03	9.55	0.24	4250.00	2.52	1.79	1.72
4300.00	4.68	4.67	0.01	9.16	0.18	4300.00	2.68	1.84	1.77
4350.00	4.83	4.82	0.01	8.73	0.16	4350.00	2.84	1.89	1.81
4400.00	5.01	5.00	0.01	8.38	0.03	4400.00	3.04	1.90	1.85
4500.00	5.40	5.37	0.03	7.65	0.06	4500.00	3.47	1.97	1.94
4550.00	5.62	5.58	0.04	7.33	0.03	4550.00	3.72	2.00	1.99
4600.00	5.85	5.79	0.06	7.03	0.03	4600.00	3.99	2.06	2.04
4700.00	6.33	6.26	0.07	6.41	0.08	4700.00	4.59	2.16	2.13
4800.00	6.85	6.81	0.04	5.84	0.28	4800.00	5.31	2.25	2.20
4850.00	7.15	7.13	0.02	5.58	0.25	4850.00	5.74	2.29	2.24
4900.00	7.47	7.47	0.01	5.30	0.16	4900.00	6.22	2.32	2.27
5000.00	8.23	8.20	0.03	4.88	0.28	5000.00	7.31	2.39	2.36

¹ Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2

SP-ED12593/4

100707

Page 1 of 1



RF/MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner

SP-ED12593/4

Typical Performance Curves



REV. X2
SP-ED12593/4
100707
Page 1 of 1




Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$



CASE #	A	B	C	D	E	F	G	H	J	K
CA531	.052 (1.32)	.067 (1.70)	.106 (2.69)	.122 (3.10)	.035 (0.89)	.064 (1.63)	.087 (2.21)	.118 (3.00)	.067 (1.70)	.083 (2.11)

CASE #	L	M	N	P	Q	R	S	WT. GRAM
CA531	.033 (0.84)	.042 (1.07)	.012 (0.30)	.020 (0.51)	.012 (0.30)	.006 (0.15)	.018 (0.46)	.020

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier.
(Unless stated otherwise on Data sheet).



INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F31

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			Standard	1000


Note: Please Consult individual model data sheet to determine device per reel availability

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M102559	NEW RELEASE	02/23/06	MMG	HY


SUGGESTED MOUNTING CONFIGURATION FOR CA531 CASE STYLE, "jk" PIN CONNECTION



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" $\pm$.0015"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	MMG	02/22/06
	CHECKED	AV	02/23/06
	APPROVED	HY	02/23/06




Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, jk, CA531, SP-2C+ (P+, U+), TB-374


Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THEREON. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.			
ASHEETA1.DWG	REV:A	DATE:01/12/95	

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-232	OR
FILE:	98PL232	SCALE:	10:1
SHEET:	1	OF	1

Evaluation Board and Circuit



TB-374



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350B or its equivalent, Dielectric Constant=3.5, Thickness=.020"

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D