

Engineering Development Model

Frequency Synthesizer

SSN-EDR9582

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : KJ1367

ELECTRICAL SPECIFICATIONS 50Ω, over -40°C to +85°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	1542		1557	MHz
Step size		200		kHz
Settling Time Within ±1kHz		2		msec
Output Power	0	+4	+7	dBm
Phase Noise				
at 100 Hz offset		-90		dBc/Hz
at 1 kHz offset		-98		dBc/Hz
at 10 kHz offset		-101	-95	dBc/Hz
at 100 kHz offset		-127	-122	dBc/Hz
at 1000 kHz offset		-148	-142	dBc/Hz
Integrated SSB Phase Noise		-57		dBc
Reference Spurious Suppression		-87		dBc
Comparison Spurious Suppression		-90		dBc
0.5 Step size Spurious Suppression		-104		dBc
Non-Harm. Spurious Suppression		-90		dBc
Harmonic Suppression		-30	-21	dBc
Supply voltage VCO		4.75		V
Supply voltage PLL		3.11		V
Supply current VCO		47	55	V
Supply current PLL		16	25	V
Reference In (External)				
Frequency		52		MHz
Amplitude		1		Vp-p
Impedance		100		kΩ
Ph. N @ 1kHz		-145		dBc/Hz
Input Logic Levels	Logic high	1.4	3.11	V
	Logic Low		0.6	V
Digital Lock Detect	Locked	1.4	3.11	V
	Unlocked		0.4	V
Frequency Synthesizer PLL		ADF4153		

ABSOLUTE MAXIMUM RATINGS	
Operating Temperature	-45°C to 85°C
Storage Temperature	-55°C to 100°C
VCO Supply Voltage	5.75V
PLL Supply Voltage	4.11V
Reference Frequency voltage	3.6Vp-p
Data, Clock & LE levels	3.41V

Power On sequence: Vcc VCO followed by Vcc PLL
Power Off sequence: Vcc PLL followed by Vcc VCO

PIN CONNECTIONS			
RF OUT	9	CLOCK	1
VCC VCO	7	DATA	2
VCC PLL	12	LATCH ENABLE	3
REF IN	4	GROUND	5,6,8,10
LOCK DETECT	11		

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
SSN-EDR9582
150205

Frequency Synthesizer

SSN-EDR9582

Typical Performance Data

FREQ. (MHz)	POWER OUTPUT (dBm)			HARMONICS						VCO CURRENT (mA)			PLL CURRENT (mA)		
				(dBc)											
	-40 °C	+25°C	+85 °C	-40 °C	+25°C	+85 °C	-40 °C	+25°C	+85 °C	-40 °C	+25°C	+85 °C	-40 °C	+25°C	+85 °C
1533.0	3.36	3.81	4.06	-22.63	-25.68	-28.69	-25.69	-26.32	-27.96	45.64	46.89	48.04	14.87	16.18	18.20
1536.4	3.42	3.85	4.08	-23.46	-26.39	-29.32	-25.59	-25.73	-27.27	45.58	46.85	48.01	14.86	16.22	18.25
1539.8	3.46	3.90	4.12	-24.69	-27.83	-30.78	-25.70	-26.05	-27.21	45.56	46.82	47.98	15.16	16.55	18.61
1542.0	3.48	3.91	4.13	-25.36	-28.75	-31.84	-25.63	-26.47	-27.87	45.53	46.79	47.97	15.22	16.65	18.72
1543.2	3.48	3.91	4.12	-25.57	-29.16	-32.32	-25.57	-26.55	-28.20	45.52	46.78	47.96	15.29	16.71	18.80
1546.6	3.47	3.89	4.10	-25.47	-29.51	-32.99	-25.31	-26.62	-28.81	45.42	46.74	47.93	15.36	16.80	18.89
1550.0	3.48	3.86	4.06	-25.47	-28.96	-32.32	-25.73	-26.85	-28.64	45.34	46.67	47.90	15.35	16.79	18.90
1553.4	3.50	3.88	4.05	-25.58	-28.92	-31.85	-25.88	-27.18	-28.81	45.29	46.61	47.85	15.21	16.65	18.76
1556.8	3.52	3.90	4.06	-25.90	-29.28	-32.24	-25.56	-27.20	-29.11	45.24	46.58	47.81	15.00	16.44	18.54
1557.0	3.52	3.90	4.06	-25.93	-29.33	-32.26	-25.53	-27.15	-29.08	45.23	46.57	47.81	14.99	16.43	18.54
1560.2	3.56	3.91	4.06	-26.53	-29.89	-32.77	-24.56	-26.19	-28.44	45.18	46.53	47.78	14.67	16.09	18.20
1563.6	3.58	3.92	4.05	-27.09	-30.57	-33.39	-24.51	-25.46	-27.55	45.12	46.48	47.75	15.00	16.45	18.57
1567.0	3.58	3.91	4.03	-27.49	-30.64	-33.66	-25.13	-25.84	-27.84	45.07	46.44	47.72	15.18	16.63	18.76

FREQ. (MHz)	PHASE NOISE (dBc/Hz)														
	@ OFFSETS														
	-40 °C					+25°C					+85 °C				
	100Hz	1kHz	10kHz	100kHz	1MHz	100Hz	1kHz	10kHz	100kHz	1MHz	100Hz	1kHz	10kHz	100kHz	1MHz
1533.0	-88.44	-95.80	-99.52	-128.08	-149.17	-90.84	-97.66	-100.79	-126.97	-147.84	-88.69	-98.83	-100.63	-125.22	-145.88
1536.4	-86.58	-96.42	-99.92	-128.27	-149.59	-89.02	-98.35	-100.77	-126.96	-147.94	-90.64	-99.63	-100.28	-124.29	-145.78
1539.8	-87.33	-94.08	-99.95	-128.36	-149.38	-89.56	-98.22	-100.68	-127.09	-147.81	-91.21	-100.95	-100.14	-125.21	-146.04
1542.0	-87.68	-96.39	-100.33	-128.13	-148.97	-89.83	-98.43	-101.04	-127.17	-148.02	-91.05	-99.24	-100.31	-125.18	-146.17
1543.2	-88.20	-96.02	-99.22	-126.29	-148.24	-90.14	-98.53	-100.66	-127.01	-148.18	-91.00	-99.57	-100.65	-125.31	-145.78
1546.6	-87.67	-97.17	-99.65	-127.92	-148.96	-89.61	-98.19	-100.64	-126.79	-147.40	-89.31	-98.21	-100.55	-125.01	-145.97
1550.0	-85.65	-94.01	-100.48	-128.15	-149.02	-92.19	-97.32	-100.66	-126.59	-147.83	-92.72	-99.75	-99.92	-124.86	-145.67
1553.4	-82.80	-95.79	-100.32	-128.16	-149.58	-88.96	-98.51	-100.60	-126.91	-147.93	-90.94	-98.60	-99.40	-124.73	-145.64
1556.8	-87.05	-95.91	-100.17	-128.03	-148.91	-91.12	-99.05	-100.83	-127.00	-147.36	-90.55	-99.14	-100.36	-124.91	-145.71
1557.0	-89.06	-95.58	-100.10	-128.04	-149.45	-90.04	-100.10	-100.76	-126.98	-147.93	-90.46	-99.35	-99.80	-124.98	-145.67
1560.2	-85.71	-95.80	-99.22	-127.96	-149.36	-91.10	-98.98	-100.46	-126.83	-147.46	-93.30	-98.34	-99.55	-124.87	-145.76
1563.6	-85.46	-94.84	-99.42	-128.01	-149.29	-89.67	-97.56	-100.26	-126.84	-147.69	-91.82	-97.80	-99.57	-124.69	-145.57
1567.0	-86.97	-95.38	-99.78	-128.05	-147.97	-92.94	-96.31	-100.34	-126.89	-147.86	-90.31	-99.63	-100.32	-124.89	-145.51

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCULStore/terms.jsp



Frequency Synthesizer

SSN-EDR9582

Typical Performance Data

COMPARISON SPURIOUS ORDER	COMPARISON SPURIOUS @Fcarrier 1542 MHz± (n*Fcomparison) (dBc) NOTE 1			COMPARISON SPURIOUS @Fcarrier 1549.6 MHz± (n*Fcomparison) (dBc) NOTE 1			COMPARISON SPURIOUS @Fcarrier 1557 MHz± (n*Fcomparison) (dBc) NOTE 1		
	-40 °C	+25°C	+85 °C	-40 °C	+25°C	+85 °C	-40 °C	+25°C	+85 °C
-5	-80.03	-83.20	-82.31	-80.22	-83.79	-82.33	-82.25	-85.41	-83.59
-4	-76.61	-76.22	-78.35	-77.04	-76.66	-79.09	-78.71	-78.41	-80.96
-3	-86.00	-86.17	-84.22	-85.81	-85.23	-83.71	-87.11	-85.34	-84.64
-2	-86.89	-88.98	-91.58	-87.14	-89.18	-91.42	-88.75	-90.63	-91.60
-1	-91.70	-90.26	-91.90	-91.66	-89.90	-91.83	-91.52	-90.93	-91.76
0 ^{note 2}	-	-	-	-	-	-	-	-	-
+1	-95.71	-94.76	-94.16	-97.24	-93.61	-95.61	-98.24	-93.62	-95.55
+2	-97.51	-92.88	-102.28	-96.28	-93.53	-107.30	-94.92	-96.08	-108.17
+3	-89.13	-87.82	-88.02	-89.62	-88.19	-88.14	-89.33	-89.22	-89.77
+4	-92.05	-89.37	-97.38	-89.72	-87.96	-93.43	-89.11	-87.82	-91.81
+5	-79.43	-79.59	-83.16	-78.78	-79.24	-83.14	-79.04	-79.78	-84.08

Note 1: Comparison frequency 26 MHz

Note 2: All spurs are referenced to carrier signal (n=0).

REFERENCE SPURIOUS ORDER	REFERENCE SPURIOUS @Fcarrier 1542 MHz± (n*Freffence) (dBc) NOTE 3			REFERENCE SPURIOUS @Fcarrier 1549.6 MHz± (n*Freffence) (dBc) NOTE 3			REFERENCE SPURIOUS @Fcarrier 1557 MHz± (n*Freffence) (dBc) NOTE 3		
	-40 °C	+25°C	+85 °C	-40 °C	+25°C	+85 °C	-40 °C	+25°C	+85 °C
-5	-89.64	-90.64	-89.05	-89.76	-91.12	-89.05	-89.57	-91.38	-89.29
-4	-95.94	-94.08	-91.76	-95.03	-92.27	-90.83	-95.76	-93.63	-90.23
-3	-83.74	-83.77	-89.15	-83.32	-83.59	-88.84	-84.81	-85.24	-92.01
-2	-76.36	-76.25	-78.37	-76.88	-76.68	-79.11	-78.62	-78.43	-80.92
-1	-86.80	-88.98	-91.75	-87.17	-89.32	-91.18	-88.74	-90.48	-91.57
0 ^{note 4}	-	-	-	-	-	-	-	-	-
+1	-97.39	-93.13	-102.96	-96.63	-93.58	-110.41	-95.45	-96.47	-107.98
+2	-92.18	-89.33	-97.68	-89.92	-87.81	-93.35	-88.56	-87.73	-91.89
+3	-85.91	-94.22	-89.78	-85.60	-92.83	-89.32	-86.84	-95.16	-91.44
+4	-94.12	-98.87	-97.12	-93.35	-97.15	-99.02	-93.00	-96.66	-98.22
+5	-89.73	-91.41	-96.87	-89.63	-91.03	-97.86	-90.79	-91.05	-100.64

Note 3: Reference frequency 52 MHz

Note 4: All spurs are referenced to carrier signal (n=0).

Notes




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

SSN-EDR9582

Typical Performance Data



Notes






- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

Typical Performance Data

SSN-EDR9582



Notes







- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Frequency Synthesizer

Typical Performance Data

SSN-EDR9582




Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M124738	NEW RELEASE	04/10	DK	HH
OR	R77823	NEW RELEASE	04/10	DK	HH

SUGGESTED MOUNTING CONFIGURATION

FOR KJ1367 CASE STYLE, 12SY01 PIN CONNECTION, 50 Ω .Ø.020 PTH. TYP.
FOR GROUNDPACKAGE
OUTLINE

NOTES:

- TRACE WIDTH IS SHOWN FOR R04350B WITH DIELECTRIC THICKNESS. .020"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS ±
3 PL DECIMALS ± .005
ANGLES ±
FRACTIONS ±

DRAWN

DK (RAVON)

06 APR 10

CHECKED

DH (RAVON)

07 APR 10

APPROVED

HH (RAVON)

07 APR 10



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 12SY01, KJ1367, SSN
TB-552+ (50 Ω)

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-317

REV:
OR

FILE: 98PL317


SCALE: 5:1

SHEET: 1 OF 1

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Evaluation Board and Circuit



TB-552+

NOTES:

1. SMA FEMALE CONNECTORS.
2. PCB MATERIAL: RO4350B OR EQUIVALENT, DIALECTRIC CONSTANT=3.5, DIALECTRIC THICKNESS=.020 INCH.



TB-552+ Schematic Diagram



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215