

Non-Catalog Model

Frequency Mixer

SRA-17WH

Level 17 (LO Power +17 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : A01

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	20		700	MHz
	RF (fL to fU)	20		700	MHz
	IF	5		340	MHz
Conversion Loss	mid band		7.7	9.0	dB
	Total Range			10.5	dB
LO-RF Isolation	Low Range	45	60		dB
	Mid Range	40	55		dB
	Upper Range	32	50		dB
LO-IF Isolation	Low Range	32	50		dB
	Mid Range	25	45		dB
	Upper Range	18	32		dB
IP3 Input		+27.5	+30		dBm
1 dB Comp. Input Power			+10		dBm

Notes: Low Range = [fL to 10fL] Mid Range = [10fL to fU/2] Upper Range = [fU/2 to fU]
mid band = [2fL to fU/2]


IP3 : RF Power = 0 dBm @ 200 MHz & 202 MHz , LO Power = +17 dBm @ 180 MHz
Hermetically sealed

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA

PIN CONNECTIONS	
LO	8
RF	1
IF	3, 4 ^
GROUND	2, 5, 6, 7

^ - pins must be connected together externally

Electrical Schematics



Frequency Mixer

SRA-17WH

Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
		@LO (dBm)				@LO (dBm)			@LO (dBm)		
		+14	+17	+20		+14	+17	+20	+14	+17	+20
20.0	50.0	7.91	7.81	7.71	50.0	78.0	81.0	83.7	63.3	67.8	72.6
40.0	70.0	7.77	7.67	7.57	70.0	76.5	79.8	82.7	60.3	63.7	67.6
74.6	104.6	7.84	7.64	7.54	104.6	77.4	82.1	87.5	55.8	58.8	62.8
80.0	110.0	7.82	7.62	7.62	110.0	78.6	82.5	88.3	55.4	58.1	62.2
90.0	120.0	7.87	7.67	7.57	120.0	78.9	83.0	88.4	54.4	57.2	61.4
100.0	130.0	7.87	7.67	7.67	130.0	78.9	86.9	89.6	53.3	56.9	61.2
125.0	155.0	7.88	7.78	7.68	155.0	81.5	86.6	83.0	51.4	55.0	58.4
175.0	205.0	8.05	7.85	7.75	205.0	76.6	72.2	69.9	48.6	52.2	54.5
200.0	230.0	8.08	7.88	7.78	230.0	73.2	69.9	68.0	47.7	51.5	52.8
225.0	255.0	8.10	7.90	7.70	255.0	68.4	65.8	64.7	47.4	50.6	50.7
275.0	305.0	8.27	7.97	7.87	305.0	64.4	61.7	60.9	46.0	48.2	47.4
295.5	325.5	8.30	8.10	7.90	325.5	63.5	61.4	60.4	45.3	47.3	46.1
300.0	330.0	8.30	8.10	7.90	330.0	63.4	61.2	60.1	45.0	47.1	45.9
320.0	350.0	8.47	8.17	7.97	350.0	61.7	59.9	58.7	44.5	45.7	44.4
335.0	365.0	8.38	8.18	7.98	365.0	61.7	59.8	58.7	44.5	45.1	43.8
369.2	399.2	8.68	8.38	8.08	399.2	64.4	61.3	59.7	44.7	44.5	42.4
442.8	472.8	8.95	8.55	8.35	472.8	61.2	58.5	57.2	44.0	41.9	39.8
516.4	546.4	9.72	9.22	8.82	546.4	56.3	54.9	54.3	41.7	38.3	36.2
590.1	620.1	9.72	9.32	9.02	620.1	52.8	51.7	51.0	38.6	35.3	33.6
737.3	767.3	9.84	9.54	9.34	767.3	48.9	47.5	46.6	35.5	32.7	31.2

REV. X1
SRA-17WH
060615
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Frequency Mixer

SRA-17WH

Typical Performance Data

RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)		
	@LO (dBm)			@LO (dBm)				@LO (dBm)		
	+14	+17	+20	+14	+17	+20		+14	+17	+20
50.0	1.35	1.36	1.37	1.59	2.06	2.43	5.0	1.12	1.21	1.28
70.0	1.23	1.22	1.23	1.59	2.03	2.43	10.0	1.09	1.19	1.26
104.6	1.18	1.17	1.17	1.59	1.99	2.35	15.7	1.09	1.19	1.26
110.0	1.18	1.17	1.17	1.62	2.03	2.37	20.0	1.10	1.19	1.26
120.0	1.18	1.16	1.17	1.64	2.01	2.40	30.5	1.11	1.20	1.27
130.0	1.18	1.16	1.16	1.62	2.06	2.43	40.0	1.12	1.21	1.28
155.0	1.19	1.17	1.16	1.64	2.10	2.46	45.2	1.13	1.21	1.27
205.0	1.27	1.24	1.23	1.65	2.04	2.43	74.7	1.15	1.22	1.28
230.0	1.32	1.29	1.27	1.70	2.14	2.52	80.0	1.16	1.23	1.29
255.0	1.37	1.34	1.32	1.73	2.12	2.52	104.2	1.19	1.24	1.30
305.0	1.47	1.43	1.40	1.75	2.12	2.46	148.4	1.24	1.29	1.33
325.5	1.53	1.48	1.44	1.80	2.20	2.61	163.1	1.27	1.31	1.36
330.0	1.54	1.49	1.46	1.80	2.23	2.61	177.9	1.28	1.32	1.36
350.0	1.61	1.56	1.52	1.81	2.23	2.58	192.6	1.30	1.33	1.37
365.0	1.67	1.60	1.57	1.78	2.14	2.49	222.1	1.32	1.34	1.38
399.2	1.81	1.75	1.69	1.85	2.20	2.55	236.8	1.34	1.36	1.39
472.8	2.08	2.01	1.94	1.73	2.04	2.30	266.3	1.37	1.37	1.40
546.4	2.37	2.25	2.16	1.75	2.03	2.27	310.5	1.40	1.39	1.40
620.1	2.65	2.52	2.43	1.89	2.14	2.37	325.3	1.38	1.37	1.37
767.3	2.76	2.61	2.55	1.92	2.03	2.20	340.0	1.33	1.30	1.30

REV. X1
SRA-17WH
060615
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


Conversion Loss




LO-RF Isolation




LO-IF Isolation




RF VSWR



LO VSWR



IF VSWR



A01
A04
A05
A06

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	WT, GRAM
A01	.770 (19.56)	.800 (20.32)	.385 (9.78)	.400 (10.16)	.370 (9.40)	.400 (10.16)	.200 (5.08)	.20 (5.08)	.14 (3.56)	.031 (.79)	5.2
A04			.200 (5.08)	.210 (5.33)							3.7
A05			.240 (6.10)	.250 (6.35)							3.7
A06			.285 (7.24)	.310 (7.87)							5.2

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.

Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D