

Surface Mount

Power Splitter/Combiner

SRSC-4-63+

4 Way-0° Resistive 50Ω DC to 6000 MHz

The Big Deal

- Wideband, DC to 6000 MHz
- Low insertion loss, 0.5 dB
- Good matching VSWR, 1.3:1
- Low amplitude unbalance, 0.4 dB



CASE STYLE: CK1704-2

Product Overview

Mini-Circuits' SRSC-4-63+ is a surface-mount 4-way 0° resistive splitter/combiner covering the DC to 6000 MHz frequency range, supporting bandwidth requirements for a wide range of RF/microwave systems. This model can handle up to 0.2W RF input power as a splitter and provides high isolation, good VSWR and low amplitude unbalance. The unit comes housed in a miniature shielded package (0.5 x 0.5 x 0.185") with wrap-around terminations for excellent solderability.

Key Features

Feature	Advantages
Wideband, DC to 6000 MHz	Resistive design enables very wideband coverage down to DC, making the splitter/combiner suitable for a wide variety of broadband applications.
Low insertion loss, 0.5 dB (above 12 dB theoretical loss)	Supports a wide variety of power requirements. The combination of 0.2W power handling and low insertion loss makes this model a suitable candidate for distributing signals while maintaining excellent transmission of signal power.
Good matching VSWR, 1.2:1	Provides excellent thru-path transmission with low signal reflection.
Low amplitude unbalance, 0.4 dB	Low amplitude unbalance makes this splitter/combiner Ideal for parallel path/multichannel systems.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Power Splitter/Combiner

SRSC-4-63+

4 Way-0° Resistive 50Ω DC to 6000 MHz



Generic photo used for illustration purposes only
CASE STYLE: CK1704-2

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	0.2W max.
Internal Dissipation	0.15W max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

SUM PORT	10
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4
GROUND	ALL OTHER


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.500	.500	.185	.100	.080	.115	.030	.040	.540
12.70	12.70	4.70	2.54	2.03	2.92	0.76	1.02	13.72
K	L	M	N	P	Q	R	T	wt.
.030	.100	.135	.135	.115	.140	.060	.080	grams
0.76	2.54	3.43	3.43	2.92	3.56	1.52	2.03	1.0

Demo Board MCL P/N: TB-816+ Suggested PCB Layout (PL-445)



Features

- wideband, DC to 6000 MHz,
- good matching VSWR 1.3:1 typ.
- good amplitude unbalance, 0.4 dB typ.

Applications

- communication systems
- CATV
- cellular, GPS, PCS
- VHF/UHF/receivers/transmitters

Electrical Specifications at 25°C




Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		DC	—	6000	MHz
Insertion Loss, including 12 dB	DC - 3600 3600 - 6000	11.5 11.5	12.0 12.5	13.2 14.0	dB
Isolation	DC - 6000	—	7	—	dB
Phase Unbalance	DC - 3600 3600 - 6000	—	3 8	8 14	Degree
Amplitude Unbalance	DC - 3600 3600 - 6000	—	0.4 0.7	0.8 1.2	dB
VSWR (Port S)	DC - 6000	—	1.35	1.65	:1
VSWR (Port 1-4)	DC - 6000	—	1.30	1.60	:1

This is a resistive power divider to enable frequency coverage from DC to the highest rated frequency. Since resistive power divider do not provide a high degree of isolation (basically isolation equals the insertion loss between ports).

Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)				Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	2-3	2-4						
1	12.09	12.08	12.04	12.04	0.05	6.06	18.08	18.09	0.30	1.00	1.00	1.00	1.01	1.01
400	12.18	12.18	12.15	12.16	0.03	6.13	18.35	18.26	0.44	1.10	1.11	1.11	1.11	1.10
800	12.47	12.50	12.47	12.49	0.04	6.31	19.27	18.87	1.25	1.17	1.21	1.19	1.17	1.17
1200	12.75	12.83	12.77	12.79	0.08	6.46	20.50	19.60	2.18	1.22	1.24	1.21	1.18	1.19
1600	12.90	13.00	12.88	12.85	0.15	6.52	21.76	20.20	3.10	1.30	1.25	1.19	1.17	1.19
2000	12.83	12.96	12.78	12.66	0.31	6.53	22.58	20.34	3.41	1.38	1.29	1.23	1.19	1.24
2400	12.52	12.72	12.51	12.29	0.43	6.58	22.56	19.85	3.28	1.39	1.33	1.28	1.22	1.28
2800	12.08	12.34	12.19	11.91	0.43	6.71	21.90	19.13	2.97	1.27	1.30	1.27	1.20	1.24
3200	11.79	12.03	11.94	11.68	0.34	6.91	20.91	18.59	3.06	1.10	1.19	1.23	1.14	1.15
3600	11.78	12.07	11.98	11.80	0.28	7.15	19.66	18.30	3.81	1.21	1.08	1.13	1.11	1.10
4000	12.03	12.39	12.20	12.13	0.36	7.37	18.63	18.39	4.85	1.35	1.08	1.12	1.09	1.11
4400	12.36	12.71	12.41	12.39	0.35	7.48	18.16	18.97	5.91	1.42	1.17	1.11	1.13	1.17
5000	12.64	12.95	12.65	12.56	0.39	7.68	17.15	19.15	7.06	1.46	1.25	1.12	1.16	1.21
5600	12.65	13.05	13.13	12.63	0.49	8.26	15.62	18.00	8.66	1.17	1.26	1.21	1.21	1.17
6000	12.77	13.11	13.42	12.73	0.68	8.55	14.72	17.32	8.39	1.02	1.28	1.29	1.24	1.18

1. Total Loss = Insertion Loss + 12dB splitter loss.



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
M149373
SRSC-4-63+
ED-17147
JX/CP/AM
200501
Page 2 of 2

4 Way-0° Power Splitter/Combiner

SRSC-4-63+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	2-3	2-4			S	1	2	3	4
1	12.09	12.08	12.04	12.04	0.05	6.06	18.08	18.09	0.30	1	1.00	1.00	1.00	1.01	1.01
5	12.07	12.07	12.04	12.04	0.04	6.06	18.06	18.07	0.10	5	1.00	1.00	1.00	1.01	1.01
10	12.07	12.06	12.03	12.04	0.03	6.06	18.06	18.06	0.11	10	1.00	1.00	1.00	1.01	1.01
50	12.06	12.06	12.03	12.02	0.03	6.06	18.04	18.04	0.12	50	1.01	1.01	1.01	1.01	1.01
70	12.06	12.06	12.03	12.03	0.04	6.06	18.04	18.04	0.07	70	1.01	1.02	1.02	1.02	1.02
100	12.05	12.05	12.03	12.03	0.02	6.06	18.04	18.04	0.12	100	1.02	1.03	1.03	1.03	1.02
200	12.08	12.08	12.05	12.05	0.03	6.07	18.10	18.07	0.22	200	1.05	1.05	1.05	1.05	1.05
400	12.18	12.18	12.15	12.16	0.03	6.13	18.35	18.26	0.44	400	1.10	1.11	1.11	1.11	1.10
600	12.32	12.32	12.30	12.32	0.02	6.21	18.76	18.54	0.79	600	1.14	1.17	1.16	1.15	1.14
800	12.47	12.50	12.47	12.49	0.04	6.31	19.27	18.87	1.25	800	1.17	1.21	1.19	1.17	1.17
1000	12.60	12.68	12.63	12.65	0.08	6.39	19.86	19.24	1.67	1000	1.20	1.23	1.20	1.18	1.19
1200	12.75	12.83	12.77	12.79	0.08	6.46	20.50	19.60	2.18	1200	1.22	1.24	1.21	1.18	1.19
1400	12.83	12.94	12.85	12.85	0.10	6.49	21.14	19.94	2.70	1400	1.26	1.25	1.20	1.17	1.19
1600	12.90	13.00	12.88	12.85	0.15	6.52	21.76	20.20	3.10	1600	1.30	1.25	1.19	1.17	1.19
1800	12.92	13.00	12.85	12.78	0.23	6.53	22.24	20.33	3.39	1800	1.34	1.26	1.21	1.18	1.21
2000	12.83	12.96	12.78	12.66	0.31	6.53	22.58	20.34	3.41	2000	1.38	1.29	1.23	1.19	1.24
2200	12.70	12.86	12.66	12.49	0.36	6.54	22.68	20.16	3.40	2200	1.40	1.31	1.24	1.21	1.27
2400	12.52	12.72	12.51	12.29	0.43	6.58	22.56	19.85	3.28	2400	1.39	1.33	1.28	1.22	1.28
2600	12.26	12.54	12.36	12.09	0.45	6.64	22.31	19.51	3.07	2600	1.35	1.33	1.30	1.21	1.27
2800	12.08	12.34	12.19	11.91	0.43	6.71	21.90	19.13	2.97	2800	1.27	1.30	1.27	1.20	1.24
3000	11.91	12.16	12.03	11.75	0.41	6.81	21.46	18.84	2.94	3000	1.17	1.26	1.25	1.17	1.20
3200	11.79	12.03	11.94	11.68	0.34	6.91	20.91	18.59	3.06	3200	1.10	1.19	1.23	1.14	1.15
3400	11.78	11.99	11.93	11.70	0.29	7.02	20.29	18.40	3.44	3400	1.12	1.12	1.18	1.12	1.11
3600	11.78	12.07	11.98	11.80	0.28	7.15	19.66	18.30	3.81	3600	1.21	1.08	1.13	1.11	1.10
3800	11.85	12.21	12.10	11.96	0.36	7.27	19.07	18.26	4.28	3800	1.29	1.05	1.13	1.09	1.09
4000	12.03	12.39	12.20	12.13	0.36	7.37	18.63	18.39	4.85	4000	1.35	1.08	1.12	1.09	1.11
4200	12.18	12.56	12.32	12.27	0.38	7.42	18.38	18.67	5.30	4200	1.40	1.12	1.10	1.11	1.15
4400	12.36	12.71	12.41	12.39	0.35	7.48	18.16	18.97	5.91	4400	1.42	1.17	1.11	1.13	1.17
4600	12.54	12.83	12.50	12.48	0.34	7.51	17.96	19.26	6.14	4600	1.47	1.20	1.13	1.15	1.19
4800	12.59	12.88	12.58	12.53	0.34	7.57	17.57	19.28	6.54	4800	1.46	1.22	1.13	1.16	1.19
5000	12.64	12.95	12.65	12.56	0.39	7.68	17.15	19.15	7.06	5000	1.46	1.25	1.12	1.16	1.21
5200	12.66	12.98	12.78	12.58	0.40	7.84	16.63	18.82	7.76	5200	1.38	1.26	1.16	1.16	1.19
5400	12.61	13.01	12.95	12.61	0.40	8.05	16.12	18.41	8.28	5400	1.29	1.25	1.20	1.18	1.18
5600	12.65	13.05	13.13	12.63	0.49	8.26	15.62	18.00	8.66	5600	1.17	1.26	1.21	1.21	1.17
5800	12.71	13.12	13.28	12.67	0.61	8.46	15.19	17.66	8.77	5800	1.11	1.29	1.25	1.22	1.16
6000	12.77	13.11	13.42	12.73	0.68	8.55	14.72	17.32	8.39	6000	1.02	1.28	1.29	1.24	1.18
6500	12.84	13.21	13.70	12.90	0.85	8.69	13.63	16.67	7.86	6500	1.02	1.18	1.23	1.14	1.18
7000	13.15	13.73	14.38	13.47	1.22	9.27	12.88	16.34	8.31	7000	1.21	1.09	1.16	1.10	1.17
7500	14.31	15.02	16.00	14.82	1.70	9.98	12.59	16.21	8.74	7500	1.73	1.28	1.33	1.44	1.31
8000	16.19	16.52	17.85	16.82	1.67	9.79	13.58	17.04	10.13	8000	2.02	1.79	1.79	2.09	1.78

¹ Total Loss = Insertion Loss + 12dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com








IF/RF MICROWAVE COMPONENTS

REV. OR
 SRSC-4-63+
 8/24/2016
 Page 1 of 1

4 Way-0° Power Splitter/Combiner

SRSC-4-63+

Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


IF/RF MICROWAVE COMPONENTS

REV. OR
SRSC-4-63+
8/24/2016
Page 1 of 1

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

 METALLIZATION

CASE #	A	B	C	D	E	F	G	H	J	K
CK1704-2	.500 (12.70)	.500 (12.70)	.185 (4.70)	.100 (2.54)	.080 (2.03)	.115 (2.92)	.030 (.760)	.040 (1.02)	.540 (13.72)	.030 (.760)

CASE #	L	M	N	P	Q	R	S	T	WT. GRAM
CK1704-2	.100 (2.54)	.135 (3.43)	.135 (3.43)	.115 (2.92)	.140 (3.56)	.060 (1.52)	-	.080 (2.03)	1.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F37



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
24	16	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200
			500	

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M149695	NEW RELEASE	01/21/15	ITG	JX

SUGGESTED MOUNTING CONFIGURATION
FOR CK1704-2 CASE STYLE, "16SP02" PIN CODE




NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $.010 \pm .001$ ". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS THESE PARAMETERS MAY NEED TO BE MODIFIED.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	ITG	01/19/15
	CHECKED	GF	01/21/15
	APPROVED	JX	01/21/15



Mini-Circuits®



13 Neptune Avenue
Brooklyn NY 11235

PL, 16SP02, CK1704-2, TB-816+

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-445	REV: OR
FILE: 98PL445	SCALE: 6:1	SHEET: 1 OF 1	


Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent, Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215