

## Engineering Development Model

# Frequency Synthesizer

# SSN-EDR11277SA

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : KJ1367

| ELECTRICAL SPECIFICATIONS 50Ω, over -15°C to +75°C |              |      |      |        |
|----------------------------------------------------|--------------|------|------|--------|
| Parameter                                          | Min.         | Typ. | Max. | Units  |
| Frequency                                          | 1380         |      | 1480 | MHz    |
| Step size                                          |              | 100  |      | kHz    |
| Settling Time Within ±1kHz                         |              | 8.5  |      | msec   |
| Output Power                                       | -3           | +1   | +5   | dBm    |
| Phase Noise                                        |              |      |      |        |
| at 100 Hz offset                                   |              | -89  |      | dBc/Hz |
| at 1 kHz offset                                    |              | -92  |      | dBc/Hz |
| at 10 KHz offset                                   |              | -100 | -94  | dBc/Hz |
| at 100 KHz offset                                  |              | -125 |      | dBc/Hz |
| at 1000 kHz offset                                 |              | -146 | -140 | dBc/Hz |
| Integrated SSB Phase Noise                         |              | -52  |      | dBc    |
| Ref & Comp Spurious Suppression                    |              | -81  |      | dBc    |
| 0.5 Step size Spurious Suppression                 |              | -96  |      | dBc    |
| Non-Harm. Spurious Suppression                     |              | -90  |      | dBc    |
| Harmonic Suppression                               |              | -37  |      | dBc    |
| Supply voltage VCO                                 |              | 5    |      | V      |
| Supply voltage PLL                                 |              | 3.3  |      | V      |
| Supply current VCO                                 |              | 48   | 56   | V      |
| Supply current PLL                                 |              | 14   | 23   | V      |
| Reference In (External)                            | Frequency    | 10   |      | MHz    |
|                                                    | Amplitude    | 1    |      | Vp-p   |
|                                                    | Impedance    | 100  |      | kΩ     |
|                                                    | Ph. N @ 1kHz | -145 |      | dBc/Hz |
| Input Logic Levels                                 | Logic high   | 1.4  | 3.3  | V      |
|                                                    | Logic Low    |      | 0.6  | V      |
| Digital Lock Detect                                | Locked       | 1.4  | 3.3  | V      |
|                                                    | Unlocked     |      | 0.4  | V      |
| Frequency Synthesizer PLL                          | ADF4153      |      |      |        |

| ABSOLUTE MAXIMUM RATINGS    |                |
|-----------------------------|----------------|
| Operating Temperature       | -45°C to 85°C  |
| Storage Temperature         | -55°C to 100°C |
| VCO Supply Voltage          | 6V             |
| PLL Supply Voltage          | 4.3V           |
| Reference Frequency voltage | 3.6Vp-p        |
| Data, Clock & LE levels     | 3.6V           |

Power On sequence: Vcc VCO followed by Vcc PLL  
Power Off sequence: Vcc PLL followed by Vcc VCO

| PIN CONNECTIONS |    |              |          |
|-----------------|----|--------------|----------|
| RF OUT          | 9  | CLOCK        | 1        |
| VCC VCO         | 7  | DATA         | 2        |
| VCC PLL         | 12 | LATCH ENABLE | 3        |
| REF IN          | 4  | GROUND       | 5,6,8,10 |
| LOCK DETECT     | 11 |              |          |

### Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCULStorageTerms.jsp](http://www.minicircuits.com/MCULStorageTerms.jsp)

# Frequency Synthesizer

SSN-EDR11277/SA

## Typical Performance Data

| FREQ.<br>(MHz) | POWER OUTPUT<br>(dBm) |       |        | HARMONICS |        |        |        |        |        | VCO CURRENT<br>(mA) |       |        | PLL CURRENT<br>(mA) |       |        |
|----------------|-----------------------|-------|--------|-----------|--------|--------|--------|--------|--------|---------------------|-------|--------|---------------------|-------|--------|
|                |                       |       |        | (dBc)     |        |        |        |        |        |                     |       |        |                     |       |        |
|                | -15 °C                | +25°C | +75 °C | -15 °C    | +25°C  | +75 °C | -15 °C | +25°C  | +75 °C | -15 °C              | +25°C | +75 °C | -15 °C              | +25°C | +75 °C |
| 1360           | 1.09                  | 1.38  | 1.43   | -23.68    | -25.05 | -26.55 | -35.98 | -39.37 | -38.68 | 47.46               | 48.32 | 49.09  | 11.98               | 13.71 | 15.51  |
| 1376           | 0.88                  | 1.18  | 1.25   | -26.99    | -28.45 | -29.10 | -39.01 | -42.66 | -41.66 | 47.35               | 48.23 | 49.02  | 13.01               | 14.80 | 16.64  |
| 1380           | 0.85                  | 1.16  | 1.23   | -27.66    | -29.26 | -29.91 | -38.86 | -42.22 | -41.42 | 47.33               | 48.21 | 49.01  | 11.98               | 13.75 | 15.57  |
| 1392           | 0.85                  | 1.15  | 1.20   | -26.34    | -27.99 | -30.03 | -39.65 | -43.04 | -40.93 | 47.27               | 48.16 | 48.98  | 12.90               | 14.70 | 16.56  |
| 1408           | 0.83                  | 1.15  | 1.19   | -30.53    | -31.66 | -31.28 | -38.98 | -42.72 | -41.30 | 47.19               | 48.10 | 48.92  | 12.94               | 14.75 | 16.61  |
| 1424           | 0.81                  | 1.11  | 1.13   | -34.39    | -35.90 | -35.07 | -35.72 | -41.10 | -41.59 | 47.11               | 48.03 | 48.88  | 12.99               | 14.81 | 16.68  |
| 1440           | 0.65                  | 0.95  | 0.95   | -35.88    | -36.23 | -34.56 | -37.16 | -44.91 | -41.64 | 47.05               | 47.98 | 48.84  | 11.97               | 13.76 | 15.60  |
| 1456           | 0.45                  | 0.75  | 0.76   | -45.90    | -41.87 | -36.95 | -36.74 | -44.57 | -40.35 | 47.00               | 47.95 | 48.82  | 13.00               | 14.82 | 16.69  |
| 1472           | 0.30                  | 0.59  | 0.58   | -43.98    | -41.33 | -37.33 | -38.04 | -46.68 | -40.35 | 46.98               | 47.93 | 48.81  | 12.89               | 14.71 | 16.59  |
| 1480           | 0.27                  | 0.56  | 0.53   | -45.07    | -42.81 | -37.86 | -37.70 | -45.15 | -39.55 | 46.97               | 47.92 | 48.80  | 11.97               | 13.77 | 15.61  |
| 1488           | 0.27                  | 0.56  | 0.51   | -46.47    | -45.11 | -39.10 | -38.43 | -43.85 | -39.45 | 46.95               | 47.92 | 48.80  | 12.93               | 14.76 | 16.63  |
| 1504           | 0.36                  | 0.63  | 0.53   | -38.65    | -40.78 | -38.72 | -37.49 | -40.03 | -38.18 | 46.91               | 47.88 | 48.78  | 12.99               | 14.82 | 16.70  |
| 1520           | 0.27                  | 0.54  | 0.44   | -35.39    | -39.35 | -38.69 | -36.34 | -35.60 | -37.71 | 46.89               | 47.86 | 48.77  | 11.97               | 13.77 | 15.62  |

| FREQ.<br>(MHz) | PHASE NOISE (dBc/Hz) |        |         |         |         |        |        |         |         |         |        |        |        |         |
|----------------|----------------------|--------|---------|---------|---------|--------|--------|---------|---------|---------|--------|--------|--------|---------|
|                | @ OFFSETS            |        |         |         |         |        |        |         |         |         |        |        |        |         |
|                | -15 °C               |        |         |         |         | +25°C  |        |         |         |         | +75 °C |        |        |         |
|                | 100Hz                | 1kHz   | 10kHz   | 100kHz  | 1MHz    | 100Hz  | 1kHz   | 10kHz   | 100kHz  | 1MHz    | 100Hz  | 1kHz   | 10kHz  | 1MHz    |
| 1360           | -86.41               | -93.99 | -100.37 | -127.27 | -147.92 | -87.38 | -94.78 | -99.77  | -126.25 | -146.53 | -90.87 | -95.12 | -98.87 | -124.09 |
| 1376           | -88.06               | -94.93 | -101.02 | -127.46 | -148.13 | -88.50 | -93.41 | -100.39 | -125.95 | -146.40 | -87.58 | -93.23 | -99.10 | -124.17 |
| 1380           | -88.75               | -93.96 | -100.90 | -127.49 | -147.92 | -89.21 | -91.11 | -99.37  | -125.85 | -146.44 | -89.56 | -92.43 | -99.00 | -123.93 |
| 1392           | -90.69               | -94.40 | -101.03 | -127.43 | -147.91 | -87.38 | -93.09 | -100.50 | -125.94 | -146.33 | -94.27 | -93.09 | -99.84 | -123.80 |
| 1408           | -87.39               | -92.83 | -100.12 | -127.41 | -147.80 | -89.88 | -92.04 | -99.92  | -125.93 | -146.08 | -89.96 | -91.87 | -98.57 | -123.50 |
| 1424           | -88.73               | -93.47 | -100.51 | -127.13 | -147.70 | -89.36 | -92.91 | -100.40 | -125.54 | -145.90 | -90.11 | -92.70 | -98.59 | -123.24 |
| 1440           | -88.20               | -92.68 | -100.02 | -127.13 | -147.78 | -87.78 | -93.23 | -99.80  | -125.59 | -145.80 | -87.91 | -91.21 | -98.07 | -123.01 |
| 1456           | -88.40               | -93.39 | -99.78  | -126.84 | -147.32 | -88.79 | -93.00 | -99.82  | -125.20 | -145.43 | -90.23 | -92.22 | -97.69 | -123.02 |
| 1472           | -87.72               | -91.88 | -100.14 | -126.60 | -145.91 | -88.23 | -90.99 | -99.68  | -123.24 | -145.24 | -88.69 | -90.80 | -97.86 | -122.88 |
| 1480           | -88.11               | -92.83 | -99.85  | -126.67 | -147.06 | -90.40 | -92.21 | -99.47  | -125.10 | -145.32 | -85.71 | -89.71 | -97.90 | -122.66 |
| 1488           | -87.36               | -92.59 | -100.04 | -126.55 | -147.12 | -88.51 | -92.98 | -99.44  | -123.94 | -145.28 | -91.65 | -88.56 | -98.21 | -122.62 |
| 1504           | -87.81               | -93.04 | -99.93  | -126.21 | -146.55 | -89.50 | -90.58 | -98.90  | -123.82 | -144.96 | -87.15 | -87.86 | -98.03 | -122.35 |
| 1520           | -89.55               | -92.29 | -99.88  | -125.92 | -146.44 | -90.77 | -91.27 | -98.71  | -124.32 | -144.69 | -87.27 | -89.39 | -97.99 | -122.21 |

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCULStore/terms.jsp](http://www.minicircuits.com/MCULStore/terms.jsp)



# Frequency Synthesizer

SSN-EDR11277/SA

## Typical Performance Data

| COMPARISON<br>SPURIOUS ORDER | COMPARISON SPURIOUS<br>@Fcarrier 1380.1 MHz±<br>(n*Fcomparison)<br>(dBc) NOTE 1 |        |        | COMPARISON SPURIOUS<br>@Fcarrier 1430.1 MHz±<br>(n*Fcomparison)<br>(dBc) NOTE 1 |        |        | COMPARISON SPURIOUS<br>@Fcarrier 1480.1 MHz±<br>(n*Fcomparison)<br>(dBc) NOTE 1 |        |        |
|------------------------------|---------------------------------------------------------------------------------|--------|--------|---------------------------------------------------------------------------------|--------|--------|---------------------------------------------------------------------------------|--------|--------|
|                              | -15 °C                                                                          | +25°C  | +75 °C | -15 °C                                                                          | +25°C  | +75 °C | -15 °C                                                                          | +25°C  | +75 °C |
| -5                           | -79.39                                                                          | -78.80 | -83.62 | -79.21                                                                          | -79.43 | -81.87 | -78.75                                                                          | -80.72 | -79.58 |
| -4                           | -79.48                                                                          | -78.89 | -85.11 | -79.63                                                                          | -78.42 | -84.23 | -78.18                                                                          | -79.97 | -81.87 |
| -3                           | -80.48                                                                          | -80.00 | -82.31 | -80.75                                                                          | -78.79 | -83.25 | -78.50                                                                          | -80.21 | -82.29 |
| -2                           | -83.44                                                                          | -83.02 | -81.08 | -83.40                                                                          | -80.87 | -82.37 | -80.89                                                                          | -81.63 | -80.31 |
| -1                           | -92.84                                                                          | -89.40 | -88.07 | -88.81                                                                          | -85.77 | -83.89 | -86.55                                                                          | -87.20 | -80.43 |
| 0 <sup>note 2</sup>          | -                                                                               | -      | -      | -                                                                               | -      | -      | -                                                                               | -      | -      |
| +1                           | -86.40                                                                          | -84.88 | -77.82 | -84.59                                                                          | -88.99 | -76.91 | -88.32                                                                          | -91.18 | -76.74 |
| +2                           | -80.95                                                                          | -79.45 | -75.77 | -79.48                                                                          | -81.98 | -76.32 | -81.61                                                                          | -82.04 | -75.30 |
| +3                           | -78.28                                                                          | -77.17 | -80.94 | -77.39                                                                          | -78.92 | -80.92 | -78.40                                                                          | -78.76 | -79.66 |
| +4                           | -75.73                                                                          | -75.12 | -85.48 | -75.64                                                                          | -76.35 | -87.36 | -75.87                                                                          | -76.47 | -90.14 |
| +5                           | -74.54                                                                          | -74.34 | -75.92 | -74.74                                                                          | -74.79 | -76.78 | -74.37                                                                          | -75.04 | -77.90 |

Note 1: Comparison & Reference frequency 10 MHz

Note 2: All spurs are referenced to carrier signal (n=0).

### Notes




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)



# Frequency Synthesizer

## Typical Performance Data

SSN-EDR11277/SA



### Notes






- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)



# Frequency Synthesizer

## Typical Performance Data

SSN-EDR11277/SA



### Notes




- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)



# Frequency Synthesizer

## Typical Performance Data

SSN-EDR11277/SA




### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)




## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION | DATE  | DR | AUTH |
|-----|---------|-------------|-------|----|------|
| OR  | M124738 | NEW RELEASE | 04/10 | DK | HH   |
| OR  | R77823  | NEW RELEASE | 04/10 | DK | HH   |
|     |         |             |       |    |      |
|     |         |             |       |    |      |

## SUGGESTED MOUNTING CONFIGURATION

FOR KJ1367 CASE STYLE, 12SY01 PIN CONNECTION, 50  $\Omega$ .Ø.020 PTH. TYP.  
FOR GROUNDPACKAGE  
OUTLINE

## NOTES:

1. TRACE WIDTH IS SHOWN FOR R04350B WITH DIELECTRIC THICKNESS.  
.020"±.0015". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:  
2 PL DECIMALS ±  
3 PL DECIMALS ± .005  
ANGLES ±  
FRACTIONS ±

DRAWN

DK (RAVON)

06 APR 10

CHECKED

DH (RAVON)

07 APR 10

APPROVED

HH (RAVON)

07 APR 10



**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

PL, 12SY01, KJ1367, SSN  
TB-552+ (50  $\Omega$ )

SIZE  
A

CODE IDENT  
15542

DRAWING NO:  
98-PL-317

REV:  
OR

FILE: 98PL317


SCALE: 5:1

SHEET: 1 OF 1

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.  
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE  
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY  
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.  
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE  
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


# Evaluation Board and Circuit



TB-552+

## NOTES:

1. SMA FEMALE CONNECTORS.
2. PCB MATERIAL: RO4350B OR EQUIVALENT, DIALECTRIC CONSTANT=3.5, DIALECTRIC THICKNESS=.020 INCH.



## TB-552+

### Schematic Diagram



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutectic Process: 225°C peak<br>Pb-Free Process, 245°C peak                                                                                               | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, Para 4.2.5, Test S, 95% Coverage                                                          |
| Vibration (High Frequency)     | 20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)                                                                                                  | MIL-STD-883, Method 2007.3, Condition A                                                              |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |