

Bandpass Filter

SXBP-140+

50Ω 130 to 150 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	1
OUTPUT	8
GROUND	2, 3, 4, 5, 6, 7

Outline Drawing




Outline Dimensions (inch mm)

A	B	C	D	E	F	
.44	.74	.27	.200	.07	.060	
11.18	18.80	6.86	5.08	1.78	1.52	
G	H	J	K	L	M	wt.
.040	.660	.200	.470	.055	.060	grams
1.02	16.76	5.08	11.94	1.40	1.52	3.0

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)




- NOTE:
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- high rejection
- good VSWR, 1.1:1 typ @ passband
- aqueous washable

Applications

- receivers/transmitters
- wireless communication systems
- radio link



Generic photo used for illustration purposes only

CASE STYLE: HF1139


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 3.5dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
F _c	F ₁ - F ₂	F ₃	F ₄	F ₅	F ₆	Typ.	Max.	Typ.
140	130 - 150	110	185	100	210 - 2000	1.1	1.5	20

Typical Frequency Response






Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	$\bar{x}$	σ			
1.0	73.30	3.99	0.40	125.0	40.18
50.0	74.59	2.17	0.31	127.0	52.13
100.0	49.79	0.31	0.19	129.0	52.31
110.0	36.54	0.36	0.30	130.0	48.85
120.0	19.41	0.50	0.89	132.0	41.10
125.0	8.65	0.52	3.06	135.0	35.53
130.0	2.65	0.11	23.63	137.0	33.52
140.0	1.89	0.02	28.56	139.0	32.42
150.0	2.24	0.06	25.90	140.0	31.84
155.0	4.86	0.50	7.97	141.0	31.41
158.0	8.93	0.68	3.61	143.0	31.20
165.0	19.05	0.59	1.27	145.0	31.15
170.0	24.86	0.51	0.87	147.0	31.99
185.0	37.36	0.39	0.47	149.0	34.18
210.0	50.09	0.35	0.28	150.0	35.60
500.0	70.65	0.64	0.10	151.0	37.89
1000.0	64.42	0.32	0.20	153.0	41.00
2000.0	54.40	0.37	0.28	155.0	40.36



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount Band Pass Filter

SXBP-140+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
10	80.82	81.80	80.81	0.38	0.49	0.59	0.37	0.48	0.56
20	76.24	77.18	82.28	0.38	0.45	0.52	0.37	0.46	0.52
30	76.04	74.98	74.54	0.35	0.41	0.45	0.34	0.41	0.45
40	76.23	73.88	78.42	0.30	0.35	0.37	0.30	0.36	0.39
50	76.60	76.73	78.13	0.24	0.29	0.31	0.25	0.30	0.33
60	74.48	77.00	79.21	0.20	0.24	0.27	0.21	0.26	0.29
70	79.66	84.84	81.20	0.16	0.20	0.22	0.16	0.21	0.23
80	89.03	80.08	78.60	0.13	0.18	0.20	0.14	0.19	0.21
90	63.66	63.01	62.93	0.12	0.17	0.20	0.12	0.17	0.20
100	50.00	49.72	49.63	0.15	0.20	0.23	0.12	0.19	0.22
120	17.67	17.32	17.00	1.00	1.25	1.44	0.82	1.02	1.16
125	6.73	6.66	6.52	4.49	5.41	6.15	3.74	4.47	5.04
130	2.09	2.42	2.61	30.89	31.63	30.15	21.56	22.25	22.49
140	1.62	1.93	2.12	22.13	22.04	21.94	21.70	22.41	23.11
150	2.07	2.55	2.89	24.64	22.52	20.43	20.73	19.23	18.00
155	5.72	6.65	7.33	4.84	4.72	4.54	4.86	4.77	4.62
158	10.18	11.10	11.81	2.30	2.40	2.41	2.38	2.50	2.53
165	20.03	20.74	21.28	0.90	1.03	1.09	0.96	1.11	1.17
170	25.62	26.19	26.64	0.63	0.74	0.80	0.68	0.80	0.87
185	37.74	38.13	38.40	0.33	0.41	0.47	0.37	0.45	0.50
210	50.38	50.58	50.75	0.18	0.24	0.29	0.21	0.27	0.31
300	73.88	72.89	73.81	0.05	0.12	0.15	0.05	0.12	0.15
400	85.76	89.96	87.34	0.02	0.08	0.13	0.01	0.09	0.13
500	86.54	87.83	92.56	0.01	0.07	0.12	0.01	0.08	0.12
600	82.45	86.50	87.54	0.01	0.08	0.13	0.01	0.09	0.13
700	83.72	94.01	95.89	0.01	0.08	0.14	0.01	0.09	0.15
800	86.58	82.77	95.72	0.02	0.10	0.16	0.00	0.11	0.17
900	86.92	93.28	80.21	0.01	0.13	0.20	0.01	0.12	0.19
1000	83.46	82.70	89.02	0.00	0.13	0.21	0.03	0.11	0.18
1200	84.25	85.67	88.71	0.00	0.16	0.24	0.01	0.16	0.24
1300	84.72	84.18	84.38	0.01	0.18	0.26	0.01	0.16	0.26
1400	76.77	75.57	78.45	0.01	0.19	0.29	0.01	0.18	0.28
1500	65.09	64.93	65.02	0.03	0.21	0.31	0.01	0.19	0.29
1600	75.55	81.32	76.02	0.03	0.22	0.32	0.02	0.22	0.33
1700	72.19	74.34	73.01	0.05	0.24	0.35	0.05	0.24	0.34
1800	60.40	66.63	60.43	0.03	0.23	0.36	0.05	0.21	0.34
1900	60.63	67.05	62.33	0.06	0.27	0.36	0.04	0.25	0.35
2000	62.25	62.21	60.91	0.03	0.25	0.38	0.05	0.26	0.39
2200	60.08	61.15	58.19	0.06	0.29	0.42	0.08	0.31	0.45
2300	53.77	56.48	54.61	0.06	0.28	0.44	0.09	0.31	0.46
2400	49.51	53.72	48.90	0.09	0.31	0.47	0.11	0.33	0.49
2500	51.69	51.53	50.45	0.10	0.32	0.49	0.07	0.33	0.48
2600	49.50	50.38	48.83	0.11	0.34	0.53	0.10	0.35	0.50
2700	52.70	53.15	52.18	0.10	0.35	0.50	0.08	0.37	0.51
2800	52.71	46.03	47.43	0.10	0.37	0.54	0.09	0.39	0.55
3000	42.33	43.56	44.01	0.08	0.41	0.55	0.10	0.41	0.59
3200	39.32	41.25	41.27	0.19	0.49	0.68	0.14	0.41	0.62
3300	39.48	40.29	40.15	0.18	0.62	0.82	0.09	0.47	0.63
3400	36.97	37.72	38.91	0.55	0.87	1.07	0.25	0.54	0.79
3500	35.74	36.86	35.59	0.42	0.70	0.87	0.33	0.65	0.82
3600	33.87	34.80	33.31	0.29	0.66	0.93	0.13	0.54	0.74
3700	35.27	35.06	33.57	0.25	0.66	0.89	0.24	0.59	0.89
3800	36.76	32.14	34.11	0.18	0.68	0.86	0.39	0.70	1.13
4000	29.91	28.55	31.45	0.35	0.77	0.99	0.27	0.79	1.02

REV. X2

SXBP-140+

101118

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Band Pass Filter

SXBP-140+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
90	2.54	7.62	2.07
95	4.51	3.31	4.41
100	4.63	4.73	5.07
110	7.82	7.97	8.23
120	20.91	21.89	22.76
125	44.00	44.74	45.37
126	48.30	48.46	48.61
127	50.79	50.36	50.02
128	51.24	50.28	49.60
129	49.74	48.57	47.70
130	47.03	45.85	45.02
131	43.91	42.92	42.23
132	41.03	40.31	39.74
133	38.68	38.14	37.73
134	36.85	36.50	36.17
135	35.46	35.16	34.94
136	34.39	34.18	33.96
137	33.50	33.36	33.24
138	32.82	32.70	32.63
139	32.29	32.21	32.21
140	31.92	31.90	31.91
141	31.64	31.68	31.74
142	31.55	31.58	31.67
143	31.55	31.66	31.78
144	31.71	31.87	32.01
145	32.02	32.23	32.45
146	32.58	32.87	33.21
147	33.43	33.80	34.23
148	34.58	35.06	35.54
149	36.07	36.60	37.07
150	37.76	38.22	38.59
151	39.36	39.55	39.65
152	40.43	40.23	39.98
153	40.64	39.93	39.28
154	39.66	38.43	37.46
155	37.47	35.93	34.68
156	34.42	32.68	31.35
157	30.88	29.14	27.86
158	27.22	25.67	24.50
159	23.73	22.53	21.40
160	20.79	19.68	18.87
170	7.51	7.35	7.23
180	3.91	4.11	3.95
190	2.84	2.60	2.54
200	1.61	1.79	1.69
210	1.70	0.88	1.63
220	0.73	0.50	1.56
230	0.99	1.32	1.15
240	0.82	0.70	1.32
250	0.50	0.53	0.74
260	0.83	0.25	1.29
270	1.60	0.23	0.83
280	1.47	0.90	0.67
290	0.81	0.39	0.75

REV. X2
SXBP-140+
101118
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE






OUTPUT RETURN LOSS vs. TEMPERATURE




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HF1139	.44 (11.18)	.74 (18.80)	.27 (6.86)	.200 (5.08)	.07 (1.78)	.060 (1.52)	.040 (1.02)	.660 (16.76)	.200 (5.08)	.470 (11.94)	.055 (1.40)	.060 (1.52)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.015 "; 3 Pl. ± 0.01 "

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101757	NEW RELEASE (FROM RAVON)	11/05	DK	HH
OR	R62293	NEW RELEASE (FROM RAVON)	11/05	DK	HH

SUGGESTED MOUNTING CONFIGURATION
FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.

**NOTE:**

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025" ± .002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN DK (RAVON)	29 NOV 05
TOLERANCES ON:	CHECKED RZ (RAVON)	29 NOV 05
2 PL DECIMALS ±	APPROVED HH (RAVON)	29 NOV 05
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, cr, HF1139, SCLF, TB-368

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-230	OR
FILE:	98PL230	SCALE: 4:1	SHEET: 1 OF 1

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



TB-368



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215