Surface Mount

Bandpass Filter

SXBP-615+

50Ω 565 to 670 MHz



Generic photo used for illustration purposes only

CASE STYLE: HF1139

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	1
OUTPUT	8
GROUND	2, 3, 4, 5, 6, 7

Features

- high rejection
- flat group delay @ passband
- good VSWR, 1.3:1 typ @ passband
- shielded case
- aqueous washable

Applications

- mobile TV
- receivers / transmitters
- harmonic rejection

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch / mm)

A	B	C	D	E	F
.44	.74	.27	.200	.07	.060
11.18	18.80	6.86	5.08	1.78	1.52

G	H	J	K	L	M	wt.
.040	.660	.200	.470	.055	.060	grams
1.02	16.76	5.08	11.94	1.40	1.52	3.0

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-368
Suggested PCB Layout (PL-230)



NOTE:
1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 4dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
Fc	F1 - F2	F3	F4	F5	F6	Typ.	Max.	Typ.
615	565 - 670	380	720	250	740 - 2300	1.3	1.9	20

Typical Frequency Response



Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB) x̄	Insertion Loss (dB) σ	Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
0.5	93.98	3.00	0.01	555.0	5.20
250.0	52.72	0.29	0.05	560.0	5.27
380.0	29.65	0.41	0.25	565.0	5.30
430.0	17.34	0.64	0.80	570.0	5.32
450.0	11.22	0.78	1.85	580.0	5.33
470.0	5.30	0.60	6.58	590.0	5.36
565.0	1.43	0.04	12.98	600.0	5.45
580.0	1.30	0.02	17.97	610.0	5.68
615.0	1.42	0.05	22.32	615.0	5.84
640.0	1.74	0.08	18.33	620.0	5.99
670.0	2.58	0.08	12.75	630.0	6.21
690.0	6.56	1.62	7.05	640.0	6.63
700.0	13.84	2.34	3.07	650.0	7.32
710.0	22.42	2.46	1.95	660.0	8.19
720.0	31.31	2.80	1.46	670.0	9.71
740.0	53.80	3.72	1.01	673.0	10.51
1000.0	55.59	0.27	0.23	676.0	11.48
2300.0	56.85	0.49	0.34	680.0	13.06

SXBP-615+
INSERTION LOSS



SXBP-615+
RETURN LOSS



SXBP-615+
GROUP DELAY



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Surface Mount Band Pass Filter SXBP-615+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	98.70	95.30	102.34	0.01	0.01	0.00	0.00	0.01	0.00
10	100.52	94.94	98.50	0.01	0.00	0.01	0.00	0.01	0.00
50	99.93	93.15	89.63	0.00	0.00	0.02	0.01	0.00	0.01
100	78.94	80.83	81.04	0.01	0.02	0.04	0.01	0.02	0.03
200	61.41	61.08	61.16	0.00	0.05	0.06	0.02	0.06	0.09
250	52.85	53.05	52.98	0.01	0.06	0.09	0.03	0.08	0.11
300	44.58	44.62	44.60	0.03	0.10	0.13	0.07	0.13	0.17
380	29.81	29.71	29.54	0.10	0.20	0.26	0.22	0.32	0.38
400	25.24	25.12	24.93	0.15	0.26	0.33	0.29	0.43	0.51
430	17.43	17.26	17.02	0.35	0.50	0.60	0.66	0.87	1.03
450	11.03	10.88	10.65	0.87	1.09	1.26	1.59	1.99	2.32
470	4.84	4.94	4.94	3.19	3.54	3.81	6.03	7.12	8.12
500	2.67	2.95	3.14	5.52	5.73	5.86	6.69	6.86	6.93
565	1.14	1.44	1.63	16.60	16.64	16.54	14.06	14.19	14.26
580	1.05	1.35	1.55	19.59	19.43	19.23	18.44	18.92	19.18
600	1.12	1.42	1.62	16.56	17.84	18.92	18.12	20.53	22.93
615	1.22	1.54	1.75	16.23	18.15	20.02	17.47	20.02	22.67
640	1.50	1.91	2.22	16.92	18.12	18.58	16.57	17.38	17.69
670	2.20	2.86	3.38	22.70	22.88	23.50	18.40	17.69	17.04
690	8.70	10.66	12.39	4.14	4.16	4.01	4.33	4.31	4.16
720	36.26	38.40	40.37	1.02	1.26	1.36	1.05	1.29	1.41
740	55.22	55.82	55.95	0.68	0.89	0.98	0.69	0.89	0.99
800	59.43	60.09	60.50	0.28	0.45	0.53	0.30	0.44	0.54
900	52.31	53.14	53.61	0.11	0.26	0.32	0.16	0.30	0.38
1000	55.42	56.06	56.70	0.07	0.22	0.28	0.14	0.28	0.35
1200	62.14	61.98	63.54	0.03	0.19	0.25	0.16	0.30	0.38
1300	64.46	65.85	66.08	0.02	0.18	0.26	0.17	0.33	0.41
1400	66.23	67.28	70.88	0.03	0.21	0.29	0.19	0.34	0.43
1500	73.09	71.69	69.84	0.02	0.19	0.27	0.18	0.36	0.45
1600	68.12	72.34	70.08	0.04	0.22	0.31	0.18	0.37	0.46
1700	65.32	66.94	65.36	0.03	0.21	0.31	0.19	0.39	0.49
1800	55.08	54.56	54.55	0.05	0.23	0.33	0.22	0.44	0.55
2000	65.53	68.23	66.45	0.06	0.25	0.35	0.12	0.37	0.49
2200	52.67	57.58	62.83	0.08	0.28	0.40	0.09	0.35	0.49
2300	65.29	61.59	63.35	0.08	0.28	0.40	0.05	0.32	0.47
2400	66.85	60.36	59.52	0.08	0.28	0.42	0.01	0.29	0.43
2500	58.49	55.27	51.96	0.07	0.29	0.44	0.03	0.29	0.45
2600	54.50	54.02	53.26	0.12	0.31	0.45	0.09	0.23	0.39
2800	46.52	48.55	47.37	0.11	0.33	0.49	0.13	0.21	0.37
3000	45.49	48.41	46.39	0.10	0.33	0.48	0.29	0.09	0.24
3200	40.98	43.68	38.80	0.16	0.39	0.59	0.23	0.04	0.22
3300	44.58	42.97	44.47	0.12	0.38	0.54	0.28	0.03	0.20
3400	37.54	39.69	40.75	0.14	0.43	0.58	0.37	0.01	0.17
3500	36.89	39.02	36.70	0.18	0.45	0.66	0.32	0.05	0.17
3600	34.91	39.20	38.37	0.11	0.44	0.57	0.27	0.03	0.20
3800	35.82	35.03	35.38	0.13	0.53	0.65	0.32	0.01	0.16
4000	29.17	32.78	35.05	0.28	0.61	0.80	0.01	0.11	0.32
4200	29.49	32.49	28.26	0.42	0.72	1.08	0.25	0.19	0.58
4300	29.61	29.39	29.42	0.35	0.83	1.06	0.24	0.25	0.46
4400	25.43	27.72	30.47	0.57	1.04	1.39	0.54	0.45	0.80
4500	25.50	25.67	24.51	0.60	1.24	1.43	0.82	0.67	1.10
4600	27.31	27.39	29.77	0.79	1.17	1.44	1.27	1.07	1.12
4800	21.61	22.92	21.67	1.05	1.55	1.84	1.06	1.22	1.49
5000	20.88	21.62	26.53	1.51	1.89	1.79	0.49	1.19	1.27

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
210	0.82	0.29	0.38
220	0.75	0.27	0.39
230	0.43	0.33	0.58
240	0.60	0.50	0.48
250	0.56	0.36	0.23
260	0.45	0.45	0.50
270	0.70	0.59	0.72
280	0.61	0.67	0.72
290	0.73	0.64	0.64
300	0.55	0.55	0.58
310	0.57	0.61	0.69
320	0.73	0.74	0.80
330	0.85	0.84	0.79
340	0.88	0.92	0.95
350	0.90	0.90	0.95
360	0.93	0.94	0.97
370	0.98	0.95	0.99
380	1.11	1.15	1.18
390	1.33	1.37	1.41
400	1.57	1.58	1.66
410	1.71	1.76	1.84
420	1.95	2.02	2.12
430	2.43	2.54	2.66
440	3.25	3.38	3.53
450	4.37	4.54	4.72
460	5.85	6.01	6.16
470	7.38	7.40	7.44
480	8.02	7.88	7.76
490	7.35	7.15	6.99
500	6.14	6.02	5.93
510	5.31	5.27	5.26
520	4.89	4.91	4.92
530	4.77	4.79	4.83
540	4.86	4.88	4.92
550	5.07	5.08	5.11
560	5.22	5.22	5.24
570	5.29	5.29	5.30
580	5.31	5.32	5.36
590	5.33	5.37	5.41
600	5.40	5.47	5.55
610	5.58	5.66	5.77
620	5.87	5.98	6.09
630	6.27	6.39	6.51
640	6.78	6.90	7.05
650	7.49	7.65	7.83
660	8.79	9.06	9.35
670	10.77	11.25	11.77
690	14.43	13.43	12.50
720	2.49	1.83	0.76

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Surface Mount Band Pass Filter SXBP-615+

Typical Performance Curves

INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Curves



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style HF

HF1139

Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HF1139	.44 (11.18)	.74 (18.80)	.27 (6.86)	.200 (5.08)	.07 (1.78)	.060 (1.52)	.040 (1.02)	.660 (16.76)	.200 (5.08)	.470 (11.94)	.055 (1.40)	.060 (1.52)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl. ±.015"; 3 Pl. ±.01"

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:
   For RoHS Case Styles: 2-5 µ inch (.05-.13 microns) Gold over 120-240 µ inch (3.05-6.10 microns) Nickel plate.
   For RoHS-5 Case Styles: Tin-Lead plate.

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F5

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101757	NEW RELEASE (FROM RAVON)	11/05	DK	HH
OR	R62293	NEW RELEASE (FROM RAVON)	11/05	DK	HH

SUGGESTED MOUNTING CONFIGURATION
FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.



NOTE:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
   FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	DK (RAVON)	29 NOV 05
TOLERANCES ON:	CHECKED	RZ (RAVON)	29 NOV 05
2 PL DECIMALS ±	APPROVED	HH (RAVON)	29 NOV 05
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits®
13 Neptune Avenue
Brooklyn NY 11235

PL, cr, HF1139, SCLF, TB-368

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-230	OR
FILE: 98PL230	SCALE: 4:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



TB-368



Schematic Diagram

Notes:
1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.