



Mini-Circuits

SURFACE MOUNT

Bi-Directional Coupler

SYDC-20-62HP+

50Ω 20 dB Coupling 10 to 540 MHz 15 W

FEATURES

- High Power Handling, 25 W Max.
- Low Mainline Loss, 0.2 dB Typ.
- Good Return Loss, 26 dB Typ.



CASE STYLE: AH202-1

Generic photo used for illustration purposes only

APPLICATIONS

- Military Mobile

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		10		540	MHz
Mainline Loss ¹	10-540		0.2	0.6	dB
Nominal Coupling	10-540		19.8±0.5		dB
Coupling Flatness (±)	10-540		±0.8		dB
Directivity	10-540	16	26		dB
Return Loss	10-540		26		dB
Input Power ²	10-540			25	W

1. Mainline loss includes theoretical power loss at coupled port.

2. The user must provide adequate means of heat removal to limit the temperature of ground connections 2,3,6,7 to +85°C, in order to ensure proper performance.

At +25°C ambient temperature this requires thermal resistance of the user's PC board heat sink to be 40°C/W or less when the unit is driven at maximum specified RF input power, 15 W.
At higher ambient temperature, with the same heat sink. Input power in watts must not exceed $15 \text{ W} \times (+85^\circ\text{C} - T_{\text{ambient}}) \div +60^\circ\text{C}$.


ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C Case ³
Storage Temperature	-55°C to +100°C

3. Case temperature is defined as temperature on ground leads.
Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC

BI-DIRECTIONAL COUPLER*



*Electrical schematic is for Bi-Directional coupler with internal transformer(s) that routes DC from all ports to ground.

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E
ECO-015369
ED-12483/2
SYDC-20-62HP+
MCL NY
251107

PAGE 1 OF 3



Mini-Circuits

SURFACE MOUNT

Bi-Directional Coupler

SYDC-20-62HP+


50Ω 20 dB Coupling 10 to 540 MHz 15 W

PAD CONNECTIONS

INPUT	8
OUTPUT	1
COUPLED (FORWARD)	5
COUPLED (REVERSE)	4
GROUND	2, 3, 6, 7

***PRODUCT MARKING:** SYDC-20-62HP

*Marking may contain other features or characters for internal lot control.

EVAL BOARD MCL P/N: TB-SYDC20-62HP+
SUGGESTED PCB LAYOUT (PL-246)


NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern

Suggested Layout,
Tolerance to be within $\pm .002$ OUTLINE DIMENSIONS (Inches)
mm

A	B	C	D	E	F	G
.38	.50	.25	.020	.115	.070	.035
9.65	12.70	6.35	0.51	2.92	1.78	0.89
H	J	K	L	M	N	wt
.050	.090	.040	.105	.140	.095	grams
1.27	2.29	1.02	2.67	3.56	2.41	0.80

TAPE & REEL INFORMATION: F61



Mini-Circuits

SURFACE MOUNT




Bi-Directional Coupler

SYDC-20-62HP+

50Ω 20 dB Coupling 10 to 540 MHz 15 W

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)		Directivity (dB)		Return Loss (dB)			
	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
10	0.08	20.20	20.14	27.39	27.16	24.12	24.24	23.90	23.97
50	0.15	20.26	20.16	47.58	47.12	35.06	35.95	33.45	33.81
100	0.16	20.28	20.19	34.70	43.72	35.11	35.24	32.06	31.68
150	0.17	20.26	20.20	30.36	36.64	34.22	34.18	30.65	29.81
200	0.18	20.21	20.20	27.57	33.63	33.40	32.58	29.07	28.15
250	0.19	20.15	20.18	25.43	31.10	32.59	31.71	27.53	26.81
350	0.21	19.95	20.10	22.53	26.74	30.67	29.41	25.30	24.70
400	0.23	19.83	20.04	21.54	25.36	30.25	28.81	24.24	23.73
500	0.25	19.49	19.87	19.74	21.71	28.06	26.60	22.44	22.13
540	0.27	19.34	19.75	18.90	20.49	27.68	26.47	21.81	21.46



- NOTES**
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Bi-Directional Coupler

SYDC-20-62HP+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQ. (MHz)	INSERTION LOSS		COUPLING		DIRECTIVITY		RETURN LOSS			
	(dB) IN-OUT	(dB) FWD-REV	(dB) IN-FWD	(dB) OUT-REV	(dB) IN-REV	(dB) OUT-FWD	(dB) IN	(dB) OUT	(dB) FWD	(dB) REV
10	0.06	0.08	20.22	20.17	27.78	27.74	25.16	25.22	25.16	25.33
20	0.10	0.11	20.23	20.16	38.19	36.53	31.45	31.80	31.64	32.31
30	0.14	0.15	20.29	20.16	49.26	43.48	33.50	34.70	33.93	35.54
40	0.15	0.17	20.32	20.17	51.96	48.15	34.21	35.50	34.64	36.73
50	0.16	0.17	20.34	20.19	45.44	55.81	34.63	35.73	35.24	37.47
75	0.16	0.17	20.36	20.24	38.19	47.25	35.10	35.48	36.79	38.40
100	0.16	0.17	20.36	20.27	34.05	40.26	35.14	35.06	37.91	38.84
125	0.17	0.18	20.37	20.29	31.28	36.62	35.16	34.38	39.28	39.29
150	0.17	0.18	20.35	20.31	29.27	34.23	34.89	33.78	40.56	39.58
175	0.18	0.19	20.33	20.33	27.66	32.29	34.53	33.10	42.15	39.86
200	0.19	0.20	20.31	20.34	26.35	30.87	33.91	32.46	43.65	39.89
250	0.20	0.21	20.25	20.35	24.20	28.37	33.12	31.42	45.43	39.52
275	0.22	0.22	20.22	20.34	23.18	27.13	32.63	30.89	47.54	39.73
300	0.22	0.22	20.17	20.35	22.32	26.20	32.11	30.46	47.49	39.87
350	0.24	0.24	20.07	20.34	21.06	24.57	31.31	29.68	46.19	39.59
375	0.26	0.25	20.02	20.32	20.49	23.86	30.80	29.21	45.16	39.54
400	0.27	0.26	19.96	20.31	19.80	23.01	30.30	28.87	43.41	39.92
450	0.30	0.29	19.82	20.23	18.97	21.74	29.62	28.01	40.32	38.74
475	0.31	0.30	19.75	20.20	18.50	21.19	29.18	27.57	39.44	38.74
500	0.33	0.31	19.67	20.15	18.09	20.68	28.75	27.20	38.06	38.99
540	0.36	0.34	19.53	20.05	17.62	19.84	28.09	26.68	35.66	39.12
550	0.36	0.34	19.49	20.02	17.54	19.64	27.96	26.54	35.24	38.88
575	0.38	0.36	19.41	19.93	17.18	19.04	27.59	26.20	34.29	38.56
600	0.40	0.37	19.29	19.85	16.91	18.65	27.11	25.88	33.11	38.77
650	0.45	0.42	19.07	19.63	16.61	17.74	26.35	25.08	30.69	37.29
675	0.48	0.44	18.95	19.48	16.53	17.29	25.93	24.66	29.66	36.31
700	0.51	0.47	18.82	19.34	16.36	16.93	25.52	24.23	28.82	35.45
750	0.57	0.53	18.57	18.99	16.18	15.82	24.58	23.54	26.60	34.21
800	0.66	0.62	18.22	18.57	16.45	15.18	23.50	22.61	24.72	31.75
850	0.77	0.73	17.89	18.09	16.33	14.07	22.36	21.63	22.66	29.64
900	0.93	0.89	17.53	17.50	16.47	12.96	21.08	20.54	20.55	26.72
950	1.14	1.11	17.13	16.84	16.16	11.67	19.63	19.30	18.48	24.08
1000	1.46	1.45	16.81	16.11	14.89	9.87	18.00	17.90	16.21	21.53
1100	2.49	2.64	16.71	15.12	9.82	5.50	14.83	15.08	12.12	16.74
1200	2.92	3.53	17.37	17.46	4.80	3.04	13.66	13.49	9.89	13.54
1300	1.90	2.45	19.06	27.03	-1.46	3.69	15.46	13.74	10.65	12.58
1400	1.35	1.62	21.54	35.29	-6.83	3.06	17.63	14.59	12.36	13.01
1500	1.20	1.30	23.24	25.27	2.90	1.56	18.91	15.16	13.85	13.55
1600	1.21	1.22	23.97	21.61	5.59	0.40	19.43	15.38	15.14	13.98
1700	1.32	1.27	24.23	19.26	6.96	0.43	19.32	15.44	16.16	14.15
1800	1.50	1.38	24.30	17.42	7.96	1.12	18.88	15.46	17.15	14.27
1900	1.75	1.58	24.06	15.82	9.01	1.26	18.30	15.62	18.09	14.29
2000	2.08	1.86	23.76	14.38	10.11	0.98	17.70	16.15	18.92	14.38
2100	2.48	2.25	22.95	13.03	11.64	0.67	17.25	17.52	19.11	14.81
2200	2.91	2.74	21.65	11.86	14.29	5.07	17.10	20.30	17.49	15.72
2300	3.17	3.21	20.05	10.97	20.07	17.53	16.91	24.26	14.79	17.63
2400	3.11	3.34	18.88	10.42	35.93	13.09	15.62	22.72	13.09	21.02
2500	2.93	3.12	18.36	10.24	17.38	6.49	13.51	19.90	12.22	24.57
2600	2.90	2.94	18.31	10.04	12.53	3.06	11.59	18.49	11.51	24.24
2700	3.12	2.99	18.49	9.64	10.27	0.61	10.09	18.49	10.71	23.71
2800	3.52	3.25	18.70	9.08	9.21	1.21	8.92	19.66	9.84	25.04
2900	3.99	3.64	18.90	8.55	8.62	2.55	7.98	21.62	8.93	28.33
3000	4.50	4.05	19.13	8.14	8.36	3.57	7.26	23.02	8.34	33.18

REV. X1

SYDC-20-62HP+

081007

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Bi-Directional Coupler

SYDC-20-62HP+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQ. (MHz)	INSERTION LOSS		COUPLING		DIRECTIVITY		RETURN LOSS			
	(dB) IN-OUT	(dB) FWD-REV	(dB) IN-FWD	(dB) OUT-REV	(dB) IN-REV	(dB) OUT-FWD	(dB) IN	(dB) OUT	(dB) FWD	(dB) REV
10	0.08	0.09	20.22	20.13	32.02	31.82	27.39	27.60	27.42	27.79
20	0.12	0.13	20.27	20.13	42.31	39.60	32.66	34.28	32.87	34.99
30	0.14	0.15	20.30	20.14	51.06	44.59	33.84	37.17	34.36	38.17
40	0.14	0.16	20.32	20.16	49.07	48.54	34.25	38.01	34.92	39.41
50	0.14	0.15	20.33	20.17	44.43	49.61	34.49	37.76	35.48	39.73
75	0.14	0.15	20.34	20.21	37.47	42.53	34.72	35.71	36.56	37.73
100	0.14	0.15	20.34	20.24	34.20	39.23	34.82	34.42	36.71	36.24
125	0.14	0.15	20.34	20.25	32.10	37.64	35.00	33.85	37.62	36.78
150	0.14	0.15	20.32	20.28	30.16	35.98	34.59	33.38	38.55	37.86
175	0.14	0.15	20.31	20.29	28.20	33.68	33.51	32.24	39.22	38.01
200	0.15	0.15	20.29	20.30	26.53	31.58	32.22	31.03	40.21	37.70
250	0.16	0.16	20.23	20.31	24.48	28.93	31.40	30.07	41.64	37.90
275	0.17	0.17	20.21	20.31	23.62	27.61	31.19	29.81	42.23	37.96
300	0.18	0.17	20.15	20.31	22.85	26.63	30.78	29.45	41.57	37.35
350	0.19	0.18	20.05	20.29	21.50	24.80	30.12	28.83	40.72	36.72
375	0.20	0.19	20.00	20.28	20.95	24.13	29.71	28.47	40.57	37.07
400	0.21	0.20	19.94	20.26	20.31	23.32	29.19	28.02	39.92	37.24
450	0.23	0.21	19.81	20.19	19.32	21.90	28.10	26.84	37.58	35.31
475	0.25	0.22	19.73	20.15	18.84	21.34	27.69	26.51	37.35	35.29
500	0.26	0.23	19.65	20.10	18.41	20.84	27.46	26.34	36.88	35.76
540	0.28	0.25	19.51	20.00	17.97	19.99	27.08	25.95	35.00	36.09
550	0.29	0.26	19.47	19.97	17.89	19.81	26.96	25.81	34.51	35.85
575	0.31	0.27	19.38	19.88	17.55	19.21	26.63	25.50	33.44	35.67
600	0.32	0.28	19.27	19.80	17.29	18.83	26.24	25.25	32.39	35.72
650	0.36	0.32	19.04	19.58	16.98	17.95	25.59	24.42	30.48	34.19
675	0.39	0.33	18.92	19.44	16.88	17.51	25.13	23.88	29.63	33.19
700	0.41	0.36	18.78	19.30	16.65	17.11	24.67	23.39	28.84	32.44
750	0.48	0.42	18.53	18.97	16.33	16.03	23.74	22.70	26.75	31.77
800	0.56	0.49	18.17	18.55	16.52	15.51	22.71	21.82	25.13	30.38
850	0.65	0.59	17.83	18.08	16.42	14.42	21.69	21.04	23.11	28.51
900	0.79	0.72	17.43	17.49	16.76	13.36	20.61	20.10	20.89	25.55
950	0.98	0.92	17.00	16.81	16.57	12.12	19.31	18.91	18.85	23.12
1000	1.28	1.23	16.62	16.03	15.41	10.39	17.81	17.53	16.65	20.94
1100	2.35	2.41	16.36	14.69	10.33	5.84	14.59	14.62	12.16	16.47
1200	3.03	3.63	16.96	16.29	5.11	2.73	13.04	13.05	9.45	13.23
1300	1.89	2.50	18.49	25.16	-0.28	3.60	14.79	13.16	10.11	12.00
1400	1.24	1.52	21.19	38.54	-9.94	3.14	17.23	14.22	11.97	12.48
1500	1.06	1.15	23.09	25.65	2.86	1.60	18.45	14.76	13.51	13.15
1600	1.06	1.04	23.89	21.72	5.72	0.39	19.32	15.30	15.07	13.83
1700	1.16	1.07	24.17	19.30	7.17	0.42	19.11	15.22	16.22	14.02
1800	1.34	1.17	24.15	17.39	8.07	1.16	18.68	15.19	17.61	14.28
1900	1.57	1.37	23.87	15.78	9.09	1.29	17.97	15.29	17.69	13.84
2000	1.89	1.63	23.35	14.31	10.02	1.04	17.69	15.85	19.13	14.12
2100	2.27	1.99	22.45	12.94	11.59	0.37	16.91	16.94	19.58	14.30
2200	2.72	2.46	20.99	11.73	13.63	4.08	17.01	19.27	18.63	15.30
2300	3.04	2.97	19.22	10.78	18.64	12.50	16.93	24.63	15.28	16.96
2400	3.01	3.20	17.88	10.17	31.26	16.10	16.11	24.17	13.13	20.19
2500	2.77	2.97	17.31	10.00	18.47	8.32	13.84	20.01	12.16	25.22
2600	2.66	2.71	17.28	9.84	12.52	4.33	11.82	18.32	11.21	24.53
2700	2.81	2.66	17.53	9.49	10.19	1.56	10.30	18.44	10.80	23.64
2800	3.19	2.92	17.86	8.88	9.05	0.50	9.00	19.19	9.55	23.72
2900	3.65	3.32	18.12	8.25	8.40	2.08	8.03	21.65	8.65	25.10
3000	4.20	3.71	18.37	7.78	8.23	3.29	7.22	24.48	8.15	33.86

REV. X1

SYDC-20-62HP+

081007

Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Bi-Directional Coupler

SYDC-20-62HP+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +85°C

FREQ. (MHz)	INSERTION LOSS		COUPLING		DIRECTIVITY		RETURN LOSS			
	(dB) IN-OUT	(dB) FWD-REV	(dB) IN-FWD	(dB) OUT-REV	(dB) IN-REV	(dB) OUT-FWD	(dB) IN	(dB) OUT	(dB) FWD	(dB) REV
10	0.09	0.09	20.23	20.18	28.47	28.39	25.56	25.62	25.52	25.70
20	0.14	0.14	20.29	20.18	38.98	37.36	31.10	31.43	31.11	31.82
30	0.17	0.18	20.34	20.19	45.66	41.98	32.56	33.14	32.67	33.76
40	0.18	0.19	20.36	20.20	47.46	45.41	33.40	33.61	33.44	34.55
50	0.19	0.19	20.38	20.22	45.19	49.07	34.04	33.91	34.23	35.47
75	0.19	0.20	20.41	20.28	39.36	53.68	35.09	34.83	36.32	38.25
100	0.19	0.20	20.41	20.31	34.63	42.42	35.23	35.40	37.56	41.09
125	0.20	0.20	20.42	20.33	31.27	36.63	34.90	34.57	38.72	41.55
150	0.20	0.21	20.40	20.36	29.00	33.67	34.58	33.70	40.49	40.84
175	0.21	0.22	20.38	20.38	27.49	31.90	34.69	33.24	42.96	40.70
200	0.22	0.23	20.36	20.40	26.46	30.78	34.79	33.18	45.21	41.17
250	0.24	0.24	20.31	20.42	24.41	28.49	34.59	32.55	47.01	40.72
275	0.25	0.26	20.28	20.42	23.27	27.21	33.90	31.82	50.00	40.40
300	0.26	0.26	20.23	20.44	22.31	26.22	33.19	31.24	52.28	40.73
350	0.29	0.28	20.14	20.43	21.07	24.74	32.46	30.58	48.25	41.94
375	0.30	0.29	20.09	20.41	20.61	24.06	31.94	30.10	46.01	41.83
400	0.31	0.30	20.03	20.41	19.92	23.22	31.39	29.70	43.65	41.86
450	0.34	0.33	19.91	20.35	19.08	21.88	30.60	28.71	40.47	40.10
475	0.36	0.35	19.83	20.32	18.62	21.33	30.16	28.27	39.33	40.19
500	0.38	0.36	19.75	20.27	18.20	20.82	29.74	27.90	37.78	40.57
540	0.41	0.39	19.62	20.17	17.75	19.97	28.99	27.33	35.57	40.79
550	0.42	0.40	19.59	20.14	17.65	19.77	28.85	27.17	35.16	40.61
575	0.44	0.42	19.51	20.06	17.28	19.16	28.44	26.87	34.24	40.02
600	0.46	0.43	19.40	19.97	17.03	18.74	27.94	26.55	33.02	40.16
650	0.51	0.48	19.18	19.75	16.75	17.81	27.18	25.74	30.68	38.65
675	0.54	0.51	19.07	19.61	16.68	17.31	26.71	25.27	29.68	37.63
700	0.57	0.54	18.95	19.46	16.53	16.94	26.24	24.79	28.80	36.78
750	0.65	0.61	18.72	19.13	16.19	15.75	25.20	24.05	26.57	35.86
800	0.74	0.69	18.38	18.71	16.49	15.08	23.99	23.12	24.71	33.16
850	0.85	0.81	18.08	18.25	16.26	13.93	22.83	22.18	22.70	30.94
900	1.00	0.97	17.75	17.71	16.24	12.80	21.56	21.08	20.67	27.85
950	1.21	1.18	17.39	17.09	15.79	11.52	20.11	19.79	18.67	25.12
1000	1.51	1.51	17.10	16.44	14.50	9.80	18.52	18.43	16.54	22.54
1100	2.41	2.56	16.98	15.66	9.95	5.87	15.60	15.78	12.74	17.67
1200	2.85	3.39	17.55	17.78	5.20	3.47	14.48	14.09	10.54	14.38
1300	2.03	2.57	19.09	26.05	-0.49	3.74	16.06	14.15	11.02	13.15
1400	1.48	1.77	21.41	36.36	-8.04	3.18	18.14	14.85	12.64	13.43
1500	1.31	1.44	23.14	26.07	2.29	1.81	19.45	15.41	14.12	13.86
1600	1.32	1.34	23.98	22.17	5.38	0.69	19.85	15.59	15.36	14.26
1700	1.42	1.38	24.36	19.75	6.92	0.19	19.73	15.70	16.37	14.41
1800	1.59	1.49	24.56	17.91	8.02	0.87	19.15	15.68	17.27	14.55
1900	1.83	1.67	24.46	16.32	9.11	1.10	18.54	15.81	18.35	14.73
2000	2.14	1.94	24.43	14.92	10.25	1.06	17.83	16.25	18.90	14.75
2100	2.51	2.29	23.92	13.60	11.73	0.23	17.36	17.53	19.07	15.24
2200	2.92	2.74	22.97	12.47	14.33	3.90	16.93	19.50	17.79	16.06
2300	3.21	3.19	21.58	11.56	19.54	13.42	16.40	22.75	15.52	17.79
2400	3.24	3.40	20.38	10.97	32.24	14.51	15.15	22.17	13.73	20.73
2500	3.13	3.29	19.68	10.71	18.33	6.70	13.46	20.25	12.65	23.82
2600	3.11	3.14	19.43	10.48	13.32	3.12	11.73	18.63	11.95	24.70
2700	3.29	3.18	19.44	10.13	10.79	0.66	10.34	18.42	11.02	24.75
2800	3.62	3.38	19.52	9.65	9.56	1.08	9.26	19.34	10.34	25.84
2900	4.04	3.71	19.62	9.18	8.88	2.33	8.34	20.30	9.40	28.93
3000	4.50	4.08	19.73	8.83	8.48	3.26	7.66	21.46	8.85	36.16

REV. X1

SYDC-20-62HP+

081007

Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661









The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Bi-Directional Coupler

Typical Performance Curves

SYDC-20-62HP+



REV. X1
SYDC-20-62HP+
081007
Page 1 of 2








Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Bi-Directional Coupler

Typical Performance Curves

SYDC-20-62HP+




REV. X1
SYDC-20-62HP+
081007
Page 2 of 2



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Outline Dimensions

AH202-1



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
AH202-1	.38 (9.65)	.50 (12.70)	.25 (6.35)	.020 (0.51)	.115 (2.92)	.070 (1.78)	.035 (0.89)	.050 (1.27)	.090 (2.29)	.040 (1.02)	.105 (2.67)	.140 (3.56)	.095 (2.41)	.80

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.01 ; 3 Pl. ± 0.005

Notes:

- Case material: Nickel Silver alloy.
- Base material: Printed wiring laminate.
- Termination finish:

For RoHS 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.

All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F61



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	12	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified




REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M107473	NEW RELEASE	09/25/06	AV	DY

**SUGGESTED MOUNTING CONFIGURATION
FOR AH202-1 CASE STYLE, "rr" PIN CONNECTION**



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	AV	09/19/06
	CHECKED	IL	09/25/06
	APPROVED	DY	09/25/06



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235



PL, rr, AH202-1, SYDC, TB-349

Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.	
ASHEETA1.DWG REV:A	DATE:01/12/95

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-246	REV: OR
FILE: 98PL246	SCALE: 5:1	SHEET: 1 OF 1	

Evaluation Board and Circuit


For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215