



SURFACE MOUNT

Directional Coupler

SYDC-7-651HP+

Mini-Circuits

50Ω 7 dB Coupling 10 to 650 MHz 15 W

THE BIG DEAL

- High Power Handling, 15 W
- Multi-Octave Bandwidth
- Very Low Mainline Loss, 0.6 dB
- Excellent VSWR, 1.15:1



Generic photo used for illustration purposes only

CASE STYLE: AH202-1

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- VHF/UHF
- Signal Monitoring
- Communications
- Military Mobile

PRODUCT OVERVIEW

Mini-Circuits' SYDC-7-651HP+ surface mount directional coupler provides high power handling up to 15 W and low mainline loss of 0.5 dB or better for applications from 10 to 650 MHz. The coupler features core and wire construction mounted on an 8-lead printed laminate base with wraparound terminations for excellent solderability. The unit measures 0.38x0.50x0.25", accommodating dense circuit board layouts.

KEY FEATURES

Feature	Advantages
High Power Handling, 15 W	Usable in many systems with high-power requirements.
Low Mainline Loss, ≤0.8 dB	Provides excellent through-path signal power transmission.
Good Directivity, 21 to 25 dB	High directivity allows accurate signal sampling through the coupled port with minimal measurement error.
Excellent VSWR, 1.15:1 (Input/Output/Coupling)	Provides excellent matching in 50Ω systems with minimal signal reflection.
Small Size, 0.38x0.50x0.25"	Provides high power capability while saving space in systems with tight layouts.

REV. B
ECO-015601
SYDC-7-651HP+
MCL NY
251107





SURFACE MOUNT

Directional Coupler

SYDC-7-651HP+

Mini-Circuits

50Ω 7 dB Coupling 10 to 650 MHz 15 W

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		10		650	MHz
Mainline Loss (Above Theoretical 0.85 dB)	10		0.4	0.8	dB
	30		0.5	0.8	
	520		0.6	0.9	
	650		0.7	1.2	
Coupling	10-650	7.0	7.3	7.6	dB
Coupling Flatness	30-520		0.1	0.3	dB
	10-650		0.2	0.5	
Directivity	10	11	15		dB
	30	20	25		
	520	17	21		
	650	12	15		
Return Loss (Input)	30-520	17	20		dB
	10-650		15		
Return Loss (Output)	30-520	16	20		dB
	10-650		14		
Return Loss (Coupling)	30-520	14	17		dB
	10-650		12		
Input Power ¹	30-520			15	W
	10-650			10	


1. The user must provide adequate means of heat removal to limit the temperature of ground connections 2,3,6,7 to +65°C, in order to ensure proper performance. At +25°C ambient temperature this requires thermal resistance of the user's PC board heat sink to be 20°C/W or less when the unit is driven at maximum specified RF input power, 15 W. At higher ambient temperature, with the same heat sink. Input power in watts must not exceed 15 W x (+85°C - Tambient) ÷ +60°C.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +65°C Case ²
Storage Temperature	-55°C to +100°C

2. Case temperature is defined as temperature on ground leads. Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



*Electrical schematic is for Directional coupler with internal transformer(s) and external termination



SURFACE MOUNT

Directional Coupler

SYDC-7-651HP+


Mini-Circuits

50Ω 7 dB Coupling 10 to 650 MHz 15 W

PAD CONNECTIONS


INPUT	8
OUTPUT	1
COUPLED (FORWARD)	5
50Ω TERM EXTERNAL	4
GROUND	2, 3, 6, 7

OUTLINE DRAWING



PRODUCT MARKING: SYDC-7-651HP

EVAL BOARD MCL P/N: TB-SYDC7-651HP+
SUGGESTED PCB LAYOUT (PL-246)



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DIMENSIONS (Inches mm)

A	B	C	D	E	F	G	H
.38	.50	.25	.020	.115	.070	.035	.050
9.65	12.70	6.35	0.51	2.92	1.78	0.89	1.27
J	K	L	M	N	wt		
.090	.040	.105	.140	.095	grams		
2.29	1.02	2.67	3.56	2.41	0.80		

TAPE & REEL INFORMATION: F61



SURFACE MOUNT

Directional Coupler




SYDC-7-651HP+

Mini-Circuits

50Ω 7 dB Coupling 10 to 650 MHz 15 W

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)		Coupling (dB)	Directivity (dB)	Return Loss (dB)		
	In-Out	In-Cpl			In	Out	Cpl
10	1.25	7.19	15.31	14.67	12.22	10.86	
50	1.34	7.36	28.34	20.90	22.02	16.74	
100	1.32	7.36	30.04	22.39	22.20	17.64	
160	1.31	7.37	32.65	24.71	22.49	18.17	
200	1.32	7.35	36.68	25.60	23.06	18.43	
260	1.34	7.32	38.93	29.03	23.85	19.57	
300	1.34	7.33	40.80	31.95	25.48	18.38	
400	1.39	7.28	29.35	38.05	30.18	18.84	
500	1.48	7.23	22.61	24.91	43.26	20.27	
650	1.70	7.19	16.05	16.84	26.43	23.69	



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Directional Coupler

SYDC-7-651HP+





Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
5	1.75	7.35	10.53	9.15	7.33	6.09
10	1.25	7.19	15.31	14.67	12.22	10.86
15	1.19	7.19	19.01	17.80	15.26	13.83
20	1.21	7.22	22.14	19.48	17.38	15.60
25	1.25	7.25	24.73	20.27	18.96	16.47
30	1.29	7.29	26.63	20.56	20.16	16.77
35	1.32	7.32	27.74	20.61	20.99	16.81
40	1.33	7.34	28.33	20.68	21.51	16.80
45	1.34	7.35	28.44	20.76	21.83	16.77
50	1.34	7.36	28.34	20.90	22.02	16.74
55	1.33	7.37	28.05	21.03	22.12	16.71
60	1.33	7.37	27.74	21.20	22.18	16.71
80	1.32	7.38	27.55	21.87	22.24	16.98
100	1.32	7.36	30.04	22.39	22.20	17.64
120	1.32	7.36	32.84	22.76	22.41	18.05
140	1.31	7.37	32.67	23.72	22.50	18.03
160	1.31	7.37	32.65	24.71	22.49	18.17
180	1.31	7.36	35.04	25.03	22.68	18.44
200	1.32	7.35	36.68	25.60	23.06	18.43
220	1.32	7.35	36.31	26.49	23.56	18.40
240	1.33	7.33	37.66	27.78	23.79	18.95
260	1.34	7.32	38.93	29.03	23.85	19.57
280	1.34	7.32	37.68	30.26	24.34	19.15
300	1.34	7.33	40.80	31.95	25.48	18.38
320	1.35	7.32	46.89	34.71	26.54	18.55
340	1.37	7.29	32.59	38.69	26.76	19.76
360	1.38	7.27	28.26	43.77	26.87	20.39
380	1.39	7.28	27.50	44.45	27.96	19.48
400	1.39	7.28	29.35	38.05	30.18	18.84
420	1.41	7.26	29.73	33.16	32.28	19.42
440	1.43	7.24	25.91	30.25	33.08	20.69
460	1.45	7.22	23.35	28.29	34.32	21.07
480	1.46	7.23	22.60	26.66	38.14	20.49
500	1.48	7.23	22.61	24.91	43.26	20.27
520	1.50	7.21	21.98	23.29	41.37	20.83
530	1.52	7.20	21.31	22.64	40.25	21.27
535	1.52	7.20	20.97	22.33	39.70	21.48
540	1.53	7.20	20.61	22.07	39.17	21.66
550	1.54	7.19	20.00	21.55	37.92	21.94
650	1.70	7.19	16.05	16.84	26.43	23.69
750	1.95	7.24	12.55	13.39	21.46	26.23

Directional Coupler


Typical Performance Curves

SYDC-7-651HP+



Outline Dimensions

AH202-1



Suggested Layout,
Tolerance to be within ± 0.002

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
AH202-1	.38 (9.65)	.50 (12.70)	.25 (6.35)	.020 (0.51)	.115 (2.92)	.070 (1.78)	.035 (0.89)	.050 (1.27)	.090 (2.29)	.040 (1.02)	.105 (2.67)	.140 (3.56)	.095 (2.41)	.80

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.01 ; 3 Pl. ± 0.005

Notes:

- Case material: Nickel Silver alloy.
- Base material: Printed wiring laminate.
- Termination finish:
 For RoHS 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 All models, (+) suffix.
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits
 ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F61



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	12	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf


 **Mini-Circuits**[®]

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified




REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M107473	NEW RELEASE	09/25/06	AV	DY

**SUGGESTED MOUNTING CONFIGURATION
FOR AH202-1 CASE STYLE, "rr" PIN CONNECTION**



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	AV 09/19/06
	CHECKED	IL 09/25/06
	APPROVED	DY 09/25/06



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, rr, AH202-1, SYDC, TB-349



Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-246	REV: OR
FILE: 98PL246	SCALE: 5:1	SHEET: 1 OF 1	

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215