


Directional Coupler

SYDC-ED14628

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : AH1647

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		136		870	MHz
Coupling	Nominal		25±1.5		dB
	Flatness		1.9		dB
Mainline Loss *	136-870 MHz		0.3		dB
Directivity	136-870 MHz		19.7		dB
VSWR	136-870 MHz		1.2		(:1)
RF Power Input	136-870 MHz			50	W


*Mainline loss includes theoretical coupled power loss of 0.014 dB at 25 dB coupling.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 65°C Case ⁽¹⁾
Storage Temperature	-55°C to 100°C

⁽¹⁾Case temperature is defined as temperature on ground leads

PIN CONNECTIONS	
INPUT	1
OUTPUT	8
COUPLED	4
50Ω TERM. EXTERNAL	5
GROUND	2,3,6,7

Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.

Directional Coupler





SYDC-ED14628

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
100.0	0.21	25.80	17.50	15.35	15.32	15.94
120.0	0.18	25.82	18.39	16.74	16.82	17.87
136.0	0.16	25.82	18.83	17.82	17.91	19.22
150.0	0.15	25.81	19.06	18.84	18.84	20.20
175.0	0.14	25.79	19.64	20.07	20.09	21.64
200.0	0.14	25.77	20.00	21.11	21.16	23.36
250.0	0.14	25.70	20.25	22.65	22.97	27.59
300.0	0.14	25.61	20.30	24.37	24.48	30.48
350.0	0.15	25.51	20.27	25.10	25.71	37.69
400.0	0.15	25.39	20.24	26.19	26.47	36.26
450.0	0.16	25.25	20.19	26.73	27.47	32.13
500.0	0.17	25.11	20.38	27.14	27.43	30.09
550.0	0.18	24.93	20.21	27.73	28.51	26.25
600.0	0.19	24.77	20.75	27.81	27.72	25.43
650.0	0.20	24.58	20.64	27.49	28.10	22.78
700.0	0.21	24.38	21.33	27.88	27.34	22.27
750.0	0.22	24.16	21.22	26.72	26.76	20.34
800.0	0.23	23.92	20.92	26.98	26.32	19.87
850.0	0.24	23.63	19.69	25.91	25.19	18.48
870.0	0.25	23.50	19.00	25.36	25.07	18.05
900.0	0.26	23.31	17.96	25.29	24.76	17.97
950.0	0.27	22.92	15.90	24.97	23.81	16.99
1000.0	0.30	22.42	13.73	23.60	23.15	16.44




Typical Performance Curves



Outline Dimensions

AH1647



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
AH1647	.433 (11.00)	.690 (17.53)	.415 (10.54)	- -	.100 (2.54)	.476 (12.09)	.394 (10.01)	.045 (1.14)	.060 (1.52)	.276 (7.01)	.194 (4.93)	.257 (6.53)	.560 (14.22)
CASE #	P	Q	R	S	T	WT, GRAM							
AH1647	.475 (12.07)	.561 (14.25)	.258 (6.55)	.069 (1.75)	.061 (1.55)	2.80							

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm.01$; 3 Pl. $\pm.005$

Notes:

- Case material: Nickel Silver alloy.
- Base material: Printed wiring laminate.
- Termination finish: Tin copper solder alloy up to 0.07% Nickel. All models, (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED


ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


RF/IF MICROWAVE COMPONENTS

THIRD ANGLE PROJECTION		REVISIONS					
		REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
		OR	M133287	NEW RELEASE	08/26/11	GF	WP

**SUGGESTED MOUNTING CONFIGURATION FOR
AH1647 CASE STYLE, "08DC05" PIN CODE**



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. SUGGEST TO PROVIDE BRASS COIN FOR BETTER HEAT TRANSFER FROM THE UNIT. OTHERWISE PROVIDE ARRAY OF THERMAL VIAS ADEQUATE TO LIMIT TEMPERATURE OF GROUND CONNECTIONS UNDER THE UNIT TO 65°C.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK
-  DENOTES BRASS COIN.

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235					
DIMENSIONS ARE IN INCHES		DRAWN	GF	08/22/11		PL, 08DC05, AH1647, TB-630+					
TOLERANCES ON:		CHECKED	IL	08/25/11							
2 PL DECIMALS ±		APPROVED	WP	08/26/11							
3 PL DECIMALS ± .005											
ANGLES ±											
FRACTIONS ±											
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY INTENDED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, & MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.											
ASHEETA1.DWG REV:A DATE:01/12/95						SIZE A CODE IDENT 15542 DRAWING NO: 98-PL-351 REV: OR					
						FILE: 98PL351		SCALE: 4:1		SHEET: 1 OF 1	

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 65° C Case Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215