



Mini-Circuits

SURFACE MOUNT

Directional Coupler

SYDC-10-42HP+


50Ω 10 dB Coupling 10 to 400 MHz 16 Watt

THE BIG DEAL

- High Power, 16 W Max.
- Flat Coupling, ± 0.3 dB Typ.
- Low Mainline Loss, 0.3 dB Typ.

APPLICATIONS

- Signal Monitoring
- Military Mobile



Generic photo used for illustration purposes only

CASE STYLE: AH1596

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		10		400	MHz
Mainline Loss (Above Theoretical 0.45 dB)	10-250		0.3	0.7	dB
	250-400		0.6	1.3	
Coupling	10-400	9.0	10	10.8	dB
Coupling Flatness ($\pm$)	10-400		± 0.3	± 0.7	dB
Directivity	10	23	32		dB
	250	12	18		
	400	7	12		
Return Loss (Input)	10-400		22		dB
Return Loss (Output)	10-400		22		dB
Return Loss (Coupling)	10-400		18		dB
Input Power ¹	10-400			16	W


1. The user must provide adequate means of heat removal to limit the temperature of ground connections under the PCB to +65°C, in order to ensure proper performance. At +25°C ambient temperature this requires thermal resistance of the user's PC board heat sink to be 3.5°C/W.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +60°C Case ²
Storage Temperature	-55°C to +100°C

2. Case temperature is defined as temperature on ground leads.
Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



*Electrical schematic is for Directional coupler with internal transformer(s) and external termination

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
ECO-015601
SYDC-10-42HP+
MCL NY
251106

PAGE 1 OF 3



Mini-Circuits

SURFACE MOUNT

Directional Coupler


SYDC-10-42HP+

50Ω 10 dB Coupling 10 to 400 MHz 16 Watt

PAD CONNECTIONS

INPUT	8
OUTPUT	1
COUPLED (FORWARD)	5
50Ω TERM EXTERNAL	4
GROUND	2, 3, 6, 7

PRODUCT MARKING: N/A


EVAL BOARD MCL P/N: TB-SYDC10-42HP+
SUGGESTED PCB LAYOUT (PL-339)

NOTES:


- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern

Suggested Layout,
Tolerance to be within ±.002

OUTLINE DIMENSIONS (Inches/mm)

A	B	C	E	F	G	H	J
.50	.62	.36	.115	.070	.073	--	.090
12.70	15.75	9.14	2.92	1.78	1.85	--	2.29
K	L	M	N	P	Q	R	wt
.040	.037	.140	.135	.010	--	.135	grams
1.02	0.94	3.56	3.43	0.25	--	3.43	3.00

TAPE & REEL INFORMATION: F107



Mini-Circuits

SURFACE MOUNT




Directional Coupler

SYDC-10-42HP+

50Ω 10 dB Coupling 10 to 400 MHz 16 Watt

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)	Directivity (dB)	Return Loss (dB)		
	In-Out			In	Out	Cpl
10	0.57	10.36	37.66	26.50	27.30	23.24
30	0.57	10.37	33.90	27.46	26.78	24.03
50	0.58	10.38	30.49	27.81	26.55	24.36
100	0.63	10.39	25.07	28.64	25.77	25.13
150	0.68	10.39	21.74	29.25	24.96	26.07
200	0.75	10.37	19.00	28.26	24.26	26.99
250	0.83	10.32	16.89	26.75	23.28	28.37
300	0.94	10.26	15.02	24.27	21.93	30.49
350	1.07	10.19	13.36	21.60	20.40	32.95
400	1.23	10.10	11.82	18.96	18.59	38.73



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Directional Coupler

SYDC-10-42HP+





Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
10.0	0.57	10.36	37.66	26.50	27.30	23.24
20.0	0.56	10.36	35.82	27.09	27.04	23.76
30.0	0.57	10.37	33.90	27.46	26.78	24.03
40.0	0.57	10.37	32.10	27.68	26.68	24.20
50.0	0.58	10.38	30.49	27.81	26.55	24.36
53.0	0.58	10.38	30.06	27.88	26.50	24.40
60.0	0.59	10.39	29.07	27.98	26.43	24.51
70.0	0.60	10.39	27.81	28.18	26.27	24.66
80.0	0.61	10.39	26.74	28.36	26.10	24.81
90.0	0.62	10.40	25.83	28.51	25.91	24.97
100.0	0.63	10.39	25.07	28.64	25.77	25.13
125.0	0.65	10.40	23.11	28.90	25.44	25.58
150.0	0.68	10.39	21.74	29.25	24.96	26.07
175.0	0.71	10.38	20.28	28.81	24.65	26.53
200.0	0.75	10.37	19.00	28.26	24.26	26.99
225.0	0.79	10.35	17.91	27.75	23.78	27.56
250.0	0.83	10.32	16.89	26.75	23.28	28.37
275.0	0.88	10.29	15.94	25.59	22.68	29.42
300.0	0.94	10.26	15.02	24.27	21.93	30.49
325.0	1.00	10.23	14.17	22.94	21.19	31.54
350.0	1.07	10.19	13.36	21.60	20.40	32.95
375.0	1.14	10.15	12.57	20.27	19.52	35.24
400.0	1.23	10.10	11.82	18.96	18.59	38.73

Directional Coupler


SYDC-10-42HP+

Typical Performance Curves



Outline Dimensions

AH1596



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
AH1596	.50 (12.70)	.62 (15.75)	.36 (9.14)	- -	.115 (2.92)	.070 (1.78)	.073 (1.85)	- -	.090 (9.65)	.040 (1.02)	.037 (0.94)	.140 (3.56)	.135 (3.43)
CASE #	P	Q	R	WT, GRAM									
AH1596	.010 (0.25)	- -	.135 (3.43)	3.00									

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, Base material: Printed wiring laminate.
- Termination finish: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F107

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
32	20	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M130233	NEW RELEASE	05/11/11	AV	YQ

SUGGESTED MOUNTING CONFIGURATION FOR
AH1596 CASE STYLE, "08DC03" PIN CODE



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	AV	04/27/11
	CHECKED	IL	05/11/11
	APPROVED	YQ	05/11/11



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235


PL, 08DC03, AH1596, TB-608+

Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.			
ASHEETA1.DWG REV:A DATE:01/12/95			


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-339	REV: OR
FILE: 98PL339	SCALE: 5:1	SHEET: 1 OF 1	

Evaluation Board and Circuit

For Pin Connection Refer to
Data Sheet of the DUT



TB-608+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215