SURFACE MOUNT

Bi-Directional Coupler

SYDC-18-23+

50Ω 18 dB Coupling 10 to 2000 MHz

FEATURES

- High Directivity, 20 dB Typ.
- Wideband Frequency, 10 to 2000 MHz
- Excellent VSWR, 1.25:1 Typ.

APPLICATIONS

- Cellular
- Instrumentation
- Communications
- GPS

Generic photo used for illustration purposes only

CASE STYLE: AH202-1

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C[1]

Parameter	Condition (MHz)	Min.	Typ.	Max.	Units
Frequency Range		10		2000	MHz
Mainline Loss	10 30 1000 2000		0.8 0.7 0.6 1.0	1.2 1.0 0.9 1.5	dB
Coupling	10-2000		17.8±0.8		dB
Coupling Flatness (±)	10-300 300-1000 1000-2000		±0.2 ±0.3 ±0.4	±0.4 ±0.5 ±0.9	dB
Directivity	10 30 1000 2000	14 18 15 14	17 21 20 20		dB
Return Loss (Input)	10 30 1000 2000		18 21 20 14		dB
Return Loss (Output)	10 30 1000 2000		18 22 20 16		dB
Return Loss (Coupling)	10 30 1000 2000		18 21 20 16		dB
Input Power[2]	10 30-1000 1000-2000			1 2 2	W

1. Tested on Evaluation Board TB-SYDC-18-23+.
2. The user must provide adequate means of heat removal to limit the temperature of ground connections 2,3,6,7 to +85°C, in order to ensure proper performance.
At +25°C ambient temperature this requires thermal resistance of the user's PC board heat sink to be 27°C/W or less when the unit is driven at maximum specified RF input power, X W.
At higher ambient temperature, with the same heat sink. Input power in watts must not exceed X W x (+85°C - Tambient) ÷ +60°C, where X = 1 at 10 MHz and 2 over 30 to 2000 MHz.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



*Electrical schematic is for Bi-Directional coupler with internal transformer(s) that routes DC from all ports to ground.

SURFACE MOUNT

Bi-Directional Coupler

SYDC-18-23+

50Ω 18 dB Coupling 10 to 2000 MHz

PAD CONNECTIONS

INPUT	8
OUTPUT	1
COUPLED (FORWARD)	5
COUPLED (REVERSE)	4
GROUND	2, 3, 6, 7

*PRODUCT MARKING: SYDC-18-23

*Marking may contain other features or characters for internal lot control.

DEMO BOARD MCL P/N: TB-SYDC-18-23+

SUGGESTED PCB LAYOUT (PL-246)



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

OUTLINE DIMENSIONS (Inches / mm)

A	B	C	D	E	F	G
.38	.50	.25	.020	.115	.070	.035
9.65	12.70	6.35	0.51	2.92	1.78	0.89

H	J	K	L	M	N	wt
.050	.090	.040	.105	.140	.095	grams
1.27	2.29	1.02	2.67	3.56	2.41	0.80

TAPE & REEL INFORMATION: F61

SURFACE MOUNT

Bi-Directional Coupler

SYDC-18-23+

50Ω 18 dB Coupling 10 to 2000 MHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)		Directivity (dB)		Return Loss (dB)			
	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
10	0.85	17.08	18.41	19.19	17.85	18.66	19.15	18.68	19.40
50	0.67	17.17	18.09	23.85	22.55	23.83	25.90	24.36	26.73
100	0.62	17.21	18.02	24.93	23.66	25.64	28.61	26.35	29.82
300	0.57	17.39	18.04	25.38	23.94	28.71	31.10	29.67	32.94
500	0.56	17.55	18.17	24.50	23.78	30.54	28.75	31.76	31.61
1000	0.63	17.68	18.34	21.40	22.73	22.31	21.17	23.81	24.29
1500	0.82	17.71	18.25	23.73	24.28	17.65	18.33	18.83	21.22
1600	0.86	17.74	18.22	24.84	25.40	17.08	18.12	18.09	20.89
1800	0.95	17.80	18.19	28.37	27.57	16.00	17.86	17.06	20.63
2000	1.07	17.93	18.16	39.90	26.56	14.85	17.79	16.22	20.51







NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Bi-Directional Coupler SYDC-18-23+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)		COUPLING (dB)		DIRECTIVITY (dB)		RETURN LOSS (dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
5	0.79	0.76	16.90	18.24	14.34	15.37	14.94	14.80	14.59	14.68
6	0.82	0.80	16.97	18.30	15.58	16.79	16.24	16.29	16.09	16.32
7	0.84	0.83	17.02	18.36	16.41	17.73	17.13	17.32	17.08	17.46
8	0.85	0.85	17.05	18.39	17.01	18.34	17.77	18.07	17.75	18.27
9	0.85	0.86	17.07	18.41	17.47	18.82	18.26	18.67	18.27	18.89
10	0.85	0.86	17.08	18.41	17.85	19.19	18.66	19.15	18.68	19.40
20	0.78	0.79	17.13	18.28	20.12	21.49	21.01	22.09	21.31	22.60
30	0.72	0.74	17.14	18.18	21.33	22.71	22.31	23.86	22.81	24.50
40	0.69	0.71	17.16	18.13	22.02	23.39	23.18	25.04	23.68	25.82
50	0.67	0.69	17.17	18.09	22.55	23.85	23.83	25.90	24.36	26.73
70	0.64	0.67	17.19	18.05	23.22	24.43	24.77	27.14	25.29	28.20
90	0.63	0.65	17.20	18.02	23.52	24.80	25.37	28.12	26.05	29.33
100	0.62	0.65	17.21	18.02	23.66	24.93	25.64	28.61	26.35	29.82
300	0.57	0.61	17.39	18.04	23.94	25.38	28.71	31.10	29.67	32.94
500	0.56	0.59	17.55	18.17	23.78	24.50	30.54	28.75	31.76	31.61
700	0.57	0.59	17.65	18.29	23.64	23.23	27.59	25.05	28.71	27.71
900	0.60	0.61	17.68	18.33	23.09	21.66	23.78	22.07	25.17	25.17
1000	0.63	0.64	17.68	18.34	22.73	21.40	22.31	21.17	23.81	24.29
1100	0.67	0.66	17.68	18.33	22.62	21.41	20.89	20.22	22.48	23.01
1200	0.70	0.69	17.68	18.30	22.96	21.56	19.94	19.68	21.60	22.56
1300	0.74	0.72	17.70	18.29	23.00	21.89	19.03	19.07	20.62	22.00
1400	0.78	0.76	17.70	18.28	23.71	22.71	18.30	18.57	19.80	21.60
1500	0.82	0.79	17.71	18.25	24.28	23.73	17.65	18.33	18.83	21.22
1600	0.86	0.83	17.74	18.22	25.40	24.84	17.08	18.12	18.09	20.89
1700	0.91	0.87	17.77	18.20	26.51	26.40	16.55	17.96	17.47	20.47
1800	0.95	0.91	17.80	18.19	27.57	28.37	16.00	17.86	17.06	20.63
1900	1.01	0.95	17.86	18.18	27.59	32.11	15.39	17.63	16.71	20.52
2000	1.07	1.01	17.93	18.16	26.56	39.90	14.85	17.79	16.22	20.51
2100	1.14	1.07	18.09	18.16	26.87	40.36	14.32	18.05	15.76	20.88
2300	1.28	1.22	18.37	18.39	21.39	26.25	13.68	19.09	14.99	22.08
2400	1.36	1.28	18.50	18.40	19.64	21.01	13.42	19.56	14.83	22.00
2500	1.45	1.37	18.71	18.47	18.34	17.95	13.21	19.96	14.58	21.44
2600	1.54	1.45	18.87	18.56	16.87	15.55	13.02	20.26	14.68	21.41

Bi-Directional Coupler SYDC-18-23+

Typical Performance Curves









Case Style AH

Outline Dimensions

AH202-1







Suggested Layout,
Tolerance to be within ±.002

DENOTES METALLIZATION

DENOTES SOLDER RESIST

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
AH202-1	.38 (9.65)	.50 (12.70)	.25 (6.35)	.020 (0.51)	.115 (2.92)	.070 (1.78)	.035 (0.89)	.050 (1.27)	.090 (2.29)	.040 (1.02)	.105 (2.67)	.140 (3.56)	.095 (2.41)	.80

Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005

Notes:

1. Case material: Nickel Silver alloy.
2. Base material: Printed wiring laminate.
3. Termination finish:

For RoHS 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate. All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F61



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	12	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M107473	NEW RELEASE	09/25/06	AV	DY

SUGGESTED MOUNTING CONFIGURATION
FOR AH202-1 CASE STYLE, "rr" PIN CONNECTION



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	AV	09/19/06
TOLERANCES ON:	CHECKED	IL	09/25/06
2 PL DECIMALS ±	APPROVED	DY	09/25/06
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, rr, AH202-1, SYDC, TB-349

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-246	OR

FILE:	SCALE:	SHEET:
98PL246	5:1	1 OF 1

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



TB-349



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers RO4350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.