

Bi-Directional Coupler

SYDC-ED14256

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : AH1596

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		1.5		30	MHz
Coupling	Nominal		20.5±1		dB
	Flatness		±0.05		dB
Mainline Loss **	1.5-30 MHz		0.06		dB
Directivity	1.5-30 MHz		33		dB
VSWR	1.5-30 MHz		1.12		(:1)
RF Power Input***	1.5-30 MHz			50	W

** Mainline loss includes theoretical coupled power loss of 0.044 dB at 20 dB coupling.


***The user must provide adequate means of heat removal to limit the temperature of ground connections 2,3,6,7 to 65°C, in order to ensure proper performance. At 25°C ambient temperature this requires thermal resistance of the user's PC board heat sink to be 10°C/W.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 65°C Case ⁽¹⁾
Storage Temperature	-55°C to 100°C

⁽¹⁾Case temperature is defined as temperature on ground leads

PIN CONNECTIONS	
INPUT	8
OUTPUT	1
COUPLED FORWARD	5
COUPLED REVERSE	4
GROUND	2,3,6,7

Functional Diagram



Bi-Directional Coupler

SYDC-ED14256

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB) IN-OUT	COUPLING (dB)		DIRECTIVITY (dB)		RETURN LOSS (dB)			
		IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
1.5	0.07	20.49	20.45	45.19	51.77	40.50	42.13	41.68	42.07
2.0	0.07	20.50	20.46	45.65	50.60	39.62	41.02	41.10	41.61
3.0	0.07	20.50	20.46	45.85	50.18	39.51	40.84	40.64	41.51
4.0	0.07	20.51	20.46	45.03	48.62	38.86	40.07	39.95	40.12
5.0	0.07	20.51	20.47	44.28	47.78	38.07	38.87	39.00	38.71
6.0	0.07	20.51	20.47	43.80	47.02	37.43	38.29	38.21	38.07
7.0	0.07	20.51	20.47	43.19	46.05	36.83	37.33	37.45	37.02
8.0	0.07	20.51	20.47	42.62	45.16	36.18	36.50	36.83	36.19
9.0	0.07	20.51	20.47	42.19	44.31	35.61	35.79	36.10	35.41
10.0	0.07	20.52	20.48	41.50	43.40	35.11	35.11	35.40	34.81
11.0	0.07	20.52	20.48	41.08	42.55	34.55	34.47	34.66	34.28
12.0	0.07	20.52	20.48	40.45	41.79	34.01	33.89	34.09	33.67
13.0	0.07	20.52	20.48	39.87	41.29	33.42	33.40	33.51	33.09
14.0	0.07	20.53	20.49	39.49	40.66	32.95	32.81	32.94	32.53
15.0	0.07	20.53	20.49	39.01	40.17	32.39	32.36	32.41	32.07
16.0	0.08	20.53	20.49	38.48	39.58	31.94	31.84	31.83	31.51
17.0	0.08	20.53	20.50	37.97	39.13	31.42	31.35	31.31	31.08
18.0	0.08	20.54	20.50	37.47	38.52	30.94	30.84	30.82	30.57
19.0	0.08	20.54	20.50	37.07	38.11	30.51	30.31	30.38	30.09
20.0	0.08	20.54	20.50	36.63	37.62	30.07	29.90	29.91	29.65
21.0	0.08	20.54	20.51	36.18	37.15	29.66	29.46	29.45	29.23
22.0	0.08	20.55	20.51	35.85	36.82	29.29	29.13	29.05	28.88
23.0	0.08	20.55	20.52	35.47	36.32	28.94	28.75	28.65	28.46
24.0	0.09	20.55	20.52	34.97	35.97	28.61	28.43	28.37	28.14
25.0	0.09	20.55	20.52	34.74	35.50	28.31	28.12	27.98	27.80
26.0	0.09	20.56	20.53	34.35	35.07	28.00	27.83	27.70	27.50
27.0	0.09	20.56	20.53	34.11	34.81	27.70	27.57	27.37	27.17
28.0	0.09	20.56	20.53	33.75	34.36	27.44	27.26	27.05	26.88
29.0	0.09	20.56	20.54	33.42	34.07	27.15	27.02	26.80	26.58
30.0	0.09	20.57	20.54	33.09	33.64	26.88	26.72	26.52	26.31



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com





IF/RF MICROWAVE COMPONENTS

REV. X1
 SYDC-ED14256
 9/26/2011
 Page 1 of 1

Bi-Directional Coupler


Typical Performance Curves

SYDC-ED14256



Outline Dimensions

AH1596



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
AH1596	.50 (12.70)	.62 (15.75)	.36 (9.14)	- -	.115 (2.92)	.070 (1.78)	.073 (1.85)	- -	.090 (9.65)	.040 (1.02)	.037 (0.94)	.140 (3.56)	.135 (3.43)

CASE #	P	Q	R	WT, GRAM
AH1596	.010 (0.25)	- -	.135 (3.43)	3.00

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, Base material: Printed wiring laminate.
 2. Termination finish: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
- All models, (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F107

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
32	20	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M130233	NEW RELEASE	05/11/11	AV	YQ

SUGGESTED MOUNTING CONFIGURATION FOR
AH1596 CASE STYLE, "08DC03" PIN CODE



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	AV	04/27/11
	CHECKED	IL	05/11/11
	APPROVED	YQ	05/11/11



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235


PL, 08DC03, AH1596, TB-608+

Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.	
ASHEETA1.DWG REV:A	DATE:01/12/95


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-339	REV: OR
FILE: 98PL339	SCALE: 5:1	SHEET: 1 OF 1	

Evaluation Board and Circuit

For Pin Connection Refer to
Data Sheet of the DUT



TB-608+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 65° C Case Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215