

# Power Splitter/Combiner

## 2 Way-180°

# SYPJ-ED14532/1

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : TTT166

| ELECTRICAL SPECIFICATIONS 50Ω @ +25°C |              |      |      |            |
|---------------------------------------|--------------|------|------|------------|
| Parameter                             |              | Min. | Typ. | Max. Units |
| Frequency                             |              | 5    |      | 1000 MHz   |
| Isolation                             | 5-50 MHz     |      | 24   | dB         |
|                                       | 50-500 MHz   |      | 21   | dB         |
|                                       | 500-1000 MHz |      | 21   | dB         |
| Insertion Loss Above 3.0 dB           | 5-50 MHz     |      | 1.20 | dB         |
|                                       | 50-500 MHz   |      | 1.30 | dB         |
|                                       | 500-1000 MHz |      | 1.80 | dB         |
| Phase Unbalance                       | 5-50 MHz     |      | 1.0  | deg.       |
|                                       | 50-500 MHz   |      | 7.0  | deg.       |
|                                       | 500-1000 MHz |      | 13.0 | deg.       |
| Amplitude Unbalance                   | 5-1000 MHz   |      | 0.30 | dB         |
| VSWR                                  | SUM Port     |      | 1.60 | (:1)       |
|                                       | OUT Ports    |      | 1.60 | (:1)       |

| MAXIMUM RATINGS       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |

| PIN CONNECTIONS |       |
|-----------------|-------|
| SUM PORT        | 3     |
| PORT 1 (0°)     | 1     |
| PORT 2 (180°)   | 2     |
| GROUND          | 4,5,6 |

### Functional Diagram



# 2 Way-180° Power Splitter/Combiner

SYPJ-ED14532/1

## Typical Performance Data

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      | AMP.<br>UNBAL.<br>(dB) | ISOLATION<br>(dB)<br>1-2 | PHASE<br>UNBAL.<br>(Deg.) | FREQ.<br>(MHz) | VSWR<br>(:1) |      |      |
|----------------|---------------------------------|------|------------------------|--------------------------|---------------------------|----------------|--------------|------|------|
|                | S-1                             | S-2  |                        |                          |                           |                | S            | 1    | 2    |
| 5.0            | 4.29                            | 4.07 | 0.22                   | 27.41                    | 179.94                    | 5.0            | 1.14         | 1.47 | 1.42 |
| 10.0           | 4.21                            | 3.99 | 0.22                   | 25.36                    | 179.88                    | 10.0           | 1.08         | 1.40 | 1.35 |
| 20.0           | 4.19                            | 3.98 | 0.22                   | 24.61                    | 179.74                    | 20.0           | 1.06         | 1.37 | 1.32 |
| 30.0           | 4.20                            | 3.98 | 0.22                   | 24.43                    | 179.61                    | 30.0           | 1.06         | 1.36 | 1.31 |
| 40.0           | 4.20                            | 3.98 | 0.22                   | 24.38                    | 179.47                    | 40.0           | 1.06         | 1.36 | 1.31 |
| 50.0           | 4.20                            | 3.98 | 0.22                   | 24.35                    | 179.35                    | 50.0           | 1.06         | 1.36 | 1.31 |
| 60.0           | 4.20                            | 3.98 | 0.22                   | 24.31                    | 179.22                    | 60.0           | 1.07         | 1.35 | 1.31 |
| 70.0           | 4.21                            | 3.99 | 0.22                   | 24.28                    | 179.11                    | 70.0           | 1.07         | 1.35 | 1.30 |
| 80.0           | 4.21                            | 3.99 | 0.22                   | 24.26                    | 178.99                    | 80.0           | 1.08         | 1.35 | 1.30 |
| 90.0           | 4.22                            | 3.99 | 0.22                   | 24.24                    | 178.87                    | 90.0           | 1.08         | 1.35 | 1.30 |
| 100.0          | 4.22                            | 4.00 | 0.22                   | 24.20                    | 178.75                    | 100.0          | 1.09         | 1.35 | 1.30 |
| 150.0          | 4.23                            | 4.01 | 0.22                   | 23.90                    | 178.16                    | 150.0          | 1.11         | 1.36 | 1.29 |
| 200.0          | 4.25                            | 4.02 | 0.22                   | 23.59                    | 177.63                    | 200.0          | 1.14         | 1.38 | 1.29 |
| 250.0          | 4.26                            | 4.04 | 0.21                   | 23.26                    | 177.10                    | 250.0          | 1.17         | 1.39 | 1.28 |
| 300.0          | 4.26                            | 4.06 | 0.20                   | 22.85                    | 176.59                    | 300.0          | 1.20         | 1.42 | 1.28 |
| 350.0          | 4.27                            | 4.08 | 0.19                   | 22.51                    | 176.10                    | 350.0          | 1.23         | 1.44 | 1.27 |
| 400.0          | 4.28                            | 4.11 | 0.17                   | 22.18                    | 175.62                    | 400.0          | 1.25         | 1.46 | 1.27 |
| 450.0          | 4.29                            | 4.15 | 0.14                   | 21.84                    | 175.17                    | 450.0          | 1.28         | 1.48 | 1.27 |
| 500.0          | 4.30                            | 4.19 | 0.11                   | 21.54                    | 174.71                    | 500.0          | 1.31         | 1.51 | 1.26 |
| 550.0          | 4.31                            | 4.23 | 0.07                   | 21.28                    | 174.32                    | 550.0          | 1.33         | 1.53 | 1.27 |
| 600.0          | 4.31                            | 4.29 | 0.02                   | 21.17                    | 173.78                    | 600.0          | 1.36         | 1.55 | 1.27 |
| 650.0          | 4.32                            | 4.35 | 0.02                   | 21.01                    | 173.28                    | 650.0          | 1.38         | 1.58 | 1.28 |
| 700.0          | 4.34                            | 4.41 | 0.07                   | 20.89                    | 172.76                    | 700.0          | 1.41         | 1.60 | 1.30 |
| 750.0          | 4.36                            | 4.48 | 0.12                   | 20.89                    | 172.22                    | 750.0          | 1.44         | 1.63 | 1.32 |
| 800.0          | 4.38                            | 4.56 | 0.17                   | 20.92                    | 171.64                    | 800.0          | 1.46         | 1.65 | 1.34 |
| 850.0          | 4.41                            | 4.63 | 0.22                   | 21.05                    | 171.03                    | 850.0          | 1.49         | 1.68 | 1.37 |
| 900.0          | 4.45                            | 4.71 | 0.26                   | 21.25                    | 170.34                    | 900.0          | 1.52         | 1.71 | 1.41 |
| 950.0          | 4.50                            | 4.78 | 0.28                   | 21.50                    | 169.65                    | 950.0          | 1.55         | 1.74 | 1.44 |
| 1000.0         | 4.56                            | 4.85 | 0.29                   | 21.87                    | 168.93                    | 1000.0         | 1.58         | 1.77 | 1.48 |
| 1050.0         | 4.64                            | 4.91 | 0.27                   | 22.26                    | 168.22                    | 1050.0         | 1.61         | 1.81 | 1.52 |
| 1100.0         | 4.73                            | 4.95 | 0.23                   | 22.69                    | 167.61                    | 1100.0         | 1.64         | 1.85 | 1.56 |
| 1150.0         | 4.83                            | 4.99 | 0.16                   | 23.14                    | 167.10                    | 1150.0         | 1.68         | 1.90 | 1.60 |
| 1200.0         | 4.96                            | 5.02 | 0.07                   | 23.56                    | 166.77                    | 1200.0         | 1.72         | 1.95 | 1.64 |

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss







P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site SYPJ-ED14532/1  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com) 9/19/2011



IF/RF MICROWAVE COMPONENTS


Page 1 of 1

## Typical Performance Curves




## Outline Dimensions

TTT166  
TTT167



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE # | A             | B              | C             | D              | E              | F              | G               | H              | J              | K              | L              | M              | N               |
|--------|---------------|----------------|---------------|----------------|----------------|----------------|-----------------|----------------|----------------|----------------|----------------|----------------|-----------------|
| TTT166 | .38<br>(9.65) | .50<br>(12.70) | .15<br>(3.81) | .020<br>(0.51) | .075<br>(1.91) | .250<br>(6.35) | .425<br>(10.80) | .187<br>(4.75) | .050<br>(1.27) | .050<br>(1.27) | .070<br>(1.78) | .270<br>(6.86) | .540<br>(13.72) |
| TTT167 |               |                | .23<br>(5.84) |                |                |                |                 |                |                |                |                |                |                 |

| CASE # | P              | Q              | R               | S              | T               | WT. GRAM |
|--------|----------------|----------------|-----------------|----------------|-----------------|----------|
| TTT166 | .060<br>(1.52) | .095<br>(2.41) | .445<br>(11.30) | .208<br>(5.28) | .415<br>(10.54) | .8       |
| TTT167 |                |                |                 |                |                 | .8       |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Note:

- Case material: Plastic.
- Base material: Printed wiring laminate.
- Termination finish:
  - For RoHS Case Styles: 3-5  $\mu$  inch (.08-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate. All models, (+) suffix.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

# Tape & Reel Packaging TR-F12



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |     |
|----------------|-------------------------|-------------------|-------------------------------------|-----|
| 24             | 12                      | 7                 | Small quantity standards (see note) | 10  |
|                |                         |                   |                                     | 20  |
|                |                         |                   |                                     | 50  |
|                |                         |                   |                                     | 100 |
|                |                         |                   |                                     | 200 |
|                |                         | 13                | Standard                            | 500 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers** NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION                 | DATE     | DR  | AUTH |
|-----|---------|-----------------------------|----------|-----|------|
| A   | M86762  | ADDED CONNECTIONS "lp & lq" | 05/23/03 | MMG | WL   |
| B   | M94598  | ADDED CONNECTION "hk"       | 10/08/04 | MMG | HY   |
| C   | M102713 | UPDATED NOTES & DESCRIPTION | 01/14/06 | GF  | IL   |
| D   | M132989 | UPDATED NOTE 2              | 08/24/11 | GF  | DJ   |


**SUGGESTED MOUNTING CONFIGURATION FOR  
TTT166/167 CASE STYLE, "hk"/"lp"/"lq"  
"x"/"ck"/"ec" PIN CONNECTIONS**

**NOTE:**

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030"  $\pm$  .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. THE USE OF SOLDER MASK OVER THE GROUND AREA UNDER THE UNIT AS SHOWN IS RECOMMENDED TO PREVENT POTENTIAL SHORTING. IF USER CHOOSES TO EXPOSE METAL UNDER THE ENTIRE UNIT GROUND PAD FOR IMPROVED GROUNDING, IT IS RECOMMENDED A SOLDER MASK DAM BE APPLIED AROUND EACH GROUND PAD TO ENSURE FILLET AND CONNECTION AT GROUND PADS.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER), SEE NOTE 2.



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

DRAWN

GF

03/18/03

CHECKED

IL

04/15/03

APPROVED

DJ

04/15/03



**Mini-Circuits®**

13 Neptune Avenue  
Brooklyn NY 11235

PL, hk/lp/lq/x/ck/ec, TTT166/167,  
SYM/HJK/SYAS/SYPD, TB-12

SIZE  
A

CODE IDENT  
15542

DRAWING NO:  
98-PL-079

REV:  
D

FILE: 98PL079

SCALE: 5:1

SHEET: 1 OF 1



Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

# Evaluation Board and Circuit

For Pin Connections Refer to Data Sheet of the DUT



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |