

Power Splitter/Combiner

SYPQ-ED13926/1

2 Way-90°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : AH1415

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C

Parameter		Min.	Typ.	Max.	Units
Frequency		120		180	MHz
Isolation	120-180 MHz		22		dB
Insertion Loss Average of Coupled Outputs above 3.0 dB	120-180 MHz		0.20		dB
Phase Unbalance	120-180 MHz		0.35		deg.
Amplitude Unbalance	120-180 MHz		0.20		dB
VSWR	SUM Port		1.14		(:1)
	OUT Ports		1.16		(:1)


MAXIMUM RATINGS

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS

SUM PORT	1
PORT 1 (0°)	5
PORT 2 (90°)	8
GROUND	2,3,6,7
50 OHM TERM EXTERNAL	4

electrical schematic



2 Way-90° Power Splitter/Combiner

SYPQ-ED13926/1

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
60.0	1.42	6.08	4.67	29.37	89.41	60.0	1.09	1.09	1.07
70.0	1.75	5.26	3.51	29.25	89.46	70.0	1.09	1.09	1.08
80.0	2.07	4.62	2.56	29.24	89.50	80.0	1.09	1.10	1.08
90.0	2.37	4.14	1.77	29.33	89.56	90.0	1.10	1.10	1.08
100.0	2.65	3.78	1.13	29.37	89.61	100.0	1.10	1.10	1.09
110.0	2.88	3.50	0.62	29.23	89.67	110.0	1.10	1.11	1.09
115.0	2.99	3.39	0.40	29.03	89.71	115.0	1.10	1.11	1.10
120.0	3.08	3.30	0.22	28.76	89.75	120.0	1.10	1.11	1.10
125.0	3.17	3.23	0.06	28.39	89.80	125.0	1.11	1.12	1.11
130.0	3.24	3.17	0.07	27.91	89.86	130.0	1.11	1.12	1.11
132.0	3.26	3.15	0.12	27.69	89.88	132.0	1.11	1.12	1.11
134.0	3.28	3.13	0.16	27.47	89.91	134.0	1.11	1.13	1.12
136.0	3.30	3.11	0.19	27.19	89.94	136.0	1.12	1.13	1.12
138.0	3.32	3.10	0.22	26.95	89.97	138.0	1.12	1.13	1.12
140.0	3.34	3.09	0.25	26.67	90.00	140.0	1.12	1.13	1.13
142.0	3.35	3.08	0.27	26.38	90.03	142.0	1.12	1.14	1.13
144.0	3.37	3.07	0.29	26.05	90.07	144.0	1.12	1.14	1.13
146.0	3.38	3.07	0.31	25.76	90.10	146.0	1.13	1.14	1.14
148.0	3.38	3.07	0.32	25.44	90.15	148.0	1.13	1.15	1.14
150.0	3.39	3.07	0.32	25.10	90.19	150.0	1.13	1.15	1.15
152.0	3.39	3.08	0.32	24.76	90.24	152.0	1.14	1.15	1.15
154.0	3.40	3.08	0.31	24.43	90.29	154.0	1.14	1.16	1.16
156.0	3.40	3.09	0.30	24.07	90.35	156.0	1.14	1.16	1.16
158.0	3.39	3.11	0.29	23.70	90.41	158.0	1.15	1.16	1.17
160.0	3.39	3.12	0.27	23.34	90.47	160.0	1.15	1.17	1.17
162.0	3.38	3.14	0.24	22.98	90.54	162.0	1.16	1.18	1.18
164.0	3.37	3.16	0.21	22.60	90.61	164.0	1.16	1.18	1.19
166.0	3.36	3.19	0.17	22.21	90.70	166.0	1.17	1.19	1.19
168.0	3.34	3.22	0.13	21.82	90.79	168.0	1.17	1.19	1.20
170.0	3.33	3.25	0.08	21.44	90.88	170.0	1.18	1.20	1.21
172.0	3.31	3.29	0.02	21.05	90.99	172.0	1.19	1.21	1.22
175.0	3.27	3.35	0.07	20.45	91.17	175.0	1.20	1.22	1.23
180.0	3.21	3.48	0.27	19.44	91.54	180.0	1.22	1.24	1.26
185.0	3.13	3.64	0.51	18.43	92.01	185.0	1.24	1.27	1.29
190.0	3.04	3.85	0.81	17.38	92.63	190.0	1.27	1.30	1.33
195.0	2.94	4.10	1.16	16.34	93.43	195.0	1.31	1.33	1.38
200.0	2.83	4.41	1.59	15.28	94.49	200.0	1.35	1.38	1.43

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com






IF/RF MICROWAVE COMPONENTS

REV. X2
 SYPQ-ED13926/1
 9/14/2010
 Page 1 of 1

2 Way-90° Power Splitter/Combiner


SYPQ-ED13926/1

Typical Performance Curves



Outline Dimensions

AH1415



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
AH1415	.375 (9.53)	.500 (12.70)	.156 (3.96)	.020 (.51)	.115 (2.92)	.070 (1.78)	.010 (0.25)	.050 (1.27)	.090 (2.29)	.040 (1.02)	.105 (2.67)	.140 (3.56)	.095 (2.41)

CASE #	P	Q	R	WT, GRAM
AH1415	.010 (0.25)	.480 (12.19)	.107 (2.72)	.80

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Nickel Silver alloy.
- Base material: Printed wiring laminate.
- Termination finish: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M88784	NEW RELEASE	10/20/03	GF	HY
A	M93261	PIN 8 WAS PIN 1	07/19/04	MMG	HY
B	M102713	ADDED "...WITH SMOBC"	01/16/06	GF	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR AH202 CASE STYLE, "av" PIN CONNECTION.**



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" $\pm$ 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

GF

09/18/03

TOLERANCES ON:

CHECKED

IL

10/20/03

2 PL DECIMALS $\pm$

APPROVED

HY

10/20/03

3 PL DECIMALS $\pm$.005

ANGLES $\pm$

FRACTIONS $\pm$

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, av, AH202, SYPQ-70, TB-265

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-138

REV:

B

FILE:

98PL138


SCALE:

5:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-265



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215