

Power Splitter/Combiner

SYPS-ED12877/2

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : AH202-2

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1		3000 MHz
Isolation	1 - 10 MHz		21	dB
	10 - 1500 MHz		23	dB
	1500 - 3000 MHz		19	dB
Insertion Loss Above 3.0 dB	1 - 10 MHz		0.90	dB
	10 - 1500 MHz		1.20	dB
	1500 - 3000 MHz		1.80	dB
Phase Unbalance	1 - 10 MHz		0.02	deg.
	10 - 1500 MHz		0.17	deg.
	1500 - 3000 MHz		1.04	deg.
Amplitude Unbalance	1 - 10 MHz		0.01	dB
	10 - 1500 MHz		0.04	dB
	1500 - 3000 MHz		0.09	dB
VSWR	SUM Port		1.60	(:1)
	OUT Ports		1.65	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Functional Diagram



2 Way-0° Power Splitter/Combiner

SYPS-ED12877/2

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1.0	6.33	6.32	0.01	19.55	0.01	1.0	5.93	4.83	4.84
2.0	4.19	4.18	0.01	18.82	0.01	2.0	2.63	2.65	2.65
3.0	3.69	3.68	0.01	19.22	0.00	3.0	1.87	2.04	2.04
4.0	3.58	3.57	0.01	20.00	0.02	4.0	1.57	1.78	1.78
5.0	3.58	3.58	0.01	20.80	0.02	5.0	1.42	1.66	1.66
6.0	3.60	3.60	0.01	21.46	0.01	6.0	1.34	1.58	1.58
7.0	3.62	3.62	0.01	22.00	0.01	7.0	1.29	1.53	1.53
8.0	3.64	3.63	0.00	22.39	0.02	8.0	1.25	1.50	1.50
9.0	3.64	3.64	0.01	22.66	0.01	9.0	1.23	1.48	1.48
10.0	3.65	3.64	0.01	22.84	0.02	10.0	1.21	1.46	1.46
20.0	3.60	3.60	0.00	22.73	0.00	20.0	1.13	1.38	1.38
40.0	3.55	3.55	0.00	21.72	0.04	40.0	1.08	1.36	1.36
60.0	3.54	3.53	0.00	21.27	0.05	60.0	1.05	1.35	1.35
80.0	3.53	3.53	0.01	21.05	0.05	80.0	1.04	1.34	1.34
100.0	3.53	3.53	0.00	20.91	0.09	100.0	1.03	1.34	1.34
150.0	3.54	3.53	0.01	20.78	0.09	150.0	1.01	1.33	1.33
200.0	3.54	3.53	0.01	20.70	0.17	200.0	1.01	1.32	1.32
300.0	3.55	3.54	0.00	20.72	0.19	300.0	1.03	1.31	1.31
350.0	3.56	3.56	0.00	20.64	0.25	350.0	1.04	1.30	1.30
400.0	3.56	3.57	0.01	20.75	0.25	400.0	1.05	1.29	1.29
450.0	3.58	3.58	0.00	20.56	0.20	450.0	1.05	1.28	1.28
500.0	3.59	3.61	0.02	20.80	0.33	500.0	1.06	1.28	1.27
550.0	3.61	3.63	0.02	20.60	0.17	550.0	1.07	1.26	1.26
600.0	3.64	3.65	0.01	20.82	0.29	600.0	1.07	1.26	1.25
650.0	3.65	3.69	0.04	20.72	0.26	650.0	1.07	1.25	1.25
700.0	3.68	3.71	0.03	20.84	0.16	700.0	1.08	1.24	1.24
750.0	3.69	3.73	0.04	20.95	0.31	750.0	1.07	1.23	1.22
800.0	3.71	3.79	0.07	20.90	0.17	800.0	1.08	1.21	1.22
900.0	3.72	3.81	0.09	21.06	0.20	900.0	1.07	1.18	1.19
1000.0	3.71	3.80	0.09	21.22	0.14	1000.0	1.05	1.15	1.16
1100.0	3.70	3.81	0.11	21.10	0.08	1100.0	1.03	1.12	1.13
1200.0	3.73	3.85	0.12	20.73	0.04	1200.0	1.04	1.08	1.09
1300.0	3.82	3.93	0.12	20.30	0.06	1300.0	1.08	1.05	1.06
1400.0	3.94	4.04	0.11	19.72	0.21	1400.0	1.13	1.04	1.05
1500.0	4.01	4.12	0.11	19.26	0.46	1500.0	1.19	1.07	1.07
1600.0	4.03	4.14	0.11	18.97	0.56	1600.0	1.25	1.11	1.12
1700.0	4.02	4.13	0.10	18.65	0.75	1700.0	1.33	1.16	1.17
1800.0	4.04	4.13	0.09	18.29	0.89	1800.0	1.41	1.21	1.22
1900.0	4.18	4.26	0.07	18.05	1.05	1900.0	1.49	1.26	1.27
2000.0	4.50	4.56	0.06	18.21	1.23	2000.0	1.55	1.31	1.31
2100.0	4.95	4.98	0.03	18.35	1.32	2100.0	1.60	1.34	1.34
2200.0	5.36	5.36	0.00	18.39	1.46	2200.0	1.63	1.36	1.36
2300.0	5.60	5.58	0.02	18.48	1.59	2300.0	1.65	1.37	1.37
2400.0	5.60	5.55	0.05	18.73	1.62	2400.0	1.67	1.38	1.37
2500.0	5.35	5.28	0.07	18.85	1.66	2500.0	1.68	1.40	1.38
2600.0	4.94	4.88	0.06	18.61	1.52	2600.0	1.69	1.42	1.38
2700.0	4.63	4.57	0.05	18.67	1.06	2700.0	1.72	1.44	1.38
2800.0	4.66	4.56	0.10	19.26	0.26	2800.0	1.73	1.45	1.37
2900.0	5.07	4.89	0.18	19.64	0.56	2900.0	1.74	1.46	1.35
3000.0	5.74	5.43	0.32	19.78	1.28	3000.0	1.73	1.46	1.32
3100.0	6.42	5.91	0.51	19.81	1.56	3100.0	1.76	1.46	1.29
3200.0	6.88	6.24	0.64	19.66	1.55	3200.0	1.88	1.46	1.26
3300.0	7.32	6.61	0.70	18.78	1.54	3300.0	2.05	1.46	1.24

¹Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2

SYPS-ED12877/2

100714

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner

SYPS-ED12877/2

Typical Performance Curves



REV. X2
SYPS-ED12877/2
100714
Page 1 of 1




Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions

AH202-2



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P
AH202-2	.38 (9.65)	.50 (12.70)	.25 (6.35)	.020 (0.51)	.115 (2.92)	.070 (1.78)	.035 (0.89)	.050 (1.27)	.090 (2.29)	.040 (1.02)	.105 (2.67)	.140 (3.56)	.095 (2.41)	.010 (0.25)
CASE#	Q	R	WT, GRAM											
AH202-2	.055 (1.40)	.185 (4.70)	.52											

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm.01$; 3 Pl. $\pm.005$

Notes:

- Case material: Plastic.
- Base material: Printed wiring laminate.
- Termination finish:
 - For RoHS 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F61



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	12	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M109780	NEW RELEASE	04/17/07	PW	HY


SUGGESTED MOUNTING CONFIGURATION FOR AH202-2 CASE STYLE, "sb" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .060" $\pm$.004"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

PW

02/09/07

CHECKED

IL

02/16/07

APPROVED

HY

04/17/07



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, sb, 75, AH202-2, SYPS-2, TB-426+

SIZE
A

CODE IDENT
15542


DRAWING NO:
98-PL-268

REV:
OR

FILE: 98PL268

SCALE: 6:1



SHEET: 1 OF 1



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 75 Ohm N-type Female connectors.
2. PCB Material: Rogers R04350 or its equivalent, Dielectric Constant=3.5, Thickness=.060"

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215