

Surface Mount RF Transformer

50Ω 30 to 1000 MHz 10 Watt

SYTX4-13HP+



Generic photo used for illustration purposes only

CASE STYLE: AH1647

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
13"	200

Maximum Ratings

Operating Temperature	-40°C to 65°C
Storage Temperature	-55°C to 100°C
RF Power	10W
DC Current	30mA

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

PRIMARY DOT	1
PRIMARY	4
SECONDARY DOT	8
SECONDARY	5
SECONDARY CT (GND)	6,7
GROUND	2,3

Features

- high power input, 10 Watt max.
- wide bandwidth, 30 to 1000 MHz
- good amplitude unbalance, 0.5 dB typ. at 1 dB bandwidth
- excellent phase unbalance 3 deg. typ. at 1 dB bandwidth
- balanced transmission line with secondary center tap

Applications

- PCS
- cellular


Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Impedance Ratio (secondary/primary)			4		Ohm
Frequency Range		30	—	1000	MHz
Insertion Loss*	100-500	—	0.3	1.0	dB
	50-700	—	0.7	1.5	
	30-1000	—	1.0	2.5	
Amplitude Unbalance	100-500	—	0.5	1.5	dB
	50-700	—	0.9	2.5	
Phase Unbalance	100-500	—	3	9	Degree
	50-700	—	5	12	

* Insertion Loss is referenced to mid-band loss 0.6 dB typ.

1. The user must provide adequate means of heat removal to limit the temperature of ground connections under the PCB to 65°C, in order to ensure proper performance. At 25°C ambient temperature this requires thermal resistance of the user's PC board heat sink to be 10°C/W.

Outline Drawing



Typical Performance Data


FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (Deg.)
30.00	0.89	19.69	0.64	0.51
50.00	0.94	22.20	0.61	0.92
100.00	0.83	27.30	0.58	1.65
200.00	0.71	30.65	0.49	2.78
500.00	0.73	21.68	0.10	2.93
600.00	0.81	21.24	0.01	0.65
700.00	0.90	20.68	0.03	2.25
800.00	1.05	18.61	0.28	6.29
900.00	1.26	15.64	0.78	10.33
1000.00	1.59	12.63	1.48	13.63

Refer to Application Note: [AN-00-017](#)

Outline Dimensions (inch/mm)





A	B	C	E	F	G	H	J	K
.433	.690	.415	.100	.476	.394	.045	.060	.276
11.00	17.53	10.54	2.54	12.09	10.01	1.14	1.52	7.01
L	M	N	P	Q	R	S	T	wt
.194	.257	.560	.475	.561	.258	.069	.061	grams
4.93	6.53	14.22	12.07	14.25	6.55	1.75	1.55	2.80

Config. H



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



RF Transformer


SYTX4-13HP+

Typical Performance Data


FREQUENCY (MHz)	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
5	2.78	3.83	0.60	0.11
6	2.15	4.85	0.60	0.10
8	1.43	6.78	0.61	0.04
10	1.06	8.59	0.62	0.01
30	0.89	19.69	0.64	0.51
50	0.94	22.20	0.61	0.92
60	0.92	23.24	0.60	1.08
80	0.87	25.34	0.59	1.36
100	0.83	27.30	0.58	1.65
125	0.78	29.94	0.55	1.94
150	0.75	31.47	0.53	2.32
175	0.73	31.99	0.51	2.54
200	0.71	30.65	0.49	2.78
250	0.69	27.85	0.44	3.25
300	0.68	25.59	0.38	3.55
350	0.68	23.92	0.32	3.74
400	0.69	22.75	0.24	3.64
450	0.70	22.04	0.17	3.37
500	0.73	21.68	0.10	2.93
550	0.76	21.44	0.03	2.15
600	0.81	21.24	0.01	0.65
650	0.84	21.01	0.01	0.53
700	0.90	20.68	0.03	2.25
750	0.97	19.79	0.13	4.16
800	1.05	18.61	0.28	6.29
850	1.14	17.20	0.51	8.39
900	1.26	15.64	0.78	10.33
950	1.41	14.11	1.11	12.13
1000	1.59	12.63	1.48	13.63
1050	1.82	11.22	1.87	14.89
1100	2.11	9.86	2.28	15.86

Typical Performance Data


Average Insertion Loss




Input Return Loss



Amplitude Unbalance




Phase Unbalance



Outline Dimensions

AH1647



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
AH1647	.433 (11.00)	.690 (17.53)	.415 (10.54)	- -	.100 (2.54)	.476 (12.09)	.394 (10.01)	.045 (1.14)	.060 (1.52)	.276 (7.01)	.194 (4.93)	.257 (6.53)	.560 (14.22)
CASE #	P	Q	R	S	T	WT, GRAM							
AH1647	.475 (12.07)	.561 (14.25)	.258 (6.55)	.069 (1.75)	.061 (1.55)	2.80							

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm.01$; 3 Pl. $\pm.005$

Notes:

- Case material: Nickel Silver alloy.
- Base material: Printed wiring laminate.
- Termination finish: Tin copper solder alloy up to 0.07% Nickel. All models, (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F109



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M133287	NEW RELEASE	08/26/11	GF	WP

SUGGESTED MOUNTING CONFIGURATION FOR
AH1647 CASE STYLE, "08DC05" PIN CODE



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. SUGGEST TO PROVIDE BRASS COIN FOR BETTER HEAT TRANSFER FROM THE UNIT. OTHERWISE PROVIDE ARRAY OF THERMAL VIAS ADEQUATE TO LIMIT TEMPERATURE OF GROUND CONNECTIONS UNDER THE UNIT TO 65°C.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK
- DENOTES BRASS COIN.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	GF	08/22/11
	CHECKED	IL	08/25/11
	APPROVED	WP	08/26/11



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 08DC05, AH1647, TB-630+

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-351	OR
FILE:	98PL351	SCALE:	SHEET:
		4:1	1 OF 1


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 65° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C