


## RF Transformer

50Ω

10 to 350 MHz

T4-1H+  
T4-1H

CASE STYLE: W38

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Maximum Ratings


|                       |                |
|-----------------------|----------------|
| Operating Temperature | -20°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Power              | 0.25W          |
| DC Current            | 30mA           |

Permanent damage may occur if any of these limits are exceeded.

## Pin Connections

|               |   |
|---------------|---|
| PRIMARY DOT   | 4 |
| PRIMARY       | 6 |
| SECONDARY DOT | 3 |
| SECONDARY     | 1 |
| SECONDARY CT  | 2 |
| NOT USED      | 5 |

## Outline Drawing




## Outline Dimensions (inch)

| A    | B    | C    | D    | E    | F    |
|------|------|------|------|------|------|
| .30  | .27  | .23  | .010 | .042 | .020 |
| 7.62 | 6.86 | 5.84 | 0.25 | 1.07 | 0.51 |

| G    | H    | J    | K    | L    | wt    |
|------|------|------|------|------|-------|
| .100 | .05  | .09  | .31  | .036 | grams |
| 2.54 | 1.27 | 2.29 | 7.87 | 0.91 | 0.50  |

## Config. A



## Features

- wideband, 10 to 350 MHz
- good return loss
- also available with surface mount gull wing (KK81) plug-in (X65) leads

## Applications

- VHF/UHF receivers
- impedance matching



## Transformer Electrical Specifications

| Ω<br>RATIO<br>(Secondary/Primary) | FREQUENCY<br>(MHz) | INSERTION LOSS* |             |             |
|-----------------------------------|--------------------|-----------------|-------------|-------------|
|                                   |                    | 3 dB<br>MHz     | 2 dB<br>MHz | 1 dB<br>MHz |
| 4                                 | 10-350             | 10-350          | 15-300      | 25-200      |

\*Insertion Loss is referenced to mid-band loss, 1 dB typ.

## Typical Performance Data

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | INPUT<br>R. LOSS<br>(dB) |
|--------------------|---------------------------|--------------------------|
| 10.00              | 3.33                      | 4.05                     |
| 10.31              | 1.22                      | 16.05                    |
| 20.00              | 1.85                      | 8.95                     |
| 54.15              | 1.10                      | 18.56                    |
| 90.76              | 1.09                      | 15.02                    |
| 99.52              | 1.13                      | 13.84                    |
| 138.71             | 1.26                      | 9.87                     |
| 200.59             | 1.34                      | 6.03                     |
| 250.29             | 1.44                      | 4.15                     |
| 350.00             | 1.68                      | 2.29                     |

T4-1H  
INSERTION LOSST4-1H  
INPUT RETURN LOSS

## Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





---

*Typical Performance Data*

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | RETURN<br>LOSS<br>(dB) |
|--------------------|---------------------------|------------------------|
| 10.00              | 3.33                      | 4.05                   |
| 10.31              | 1.22                      | 16.05                  |
| 20.00              | 1.85                      | 8.95                   |
| 54.15              | 1.10                      | 18.56                  |
| 90.76              | 1.09                      | 15.02                  |
| 99.52              | 1.13                      | 13.84                  |
| 138.71             | 1.26                      | 9.87                   |
| 200.59             | 1.34                      | 6.03                   |
| 250.29             | 1.44                      | 4.15                   |
| 350.00             | 1.68                      | 2.29                   |

## Typical Performance Curves



## Outline Dimensions

W38



| CASE # | A             | B             | C             | D              | E              | F              | G              | H             | J             | K             | L              | WT.<br>GRAM |
|--------|---------------|---------------|---------------|----------------|----------------|----------------|----------------|---------------|---------------|---------------|----------------|-------------|
| W38    | .30<br>(7.62) | .27<br>(6.86) | .23<br>(5.84) | .010<br>(0.25) | .042<br>(1.07) | .020<br>(0.51) | .100<br>(2.54) | .05<br>(1.27) | .09<br>(2.29) | .31<br>(7.87) | .036<br>(0.91) | .50         |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$ .

### Notes:

- Case material: Plastic.  
Termination finish: For RoHS Case Styles: Tin Plate over Nickel Plate.  
For RoHS-5 Case Styles: Tin-Lead Plate.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                        |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| Operating Temperature          | -20° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                           |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                           |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1         |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, Para 4.2.5, Test S, 95% Coverage           |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                  |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                  |
| Lead Integrity                 | 2 Pound Pull, perpendicular to edge of unit                                                                                                                     | MIL-STD-202, Method 211, Condition A                  |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                               |