


# Evaluation Board and Circuit


## TOP VIEW

SEE NOTE 1



TB-715-VCM


## SIDE VIEW



### Notes:

1. Shield is not shown on the top view for clarity.
2. Test cable for "N1" is included in TB-715-VCM.
3. 50 Ohm 2.92 mm End Launch Female connectors.
4. PCB Material: R04350 or equivalent, Dielectric Constant=3.5, Thickness=.0066 inch.

 Mini-Circuits®



Schematic Diagram

COMPONENT	VALUE/ PART NUMBER	SIZE
DUT	AVM-273HP+	-
N1	CONN VERTICAL HEADER 4 POS	-
U1	SEQUENCING & DC CONTROL MODULE	-
C1,C6,C7,C12-C24	.1 uF	.04 X .02
C2-C5,C8-C11	470 pF	.02 X .01
C25	.1 uF	.04 X .02
R1-R4	0 Ohm	.08 X .05
TEST CABLE	B66-225+M	-