

## Engineering Development Model

# RF Transformer


# TC1-ED8604B/1

Impedance Ratio : 1

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : DB714


| ELECTRICAL SPECIFICATIONS 50Ω @ +25°C |                |      |         |            |
|---------------------------------------|----------------|------|---------|------------|
| Parameter                             |                | Min. | Typ.    | Max. Units |
| Frequency                             |                | 45   |         | 1800 MHz   |
| Insertion Loss *                      | 3 dB Bandwidth |      | 45-1800 | MHz        |
|                                       | 2 dB Bandwidth |      | 70-1600 | MHz        |
|                                       | 1 dB Bandwidth |      | 200-600 | MHz        |

**Note:** \* Insertion Loss is referenced to mid-band loss, .37 dB typ., and measured with input at primary dot, output at secondary while secondary dot and primary are grounded.

| MAXIMUM RATINGS       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |

| PIN CONNECTIONS |     |
|-----------------|-----|
| PRIMARY DOT     | 6   |
| PRIMARY         | 4   |
| SECONDARY DOT   | 1   |
| SECONDARY       | 3   |
| NOT USED        | 2,5 |



### Configuration : C



*Typical Performance Data*


| FREQUENCY | INSERTION<br>LOSS | RETURN<br>LOSS |
|-----------|-------------------|----------------|
| (MHz)     | (dB)              | (dB)           |
| 45.00     | 1.88              | 4.94           |
| 50.00     | 1.61              | 5.56           |
| 60.00     | 1.23              | 6.70           |
| 70.00     | 0.98              | 7.71           |
| 80.00     | 0.82              | 8.62           |
| 90.00     | 0.71              | 9.43           |
| 100.00    | 0.63              | 10.15          |
| 200.00    | 0.38              | 14.41          |
| 300.00    | 0.37              | 15.78          |
| 400.00    | 0.41              | 15.87          |
| 500.00    | 0.45              | 15.29          |
| 600.00    | 0.50              | 14.57          |
| 700.00    | 0.56              | 13.75          |
| 800.00    | 0.61              | 13.10          |
| 850.00    | 0.65              | 12.84          |
| 900.00    | 0.67              | 12.69          |
| 950.00    | 0.68              | 12.58          |
| 1000.00   | 0.69              | 12.58          |
| 1050.00   | 0.70              | 12.74          |
| 1100.00   | 0.70              | 13.02          |
| 1108.00   | 0.70              | 13.08          |
| 1138.00   | 0.70              | 13.35          |
| 1150.00   | 0.70              | 13.45          |
| 1200.00   | 0.68              | 14.09          |
| 1250.00   | 0.68              | 15.03          |
| 1300.00   | 0.66              | 16.45          |
| 1400.00   | 0.66              | 21.75          |
| 1500.00   | 0.71              | 31.70          |
| 1600.00   | 0.91              | 17.08          |
| 1650.00   | 1.08              | 13.61          |
| 1700.00   | 1.32              | 11.16          |
| 1750.00   | 1.64              | 9.13           |
| 1800.00   | 2.02              | 7.59           |

## Typical Performance Data




## Outline Dimensions

DB714



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE # | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| DB714  | .160<br>(4.06) | .150<br>(3.81) | .160<br>(4.06) | .050<br>(1.27) | .040<br>(1.02) | .025<br>(0.64) | .028<br>(0.71) | .065<br>(1.65) | .190<br>(4.83) | .030<br>(0.76) | .15      |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Lead #1 identifier shall be located in the cross-hatched area shown.  
Identifier may be either a molded or marked feature.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F47

## DEVICE ORIENTATION IN T&R



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel<br>see note |
|-------------------|----------------------------|----------------------|------------------------------|
| 12                | 8                          | 13                   | 1000, 2000                   |
|                   |                            | 7                    | 20, 50, 100, 200, 500        |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

# Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



TB-145



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350B or its equivalent, Dielectric Constant=3.5, Thickness=.020"

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |