

TC4-14X+

50Ω

200 to 1400 MHz

FEATURES

- · Good return loss
- · Wideband, 200 to 1400 MHz
- · Plastic base with leads
- · Aqueous washable



Generic photo used for illustration purposes only

CASE STYLE: AT1521

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- · Impedance matching
- · Push-pull amplifiers

ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit
Impedance Ratio (secondary/primary)			4		
Frequency Range		200	_	1400	MHz
	200-1400		3		
Insertion Loss*	300-1300		2		dB
	800-1100		1		


 $^{^{\}star}$ Insertion Loss is referenced to mid-band loss, 0.6 dB typ.

MAXIMUM RATINGS

Parameter	Ratings		
Operating Temperature	-20°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power	0.25W		
DC Current	30mA		


Permanent damage may occur if any of these limits are exceeded.

CONFIG. A



REV. B ECO-014884 TC4-14X+ IG/TD/CP/AM 230808





TC4-14X+

50Ω


200 to 1400 MHz

PIN CONNECTIONS

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	2


PRODUCT MARKING: CV

OUTLINE DRAWING



Top-hat total thickness: .013 inches MAX.

PCB Land Pattern




Suggested Layout, Tolerance to be within ±.002

OUTLINE DIMENSIONS (Inch)

F В С D Ε G Κ .150 .150 .160 .050 .040 .025 .028 .065 .190 .030 3.81 3.81 4.06 1.27 1.02 0.64 0.71 1.65 4.83 0.76

Weight: 0.15 grams

TAPE & REEL INFORMATION: F17




TC4-14X+


50Ω

200 to 1400 MHz

TYPICAL PERFORMANCE DATA

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)
200.00	1.33	6.74
210.00	1.26	6.88
300.00	1.22	8.07
550.00	0.92	9.54
800.00	0.88	10.68
950.00	0.82	13.05
1100.00	0.70	21.93
1300.00	1.53	10.04
1350.00	1.77	7.15
1400.00	2.77	5.05





NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html


Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
200.0	1.33	6.74
210.0	1.26	6.88
300.0	1.22	8.07
550.0	0.92	9.54
800.0	0.88	10.68
950.0	0.82	13.05
1100.0	0.70	21.93
1300.0	1.53	10.04
1350.0	1.77	7.15
1400.0	2.77	5.05



Typical Performance Data






Outline Dimensions

AT1521

PCB Land Pattern



Suggested Layout, Tolerance to be within ±.002

CASE #	A	В	С	D	Е	F	G	Н	J	K	WT. GRAMS
AT1521	.150 (3.81)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (.64)	.028 (.71)	.065 (1.65)	.190 (4.83)	.030 (.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. \pm .01; 3 Pl. \pm .005

Notes:

- Case material: Plastic.
- Termination finish:

For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

- Orientation Dot on Top Hat & Marking on the Substrate both refers to Pin #1 of the Unit.
- 4. Top-Hat total thickness: .013 inches MAX.






P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

Tape & Reel Packaging TR-F17

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices	per Reel
12	8	7	Small quantity standards (see note)	20 50 100 200 500
		13	Standard	1000 2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf






P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

THIRD ANG	LE PROJECTION
(

		REVISIONS			
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M106563	NEW RELEASE	08/23/06	AV	IG

SUGGESTED MOUNTING CONFIGURATION FOR AT224/DB714 CASE STYLE, "gs/ha/hd" PIN CONNECTIONS (FOR SINGLE ENDED TO BALANCED APPLICATION)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - 3. THIS PAD IS NOT REQUIRED FOR AT224 CASE STYLE.


DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


UNLESS OTHERWISE SPECIFIED)	INITIALS	DATE				•	• 4 ®		
DIMENSIONS ARE IN INCHES	DRAWN	AV	07/28/06		-1 Mini	ı — C	ircu	1ts :	Neptu	ne Avenue NY 11235
TOLERANCES ON:	CHECKED	IL	08/23/06					DI	OOKIYII	N1 11235
3 PL DECIMALS ± .005	APPROVED	IG	08/23/06							
FRACTIONS ±				PL.	gs/ha/hd	. AT2	24/DB71	4. TC/T	CM.	TB-145
],	6-77	,	,	-,, -	,			
THIS DOCUMENT AND ITS CONTENTS EXCEPT FOR USE EXPRESSLY GRANTE				SIZE	CODE IDENT	DRAWING	NO.			REV:
AND THE UNITED STATES GOVERNMEN DESIGN, USE , MANUFACTURING AND THESE CONTENTS SHALL NOT BE USI	IT, MINI—CIRCUITS REPRODUCTION I D, DUPLICATED	RESERVES ALL RIGHTS THERETO. OR DISCLOSED TO	PROPRIETARY ANY OUTSIDE	A	15542	DRAWING	98-PL	-244		OR
PARTY, IN WHOLE OR IN PART, WITH				FILE:	98PL244	SCALE:	8:1	SHEET:	1	OF 1
	ASHEETA1.	WG REV:A	DATE:01/12/95		COLLAIT		U.1			V1 1

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



TB-145



Schematic Diagram

Notes:

- 1. 50 Ohm SMA Female connectors.
- 2. PCB Material: Rogers RO4350B or its equivalent, III Mini-Circuits® Dielectric Constant=3.5, Thickness=.020"



Environmental Specifications

ENV02

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

ENV02 Rev: A

02/25/11

M130240 File: ENV02.pdf

This document and its contents are the property of Mini-Circuits.