




## FEATURES

- Wideband, 10-1900 MHz
- Balanced transmission line with secondary center tap
- Plastic base with leads
- Aqueous washable



Generic photo used for illustration purposes only

CASE STYLE: AT224-1A

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## APPLICATIONS

- PCS
- Cellular

## ELECTRICAL SPECIFICATIONS AT +25°C

| Parameter                           | Frequency (MHz) | Min. | Typ. | Max. | Unit |
|-------------------------------------|-----------------|------|------|------|------|
| Impedance Ratio (Secondary/Primary) |                 |      | 4    |      | Ohm  |
| Frequency Range                     |                 | 10   |      | 1900 | MHz  |
| Insertion Loss*                     | 10-1900         |      | 3    |      | Deg. |
|                                     | 20-1000         |      | 2    |      |      |
|                                     | 30-700          |      | 1    |      |      |
| Phase Unbalance                     | 30-700          |      | 4    |      | dB   |
|                                     | 20-1000         |      | 6    |      |      |
| Amplitude Unbalance                 | 30-700          |      | 0.3  |      | dB   |
|                                     | 20-1000         |      | 0.5  |      |      |

\* Insertion Loss is referenced to mid-band loss, 1.0 dB typ


## MAXIMUM RATINGS

| Parameter             | Ratings        |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Power              | 0.25W          |
| DC Current            | 150** mA       |

Permanent damage may occur if any of these limits are exceeded.

\*\* Equal current applied through center tap to secondary dot &amp; secondary, need DC blocking capacitors on primary dot &amp; primary.

## CONFIG. H





SURFACE MOUNT

# RF Transformer

**TC4-19LN+**

Mini-Circuits


50Ω 10 to 1900 MHz

## PIN CONNECTIONS


| Function      | Pin Number |
|---------------|------------|
| PRIMARY DOT   | 6          |
| PRIMARY       | 4          |
| SECONDARY DOT | 3          |
| SECONDARY     | 1          |
| SECONDARY CT  | 2          |

PRODUCT MARKING: N/A

## OUTLINE DRAWING



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

## OUTLINE DIMENSIONS (Inch mm)

| A    | B    | C    | D    | E     | F    |
|------|------|------|------|-------|------|
| .150 | .150 | .160 | .050 | .040  | .025 |
| 3.81 | 3.81 | 4.06 | 1.27 | 1.02  | 0.64 |
| G    | H    | J    | K    | wt    |      |
| .028 | .065 | .190 | .030 | grams |      |
| 0.71 | 1.65 | 4.83 | 0.76 | grams | 0.15 |

## TAPE & REEL INFORMATION: F17



SURFACE MOUNT

# RF Transformer


TC4-19LN+

Mini-Circuits

50Ω 10 to 1900 MHz

## TYPICAL PERFORMANCE DATA

| FREQUENCY (MHz) | INSERTION LOSS (dB) | INPUT R. LOSS (dB) | AMPLITUDE UNBALANCE (dB) | PHASE UNBALANCE (deg.) |
|-----------------|---------------------|--------------------|--------------------------|------------------------|
| 10.00           | 1.24                | 16.03              | 0.06                     | 0.03                   |
| 50.00           | 1.04                | 19.54              | 0.04                     | 0.39                   |
| 100.00          | 0.99                | 19.98              | 0.01                     | 0.83                   |
| 500.00          | 1.13                | 14.68              | 0.02                     | 3.20                   |
| 700.00          | 1.24                | 12.43              | 0.17                     | 3.49                   |
| 1000.00         | 1.55                | 9.92               | 0.49                     | 3.74                   |
| 1200.00         | 1.80                | 8.83               | 0.85                     | 3.53                   |
| 1500.00         | 2.34                | 7.69               | 1.47                     | 3.59                   |
| 1700.00         | 2.64                | 7.26               | 1.74                     | 4.43                   |
| 1900.00         | 2.99                | 7.01               | 1.95                     | 4.99                   |



### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)




## Typical Performance Data


| FREQUENCY<br>(MHz) | AVERAGE<br>INSERTION<br>LOSS<br>(dB) | INPUT<br>RETURN<br>LOSS<br>(dB) | AMPLITUDE<br>UNBALANCE<br>(dB) | PHASE<br>UNBALANCE<br>(deg.) |
|--------------------|--------------------------------------|---------------------------------|--------------------------------|------------------------------|
| 10.0               | 1.24                                 | 16.03                           | 0.06                           | 0.03                         |
| 50.0               | 1.04                                 | 19.54                           | 0.04                           | 0.39                         |
| 100.0              | 0.99                                 | 19.98                           | 0.01                           | 0.83                         |
| 500.0              | 1.13                                 | 14.68                           | 0.02                           | 3.20                         |
| 700.0              | 1.24                                 | 12.43                           | 0.17                           | 3.49                         |
| 1000.0             | 1.55                                 | 9.92                            | 0.49                           | 3.74                         |
| 1200.0             | 1.80                                 | 8.83                            | 0.85                           | 3.53                         |
| 1500.0             | 2.34                                 | 7.69                            | 1.47                           | 3.59                         |
| 1700.0             | 2.64                                 | 7.26                            | 1.74                           | 4.43                         |
| 1900.0             | 2.99                                 | 7.01                            | 1.95                           | 4.99                         |

## Typical Performance Data


Average Insertion Loss




Input Return Loss



Amplitude Unbalance




Phase Unbalance




## Outline Dimensions

AT224-1A



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm.002$

| CASE #   | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | WT. GRAMS |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------|
| AT224-1A | .150<br>(3.81) | .150<br>(3.81) | .160<br>(4.06) | .050<br>(1.27) | .040<br>(1.02) | .025<br>(0.64) | .028<br>(0.71) | .065<br>(1.65) | .190<br>(4.83) | .030<br>(0.76) | .15       |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
- Lead #1 identifier shall be located in the cross-hatched area shown.  
Identifier may be either a molded or marked feature.



P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F17

## DEVICE ORIENTATION IN T&R



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 12             | 8                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         | 13                | Standard                            | 1000 |
|                |                         |                   |                                     | 2000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition   | Reference/Spec   |
|--------------------------------|---|--|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment   | Individual Model Data Sheet  |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment   | Individual Model Data Sheet  |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles   | MIL-STD-202, Method 107, Condition A-3, except +100°C  |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak  | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1  |
| Solderability                  | 10X Magnification   | J-STD-002, 95% Coverage  |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)   | MIL-STD-202, Method 204, Condition D   |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes   | MIL-STD-202, Method 213, Condition A   |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215  |