

Surface Mount 
Bias-Tee

TCBT-2R5G+


50Ω Wideband 20 to 2500 MHz

Features

- wideband, 20 to 2500 MHz
- low insertion loss, 0.4 dB typ.
- miniature surface mount 0.15"x0.15"
- aqueous washable
- protected by US Patent 7,012,486

Applications

- biasing amplifiers
- biasing of laser diodes
- biasing of active antennas



Generic photo used for illustration purposes only

CASE STYLE: GU1604

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost	
Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500, 1000
13"	2000

Electrical Specifications

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		20		2500	MHz
Insertion Loss	20-2500	—	0.2	0.8	dB
	200-1250	—	0.35	0.8	
	1250-2500	—	0.7	1.2	
Isolation (RF port to DC port) (RF & DC port to DC port)	20-2500	40	65	—	dB
	200-1250	25	44	—	
	1250-2500	20	40	—	
VSWR	20-2500	—	1.05	1.5	:1
	200-1250	—	1.05	1.2	
	1250-2500	—	1.1	1.25	

External C1(0.01μF) is required. See functional schematic and PCB layout.

Maximum Ratings


Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	30 dBm max.
Voltage at DC port	25 V max.
DC Current	200mA

Permanent damage may occur if any of these limits are exceeded.


Pad Terminations

Function	Pad Number
RF	4
RF&DC	3
DC	1
ISOLATE (see PCB Layout)	2


Product Marking




Functional Schematic




Outline Drawing



PCB Land Pattern



Demo Board MCL P/N: TB-268 Suggested PCB Layout (PL-146)



NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020 ± 0.0015 ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Notes:






3. Must be isolated from external conductors on mounting surface. Suggested solder mask area is $.025 \times .025$. At Mini-Circuits option via may be removed.
4. Top-Hat total thickness: .013 inches MAX.

Outline Dimensions (Inch/mm)

A	B	C	D	E	F
.150	.150	.150	.100	.030	.025
3.81	3.81	3.81	2.54	0.76	0.64
G	H	J	K	wt	
.028	.050	.160	.030	grams	
0.71	1.27	4.06	0.76	0.10	

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB) with current			VSWR (:1) with current			FREQUENCY (MHz)	ISOLATION (dB) 0mA	
	0mA	50mA	100mA	0mA	50mA	100mA		RF - DC	RF&DC-DC
20.00	0.24	0.22	0.27	1.09	1.03	1.17	20	61.91	61.88
30.00	0.22	0.22	0.24	1.08	1.03	1.09	50	70.90	82.16
50.00	0.20	0.21	0.21	1.11	1.08	1.02	200	74.93	59.19
100.00	0.20	0.24	0.32	1.01	1.03	1.07	350	60.74	53.73
250.00	0.21	0.23	0.31	1.02	1.01	1.02	500	53.42	49.17
400.00	0.21	0.22	0.30	1.01	1.02	1.03	710	46.96	44.20
500.00	0.23	0.24	0.31	1.04	1.03	1.04	890	42.32	39.88
750.00	0.26	0.28	0.35	1.04	1.03	1.04	1070	38.90	36.40
900.00	0.29	0.31	0.37	1.02	1.02	1.03	1250	36.26	33.23
1000.00	0.32	0.34	0.40	1.03	1.02	1.03	1375	34.93	31.36
1450.00	0.51	0.51	0.56	1.10	1.09	1.11	1500	33.06	28.86
1900.00	0.70	0.68	0.75	1.02	1.03	1.05	1852	31.65	25.51
2350.00	0.73	0.76	0.85	1.08	1.09	1.09	2380	29.08	22.65
2800.00	0.69	0.74	0.83	1.08	1.09	1.08	2440	28.00	21.74
3250.00	0.71	0.76	0.85	1.07	1.09	1.07	2500	28.05	22.03



Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp







Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (RF Port to RF&DC Port) (dB)						RETURN LOSS 20-50MHz: RF Port, >50MHz: RF&DC Port (dB)					
	+25°			-45°	0mA		+25°			-45°	0mA	
	0mA	50mA	100mA		+25°	+85°	0mA	50mA	100mA		+25°	+85°
20	0.24	0.22	0.27	0.16	0.24	0.26	27.16	35.98	22.19	28.34	27.16	26.08
30	0.22	0.22	0.24	0.17	0.22	0.24	28.79	36.17	26.91	28.38	28.79	28.16
50	0.20	0.21	0.21	0.20	0.20	0.22	25.50	28.50	38.97	25.13	25.50	25.43
100	0.20	0.24	0.32	0.13	0.17	0.23	44.58	37.41	29.64	33.05	33.37	31.91
250	0.21	0.23	0.31	0.14	0.20	0.27	39.57	51.28	39.20	34.84	35.90	33.82
400	0.21	0.22	0.30	0.14	0.22	0.30	43.08	42.17	37.80	32.31	32.02	31.26
500	0.23	0.24	0.31	0.14	0.22	0.30	33.57	35.68	34.56	32.88	32.21	29.89
750	0.26	0.28	0.35	0.16	0.26	0.36	34.29	35.73	33.92	33.09	32.52	31.83
900	0.29	0.31	0.37	0.17	0.28	0.40	40.78	40.84	36.20	36.14	34.42	32.48
1000	0.32	0.34	0.40	0.20	0.32	0.45	36.97	39.09	36.60	35.08	34.70	35.14
1450	0.51	0.51	0.56	0.45	0.54	0.58	26.12	27.70	25.83	22.56	23.15	24.77
1900	0.70	0.68	0.75	0.58	0.66	0.71	40.17	36.30	31.70	33.68	39.54	37.01
2350	0.73	0.76	0.85	0.46	0.64	0.81	28.01	27.66	27.33	37.59	44.19	38.97
2800	0.69	0.74	0.83	0.39	0.61	0.86	28.83	27.73	28.82	24.66	23.42	22.08
3250	0.71	0.76	0.85	0.43	0.68	0.96	29.04	27.03	29.05	24.57	26.62	29.23

Bias Tee , Surface Mount

Typical Performance Curves

TCBT-2R5G+



REV. X1
TCBT-2R5G+
061126
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Outline Dimensions

GU1604



PCB Land Pattern



TOP VIEW OF "TCBT" SERIES MODELS

CASE #	A	B	C	D	E	F	G	H	J	K	WT.GRAMS
GU1604	.150 (3.81)	.150 (3.81)	.150 (3.81)	.100 (2.54)	.030 (.76)	.025 (.64)	.028 (.71)	.050 (1.27)	.160 (4.06)	.030 (.76)	.10

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, Ceramic Base.
2. Termination finish: Silver Palladium or Gold Over Nickel based on stock availability.
3. Must be isolated from external conductors on mounting surface. Suggested solder mask area is .025 x .025.
At Mini-Circuits option via may be removed.
4. Top-Hat total thickness: .013 inches MAX.
5. Orientation Dot on Top Hat corresponds to Pin #1.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F77



Note: The shape of the pocket may differ



Note: The location and shape of the metallization may differ

Applicable Case Styles

GU1604, GU1804, GU2644,
TT1618-2

Applicable Case Styles

MZ4532C, NM1812C,
NM1812C-1, NM1812C-2,
NM1812C-3, NM1812C-5,
NM1812C-6, NM3237

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
		1000		
		13	Standard	2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
B	M102713	ADDED "...WITH SMOBC"	01/12/06	GF	IL
C	M103775	.010 uF WAS .010 mF	03/01/06	MMG	DJ
D	M154947	CHANGED PIN1 & PIN CONNECTION	02/03/16	ITG	DJ
E	M167305	CHANGED CASE STYLE & PIN CONNECT.	04/18/18	ITG	IG

SUGGESTED MOUNTING CONFIGURATION FOR
GU1604 CASE STYLE, "04BT01" PIN CONNECTION



CAPACITOR C1: .010 uF, 0603 SIZE

NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020 ± 0.0015 ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES	DRAWN	AV	10/13/03
TOLERANCES ON:	CHECKED	IL	10/23/03
2 PL DECIMALS ±	APPROVED	DJ	10/23/03
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits[®] 13 Neptune Avenue
Brooklyn NY 11235


PL, 04BT01, GU1604, TCBT, TB-268

Mini-Circuits[®]
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-146	E
FILE:	98PL146	SCALE:	10:1
		SHEET:	1 OF 1

Evaluation Board and Circuit




TB-268



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215