



Mini-Circuits


# SURFACE MOUNT <sup>top hat</sup> Bias Tee

50Ω Wideband 50 to 6000 MHz

TCBT-6G+

## FEATURES

- Wideband, 50 to 6000 MHz
- Low Insertion Loss, 0.7 dB Typ.
- Miniature Surface Mount 0.15x0.15"
- Aqueous Washable
- Protected by US Patent 7,012,486



Generic photo used for illustration purposes only

CASE STYLE: GU1604

## APPLICATIONS

- Biasing Amplifiers
- Biasing of Laser Diodes
- Biasing of Active Antennas

### +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		50		6000	MHz
Insertion Loss	50-500		0.2	0.8	dB
	500-3000		0.7	1.8	
	3000-6000		1.1	2.5	
Isolation (RF Port to DC Port) (RF & DC Port to DC Port)	50-500	38	52		dB
	500-3000	18	28		
	3000-6000	14	19		
VSWR	50-500		1.05	1.5	:1
	500-3000		1.1	1.3	
	3000-6000		1.2	2.2	


External C1(0.01 µF) is required. See functional schematic and PCB layout.

## ABSOLUTE MAXIMUM RATINGS

Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
RF Power	+30 dBm max.
Voltage at DC Port	+25 V max.
DC Current	200 mA

Permanent damage may occur if any of these limits are exceeded.

## FUNCTIONAL SCHEMATIC



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. J  
ECO-026344  
TCBT-6G+  
MCL NY  
250728

PAGE 1 OF 3



Mini-Circuits

# SURFACE MOUNT <sup>top hat</sup> Bias Tee

50Ω Wideband 50 to 6000 MHz


TCBT-6G+

## PAD CONNECTIONS

RF	4
RF & DC	3
DC	1
ISOLATE (See PCB Layout)	2

PRODUCT MARKING: BB

## DEMO BOARD MCL P/N: TB-TCBT-6G+ SUGGESTED PCB LAYOUT (PL-146)





## NOTES:

- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS  $0.020 \pm 0.0015$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

## OUTLINE DRAWING



## PCB Land Pattern



SUGGESTED LAYOUT  
TOLERANCE TO BE WITHIN  $\pm .002$

## Notes:

- Must be isolated from external conductors on mounting surface. Suggested solder mask area is .025 x .025. At Mini-Circuits option via may be removed.
- Top-Hat total thickness: .013 inches MAX.

OUTLINE DIMENSIONS (Inches)  
mm

A	B	C	D	E	F
.150	.150	.150	.100	.030	.025
3.81	3.81	3.81	2.54	0.76	0.64
G	H	J	K		wt
.028	.050	.160	.030		grams
0.71	1.27	4.06	0.76		0.10

## TAPE &amp; REEL INFORMATION: F77



Mini-Circuits






# SURFACE MOUNT <sup>top hat</sup> Bias Tee

TCBT-6G+

50Ω Wideband 50 to 6000 MHz

## TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB) with Temperature			VSWR (:1) with Temperature			Isolation (dB) 0 mA	
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	RF-DC	RF & DC - DC
50	0.18	0.23	0.43	1.23	1.24	1.27	62.01	63.14
250	0.24	0.30	0.50	1.06	1.07	1.10	58.05	54.10
500	0.23	0.29	0.49	1.07	1.08	1.11	48.04	43.88
750	0.27	0.35	0.57	1.06	1.07	1.10	44.58	40.67
1000	0.30	0.39	0.63	1.05	1.05	1.08	41.47	37.79
1450	0.39	0.49	0.69	1.15	1.15	1.15	35.33	31.47
1900	0.61	0.70	0.81	1.04	1.04	1.03	31.51	26.67
2350	0.79	0.84	0.87	1.08	1.07	1.03	30.13	25.03
3250	0.91	1.02	1.14	1.09	1.09	1.11	27.98	21.20
3700	0.92	1.07	1.32	1.07	1.10	1.17	27.37	20.10
4150	0.62	0.79	1.26	1.28	1.28	1.34	27.10	19.55
4600	0.91	1.05	1.48	1.06	1.07	1.20	26.78	18.79
5050	0.84	0.96	1.21	1.34	1.38	1.48	27.64	19.18
5500	0.92	1.04	1.23	1.34	1.30	1.25	29.30	20.39
6400	0.83	0.96	1.25	1.74	1.70	1.51	31.01	21.50



## NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)







## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (RF Port to RF&DC Port) (dB)						VSWR (:1)					
	+25°			-45°	0mA		+25°			-45°	0mA	
	0mA	50mA	100mA		+25°	+85°	0mA	50mA	100mA		+25°	+85°
50	0.36	0.41	0.49	0.18	0.23	0.43	1.33	1.29	1.20	1.23	1.24	1.27
250	0.37	0.38	0.49	0.24	0.30	0.50	1.04	1.03	1.03	1.06	1.07	1.10
500	0.37	0.38	0.46	0.23	0.29	0.49	1.02	1.02	1.02	1.07	1.08	1.11
750	0.40	0.40	0.48	0.27	0.35	0.57	1.01	1.02	1.03	1.06	1.07	1.10
1000	0.45	0.46	0.54	0.30	0.39	0.63	1.02	1.02	1.03	1.05	1.05	1.08
2350	0.99	0.90	0.94	0.79	0.84	0.87	1.08	1.10	1.12	1.08	1.07	1.03
3250	1.06	0.99	1.11	0.91	1.02	1.14	1.06	1.06	1.05	1.09	1.09	1.11
4150	1.52	1.51	1.69	0.62	0.79	1.26	1.25	1.26	1.22	1.28	1.28	1.34
5050	1.35	1.32	1.43	0.84	0.96	1.21	1.69	1.72	1.76	1.34	1.38	1.48

# Bias Tee , Surface Mount


## Typical Performance Curves

TCBT-6G+




## Outline Dimensions

GU1604



TOP VIEW OF "TCBT" SERIES MODELS

## PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	WT.GRAMS
GU1604	.150 (3.81)	.150 (3.81)	.150 (3.81)	.100 (2.54)	.030 (.76)	.025 (.64)	.028 (.71)	.050 (1.27)	.160 (4.06)	.030 (.76)	.10

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

1. Open style, Ceramic Base.
2. Termination finish: Silver Palladium or Gold Over Nickel based on stock availability.
3. Must be isolated from external conductors on mounting surface. Suggested solder mask area is .025 x .025.  
At Mini-Circuits option via may be removed.
4. Top-Hat total thickness: .013 inches MAX.
5. Orientation Dot on Top Hat corresponds to Pin #1.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F77



Note: The shape of the pocket may differ



Note: The location and shape of the metallization may differ

## Applicable Case Styles

GU1604, GU1804, GU2644,  
TT1618-2

## Applicable Case Styles

MZ4532C, NM1812C,  
NM1812C-1, NM1812C-2,  
NM1812C-3, NM1812C-5,  
NM1812C-6, NM3237

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
		13	Standard	2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
B	M102713	ADDED "...WITH SMOBC"	01/12/06	GF	IL
C	M103775	.010 uF WAS .010 mF	03/01/06	MMG	DJ
D	M154947	CHANGED PIN1 & PIN CONNECTION	02/03/16	ITG	DJ
E	M167305	CHANGED CASE STYLE & PIN CONNECT.	04/18/18	ITG	IG


SUGGESTED MOUNTING CONFIGURATION FOR  
GU1604 CASE STYLE, "04BT01" PIN CONNECTION



CAPACITOR C1: .010 uF, 0603 SIZE

**NOTES:**

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS  $0.020 \pm 0.0015$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$ .005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	AV	10/13/03
	CHECKED	IL	10/23/03
	APPROVED	DJ	10/23/03



**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235


PL, 04BT01, GU1604, TCBT, TB-268

Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.			
ASHEETA1.DWG REV:A DATE:01/12/95			


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-146	E
FILE:	98PL146	SCALE:	10:1
		SHEET:	1 OF 1



# Evaluation Board and Circuit




TB-268



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215