



Mini-Circuits

SURFACE MOUNT top hat

Directional Coupler

TCD-12-222X+

50Ω

5 to 2250 MHz

THE BIG DEAL

- Wideband, 5 to 2250 MHz
- Low Mainline Loss, 2.0 dB Typ.
- Aqueous Washable
- Leads for Excellent Solderability
- Protected by US Patent 6,140,887



Generic photo used for illustration purposes only

CASE STYLE: DB1627

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- VHF/UHF
- CATV
- Cellular

PRODUCT OVERVIEW

Mini-Circuits' TCD-12-222X+ surface mount directional coupler provides 12.6 dB nominal coupling with excellent flatness from 5 to 2250 MHz, supporting a wide variety of applications including VHF/UHF, CATV, cellular and more. This model provides low mainline loss, high directivity and excellent return loss. The coupler is built with core and wire construction mounted on a 6-lead plastic base (0.16x0.15x0.16") and includes Mini-Circuits' TopHat® feature for faster, more accurate pick-and-place assembly.

KEY FEATURES

Feature	Advantages
Low Mainline Loss, 2.0 dB	Provides good through-path signal power transmission.
High Directivity, 10 to 21 dB	High directivity allows accurate signal sampling through the coupled port with minimal measurement error.
Excellent Return Loss, 14 to 25 dB (Input/Output/Coupling)	Provides excellent matching for 50Ω systems and minimal signal reflection.
1 W Power Handling	Usable in systems with a variety of high-power requirements.
Top Hat® Feature	Improves speed and accuracy of pick and place assembly and provides clear device marking for visual inspection.

REV. B
ECO-027946
TCD-12-222X+
MCL NY
260205





ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		5		2250	MHz
Mainline Loss ¹ (Above Theoretical 0.3 dB)	5		0.4	1.0	dB
	950		0.6	1.1	
	2250		2.5	3.5	
Coupling	5-2250		12.6±0.8		dB
Coupling Flatness (±)	5-2250		±0.6	±1.0	dB
Directivity	5	17	21		dB
	950	11	15		
	2250	6	10		
Return Loss (Input)	5		21		dB
	950		17		
	2250		16		
Return Loss (Output)	5		25		dB
	950		17		
	2250		14		
Return Loss (Coupling)	5		24		dB
	950		17		
	2250		15		
Input Power	5-100			0.5	W
	100-2250			1.0	


1. Mainline loss includes theoretical power loss 0.3 dB at coupled port.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C ²
Storage Temperature	-55°C to +100°C

2. Case temperature is defined as temperature on ground leads. Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



*Electrical schematic is for Directional coupler with internal transformer(s) and external termination



Directional Coupler

TCD-12-222X+

50Ω


5 to 2250 MHz

PIN CONNECTIONS

INPUT	3
OUTPUT	4
COUPLED	1
GROUND	2
50Ω TERM EXTERNAL	6
NOT USED	5

PRODUCT MARKING: DA

DEMO BOARD MCL P/N: TB-TCD-12-222X+ SUGGESTED PCB LAYOUT (PL-009)




RESISTOR R1: 49.9 ± 1% Ohm, 0805 SIZE

NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.


2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern



SUGGESTED LAYOUT TOLERANCE TO BE WITHIN ±.002

OUTLINE DIMENSIONS (Inches mm)

A	B	C	D	E	F
.160	.150	.160	.050	.040	.025
4.06	3.81	4.06	1.27	1.02	0.64
G	H	J	K		wt
.028	.065	.190	.030		grams
0.71	1.65	4.83	0.76		0.15

TAPE & REEL INFORMATION: F47





Directional Coupler

TCD-12-222X+

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)		Coupling (dB)	Directivity (dB)	Return Loss (dB)		
	In-Out	In-Cpl			In	Out	Cpl
5	0.68	12.93	21.57	22.32	29.51	24.61	
50	0.67	12.93	21.29	23.52	32.47	25.50	
150	0.69	12.95	21.07	23.03	28.80	24.43	
450	0.79	12.91	18.41	19.74	21.23	20.14	
750	0.97	12.76	15.89	17.36	18.25	17.65	
950	1.11	12.59	14.35	16.58	17.20	16.83	
1350	1.51	12.09	12.29	16.52	15.97	16.81	
1650	1.96	11.72	11.78	18.33	15.47	17.99	
1950	2.61	11.66	12.08	23.10	14.97	19.94	
2250	3.36	12.35	12.80	28.39	14.69	21.95	



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Directional Coupler

TCD-12-222X+




Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT (dB)	CPL
1	0.95	13.17	21.64	17.34	19.50	19.63
3	0.73	12.97	21.55	21.29	26.47	23.52
5	0.68	12.93	21.57	22.32	29.51	24.61
10	0.66	12.91	21.57	22.85	32.47	25.31
20	0.67	12.91	21.61	23.31	33.33	25.52
30	0.67	12.92	21.59	23.46	33.10	25.52
40	0.67	12.92	21.49	23.49	32.60	25.52
50	0.67	12.93	21.29	23.52	32.47	25.50
150	0.69	12.95	21.07	23.03	28.80	24.43
250	0.71	12.95	20.09	21.98	25.16	22.89
350	0.75	12.94	19.46	20.83	23.07	21.44
450	0.79	12.91	18.41	19.74	21.23	20.14
550	0.85	12.87	17.64	18.74	20.01	19.12
650	0.90	12.82	16.67	17.97	19.04	18.29
750	0.97	12.76	15.89	17.36	18.25	17.65
850	1.03	12.68	15.03	16.91	17.77	17.18
950	1.11	12.59	14.35	16.58	17.20	16.83
1050	1.19	12.48	13.69	16.37	16.91	16.64
1150	1.29	12.36	13.14	16.28	16.46	16.58
1250	1.39	12.23	12.69	16.32	16.26	16.64
1350	1.51	12.09	12.29	16.52	15.97	16.81
1450	1.64	11.96	12.04	16.92	15.83	17.09
1550	1.79	11.82	11.81	17.50	15.62	17.50
1650	1.96	11.72	11.78	18.33	15.47	17.99
1750	2.16	11.64	11.76	19.44	15.29	18.57
1850	2.38	11.62	11.91	21.03	15.14	19.20
1950	2.61	11.66	12.08	23.10	14.97	19.94
2050	2.86	11.80	12.35	25.57	14.85	20.60
2150	3.12	12.02	12.57	27.78	14.71	21.29
2250	3.36	12.35	12.80	28.39	14.69	21.95
2350	3.57	12.78	12.80	27.01	14.73	22.77
2450	3.77	13.31	12.54	24.82	14.91	23.76
2550	3.94	13.93	11.84	23.18	15.14	25.13
2650	4.09	14.63	10.81	22.06	15.47	27.08


Directional Coupler

Typical Performance Curves


TCD-12-222X+



Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
DB1627	.160 (4.06)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (0.64)	.028 (0.71)	.065 (1.65)	.190 (4.83)	.030 (0.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits[®]


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M73159	NEW RELEASE	08/00	IL	DB
A	M82377	UPDATED DRAWING	07/21/02	AV	LC
B	M102713	UPDATED NOTES	01/12/08	GF	IL

SUGGESTED MOUNTING CONFIGURATION FOR DB714 CASE STYLE, "mm" PIN CONNECTION



RESISTOR R1: 49.9 ± 1% Ohm, 0805 SIZE

- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES	DRAWN	IL	08/03/00
TOLERANCES ON:	CHECKED	WP	08/08/00
2 PL DECIMALS ± .005	APPROVED	DB	08/08/00
3 PL DECIMALS ±			
ANGLES ±			
FRACTIONS ±			


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, mm, DB714, TCD, TB-71


Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-009	REV: B
FILE: 98PL009	SCALE: 10:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



TB-71



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215