



Mini-Circuits

SURFACE MOUNT top hat

Directional Coupler


TCD-17-282X+

50Ω

5 to 2850 MHz

THE BIG DEAL

- Wideband, 5 to 2850 MHz
- Low mainline loss, 1.9 dB typ. up to 2850 MHz
- Aqueous washable
- Leads for excellent solderability
- Protected by US Patent 6,140,887



Generic photo used for illustration purposes only

CASE STYLE: DB1627

APPLICATIONS

- VHF/UHF
- PCS
- ISM
- PCN
- Cellular
- UMTS
- GPS

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

PRODUCT OVERVIEW

Mini-Circuits' TCD-17-282X+ surface mount directional coupler provides 17 dB nominal coupling with excellent flatness from 5 to 2850 MHz, supporting a wide variety of applications including VHF/UHF, CATV, cellular, SatCom and more. This model provides low mainline loss, high directivity and excellent return loss. The coupler is built with core and wire construction mounted on a 6-lead plastic base (0.16 × 0.15 × 0.16") and includes Mini-Circuits' TopHat® feature for faster, more accurate pick-and-place assembly.

KEY FEATURES

Feature	Advantages
Low mainline loss • 0.7 dB to 950 MHz • 1.9 dB to 2850 MHz	Provides good through-path signal power transmission.
High directivity, 10–5 dB	High directivity allows accurate signal sampling through the coupled port with minimal measurement error.
Excellent return loss, 14–22 dB (input/output/coupling)	Provides excellent matching for 50Ω systems and minimal signal reflection.
Good power handling • 1 W, 100 to 2850 MHz • 0.5 W, 5 to 100 MHz	Usable in systems with a variety of high-power requirements.
Top Hat® feature	Improves speed and accuracy of pick and place assembly and provides clear device marking for visual inspection.





Mini-Circuits®

SURFACE MOUNT 

Directional Coupler

TCD-17-282X+

50Ω

5 to 2850 MHz

ELECTRICAL SPECIFICATIONS AT +25 °C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range	—	5	—	2850	MHz
Mainline Loss ¹ (above theoretical 0.1 dB)	5	—	0.7	1.3	dB
	950	—	0.7	1.1	
	2850	—	1.9	2.4	
Coupling	5–2850	—	17±1	—	dB
Coupling Flatness (±)	5–950	—	0.3	0.6	dB
	950–2850	—	1.2	1.5	
Directivity	5–100	18	25	—	dB
	100–950	13	20	—	
	950–2850	6	10	—	
Return Loss (Input)	5	—	20	—	dB
	950	—	17	—	
	2850	—	14	—	
Return Loss (Output)	5	—	22	—	dB
	950	—	18	—	
	2850	—	14	—	
Return Loss (Coupling)	5	—	20	—	dB
	950	—	16	—	
	2850	—	15	—	
Input Power	5–100	—	—	0.5	W
	100–2850	—	—	1.0	

1. Mainline loss includes theoretical power loss at coupled port.


ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40 °C to 85 °C*
Storage Temperature	-55 °C to 100 °C

Permanent damage may occur if any of these limits are exceeded.

* Case temperature is defined as temperature on ground leads.

ELECTRICAL SCHEMATIC



*Electrical schematic is for Directional coupler with internal transformer(s) and external termination

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
ECO-014204
TCD-17-282X+
MCL NY
260713
PAGE 2 OF 4



Directional Coupler

50Ω


5 to 2850 MHz

OUTLINE DRAWING

INPUT	3
OUTPUT	4
COUPLED	1
GROUND	2
50Ω TERM EXTERNAL	6
NOT USED	5

PRODUCT MARKING: DF


DEMO BOARD MCL P/N: TB-71
SUGGESTED PCB LAYOUT (PL-009)

RESISTOR R1: 49.9 $\pm$ 1% Ohm, 0805 SIZE


NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.030" $\pm$ 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

PCB Land Pattern



SUGGESTED LAYOUT
TOLERANCE TO BE WITHIN $\pm .002$

OUTLINE DIMENSIONS (Inches)

A	B	C	D	E	F
.160	.150	.160	.050	.040	.025
4.06	3.81	4.06	1.27	1.02	0.64
G	H	J	K		wt
.028	.065	.190	.030		grams
0.71	1.65	4.83	0.76		0.15

TAPE & REEL INFORMATION: F47





Mini-Circuits

SURFACE MOUNT 

Directional Coupler




TCD-17-282X+

50Ω

5 to 2850 MHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)	Directivity (dB)	Return Loss (dB)		
	In-Out			In	Out	Cpl
5	0.62	17.63	32.71	22.72	25.10	22.92
50	0.60	17.61	38.38	24.47	27.28	24.42
350	0.66	17.71	30.67	21.79	22.63	21.28
650	0.77	17.79	22.79	18.79	19.05	18.33
950	0.90	17.87	17.87	16.99	17.11	16.63
1250	1.03	17.77	14.58	15.90	16.01	15.81
1650	1.20	17.28	11.83	15.31	15.14	15.57
2050	1.40	16.52	10.09	15.38	14.70	16.04
2450	1.63	15.79	8.93	16.19	14.74	17.16
2850	1.93	15.27	8.21	17.12	14.89	18.94



- NOTES
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Directional Coupler

TCD-17-282X+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
3	0.69	17.74	28.43	21.06	22.87	21.15
5	0.62	17.63	32.71	22.72	25.10	22.92
10	0.59	17.58	37.68	23.71	26.87	24.12
20	0.60	17.59	38.74	24.32	27.22	24.44
30	0.60	17.60	38.44	24.45	27.17	24.45
40	0.60	17.61	37.88	24.46	27.11	24.42
50	0.60	17.61	38.38	24.47	27.28	24.42
150	0.62	17.64	37.42	23.96	26.04	23.65
250	0.63	17.67	33.22	22.92	24.24	22.50
350	0.66	17.71	30.67	21.79	22.63	21.28
450	0.69	17.73	27.27	20.66	21.09	20.13
550	0.73	17.76	24.98	19.62	19.96	19.16
650	0.77	17.79	22.79	18.79	19.05	18.33
750	0.81	17.83	20.99	18.08	18.25	17.65
850	0.85	17.85	19.28	17.50	17.73	17.09
950	0.90	17.87	17.87	16.99	17.11	16.63
1050	0.94	17.85	16.61	16.55	16.75	16.28
1150	0.99	17.82	15.53	16.19	16.26	16.01
1250	1.03	17.77	14.58	15.90	16.01	15.81
1350	1.07	17.68	13.71	15.65	15.68	15.67
1450	1.12	17.58	12.98	15.50	15.51	15.59
1550	1.16	17.44	12.33	15.37	15.26	15.56
1650	1.20	17.28	11.83	15.31	15.14	15.57
1750	1.25	17.11	11.30	15.28	14.97	15.61
1850	1.30	16.92	10.88	15.30	14.87	15.70
1950	1.35	16.72	10.46	15.33	14.74	15.87
2050	1.40	16.52	10.09	15.38	14.70	16.04
2150	1.45	16.33	9.74	15.49	14.60	16.27
2250	1.51	16.14	9.45	15.68	14.63	16.52
2350	1.56	15.95	9.16	15.92	14.65	16.83
2450	1.63	15.79	8.93	16.19	14.74	17.16
2550	1.69	15.63	8.68	16.48	14.78	17.55
2650	1.77	15.50	8.54	16.73	14.84	17.97
2750	1.85	15.37	8.32	16.98	14.91	18.43
2850	1.93	15.27	8.21	17.12	14.89	18.94
2950	2.02	15.18	8.04	17.24	14.95	19.42
3050	2.11	15.10	7.95	17.24	14.92	19.94
3150	2.21	15.05	7.84	17.12	14.96	20.44
3250	2.30	15.01	7.79	16.94	14.91	21.01
3350	2.40	15.00	7.74	16.76	14.89	21.48







P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS


REV. OR
TCD-17-282X+
11/6/2017
Page 1 of 1

Typical Performance Curves




Outline Dimensions

DB1627



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
DB1627	.160 (4.06)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (0.64)	.028 (0.71)	.065 (1.65)	.190 (4.83)	.030 (0.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M73159	NEW RELEASE	08/00	IL	DB
A	M82377	UPDATED DRAWING	07/21/02	AV	LC
B	M102713	UPDATED NOTES	01/12/08	GF	IL


SUGGESTED MOUNTING CONFIGURATION FOR DB714 CASE STYLE, "mm" PIN CONNECTION



RESISTOR R1: $49.9 \pm 1\%$ Ohm, 0805 SIZE

NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $0.030'' \pm 0.002''$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS $\pm .005$
3 PL DECIMALS $\pm$
ANGLES $\pm$
FRACTIONS $\pm$

DRAWN

IL

08/03/00

CHECKED

WP

08/08/00

APPROVED

DB

08/08/00

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, mm, DB714, TCD, TB-71

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-009


REV:
B

FILE: 98PL009


SCALE: 10:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-71



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215