



Mini-Circuits

SURFACE MOUNT 

Directional Coupler TCD-16-12W-75X+

75Ω 16 dB 5 to 1218 MHz

FEATURES

- Wideband, 5 to 1218 MHz
- Low Mainline Loss, 0.7 dB Typ.
- Aqueous Washable
- Leads for Excellent Solderability
- Protected by US Patent 6,140,887

APPLICATIONS

- DOCSIS® Systems
- VHF/UHF
- CATV
- Cellular



Generic photo used for illustration purposes only

CASE STYLE: DB1627

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		5		1218	MHz
Mainline Loss ¹ (Above Theoretical 0.1 dB)	5-50		0.65	0.9	dB
	50-870		0.5	0.8	
	870-1218		0.70	1.0	
Coupling	5-1218		16.0±0.5		dB
Coupling Flatness (±)	5-1218		±0.8	±1.2	dB
Directivity	5-50	25	35		dB
	50-870	11	16		
	870-1218	8	12		
Return Loss (Input)	5-50	18	22		dB
	50-870	14	18		
	870-1218	16	19		
Return Loss (Output)	5-50	20	25		dB
	50-870	17	19		
	870-1218	18	22		
Return Loss (Coupling)	5-50	18	22		dB
	50-870	15	17		
	870-1218	14	16		
Input Power	5-1218			1.0	W


1. Mainline loss includes theoretical power loss at coupled port.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C ²
Storage Temperature	-55°C to +100°C

2. Case temperature is defined as temperature on ground leads. Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



*Electrical schematic is for Directional coupler with internal transformer(s) and external termination







Directional Coupler **TCD-16-12W-75X+**

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)		Coupling (dB)	Directivity (dB)	Return Loss (dB)		
	In-Out	In-Cpl			In	Out	Cpl
5	0.70	16.30	38.48	21.56	24.12	21.32	
50	0.68	16.20	34.99	23.66	27.86	23.32	
100	0.72	16.23	30.01	23.52	27.85	23.18	
200	0.73	16.21	24.23	23.47	27.55	23.33	
350	0.74	16.16	19.59	22.84	26.30	23.30	
500	0.74	16.00	16.71	21.68	24.73	23.18	
650	0.75	15.79	14.87	20.83	23.65	22.42	
800	0.77	15.54	13.63	20.61	22.88	21.81	
1000	0.81	15.12	12.55	21.11	23.12	21.32	
1218	0.90	14.62	11.68	22.95	25.89	21.09	



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Directional Coupler

TCD-16-12W-75X+





Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
1	1.18	16.87	28.62	15.12	16.03	14.89
2	0.92	16.56	33.71	17.96	19.33	17.75
3	0.80	16.42	36.16	19.67	21.48	19.45
4	0.74	16.35	37.52	20.79	23.00	20.56
5	0.70	16.30	38.48	21.56	24.12	21.32
6	0.68	16.28	39.17	22.13	25.02	21.89
8	0.65	16.23	39.92	22.84	26.25	22.59
10	0.65	16.20	39.55	23.25	26.99	22.97
20	0.64	16.18	39.34	23.82	28.19	23.53
30	0.66	16.18	38.36	23.78	28.12	23.48
50	0.68	16.20	34.99	23.66	27.86	23.32
80	0.71	16.22	31.80	23.56	27.80	23.20
100	0.72	16.23	30.01	23.52	27.85	23.18
150	0.73	16.22	26.51	23.60	27.98	23.40
200	0.73	16.21	24.23	23.47	27.55	23.33
250	0.73	16.20	22.30	23.17	27.39	23.36
300	0.74	16.19	20.79	23.06	27.08	23.32
350	0.74	16.16	19.59	22.84	26.30	23.30
400	0.73	16.10	18.47	22.39	25.85	23.30
450	0.73	16.06	17.52	22.01	25.21	23.17
500	0.74	16.00	16.71	21.68	24.73	23.18
550	0.74	15.94	16.08	21.31	24.20	22.90
600	0.74	15.87	15.38	21.04	23.74	22.79
650	0.75	15.79	14.87	20.83	23.65	22.42
700	0.76	15.72	14.32	20.70	22.97	22.32
750	0.76	15.63	13.91	20.57	22.97	22.01
800	0.77	15.54	13.63	20.61	22.88	21.81
850	0.78	15.44	13.23	20.67	22.55	21.71
900	0.79	15.34	13.02	20.71	22.80	21.42
950	0.80	15.24	12.72	20.92	22.72	21.40
1000	0.81	15.12	12.55	21.11	23.12	21.32
1050	0.82	15.01	12.35	21.42	23.37	21.20
1100	0.84	14.90	12.15	21.76	24.01	21.17
1150	0.86	14.78	12.01	22.19	24.47	21.08
1200	0.89	14.67	11.77	22.72	25.48	21.11
1218	0.90	14.62	11.68	22.95	25.89	21.09
1250	0.92	14.54	11.57	23.43	26.46	21.06
1350	0.98	14.28	10.84	25.28	29.63	21.04
1450	1.05	14.01	9.89	27.76	31.30	21.07
1550	1.13	13.78	8.92	29.31	29.25	20.97
1650	1.23	13.58	8.11	28.95	27.23	20.70


Directional Coupler

TCD-16-12W-75X+


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
DB1627	.160 (4.06)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (0.64)	.028 (0.71)	.065 (1.65)	.190 (4.83)	.030 (0.76)	.15


Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M76190	CHANGED DISCRIPTION	04/01	GF	CT
B	M82575	UPDATED DRAWING	08/05/02	AV	LC
C	M102713	ADDED NOTE 2 & "...WITH SMOBC"	01/17/06	MMG	IL
D	M108434	UPDATED DRAWING PER TB-409+	11/14/06	PW	IG

SUGGESTED MOUNTING CONFIGURATION
FOR DF782 CASE STYLE, "mz" PIN CONNECTION



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	AV 01/15/01
	CHECKED	YB 01/23/01
	APPROVED	DB 01/23/01




Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, mz, DF782, GALI, TB-409-XXX+


Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-019	D
FILE:	98PL019	SCALE:	10:1
		SHEET:	1 OF 1

Evaluation Board and Circuit



TB-72



Schematic Diagram

Notes:

1. 75 Ohm BNC Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215