

## Directional Coupler

## TCD-ED13989/1

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DB1627


| ELECTRICAL SPECIFICATIONS 75Ω @ +25°C |            |      |          |      |       |
|---------------------------------------|------------|------|----------|------|-------|
| Parameter                             |            | Min. | Typ.     | Max. | Units |
| Frequency                             |            | 5    |          | 2000 | MHz   |
| Coupling                              | Nominal    |      | 16.5±0.5 |      | dB    |
|                                       | Flatness   |      | ±0.7     |      | dB    |
| Mainline Loss *                       | 5 MHz      |      | 1.5      |      | dB    |
|                                       | 950 MHz    |      | 1.2      |      | dB    |
|                                       | 2000 MHz   |      | 1.6      |      | dB    |
| Directivity                           | 5 MHz      |      | 14       |      | dB    |
|                                       | 950 MHz    |      | 29       |      | dB    |
|                                       | 2000 MHz   |      | 14       |      | dB    |
| VSWR                                  | 5-2000 MHz |      | 1.11     |      | (:1)  |
| RF Power Input                        | 5-2000 MHz |      |          | 1    | W     |

**Note:** \* Mainline loss includes theoretical coupled power loss of 0.1dB at 16.5dB coupling.

| MAXIMUM RATINGS       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |

| PIN CONNECTIONS    |   |
|--------------------|---|
| INPUT              | 3 |
| OUTPUT             | 4 |
| COUPLED            | 1 |
| NOT USED           | 5 |
| 75Ω TERM. EXTERNAL | 6 |
| GROUND             | 2 |

### Electrical Schematic



\* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.

# Directional Coupler

## TCD-ED13989/1

### Typical Performance Data




| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS<br>(dB) |       |       |
|--------------------|---------------------------|------------------|---------------------|---------------------|-------|-------|
|                    |                           |                  |                     | IN                  | OUT   | CPL   |
| 5.0                | 1.31                      | 16.87            | 17.05               | 15.63               | 17.21 | 13.09 |
| 6.0                | 1.26                      | 16.72            | 17.48               | 16.22               | 18.02 | 13.66 |
| 7.0                | 1.22                      | 16.67            | 17.77               | 16.69               | 18.61 | 14.10 |
| 8.0                | 1.19                      | 16.60            | 18.07               | 17.04               | 19.14 | 14.46 |
| 9.0                | 1.17                      | 16.55            | 18.20               | 17.38               | 19.53 | 14.73 |
| 10.0               | 1.15                      | 16.51            | 18.49               | 17.61               | 19.89 | 14.97 |
| 50.0               | 1.08                      | 16.26            | 20.61               | 19.12               | 22.11 | 16.37 |
| 100.0              | 1.09                      | 16.26            | 21.09               | 19.31               | 22.34 | 16.49 |
| 200.0              | 1.09                      | 16.28            | 21.34               | 19.77               | 22.60 | 16.81 |
| 300.0              | 1.09                      | 16.33            | 21.68               | 20.56               | 23.42 | 17.19 |
| 400.0              | 1.09                      | 16.37            | 22.29               | 21.43               | 24.15 | 17.96 |
| 500.0              | 1.08                      | 16.41            | 23.08               | 22.62               | 25.13 | 19.03 |
| 600.0              | 1.08                      | 16.45            | 24.26               | 24.06               | 26.44 | 20.11 |
| 700.0              | 1.09                      | 16.50            | 25.43               | 25.90               | 27.48 | 21.49 |
| 800.0              | 1.10                      | 16.56            | 26.89               | 28.13               | 28.97 | 22.73 |
| 900.0              | 1.11                      | 16.62            | 28.23               | 31.20               | 31.07 | 24.03 |
| 1000.0             | 1.13                      | 16.67            | 29.36               | 34.94               | 33.95 | 25.16 |
| 1100.0             | 1.15                      | 16.71            | 29.63               | 36.33               | 38.94 | 26.22 |
| 1300.0             | 1.20                      | 16.75            | 27.06               | 29.63               | 35.05 | 26.49 |
| 1500.0             | 1.27                      | 16.74            | 23.38               | 25.05               | 28.04 | 26.12 |
| 1700.0             | 1.35                      | 16.68            | 20.17               | 23.10               | 24.87 | 26.23 |
| 1900.0             | 1.43                      | 16.58            | 17.53               | 23.31               | 23.91 | 26.32 |
| 2000.0             | 1.47                      | 16.51            | 16.53               | 24.59               | 24.08 | 26.53 |



# Directional Coupler

TCD-ED13989/1

## Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)




IF/RF MICROWAVE COMPONENTS




REV. X1  
TCD-ED13989/1  
1/24/2014  
Page 1 of 1

## Outline Dimensions

DB1627



## PCB Land Pattern



| CASE # | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| DB1627 | .160<br>(4.06) | .150<br>(3.81) | .160<br>(4.06) | .050<br>(1.27) | .040<br>(1.02) | .025<br>(0.64) | .028<br>(0.71) | .065<br>(1.65) | .190<br>(4.83) | .030<br>(0.76) | .15      |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



# Tape & Reel Packaging TR-F47

## DEVICE ORIENTATION IN T&R



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel<br>see note |
|-------------------|----------------------------|----------------------|------------------------------|
| 12                | 8                          | 13                   | 1000, 2000                   |
|                   |                            | 7                    | 20, 50, 100, 200, 500        |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

| REV | ECN No. | DESCRIPTION     | DATE     | DR | AUTH |
|-----|---------|-----------------|----------|----|------|
| OR  | M73159  | NEW RELEASE     | 08/00    | IL | DB   |
| A   | M82377  | UPDATED DRAWING | 07/30/02 | AV | LC   |
| B   | M102713 | UPDATED NOTES   | 01/12/06 | GF | IL   |
|     |         |                 |          |    |      |

[illegible]

NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030"  $\pm$  0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.



UNLESS OTHERWISE SPECIFIED

INITIALS

DATE \_\_\_\_\_

**DIMENSIONS ARE IN INCHES**

DRAWN

---

IL

08/03/00

**TOLERANCES ON:**

**CHECKED**

08/08/00

2 PL DECIMALS ±  
3 PL DECIMALS ±

|          |
|----------|
| CHECKED  |
| APPROVED |

00 / 00 / 00

3 PL DECIMAL  
ANGLES  $\pm$   
FRACTIONS  $\pm$

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.



# Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, mm, 75, DB714, TCD, TB-72

## SIZE

| CODE | IDENT |
|------|-------|
|------|-------|

DRAWING NO:

98-PL-010

|      |  |
|------|--|
| REV: |  |
|------|--|

B


FILE: 98PL010

SCALE: 10:1


|  |               |
|--|---------------|
|  | <b>SHEET:</b> |
|--|---------------|

1 OF 1

# Evaluation Board and Circuit



TB-72



Schematic Diagram

## Notes:

1. 75 Ohm BNC Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |