



Mini-Circuits

SURFACE MOUNT




RF Transformer

TCM1.5-63WX+

50/75Ω 200 to 6000 MHz

KEY FEATURES

- Ultra-wide bandwidth 200 – 6000 MHz
- One model covers all telecommunication bands
- Aqueous washable
- Protected by US Patent 9,071,229B1




Generic photo used for illustration purposes only

APPLICATIONS

- Differential modulator/demodulator and active mixers
- Wideband push-pull amplifiers
- LTE, Cellular, PCS, UMTS, Wi-Fi, WiMAX

CONFIGURATION G



PRODUCT OVERVIEW

Mini-Circuits' TCM1.5-63WX+ is a surface-mount, transmission line, core and wire transformer covering a very wide frequency range, specified from 200 to 6000 MHz and usable from 100 to 6000 MHz. The transformer provides a 1:1.5 impedance ratio with low insertion loss, excellent flatness, as well as low phase and amplitude unbalance. Featuring core and wire construction on a 6-lead plastic base with tin over nickel termination finish. The unit measures 0.16" x 0.15" x 0.16" accommodating dense circuit board layouts. It also incorporates the Mini-Circuits' Top Hat® feature for faster, more accurate pick-and-place assembly and easy visual inspection.

ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Impedance Ratio		1.5			
Frequency Range		200		6000	MHz
Insertion Loss (Avg.)	200 – 4300	—	1	1.5	dB
	4300 – 6000	—	2	2.6	
Amplitude Unbalance	200 – 4300	—	1.2	—	dB
	4300 – 6000	—	0.6	—	
Phase Unbalance	200 – 4300	—	8	—	Degree
	4300 – 6000	—	4	—	
Primary Return Loss (Input)	200 – 4300	—	15	—	dB
	4300 – 6000	—	12	—	

1. Performance is specified with shunt capacitor of 0.1pF suggested value of 0402 size between Pri Dot (Pin 3) and Pri (Pin2, GND)

ABSOLUTE MAXIMUM RATINGS²

Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Input Power	0.2 W

2. Permanent damage may occur if any of these limits are exceeded.

REV. A
ECO-025232
TCM1.5-63WX+
URJ
250426





Mini-Circuits

SURFACE MOUNT







RF Transformer

TCM1.5-63WX+

50/75Ω 200 to 6000 MHz

TYPICAL PERFORMANCE GRAPHS





Mini-Circuits

SURFACE MOUNT 

RF Transformer

TCM1.5-63WX+

50/75Ω 200 to 6000 MHz

CONFIGURATION G





Figure 1. TCM1.5-63WX+ Configuration

PAD DESCRIPTION

Function	Pad Number	Description
Primary Dot	3	Connects to RF - IN
Primary	1,2	Connects to GND
Secondary Dot	5	Out 1
Secondary	4	Out 2
Not Connected (NC)	6	Not Used

SUGGESTED PCB LAYOUT (PL-819)




NOTES:


- TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020±.0015 COPPER: 1/2 Oz ON EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-717-1+.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
-  DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK.

Figure 2. Suggested PCB Layout PL-819

CASE STYLE DRAWING



PCB Land Pattern

SUGGESTED LAYOUT
TOLERANCE TO BE WITHIN ±.002

OUTLINE DIMENSIONS (Inch mm)

A	B	C	D	E	F
.160	.150	.160	.050	.040	.025
4.06	3.81	4.06	1.27	1.02	0.64
G	H	J	K	wt	
.028	.065	.190	.030	grams	
0.71	1.65	4.83	0.76	0.15	

PRODUCT MARKING*: BH

*Marking may contain other features or characters for internal lot control.



Mini-Circuits

SURFACE MOUNT

top hat



RF Transformer

TCM1.5-63WX+

50/75Ω 200 to 6000 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	DB1627 Lead Finish: Pure Tin
RoHS Status	Compliant
Tape and Reel	F47
Suggested Layout for PCB Design	PL-819
Evaluation Board	TB-TCM1.5-63WX+ Gerber File
Environmental Rating	ENV02T1

NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html







RF Transformer

TCM1.5-63WX+


Typical Performance Data

FREQUENCY (MHz)	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
10.00	5.13	16.34	5.36	109.18
50.00	1.07	15.35	0.96	150.74
100.00	0.57	14.99	0.82	165.34
150.00	0.57	15.11	0.93	171.24
200.00	0.58	15.20	0.98	173.31
300.00	0.56	15.21	0.99	175.49
400.00	0.53	15.19	0.99	176.87
500.00	0.50	15.33	0.98	177.97
600.00	0.49	15.57	0.90	178.96
700.00	0.49	15.91	0.83	179.76
800.00	0.48	16.44	0.73	179.60
900.00	0.47	17.12	0.65	179.07
1000.00	0.46	17.89	0.57	178.66
1250.00	0.47	20.34	0.40	177.92
1500.00	0.51	22.24	0.26	177.21
1750.00	0.57	20.93	0.09	176.42
2000.00	0.67	18.15	0.15	175.96
2250.00	0.77	16.16	0.35	176.15
2500.00	0.86	15.16	0.46	176.52
2750.00	0.91	14.89	0.53	176.77
3000.00	0.95	15.01	0.62	176.89
3250.00	0.99	15.46	0.70	177.35
3500.00	1.05	16.01	0.71	178.32
3750.00	1.10	16.82	0.64	179.37
4000.00	1.15	17.92	0.57	179.74
4250.00	1.18	19.10	0.51	178.70
4500.00	1.23	19.78	0.42	177.34
4750.00	1.32	19.23	0.28	175.89
5000.00	1.45	17.51	0.12	174.68
5250.00	1.58	15.70	0.01	174.01
5500.00	1.69	14.41	0.07	173.26
5750.00	1.79	13.87	0.20	172.64
6000.00	1.86	13.89	0.34	172.53
6250.00	1.92	14.22	0.45	173.53
6500.00	2.02	14.61	0.53	175.05
6750.00	2.07	14.79	0.65	176.81
7000.00	2.18	14.30	0.73	178.49


Typical Performance Data



Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
DB1627	.160 (4.06)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (0.64)	.028 (0.71)	.065 (1.65)	.190 (4.83)	.030 (0.76)	.15


Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION		REVISIONS					
		REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
		OR	ECO-025101	NEW RELEASE	APR 25	DDR	VC

SUGGESTED MOUNTING CONFIGURATION
FOR DB1627 CASE STYLE



COMPONENT	SIZE
C1	0402

NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020±.0015
COPPER: 1/2 Oz ON EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER
TO TB-717-1+.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).


 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK.

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235							
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±		DRAWN	DDR	03 APR 25									
		CHECKED	VP	03 APR 25									
		APPROVED	ASJ	03 APR 25									
						PL, DB1627, TB-717-1+							
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.													
		ASHEETA1.DWG REV:A		DATE:01/12/95		SIZE A		CODE IDENT 15542		DRAWING NO: 98-PL-819		REV: OR	
						FILE: 98-PL-819		SCALE: 11:1		SHEET: 1 OF 1			


Evaluation Board and Circuit

TB-TCM1.5-63WX+

Refer data sheet of the model for pin connections



Schematic diagram



Notes:

1. PCB Material: ROGERS (R04350B) OR Equivalent, Dielectric Constant=3.48
Thickness=.020±.0015 inch
2. 50 Ohm SMA Female Connectors.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215