



Mini-Circuits®

SURFACE MOUNT 

RF Transformer

TCM2-33X-3+

50Ω

30 to 3000 MHz

FEATURES

- Wide Bandwidth 30 to 3000 MHz
- Balanced Transmission Line
- Excellent Return Loss
- Aqueous Washable
- Protected by US Patent 8,576,037

*Generic photo used for illustration purposes only*

CASE STYLE: DB1627

APPLICATIONS

- PCS
- Wideband Push-Pull Amplifiers
- Cellular

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Impedance Ratio (Secondary/Primary)		2			
Frequency Range		30		3000	MHz
Insertion Loss ¹	30-3000		1.5	3.0	dB
Amplitude Unbalance	30-3000		0.5		dB
Phase Unbalance	30-3000		4		Degree


1. Insertion Loss is referenced to mid-band loss, 0.8 dB typ.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
RF Power	0.4 W
DC Current	30 mA

Permanent damage may occur if any of these limits are exceeded.

CONFIGURATION N



REV. B
ECO-013842
TCM2-33X-3+
MCL NY
251120





50Ω

30 to 3000 MHz

PRIMARY DOT	6
PRIMARY	2
SECONDARY DOT	4
SECONDARY	3
GND	2,5
NOT USED	1

[illegible]

- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

The diagram illustrates the PCB Land Pattern for a component. It includes three views: a top view, a side view, and a cross-sectional view.

- Top View:** Shows a central rectangular area labeled "COMPONENT AREA". The overall dimensions are A (height) and B (width). The component area dimensions are C (width) and D (height). The component area is divided into six numbered regions (1-6) around a central "Y" shaped feature. A "MODEL MARKING (ORIENTATION)" is shown as a dot on the top hat. The "ORIENTATION DOT ON TOP HAT" is also indicated. The "TOP-HAT / PICK & PLACE SURFACE AREA (.10X.10) MIN" is specified. The "TOP-HAT TOTAL THICKNESS: .013 inches MAX." is also noted. The "G TYP" dimension is shown for the top hat area.
- Side View:** Shows the component area with a dashed line indicating the internal structure. The dimension C MAX is shown for the width of the component area.
- Cross-sectional View:** Shows the component area with a dashed line indicating the internal structure. The dimension E TYP is shown for the thickness of the component area. The dimension F TYP is shown for the width of the component area.

PCB Land Pattern

OUTLINE DIMENSIONS (Inches) mm

A	B	C	D	E	F
.160	.150	.160	.050	.040	.025
4.06	3.81	4.06	1.27	1.02	0.64
G	H	J	K		wt
.028	.065	.190	.030		grams
0.71	1.65	4.83	0.76		0.15

TAPE & REEL INFORMATION: F47



Mini-Circuits

SURFACE MOUNT 

RF Transformer




TCM2-33X-3+

50Ω

30 to 3000 MHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Amplitude Unbalance (dB)	Phase Unbalance (deg)
30	1.27	27.41	0.04	0.10
50	1.26	27.54	0.03	0.16
200	1.29	25.23	0.08	0.68
500	1.29	21.59	0.21	0.86
1000	1.35	19.44	0.17	0.96
1600	1.52	18.86	0.41	2.96
2000	1.67	18.55	0.68	3.79
2500	1.91	18.11	0.97	4.02
2800	2.02	18.61	1.07	4.52
3000	2.10	19.46	1.10	5.38



- NOTES
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



RF Transformer

TCM2-33X-3+

Typical Performance Data

FREQUENCY (MHz)	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
30.0	1.27	27.41	0.04	0.10
50.0	1.26	27.54	0.03	0.16
70.0	1.27	27.28	0.03	0.23
90.0	1.27	27.01	0.04	0.32
200.0	1.29	25.23	0.08	0.68
300.0	1.29	23.71	0.13	0.83
400.0	1.30	22.39	0.18	0.89
500.0	1.29	21.59	0.21	0.86
600.0	1.30	20.98	0.22	0.83
700.0	1.30	20.48	0.24	0.78
800.0	1.32	20.01	0.23	0.76
900.0	1.33	19.70	0.20	0.82
1000.0	1.35	19.44	0.17	0.96
1200.0	1.40	19.03	0.14	1.53
1400.0	1.45	18.87	0.25	2.30
1600.0	1.52	18.86	0.41	2.96
1800.0	1.59	18.77	0.56	3.40
2000.0	1.67	18.55	0.68	3.79
2200.0	1.77	18.31	0.77	3.76
2400.0	1.86	18.08	0.91	3.84
2500.0	1.91	18.11	0.97	4.02
2600.0	1.95	18.13	1.02	4.24
2700.0	1.99	18.28	1.05	4.32
2800.0	2.02	18.61	1.07	4.52
2900.0	2.06	18.99	1.08	4.87
3000.0	2.10	19.46	1.10	5.38



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS


REV. OR
TCM2-33X-3+
4/7/2016
Page 1 of 1

Typical Performance Data


Average Insertion Loss




Input Return Loss



Amplitude Unbalance




Phase Unbalance




Outline Dimensions

DB1627



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
DB1627	.160 (4.06)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (0.64)	.028 (0.71)	.065 (1.65)	.190 (4.83)	.030 (0.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION




REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M136032	NEW RELEASE	03/07/12	GF	DJ
A	M141464	ADDED PIN CODE "06TK04"	05/06/13	IL	DJ

SUGGESTED MOUNTING CONFIGURATION

FOR DB1627 CASE STYLE, "06TN01" & "06TK04" PIN CODES



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" $\pm$.0015"; COPPER: 1/2 OZ. ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

GF

02/17/12

CHECKED

IL

03/07/12

APPROVED

DJ

03/07/12

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 06TN01/06TK04, DB1627, TB-654+

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-364

REV:

A

FILE: 98PL364

SCALE:



8:1

SHEET:

1 OF 1

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215