

# Engineering Development Model

## RF Transformer

## TCM3-ED14833/2A

Impedance Ratio : 3

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.




Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DB1627

| ELECTRICAL SPECIFICATIONS 50Ω @ +25°C |                    |      |      |      |       |
|---------------------------------------|--------------------|------|------|------|-------|
| Parameter                             |                    | Min. | Typ. | Max. | Units |
| Frequency                             |                    | 20   |      | 4500 | MHz   |
| Insertion Loss                        | 3 dB Bandwidth     |      | 1.5  |      | MHz   |
|                                       | 2 dB Bandwidth     |      | --   |      | MHz   |
|                                       | 1 dB Bandwidth     |      | --   |      | MHz   |
| Amplitude Unbalance                   | Over 3dB Bandwidth |      | 0.5  |      | dB    |
|                                       | Over 2dB Bandwidth |      | --   |      | dB    |
|                                       | Over 1dB Bandwidth |      | --   |      | dB    |
| Phase Unbalance                       | Over 3dB Bandwidth |      | 4.0  |      | deg.  |
|                                       | Over 2dB Bandwidth |      | --   |      | deg.  |
|                                       | Over 1dB Bandwidth |      | --   |      | deg.  |

| MAXIMUM RATINGS       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Power              | 0.4W           |
| DC Current            | 30mA           |



| PIN CONNECTIONS |     |
|-----------------|-----|
| PRIMARY DOT     | 3   |
| PRIMARY         | 2   |
| SECONDARY DOT   | 4   |
| SECONDARY       | 6   |
| GND             | 2,5 |
| NOT USED        | 1   |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)




REV. X1  
TCM3-ED14833/2A  
4/25/2013  
Page 1 of 1

## Typical Performance Data


| FREQUENCY<br>(MHz) | AVERAGE<br>INSERTION LOSS<br>(dB) | INPUT<br>RETURN LOSS<br>(dB) | AMPLITUDE<br>UNBALANCE<br>(dB) | PHASE<br>UNBALANCE<br>(deg.) |
|--------------------|-----------------------------------|------------------------------|--------------------------------|------------------------------|
| 5.0                | 1.84                              | 10.04                        | 0.01                           | 0.06                         |
| 10.0               | 1.58                              | 11.11                        | 0.01                           | 0.07                         |
| 30.0               | 1.46                              | 11.72                        | 0.01                           | 0.27                         |
| 50.0               | 1.45                              | 11.79                        | 0.02                           | 0.43                         |
| 70.0               | 1.45                              | 11.89                        | 0.02                           | 0.59                         |
| 90.0               | 1.44                              | 11.95                        | 0.02                           | 0.73                         |
| 100.0              | 1.44                              | 11.98                        | 0.02                           | 0.78                         |
| 200.0              | 1.44                              | 12.13                        | 0.01                           | 1.44                         |
| 300.0              | 1.43                              | 12.26                        | 0.02                           | 2.15                         |
| 400.0              | 1.41                              | 12.40                        | 0.03                           | 2.77                         |
| 500.0              | 1.39                              | 12.51                        | 0.03                           | 3.37                         |
| 600.0              | 1.37                              | 12.56                        | 0.03                           | 3.93                         |
| 700.0              | 1.36                              | 12.59                        | 0.05                           | 4.46                         |
| 800.0              | 1.34                              | 12.60                        | 0.06                           | 4.97                         |
| 900.0              | 1.33                              | 12.60                        | 0.08                           | 5.44                         |
| 1000.0             | 1.32                              | 12.58                        | 0.09                           | 5.92                         |
| 1100.0             | 1.31                              | 12.51                        | 0.11                           | 6.34                         |
| 1200.0             | 1.31                              | 12.47                        | 0.13                           | 6.74                         |
| 1300.0             | 1.31                              | 12.43                        | 0.14                           | 7.15                         |
| 1400.0             | 1.31                              | 12.40                        | 0.14                           | 7.55                         |
| 1500.0             | 1.31                              | 12.44                        | 0.14                           | 7.91                         |
| 1600.0             | 1.30                              | 12.50                        | 0.13                           | 8.26                         |
| 1700.0             | 1.30                              | 12.61                        | 0.14                           | 8.57                         |
| 1800.0             | 1.30                              | 12.77                        | 0.15                           | 8.87                         |
| 1900.0             | 1.30                              | 12.98                        | 0.16                           | 9.05                         |
| 2000.0             | 1.30                              | 13.27                        | 0.17                           | 9.03                         |
| 2100.0             | 1.30                              | 13.64                        | 0.18                           | 8.90                         |
| 2200.0             | 1.29                              | 14.06                        | 0.18                           | 8.77                         |
| 2300.0             | 1.29                              | 14.56                        | 0.19                           | 8.66                         |
| 2400.0             | 1.29                              | 15.09                        | 0.19                           | 8.68                         |
| 2500.0             | 1.30                              | 15.62                        | 0.18                           | 8.53                         |
| 2600.0             | 1.30                              | 16.17                        | 0.18                           | 8.42                         |
| 2700.0             | 1.31                              | 16.68                        | 0.18                           | 8.31                         |
| 2800.0             | 1.31                              | 17.12                        | 0.18                           | 8.35                         |
| 2900.0             | 1.31                              | 17.45                        | 0.19                           | 8.31                         |
| 3000.0             | 1.32                              | 17.66                        | 0.21                           | 8.24                         |
| 3100.0             | 1.33                              | 17.81                        | 0.23                           | 8.13                         |
| 3200.0             | 1.34                              | 17.97                        | 0.27                           | 7.81                         |
| 3300.0             | 1.35                              | 18.04                        | 0.34                           | 7.43                         |
| 3400.0             | 1.36                              | 18.10                        | 0.41                           | 7.00                         |
| 3500.0             | 1.38                              | 17.99                        | 0.46                           | 6.49                         |
| 3600.0             | 1.41                              | 17.75                        | 0.50                           | 5.86                         |
| 3700.0             | 1.45                              | 17.55                        | 0.55                           | 5.18                         |
| 3800.0             | 1.49                              | 17.39                        | 0.58                           | 4.48                         |
| 3900.0             | 1.52                              | 17.46                        | 0.63                           | 4.02                         |
| 4000.0             | 1.56                              | 17.66                        | 0.67                           | 3.78                         |
| 4100.0             | 1.59                              | 17.87                        | 0.71                           | 3.72                         |
| 4200.0             | 1.62                              | 18.08                        | 0.72                           | 3.76                         |
| 4300.0             | 1.64                              | 18.23                        | 0.71                           | 3.91                         |
| 4400.0             | 1.66                              | 18.55                        | 0.74                           | 4.03                         |
| 4500.0             | 1.67                              | 18.98                        | 0.76                           | 4.17                         |
| 4600.0             | 1.69                              | 19.60                        | 0.79                           | 4.26                         |
| 4700.0             | 1.72                              | 20.15                        | 0.82                           | 4.38                         |
| 4800.0             | 1.75                              | 20.70                        | 0.84                           | 4.48                         |
| 4900.0             | 1.78                              | 21.24                        | 0.81                           | 4.57                         |
| 5000.0             | 1.81                              | 21.54                        | 0.77                           | 4.64                         |
| 5100.0             | 1.86                              | 21.95                        | 0.72                           | 4.67                         |
| 5200.0             | 1.91                              | 22.10                        | 0.67                           | 4.76                         |
| 5300.0             | 1.97                              | 22.46                        | 0.63                           | 5.08                         |
| 5400.0             | 2.03                              | 22.80                        | 0.58                           | 5.55                         |
| 5500.0             | 2.09                              | 22.97                        | 0.54                           | 6.07                         |
| 5600.0             | 2.16                              | 23.49                        | 0.49                           | 6.71                         |
| 5700.0             | 2.23                              | 22.81                        | 0.46                           | 7.30                         |
| 5800.0             | 2.31                              | 21.44                        | 0.44                           | 7.77                         |
| 5900.0             | 2.41                              | 19.77                        | 0.41                           | 8.35                         |
| 6000.0             | 2.51                              | 18.04                        | 0.41                           | 9.05                         |

## Typical Performance Data


Average Insertion Loss




Input Return Loss



Amplitude Unbalance




Phase Unbalance




## Outline Dimensions

DB1627



## PCB Land Pattern



| CASE # | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| DB1627 | .160<br>(4.06) | .150<br>(3.81) | .160<br>(4.06) | .050<br>(1.27) | .040<br>(1.02) | .025<br>(0.64) | .028<br>(0.71) | .065<br>(1.65) | .190<br>(4.83) | .030<br>(0.76) | .15      |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F47

## DEVICE ORIENTATION IN T&R



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel<br>see note |
|-------------------|----------------------------|----------------------|------------------------------|
| 12                | 8                          | 13                   | 1000, 2000                   |
|                   |                            | 7                    | 20, 50, 100, 200, 500        |


Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661  
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010  
Mini-Circuits ISO 9001 & ISO 14001 Certified




| REVISIONS |         |             |          |    |      |
|-----------|---------|-------------|----------|----|------|
| REV       | ECN No. | DESCRIPTION | DATE     | DR | AUTH |
| OR        | M138571 | NEW RELEASE | 10/02/12 | GF | DJ   |
|           |         |             |          |    |      |
|           |         |             |          |    |      |

SUGGESTED MOUNTING CONFIGURATION FOR  
DB1627 CASE STYLE, "06TH02" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020"  $\pm$  0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. 0402 SIZE CHIP COMPONENT FOOTPRINT IS SHOWN FOR REFERENCE. FOR COMPONENT VALUE REFER TO TB-697+.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)


 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED                                                                                                       | INITIALS |    | DATE     |
|----------------------------------------------------------------------------------------------------------------------------------|----------|----|----------|
| DIMENSIONS ARE IN INCHES<br>TOLERANCES ON:<br>2 PL DECIMALS $\pm$<br>3 PL DECIMALS $\pm$ .005<br>ANGLES $\pm$<br>FRACTIONS $\pm$ | DRAWN    | GF | 09/28/12 |
|                                                                                                                                  | CHECKED  | IL | 10/02/12 |
|                                                                                                                                  | APPROVED | DJ | 10/02/12 |

 **Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235


PL, 06TH02, DB1627, TB-697+

|                  |                     |                          |            |
|------------------|---------------------|--------------------------|------------|
| SIZE<br>A        | CODE IDENT<br>15542 | DRAWING NO:<br>98-PL-381 | REV:<br>OR |
| FILE:<br>98PL381 | SCALE:<br>10:1      | SHEET:<br>1 OF 1         |            |

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit



## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |