Engineering Development Model

RF Transformer

TCM4-ED8169/1

Impedance Ratio: 4

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : DB714

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Тур.	Max.	Units
Frequency		0.3		350	MHz
Insertion Loss *	3 dB Bandwidth		0.3 - 350		MHz
	2 dB Bandwidth		0.3 - 350		MHz
	1 dB Bandwidth		0.3 - 250		MHz
Ampitude Unbalance	over 3dB Bandwidth		0.5		dB
	over 1dB Bandwidth		0.1		dB
Phase Unbalance	over 3dB Bandwidth		5.0		deg.
	over 1dB Bandwidth		1.00		deg.

Note:

* Insertion Loss is referenced to mid-band loss, 0.3dB typ.

MAXIMUM RATINGS			
Operating Temperature -20°C to 85°C			
Storage Temperature	-55°C to 100°C		
RF Power	0.25 W		
DC Current	30 mA		

PIN CONNECTIONS		
PRIMARY DOT	6	
PRIMARY	4	
SECONDARY DOT	1	
SECONDARY	3	
SECONDARY CT	2	
ISOLATE	5	

Configuration : A





INTERNET http://www.minicircuits.com P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010 Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. X1 TCM4-ED8169/1 060808 Page 1 of 1

RF Transformer

Typical Performance Data

FREQUENCY	INSERTION	
(MHz)	(dB)	(dB)
0.30	0.61	14.29
0.40	0.55	16.52
0.50	0.52	18.15
0.60	0.51	19.40
0.70	0.50	20.41
0.80	0.49	21.25
1.00	0.47	22.61
2.00	0.42	26.10
3.00	0.38	27.98
4.00	0.35	29.42
5.00	0.33	30.63
7.00	0.31	32.54
9.00	0.30	34.09
10.00	0.30	34.74
30.00	0.31	42.97
50.00	0.35	44.29
70.00	0.38	38.52
90.00	0.41	33.57
100.00	0.42	31.95
150.00	0.53	25.83
200.00	0.63	20.71
250.00	0.66	16.66
300.00	0.95	14.01
350.00	0.98	11.36



INTERNET http://www.minicircuits.com REV. X1 INTERNET http://www.minicircuits.com TCM4-ED8169/1 Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010 Mini-Circuits ISO 9001 & ISO 14001 Certified

RF Transformer

TCM4-ED8169/1

Typical Performance Curves







INTERNET http://www.minicircuits.com REV. X1 INTERNET http://www.minicircuits.com P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 TCM4-ED8169/1 060803 Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010 Mini-Circuits ISO 9001 & ISO 14001 Certified

Page 2 of 2

Case Style

Outline Dimensions

PCB Land Pattern



CASE #	А	В	С	D	Е	F	G	Н	J	K	WT. GRAM
DD714	.160	.150	.160	.050	.040	.025	.028	.065	.190	.030	15
DD/14	(4.06)	(3.81)	(4.06)	(1.27)	(1.02)	(0.64)	(0.71)	(1.65)	(4.83)	(0.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. <u>+</u>.01; 3Pl. <u>+</u>.005

Notes:

- 1. Case material: Plastic.
- Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix. For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- 3. Lead #1 identifier shall be located in the cross-hatched area shown. Identifier may be either a molded or marked feature.





P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

98-DB Rev.: S (09/10/18) M169593 File: 98-DB.docx This document and its contents are the property of Mini-Circuits.

DB

DB714

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



98-TR-F47 Rev.: D (01/03/12) M134880 File: 98-TR-F47.doc This document and its contents are the property of Mini-Circuits.

Mini-Circuits

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

ENV02 Rev: A 02/25/11 M130240 File: ENV02.pdf

This document and its contents are the property of Mini-Circuits.