

# RF Transformer

50Ω      1600 to 2600 MHz

## Maximum Ratings

|                              |                |
|------------------------------|----------------|
| <u>Operating Temperature</u> | -55°C to 100°C |
|------------------------------|----------------|

|                            |                |
|----------------------------|----------------|
| <u>Storage Temperature</u> | -55°C to 100°C |
|----------------------------|----------------|

---

|                  |    |
|------------------|----|
| Input RF Power** | 5W |
|------------------|----|

\*\* Derate linearly to 2.5W at 100°C

Permanent damage may occur if any of these limits are exceeded.

## Pin Connections

|             |   |
|-------------|---|
| PRIMARY DOT | 4 |
|-------------|---|


|         |     |
|---------|-----|
| PRIMARY | 2,5 |
|---------|-----|

SECONDARY DOT 6

SECONDARY 1

NOT USED 3

## Outline Drawing




### Outline Dimensions (inch)

| A    | B    | C    | D    | E    | F    |
|------|------|------|------|------|------|
| .126 | .063 | .035 | .024 | .022 | .011 |
| 3.20 | 1.60 | 0.89 | 0.61 | 0.56 | 0.28 |

| G    | H    | J    | K    | wt    |
|------|------|------|------|-------|
| .039 | .024 | .042 | .123 | grams |
| 0.99 | 0.61 | 1.07 | 3.12 | .020  |

**Demo Board MCL P/N: TB-287**  
**Suggested PCB Layout (PL-163)**



## Notes

- A.** Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
**B.** Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
**C.** The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

## Features

- wideband, 1600 to 2600 MHz
- miniature size, 0.12"x.06"x.037"
- LTCC construction
- low cost
- aqueous washable

## Applications

- PCS
- DECT
- ISM
- WIFI
- BLUE TOOTH
- PHS

## Electrical Specifications





| $\Omega$<br>RATIO<br>(Secondary/Primary) | FREQUENCY<br>(MHz) | INSERTION*<br>LOSS<br>(dB) | PHASE<br>UNBALANCE <sup>†</sup><br>(Deg.)<br>Typ. | AMPLITUDE<br>UNBALANCE<br>(dB)<br>Typ. |
|------------------------------------------|--------------------|----------------------------|---------------------------------------------------|----------------------------------------|
| 2                                        | 1600-1800          | 0.5                        | 2.0                                               | 0.8                                    |
|                                          | 1800-2000          | 0.5                        | 3.0                                               | 0.5                                    |
|                                          | 2000-2600          | 1.0                        | 6.0                                               | 0.6                                    |

\* Insertion Loss is referenced to mid-band loss, 0.5 dB

<sup>†</sup> Relative to 180°

## Typical Performance Data





| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | INPUT<br>R. LOSS<br>(dB) | AMPLITUDE<br>UNBALANCE<br>(dB) | PHASE<br>UNBALANCE<br>(Deg.) |
|--------------------|---------------------------|--------------------------|--------------------------------|------------------------------|
| 1600.00            | 0.52                      | 23.40                    | 1.11                           | 0.94                         |
| 1700.00            | 0.53                      | 24.36                    | 0.94                           | 0.67                         |
| 1800.00            | 0.54                      | 23.96                    | 0.80                           | 0.76                         |
| 1900.00            | 0.56                      | 22.36                    | 0.69                           | 1.14                         |
| 2000.00            | 0.59                      | 20.40                    | 0.60                           | 1.71                         |
| 2100.00            | 0.63                      | 18.44                    | 0.57                           | 2.56                         |
| 2200.00            | 0.69                      | 16.59                    | 0.56                           | 3.63                         |
| 2300.00            | 0.76                      | 14.88                    | 0.60                           | 4.68                         |
| 2400.00            | 0.85                      | 13.34                    | 0.69                           | 5.82                         |
| 2600.00            | 1.09                      | 10.72                    | 0.93                           | 7.92                         |




## Typical Performance Data

| FREQUENCY<br>(MHz) | AVERAGE<br>INSERTION<br>LOSS<br>(dB) | INPUT<br>RETURN<br>LOSS<br>(dB) | AMPLITUDE<br>UNBALANCE<br>(dB) | PHASE<br>UNBALANCE<br>(deg) |
|--------------------|--------------------------------------|---------------------------------|--------------------------------|-----------------------------|
| 1600               | 0.52                                 | 23.40                           | 1.11                           | 0.94                        |
| 1700               | 0.53                                 | 24.36                           | 0.94                           | 0.67                        |
| 1800               | 0.54                                 | 23.96                           | 0.80                           | 0.76                        |
| 1900               | 0.56                                 | 22.36                           | 0.69                           | 1.14                        |
| 2000               | 0.59                                 | 20.40                           | 0.60                           | 1.71                        |
| 2100               | 0.63                                 | 18.44                           | 0.57                           | 2.56                        |
| 2200               | 0.69                                 | 16.59                           | 0.56                           | 3.63                        |
| 2300               | 0.76                                 | 14.88                           | 0.60                           | 4.68                        |
| 2400               | 0.85                                 | 13.34                           | 0.69                           | 5.82                        |
| 2600               | 1.09                                 | 10.72                           | 0.93                           | 7.92                        |


## Typical Performance Curves



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE #   | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L  | M  | N  | P  | WT. GRAM |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----|----|----|----|----------|
| FV1206-1 | .126<br>(3.20) | .063<br>(1.60) | .035<br>(0.89) | .024<br>(0.61) | .022<br>(0.56) | .011<br>(0.28) | .039<br>(0.99) | .024<br>(0.61) | .042<br>(1.07) | .123<br>(3.12) | -- | -- | -- | -- | .020     |

Dimensions are in inches (mm). Tolerances: 2 PL.  $\pm .01$ ; 3 PL.  $\pm .005$

#### Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**  
 For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

### Applicable Case Styles

FV1206-1  
FV1206-3

### Applicable Case Styles

FV1206-4  
FV1206-5  
FV1206-6  
FV1206-7  
FV1206-9

### Applicable Case Styles

FV1206-11  
FV1206-12  
GE0805C-18  
NL1008C-6  
NL1008C-7  
NL1008C-9  
NL1008C-10  
NL1008C-12

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers NORTH AMERICA** 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010  
Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION                  | DATE     | DR | AUTH |
|-----|---------|------------------------------|----------|----|------|
| OR  | M93213  | NEW RELEASE                  | 07/20/04 | GF | LR   |
| A   | M102713 | TCN WAS BCN-2, UPDATED NOTES | 01/12/06 | GF | IL   |
|     |         |                              |          |    |      |
|     |         |                              |          |    |      |


**SUGGESTED MOUNTING CONFIGURATION  
FOR FV1206-1 CASE STYLE, "px" PIN CONNECTION**

**NOTE:**

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS  $.020'' \pm .0015''$ . COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

GF

07/02/04

TOLERANCES ON:

CHECKED

AY


07/20/04

2 PL DECIMALS  $\pm$ 

APPROVED

LR

07/20/04

3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, px, FV1206-1, TCN, TB-287

SIZE

CODE IDENT

DRAWING NO:

REV:

A

15542

98-PL-163

A

FILE:

98PL163


SCALE:

10:1


SHEET:

1 OF 1

# Evaluation Board and Circuit



TB-287



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                           | Reference/Spec                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                | Individual Model Data Sheet                                                                          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                               | Individual Model Data Sheet                                                                          |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C                                                       | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability              | 10X Magnification                                                                   | J-STD-002, Para 4.2.5, Test S, 95% Coverage                                                          |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A                                                                 |