

Engineering Development Model

Power Splitter/Combiner

TCP-ED11815/2

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DB714

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		762		2150 MHz
Isolation	762 - 2150 MHz		17	dB
Insertion Loss Above 3.0 dB	762 - 2150 MHz		0.70	dB
Phase Unbalance	762 - 2150 MHz		1.033	deg.
Amplitude Unbalance	762 - 2150 MHz		0.198	dB
VSWR	SUM Port		1.80	(:1)
	OUT Ports		1.55	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	6, 5, 2
PORT 1	3
PORT 2	4
GND EXT	1

Functional Diagram



2 Way-0° Power Splitter/Combiner

TCP-ED11815/2

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
0.30	3.45	3.47	0.03	3.49	0.00	0.30	2.00	2.00	2.00
1.00	3.48	3.50	0.02	3.54	0.01	1.00	2.00	1.99	1.99
5.00	3.49	3.51	0.02	4.38	0.03	5.00	2.00	1.82	1.82
10.00	3.53	3.55	0.02	5.98	0.02	10.00	1.99	1.55	1.55
104.00	3.56	3.57	0.01	10.58	0.03	104.00	1.96	1.21	1.21
198.00	3.65	3.67	0.02	11.66	0.07	198.00	1.92	1.23	1.23
292.00	3.63	3.66	0.02	12.27	0.12	292.00	1.91	1.25	1.26
386.00	3.61	3.64	0.03	12.79	0.14	386.00	1.95	1.25	1.27
480.00	3.62	3.67	0.04	13.35	0.17	480.00	1.98	1.27	1.27
574.00	3.65	3.70	0.05	13.97	0.19	574.00	2.01	1.29	1.29
668.00	3.67	3.73	0.06	14.63	0.22	668.00	2.04	1.31	1.31
762.00	3.69	3.77	0.08	15.34	0.26	762.00	2.06	1.33	1.33
856.00	3.71	3.80	0.09	16.09	0.30	856.00	2.08	1.34	1.34
950.00	3.72	3.82	0.10	16.86	0.35	950.00	2.08	1.36	1.35
1012.50	3.72	3.83	0.11	17.36	0.38	1012.50	2.02	1.36	1.36
1075.00	3.71	3.82	0.12	17.81	0.44	1075.00	2.01	1.37	1.38
1135.00	3.69	3.82	0.13	18.17	0.49	1135.00	1.98	1.39	1.39
1195.00	3.68	3.81	0.13	18.47	0.56	1195.00	1.93	1.40	1.41
1255.00	3.67	3.81	0.15	18.65	0.62	1255.00	1.89	1.44	1.43
1315.00	3.66	3.81	0.15	18.73	0.70	1315.00	1.80	1.46	1.47
1375.00	3.66	3.83	0.17	18.73	0.79	1375.00	1.76	1.49	1.49
1454.17	3.68	3.86	0.18	18.65	0.91	1454.17	1.67	1.55	1.54
1533.33	3.71	3.91	0.19	18.53	1.05	1533.33	1.57	1.57	1.59
1612.50	3.76	3.97	0.21	18.42	1.20	1612.50	1.50	1.60	1.63
1691.67	3.81	4.04	0.23	18.33	1.37	1691.67	1.46	1.63	1.66
1770.83	3.85	4.10	0.25	18.26	1.55	1770.83	1.48	1.67	1.70
1850.00	3.87	4.14	0.28	18.19	1.69	1850.00	1.52	1.69	1.72
1925.00	3.86	4.16	0.30	18.07	1.85	1925.00	1.62	1.71	1.75
2000.00	3.82	4.15	0.34	17.87	1.98	2000.00	1.72	1.71	1.77
2075.00	3.75	4.12	0.37	17.58	2.03	2075.00	1.83	1.74	1.78
2150.00	3.68	4.06	0.38	17.20	2.13	2150.00	1.95	1.74	1.80
2192.00	3.63	4.03	0.40	16.93	2.15	2192.00	2.03	1.72	1.79
2234.00	3.60	4.00	0.40	16.67	2.25	2234.00	2.08	1.72	1.79
2276.00	3.56	3.96	0.40	16.39	2.25	2276.00	2.11	1.72	1.78
2318.00	3.52	3.93	0.41	16.07	2.33	2318.00	2.12	1.68	1.77
2360.00	3.49	3.89	0.40	15.80	2.41	2360.00	2.15	1.69	1.77
2402.00	3.47	3.88	0.40	15.53	2.49	2402.00	2.14	1.64	1.73
2444.00	3.44	3.84	0.40	15.26	2.67	2444.00	2.14	1.63	1.71
2486.00	3.43	3.82	0.39	15.06	2.74	2486.00	2.11	1.59	1.68
2528.00	3.41	3.81	0.40	14.86	2.92	2528.00	2.09	1.54	1.65
2570.00	3.39	3.78	0.38	14.71	3.14	2570.00	2.05	1.54	1.64

¹ Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2

TCP-ED11815/2

100707

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661







The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner

TCP-ED11815/2


Typical Performance Curves




REV. X2
TCP-ED11815/2
100707
Page 1 of 1

Outline Dimensions

DB714



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
DB714	.160 (4.06)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (0.64)	.028 (0.71)	.065 (1.65)	.190 (4.83)	.030 (0.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Lead #1 identifier shall be located in the cross-hatched area shown.
Identifier may be either a molded or marked feature.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215