

Surface Mount High Pass Filter

THP-1050+

50Ω 1050 to 4000 MHz

The Big Deal

- Small size (0.25" x 0.25" x 0.10")
- Good matching
- Low insertion loss



Generic photo used for illustration purposes only
CASE STYLE: GQ1018

Product Overview

THP-1050+ is a 50Ω high pass filter fabricated using SMT technology. This high pass filter covers from 1050-4000 MHz. This series of filters are constructed in a tiny package offering dual advantage of superior lumped element filter performance in a space saving SMT package. These models are suitable for mass production without losing flexibility of small volume requirements. It has repeatable performance across lots and consistent performance across temperature.

Key Features

Feature	Advantages
Low insertion loss	Can be used in high performance applications.
Good rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.
Small size, 0.25" x 0.25" x 0.10"	The small surface mount package enables the THP-1050+ to be used in compact designs.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

High Pass Filter

50Ω

1050 to 4000 MHz



THP-1050+

**Features**

- Low insertion loss
- Good matching
- Small size (0.25" x 0.25" x 0.10")

Applications

- Radio navigation satellite
- Space research

Functional Schematic**Typical Frequency Response****Electrical Specifications at 25°C**

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection Loss	DC-F1	DC-620	20	30	-
	VSWR	DC-F1	DC-620	-	20	:1
Pass Band	Insertion Loss	F2-F3	1050-4000	-	0.6	2.0
	VSWR	F2-F3	1050-4000	-	1.2	1.67





Generic photo used for illustration purposes only
CASE STYLE: GQ1018

Maximum Ratings	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5 W max.

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	60.15	434.30
620	30.10	51.10
710	15.63	23.81
770	8.31	10.19
810	4.75	5.30
840	2.97	3.40
915	1.02	1.66
1050	0.46	1.17
1150	0.37	1.16
1300	0.33	1.22
1550	0.31	1.30
1620	0.30	1.31
1830	0.29	1.31
2000	0.28	1.30
2220	0.26	1.27
2500	0.25	1.24
2860	0.23	1.19
3100	0.23	1.16
3600	0.22	1.10
4000	0.23	1.04

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Pad Connections

INPUT	8
OUTPUT	4
GROUND	1, 2, 3, 5, 6, 7



Demo Board MCL P/N: TB-680
Suggested PCB Layout (PL-372)

**NOTES:**

1. TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SODERMASK

Outline Drawing**Outline Dimensions (inch mm)**

A	B	C	D	E	F	G
.25	.25	.10	.125	.080	.045	.040
6.35	6.35	2.54	3.18	2.03	1.14	1.02
H	J	K	L	M		Wt.
.040	.145	.290	.065	.060		grams
1.02	3.68	7.37	1.65	1.52		.25

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



High Pass Filter

THP-1050+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40°C	@ +25°C	@ +85°C	@ -40°C	@ +25°C	@ +85°C	@ -40°C	@ +25°C	@ +85°C
	10	60.20	60.15	60.06	0.04	0.04	0.04	0.04	0.04
25	52.22	52.25	52.21	0.03	0.03	0.03	0.03	0.03	0.03
50	46.33	46.28	46.26	0.03	0.03	0.03	0.02	0.03	0.03
70	43.55	43.45	43.43	0.02	0.03	0.03	0.02	0.02	0.02
100	40.71	40.62	40.56	0.02	0.02	0.02	0.02	0.02	0.02
180	36.75	36.63	36.53	0.01	0.03	0.03	0.01	0.02	0.03
250	35.50	35.49	35.42	0.02	0.04	0.04	0.02	0.04	0.04
325	36.07	36.19	36.22	0.04	0.06	0.07	0.03	0.05	0.07
395	38.85	39.04	39.16	0.06	0.08	0.10	0.05	0.08	0.09
415	40.19	40.38	40.52	0.07	0.10	0.11	0.06	0.09	0.11
480	46.27	46.46	46.65	0.11	0.15	0.16	0.10	0.14	0.16
500	47.81	47.99	48.18	0.12	0.16	0.18	0.12	0.15	0.18
510	48.17	48.27	48.38	0.13	0.17	0.19	0.13	0.16	0.19
550	44.36	44.25	44.16	0.17	0.22	0.24	0.17	0.21	0.23
570	40.40	40.22	40.09	0.20	0.25	0.27	0.19	0.23	0.26
620	30.27	30.10	29.96	0.27	0.34	0.37	0.26	0.32	0.36
675	20.89	20.74	20.61	0.43	0.51	0.55	0.41	0.49	0.54
725	13.77	13.62	13.51	0.75	0.87	0.95	0.74	0.85	0.93
750	10.65	10.53	10.42	1.09	1.25	1.34	1.07	1.22	1.32
775	7.89	7.80	7.71	1.66	1.86	1.99	1.64	1.83	1.96
810	4.78	4.75	4.70	3.04	3.32	3.52	3.02	3.28	3.50
840	2.93	2.97	2.94	4.94	5.26	5.56	4.90	5.22	5.53
855	2.27	2.34	2.33	6.12	6.46	6.81	6.08	6.42	6.78
885	1.40	1.49	1.51	8.84	9.19	9.65	8.79	9.15	9.61
930	0.77	0.88	0.92	13.27	13.61	14.24	13.23	13.58	14.21
1000	0.45	0.55	0.60	19.17	19.58	20.25	19.19	19.60	20.28
1015	0.42	0.51	0.56	20.08	20.51	21.12	20.10	20.53	21.16
1050	0.36	0.46	0.51	21.54	22.00	22.39	21.58	22.05	22.44
1100	0.31	0.40	0.46	22.35	22.77	22.75	22.29	22.76	22.71
1200	0.27	0.35	0.41	21.49	21.61	21.00	21.36	21.54	20.91
1260	0.25	0.34	0.39	20.70	20.58	19.83	20.60	20.51	19.74
1300	0.24	0.33	0.39	20.23	19.94	19.15	20.15	19.88	19.08
1400	0.22	0.32	0.38	19.24	18.71	17.91	19.28	18.74	17.92
1500	0.21	0.31	0.37	18.47	17.96	17.16	18.56	18.01	17.19
1600	0.20	0.30	0.37	18.26	17.55	16.77	18.40	17.64	16.84
1700	0.19	0.30	0.37	18.49	17.41	16.65	18.61	17.48	16.70
1800	0.18	0.29	0.36	18.42	17.41	16.71	18.52	17.46	16.75
1900	0.18	0.28	0.35	18.09	17.50	16.91	18.19	17.56	16.95
2000	0.17	0.28	0.34	18.28	17.73	17.23	18.37	17.76	17.25
2100	0.16	0.27	0.33	18.87	18.00	17.59	18.96	18.03	17.61
2200	0.15	0.26	0.33	19.20	18.36	18.05	19.26	18.36	18.04
2300	0.15	0.26	0.32	19.07	18.71	18.52	19.12	18.71	18.51
2400	0.15	0.25	0.31	19.07	19.11	19.06	19.10	19.09	19.05
2500	0.14	0.25	0.31	19.19	19.45	19.58	19.19	19.37	19.50
2600	0.14	0.24	0.30	19.32	19.98	20.29	19.25	19.84	20.13
2700	0.14	0.24	0.30	19.28	20.43	20.91	19.18	20.26	20.74
2800	0.13	0.23	0.30	19.40	20.89	21.52	19.29	20.73	21.36
2900	0.13	0.23	0.30	19.78	21.39	22.19	19.66	21.25	22.04
3000	0.12	0.23	0.30	20.17	21.87	22.81	20.01	21.70	22.68
3100	0.12	0.23	0.30	20.79	22.52	23.47	20.65	22.36	23.36
3200	0.11	0.23	0.31	21.52	23.07	24.03	21.33	22.89	23.92
3300	0.09	0.22	0.30	22.59	23.78	24.60	22.43	23.64	24.59
3400	0.10	0.23	0.31	24.00	24.76	25.20	23.87	24.68	25.32
3450	0.11	0.24	0.32	24.90	25.40	25.83	24.59	25.11	25.68
3500	0.08	0.22	0.31	25.51	25.62	25.81	24.95	25.24	25.65
3600	0.08	0.22	0.31	27.25	26.79	26.52	26.40	26.20	26.25
3700	0.08	0.23	0.33	29.40	27.84	27.33	28.33	27.17	27.05
3800	0.09	0.25	0.32	33.78	30.05	28.25	32.06	29.12	27.91
3900	0.06	0.22	0.32	49.96	31.60	28.83	38.78	30.48	28.57
4000	0.08	0.23	0.33	39.64	34.61	29.99	39.98	33.15	29.83



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site www.minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

THP-1050+

130408

Page 1 of 2

High Pass Filter

THP-1050+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@ -40°C	@ +25°C	@ +85°C
1050	0.73	0.71	0.70
1055	0.71	0.70	0.69
1060	0.70	0.69	0.68
1065	0.69	0.67	0.67
1070	0.68	0.66	0.65
1075	0.67	0.65	0.64
1080	0.66	0.64	0.63
1085	0.65	0.63	0.62
1090	0.64	0.62	0.61
1095	0.63	0.61	0.61
1100	0.62	0.60	0.59
1110	0.60	0.58	0.58
1115	0.59	0.58	0.57
1120	0.58	0.57	0.56
1125	0.57	0.56	0.55
1130	0.56	0.55	0.54
1140	0.55	0.53	0.53
1145	0.54	0.52	0.52
1150	0.53	0.51	0.51
1160	0.52	0.50	0.50
1170	0.51	0.49	0.49
1180	0.50	0.48	0.48
1190	0.49	0.47	0.47
1200	0.48	0.46	0.46
1210	0.47	0.45	0.45
1220	0.46	0.44	0.44
1230	0.45	0.43	0.43
1240	0.44	0.42	0.42
1250	0.43	0.41	0.41
1260	0.42	0.41	0.40
1270	0.41	0.40	0.39
1280	0.40	0.39	0.38
1290	0.39	0.38	0.38
1320	0.37	0.36	0.35
1330	0.36	0.35	0.35
1350	0.35	0.34	0.33
1370	0.34	0.33	0.32
1380	0.33	0.32	0.32
1410	0.32	0.31	0.30
1450	0.30	0.29	0.28
1460	0.29	0.28	0.28
1500	0.28	0.27	0.26
1510	0.27	0.26	0.26
1560	0.26	0.25	0.24
1570	0.25	0.24	0.24
1610	0.24	0.23	0.22
1670	0.23	0.22	0.21
1770	0.21	0.20	0.19
1880	0.19	0.18	0.17
1890	0.18	0.17	0.17
2040	0.17	0.15	0.15
2050	0.16	0.15	0.15
2280	0.15	0.13	0.13
2290	0.14	0.13	0.13
2590	0.13	0.12	0.11
2600	0.12	0.11	0.11
2620	0.13	0.11	0.11
2840	0.12	0.11	0.10
2850	0.11	0.11	0.10
4000	0.10	0.08	0.08



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

THP-1050+







130408

Page 2 of 2

High Pass Filter

THP-1050+

Typical Performance Curves



 **Mini-Circuits®**

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 minicircuits.com

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



minicircuits.com

REV. OR
THP-1050+
130408
Page 1 of 2

High Pass Filter

THP-1050+

Typical Performance Curves



 **Mini-Circuits®**

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS


minicircuits.com


REV. OR
THP-1050+
130408
Page 2 of 2

Case Style



GQ

Outline Dimensions

GQ1018



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
GQ1018	.25 (6.35)	.25 (6.35)	.10 (2.54)	.125 (3.18)	.080 (2.03)	.045 (1.14)	.040 (1.02)	.040 (1.02)	.145 (3.68)	.290 (7.37)	.065 (1.65)	.060 (1.52)	.25

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$ "; 3 Pl. $\pm .005$ "

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:
For RoHS Case Styles: 3-5 μ inch Gold over 120-240 μ inch Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F78

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
16	12	7	10
			20
			50
			100
			200
		13	500, 1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION




REVISI0NS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M135450	NEW RELEASE	JUN 12	DDR	KG

SUGGESTED MOUNTING CONFIGURATION FOR
GQ1018 CASE STYLE "08FL04" PIN CODE


NOTES:

1. TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES
TOLERANCES ON:
2 PL DECIMALS ± .005"
3 PL DECIMALS ± .005"
ANGLES ±
FRACTIONS ±

✓ Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95





Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 08FL04, GQ1018, THP,
TB-680+, 50 Ohm

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-372	OR
FILE: 98PL372	SCALE: 4:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: OAK-602 OR Equivalent
Dielectric Constant=2.50±.04, Thickness=.022 inch.

Mini-Circuits®



Environmental Specifications

ENV03T2

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215