

Engineering Development Model

RF Transformer

TMO6-ED11083/1

Impedance Ratio : 6

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : A03

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		0.3		60 MHz
Insertion Loss *	3 dB Bandwidth		0.3 - 60	MHz
	2 dB Bandwidth		0.3 - 10	MHz
	1 dB Bandwidth		0.5 - 3	MHz


Notes:

* Insertion Loss is referenced to mid-band loss, 0.27dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

PIN CONNECTIONS	
PRIMARY DOT	1
PRIMARY	5
SECONDARY DOT	2
SECONDARY	6
CASE GROUND	7,8
NOT USED	3,4

Configuration :C



RF Transformer

TMO6-ED11083/1

Typical Performance Data

FREQUENCY (MHz)	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
0.30	0.88	8.08	0.01	0.08
0.40	0.56	10.13	0.01	0.11
0.50	0.41	11.79	0.01	0.11
0.60	0.33	13.17	0.01	0.13
0.70	0.29	14.34	0.00	0.14
0.80	0.27	15.31	0.00	0.14
0.90	0.27	16.13	0.00	0.15
1.00	0.28	16.81	0.00	0.17
1.50	0.37	18.91	0.01	0.23
2.00	0.45	20.06	0.01	0.31
2.25	0.48	20.49	0.01	0.35
2.50	0.51	20.87	0.01	0.39
2.75	0.54	21.20	0.01	0.43
3.00	0.57	21.49	0.01	0.48
3.25	0.59	21.76	0.01	0.53
3.50	0.61	21.99	0.01	0.57
3.75	0.63	22.21	0.01	0.60
4.00	0.65	22.40	0.01	0.66
4.50	0.68	22.73	0.01	0.75
5.00	0.71	23.00	0.02	0.81
5.25	0.73	23.11	0.02	0.87
5.50	0.74	23.21	0.02	0.92
5.75	0.75	23.30	0.02	0.97
6.00	0.76	23.38	0.02	1.00
6.50	0.79	23.52	0.02	1.10
7.00	0.81	23.62	0.02	1.19
7.50	0.83	23.71	0.02	1.27
8.00	0.85	23.76	0.02	1.36
8.50	0.86	23.80	0.02	1.45
9.00	0.88	23.83	0.02	1.55
10.00	0.92	23.84	0.04	1.68
20.00	1.18	23.28	0.04	3.61
30.00	1.40	22.94	0.03	5.55
40.00	1.59	23.03	0.01	7.46
50.00	1.76	23.44	0.02	9.32
60.00	1.94	24.15	0.06	11.08
70.00	2.11	25.15	0.10	12.78
80.00	2.29	26.50	0.14	14.38
90.00	2.47	28.32	0.17	15.91
100.00	2.66	30.82	0.19	17.37



P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4861 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



REV. X1

TMO6-ED11083/1





11/29/2007

Page 1 of 1

RF Transformer

TMO6-ED11083/1

Typical Performance Data



ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4861 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS




REV. X1
TMO6-ED11083/1
11/29/2007
Page 1 of 1

A03

A11

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	WT, GRAM
A03	.480 (12.19)	.500 (12.70)	.390 (9.91)	.405 (10.29)	.210 (5.33)	.230 (5.84)	.100 (2.54)	.20 (5.08)	.14 (3.56)	.020 (.51)	2.3
A11			.240 (6.10)	.255 (6.48)							1.9

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-047-01.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215