SURFACE MOUNT

RF Transformer

TRS1-182-75-7+

75Ω 10 to 1800 MHz 1:1 Ratio

FEATURES

- Suitable for Tin/Lead and RoHS Solder Systems
- Wideband, 10 to 1800 MHz
- Balanced Transmission Line
- Good Return Loss, 20 dB Typ. at 1 dB Band
- Excellent Amplitude Unbalance, 0.3 dB Typ.
- Aqueous Washable
- Excellent Intermod Suppression



Generic photo used for illustration purposes only

CASE STYLE: TT1618-2

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Impedance Ratio			1		
Frequency Range		10		1800	MHz
Insertion Loss[1]	50 - 1200		0.6	1.0	dB
	10 - 1800		0.9	2.0	
Amplitude Unbalance	50 - 1000		0.3	0.7	dB
	1000 - 1200		0.5	1.1	
	10 - 1800		0.7	1.5	
Phase Unbalance	50 - 1000		2	4	Degree
	1000 - 1200		3	6	
	10 - 1800		7.5	15	
Primary Return Loss	50 - 500	16	22		dB
	500 - 1000	13	20		
	1000 - 1200	12	20		
	10 - 1800	8	12.5		


1. Insertion Loss is referenced to mid-band loss, 0.25 dB typ.

ABSOLUTE MAXIMUM RATINGS[2,3]

Parameter	Ratings
Operating Temperature	-40°C to +100°C
Storage Temperature	-55°C to +125°C
RF Power	1 W
DC Current	30 mA

2. Permanent damage may occur if any of these limits are exceeded.
3. The unit has been assessed for survivability up to 105°C; there is no permanent damage.

ELECTRICAL SCHEMATIC



REV. E
ECO-031290
TRS1-182-75-7+
MCINU
260923

SURFACE MOUNT

RF Transformer

TRS1-182-75-7+

75Ω 10 to 1800 MHz 1:1 Ratio


PIN CONNECTIONS

PRIMARY DOT	1
PRIMARY	2
SECONDARY DOT	3
SECONDARY	4

PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-875+

OUTLINE DRAWING



SUGGESTED FOOTPRINT FOR PC LAYOUT
TOLERANCE TO BE WITHIN ±.002

OUTLINE DIMENSIONS (Inch / mm)

A	B	C	D	E	F
.240	.170	.160	.100	.070	.040
6.10	4.32	4.06	2.54	1.78	1.02

G	H	J	K	L	wt.
.054	.202	.100	.057	.055	grams
1.37	5.13	2.54	1.45	1.40	2.8

TAPE & REEL INFORMATION: F77

SURFACE MOUNT


RF Transformer


TRS1-182-75-7+


75Ω 10 to 1800 MHz 1:1 Ratio


TYPICAL PERFORMANCE DATA

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (Deg.)
10	0.40	12.17	0.62	8.22
50	0.33	26.38	0.21	1.41
100	0.34	31.22	0.20	0.64
200	0.34	35.82	0.16	0.12
400	0.37	33.92	0.07	0.19
500	0.39	30.13	0.00	0.14
600	0.41	27.88	0.08	0.12
1000	0.50	23.13	0.44	0.91
1200	0.55	22.28	0.66	1.87
1800	0.68	22.28	1.14	7.84









NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html


RF Transformer TRS1-182-75-7+


Typical Performance Data


FREQUENCY MHz	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
7	0.69	9.31	1.03	10.09
10	0.40	12.17	0.62	8.22
20	0.20	18.88	0.22	4.20
30	0.27	22.90	0.20	2.50
50	0.33	26.38	0.21	1.41
70	0.33	28.58	0.21	0.99
100	0.34	31.22	0.20	0.64
150	0.35	34.88	0.17	0.39
200	0.34	35.82	0.16	0.12
300	0.35	35.53	0.12	0.07
400	0.37	33.92	0.07	0.19
450	0.38	32.08	0.04	0.17
500	0.39	30.13	0.00	0.14
550	0.40	28.64	0.04	0.12
600	0.41	27.88	0.08	0.12
700	0.43	26.41	0.15	0.03
800	0.46	24.52	0.24	0.27
900	0.48	23.74	0.34	0.58
950	0.49	23.50	0.39	0.71
1000	0.50	23.13	0.44	0.91
1050	0.52	22.56	0.49	1.14
1100	0.53	22.22	0.55	1.36
1150	0.54	22.21	0.60	1.59
1200	0.55	22.28	0.66	1.87
1220	0.55	22.30	0.68	1.99
1250	0.56	22.27	0.71	2.22
1300	0.57	22.03	0.76	2.56
1400	0.59	21.75	0.86	3.34
1500	0.61	22.12	0.96	4.32
1600	0.63	21.85	1.04	5.39
1700	0.66	21.90	1.11	6.57
1750	0.67	22.24	1.13	7.22
1800	0.68	22.28	1.14	7.84
1850	0.69	22.11	1.15	8.59
1900	0.71	21.88	1.15	9.24
1950	0.73	21.86	1.16	9.90
2000	0.75	21.96	1.15	10.61


RF Transformer TRS1-182-75-7+

Typical Performance Data










Case Style TT

Outline Dimensions

TT1618-2



SUGGESTED FOOTPRINT FOR PC LAYOUT
TOLERANCE TO BE WITHIN ±.002

CASE #	A	B	C	D	E	F	G	H	J	K	L	WT GRAMS
TT1618-2	.240 (6.10)	.170 (4.32)	.160 (4.06)	.100 (2.54)	.070 (1.78)	.040 (1.02)	.054 (1.37)	.202 (5.13)	.100 (2.54)	.057 (1.45)	.055 (1.40)	2.80


Dimensions are in inches (mm). Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

Notes:


1. Open style, Base material: Printed wiring laminate.
2. Termination finish: 3-5 µ inch (.08-.13 microns) Gold over 120-240 µ inch (3.05-6.10 microns) Nickel plate. All models, (+) suffix.
3. Orientation Dot on Unit corresponds to Pin #1.

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F77



Note: The shape of the pocket may differ



Note: The location and shape of the metallization may differ

Applicable Case Styles
GU1604, GU1804, GU2644, TT1618-2

Applicable Case Styles
MZ4532C, NM1812C, NM1812C-1, NM1812C-2, NM1812C-3, NM1812C-5, NM1812C-6, NM3237 NM1812C-9

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
		13	Standard	2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

Mini-Circuits

Environmental Specifications ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.