

Surface Mount 

# Low Pass Filter

ULP-190+

50Ω DC to 190 MHz



CASE STYLE: QA2224

## The Big Deal

- Low Insertion loss, 1.5dB Typ.
- High rejection, > 40dB
- Sharp insertion loss roll-off
- Ultra miniature surface mount package

## Product Overview

The ULP-190+ is a lowpass filter in a top hat package (size of 0.25" x 0.25") fabricated using SMT technology. Covering DC to 190 MHz band width, these units offer good matching within the passband and high rejection. This model uses a miniature high Q capacitors and chip inductors for high reliability. In addition it has repeatable performance across production lots and consistent performance across temperature.

## Key Features

Feature	Advantages
Low passband insertion loss	Passband insertion loss 1.5dB typical ensures low signal loss throughout the passband
Excellent stopband rejection	Rejection of 40 dB ensures unwanted spurious are eliminated
Small size, 0.25" x 0.25"	The Ultra miniature surface mount package enables the ULP-190+ to be used in compact designs.

### Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

# Low Pass Filter

50Ω

DC to 190 MHz

**ULP-190+**



CASE STYLE: QA2224

**Features**

- High rejection
- Sharp insertion loss roll-off
- Ultra miniature surface mount package

**Applications**

- Wireless communications
- Receivers / Transformers
- Lab use

**Functional Schematic****Typical Frequency Response****Electrical Specifications at 25°C**

	Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	DC-190	—	1.5	2.0	dB
	Freq. Cut-Off	F2	220	—	3.0	—	dB
	VSWR	DC-F1	DC-190	—	1.5	—	:1
Stop Band	Rejection Loss	F3-F4	264-300	20	27	—	dB
		F4-F5	300-1300	40	47	—	dB
		F5-F6	1300-3000	—	20	—	dB
	VSWR	F3-F5	264-1300	—	20	—	:1





**Maximum Ratings**

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.6 W max.

Permanent damage may occur if any of these limits are exceeded.

**Typical Performance Data at 25°C**

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	0.18	1.03	1	3.77
50	0.37	1.24	5	3.43
100	0.50	1.04	8	3.42
190	1.29	1.34	24	3.37
200	1.53	1.31	40	3.37
217	3.23	1.92	56	3.44
220	4.30	2.60	80	3.65
230	9.97	6.78	96	3.83
245	20.18	14.68	104	3.92
260	30.37	20.57	112	4.01
264	33.22	21.93	120	4.12
300	52.43	32.24	128	4.25
500	59.00	87.32	136	4.42
750	61.84	175.38	144	4.64
1000	63.14	252.97	160	5.29
1300	59.71	272.65	168	5.69
1500	48.57	230.26	176	6.15
2000	43.89	154.74	184	6.66
2500	68.01	114.26	186	6.80
3000	57.75	89.75	190	7.15

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)


[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

**Pad Connections**

INPUT	1
OUTPUT	3
GROUND	2,4,5,6

**Demo Board MCL P/N: TB-894+  
Suggested PCB Layout (PL-484)**

SUGGESTED MOUNTING CONFIGURATION FOR  
QA2224 CASE STYLE "06FL09" PIN CODE





## NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020"±.0015", COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

**Outline Drawing**

Suggested Layout,  
Tolerance to be within ±.002

**Outline Dimensions ( inch mm )**

A	B	C	D	E	F	G	H	J	K
-	-	Min Max	-	-	-	-	-	-	-
.250	.250	.075 .100	.075	.125	.092	.201	.041	.050	.046
6.35	6.35	1.91 2.54	1.91	3.18	2.34	5.11	1.04	1.27	1.17

L	M	N	P	Q	Wt. grams
.168	.117	.042	.260	.234	0.25
4.27	2.97	1.07	6.60	5.94	

## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Low Pass Filter

**ULP-190+**

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
	0.15	0.18	0.21	38.23	35.92	34.49	37.97	35.74	34.34
1	0.15	0.18	0.21	37.33	35.35	34.07	37.01	35.13	33.88
2	0.16	0.19	0.22	33.22	32.10	31.36	33.18	32.08	31.35
5	0.18	0.21	0.23	28.57	27.85	27.41	28.49	27.78	27.36
10	0.33	0.37	0.40	19.53	19.37	19.23	19.43	19.25	19.11
50	0.44	0.50	0.55	39.63	33.39	30.24	39.20	33.45	30.26
100	0.71	0.80	0.86	18.70	19.30	19.42	18.79	19.40	19.56
150	0.84	0.97	1.07	30.70	27.16	25.03	30.89	27.18	24.96
175	1.11	1.29	1.42	17.47	16.83	16.19	17.44	16.73	16.04
190	1.32	1.53	1.67	17.14	17.34	17.18	16.69	16.66	16.34
200	2.28	2.71	3.04	14.02	12.85	12.12	12.45	11.41	10.74
215	3.01	3.55	3.95	9.58	8.93	8.48	8.80	8.16	7.72
218	3.70	4.30	4.75	7.48	7.06	6.74	6.93	6.51	6.19
220	9.28	9.97	10.53	2.52	2.58	2.59	2.35	2.40	2.39
230	16.20	16.78	17.29	1.30	1.42	1.48	1.22	1.33	1.38
240	19.64	20.18	20.65	1.07	1.19	1.25	1.00	1.11	1.17
250	23.05	23.55	24.00	0.92	1.03	1.09	0.87	0.97	1.03
255	26.46	26.93	27.36	0.82	0.92	0.98	0.77	0.88	0.93
260	29.92	30.37	30.80	0.74	0.85	0.90	0.70	0.80	0.86
264	32.76	33.22	33.65	0.69	0.79	0.85	0.66	0.76	0.81
264	32.76	33.22	33.65	0.69	0.79	0.85	0.66	0.76	0.81
265	33.50	33.96	34.39	0.68	0.78	0.84	0.65	0.75	0.80
270	37.33	37.81	38.26	0.63	0.73	0.78	0.61	0.70	0.75
280	46.75	47.39	47.97	0.56	0.65	0.70	0.54	0.63	0.67
290	62.01	60.74	59.77	0.51	0.59	0.63	0.48	0.57	0.61
300	52.87	52.43	52.09	0.46	0.54	0.58	0.44	0.52	0.57
310	49.94	49.76	49.58	0.43	0.50	0.54	0.41	0.48	0.52
320	49.08	48.99	48.93	0.40	0.46	0.50	0.38	0.45	0.49
325	49.00	48.97	48.91	0.38	0.45	0.48	0.36	0.43	0.47
350	50.03	50.06	50.09	0.32	0.38	0.42	0.31	0.37	0.40
375	51.92	52.01	51.95	0.28	0.34	0.36	0.27	0.32	0.35
400	53.83	53.95	53.93	0.25	0.30	0.32	0.23	0.29	0.31
450	57.00	57.09	57.06	0.19	0.24	0.26	0.18	0.23	0.25
500	58.89	59.00	59.06	0.15	0.20	0.22	0.14	0.19	0.21
550	60.12	60.13	60.08	0.12	0.17	0.18	0.11	0.16	0.18
600	60.68	60.84	60.75	0.09	0.14	0.16	0.09	0.14	0.16
650	61.17	61.23	61.14	0.08	0.13	0.14	0.07	0.12	0.14
700	61.33	61.35	61.39	0.06	0.11	0.13	0.06	0.10	0.13
750	61.77	61.84	61.76	0.05	0.10	0.12	0.04	0.09	0.11
800	61.98	62.31	62.12	0.04	0.09	0.11	0.03	0.08	0.10
850	62.23	62.47	62.36	0.03	0.08	0.10	0.03	0.08	0.10
900	62.51	62.66	62.57	0.02	0.08	0.10	0.02	0.07	0.09
950	62.67	62.92	62.89	0.02	0.07	0.09	0.01	0.07	0.09
1000	62.84	63.14	63.20	0.01	0.07	0.09	0.01	0.07	0.09
1200	61.84	61.81	62.00	0.00	0.06	0.09	0.00	0.06	0.09
1250	60.89	60.91	60.94	0.01	0.06	0.09	0.00	0.06	0.09
1300	59.39	59.71	59.57	0.01	0.06	0.09	0.01	0.06	0.09
1400	55.50	55.53	55.52	0.01	0.07	0.09	0.01	0.07	0.10
1500	48.69	48.57	48.46	0.00	0.08	0.10	0.01	0.07	0.10
1750	44.44	44.74	44.94	0.01	0.09	0.12	0.00	0.08	0.12
2000	43.82	43.89	43.90	0.03	0.11	0.14	0.01	0.10	0.14
2250	52.60	53.42	53.89	0.06	0.14	0.17	0.03	0.12	0.16
2300	58.38	59.38	59.85	0.06	0.14	0.17	0.03	0.12	0.16
2400	74.21	75.77	75.54	0.07	0.15	0.18	0.04	0.13	0.17
2500	69.48	68.01	67.71	0.07	0.15	0.18	0.05	0.14	0.18
2600	63.65	63.50	63.95	0.08	0.16	0.19	0.06	0.14	0.19
2700	61.84	61.59	61.76	0.09	0.17	0.20	0.07	0.15	0.19
2800	60.46	60.18	60.43	0.10	0.18	0.21	0.07	0.16	0.20
2900	58.71	59.40	58.87	0.11	0.18	0.21	0.07	0.17	0.20
3000	57.36	57.75	57.55	0.12	0.19	0.21	0.08	0.17	0.21



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

Mouser Electronics The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR

ULP-190+







170215

Page 1 of 2


*Typical Performance Data*

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
1	3.75	3.77	3.74
2	3.58	3.58	3.57
4	3.48	3.48	3.48
6	3.42	3.43	3.44
8	3.41	3.42	3.42
10	3.41	3.41	3.41
12	3.40	3.40	3.41
14	3.39	3.40	3.40
16	3.38	3.39	3.39
18	3.37	3.38	3.39
20	3.37	3.37	3.38
22	3.37	3.37	3.37
24	3.36	3.37	3.37
26	3.36	3.36	3.37
28	3.36	3.36	3.37
30	3.36	3.36	3.37
32	3.36	3.36	3.36
34	3.36	3.36	3.37
36	3.36	3.36	3.37
38	3.37	3.37	3.37
40	3.37	3.37	3.37
42	3.37	3.37	3.38
44	3.38	3.38	3.39
46	3.39	3.39	3.39
48	3.39	3.40	3.40
50	3.40	3.41	3.41
52	3.42	3.42	3.42
54	3.43	3.43	3.43
56	3.43	3.44	3.45
58	3.45	3.46	3.46
60	3.46	3.47	3.47
62	3.48	3.49	3.49
64	3.49	3.50	3.51
66	3.51	3.52	3.53
68	3.53	3.53	3.54
70	3.54	3.55	3.56
72	3.56	3.57	3.58
75	3.59	3.60	3.61
80	3.64	3.65	3.66
85	3.69	3.70	3.71
90	3.75	3.76	3.77
95	3.81	3.81	3.82
110	4.00	3.99	3.99
115	4.06	4.05	4.05
120	4.13	4.12	4.12
125	4.21	4.20	4.20
130	4.29	4.29	4.29
135	4.40	4.40	4.40
140	4.51	4.52	4.53
145	4.65	4.67	4.69
150	4.83	4.85	4.88
155	5.03	5.06	5.09
160	5.25	5.29	5.32
165	5.50	5.54	5.57
168	5.66	5.69	5.73
170	5.77	5.81	5.84
175	6.06	6.09	6.11
180	6.37	6.39	6.41
185	6.71	6.73	6.75
190	7.12	7.15	7.18

## Typical Performance Curves



## Typical Performance Curves





# Case Style

QA

## Outline Dimensions

QA2224



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
QA2224	.250 (6.35)	.250 (6.35)	.070 (1.78)	.075 (1.91)	.125 (3.18)	.092 (2.34)	.201 (5.11)	.041 (1.04)	.050 (1.27)	.046 (1.17)	.168 (4.27)	.117 (2.97)

CASE#	N	P	Q	WT. GRAM
QA2224	.042 (1.07)	.260 (6.60)	.234 (5.94)	0.25

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

### Notes:

1. Case material: Ceramic base.
2. Base: Printed wiring laminate.
3. Termination finish:  
For RoHS Case Styles: 3-5  $\mu$  inch Gold over 120-240  $\mu$  inch Nickel plate.  
For RoHS-5 Case Styles: Tin-Lead plate.
4. Top-Hat total thickness: .013 inches MAX

 **Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
[minicircuits.com](http://minicircuits.com)

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/F MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F34

## DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.

Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVISONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M156213	NEW RELEASE	MAY 16	TM	MD
A	M161508	COPPER LAND PATTERN UPDATED	APR 17	EJ	MD

SUGGESTED MOUNTING CONFIGURATION FOR  
QA2224 CASE STYLE "06FL09" PIN CODE



## NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES


TOLERANCES ON:

2 PL DECIMALS ±

3 PL DECIMALS ± .005"

ANGLES ±

FRACTIONS ±



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.  
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE  
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY  
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.  
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE  
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



**Mini-Circuits®**

13 Neptune Avenue  
Brooklyn NY 11235

PL, 06FL09, QA2224, ULP,  
TB-894+, 50 Ohm

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-484	A
FILE:	98PL484	SCALE: 4:1	SHEET: 1 OF 1

# Evaluation Board and Circuit



NOTES:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS (R04350B) OR Equivalent  
Dielectric Constant= $3.48 \pm 0.05$ , Thickness=.020 inch.

Schematic Diagram

Mini-Circuits®



## Environmental Specifications

## ENV03T2

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215