

Non-Catalog Model

Frequency Mixer

TUF-11AH

Level 17 (LO Power +17 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : B02


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1400		1900	MHz
	RF (fL to fU)	1400		1900	MHz
	IF	40		500	MHz
Conversion Loss			7.3	9.0	dB
LO-RF Isolation		25	35		dB
LO-IF Isolation		15	30		dB
IP3 Input		+27.5	+30		dBm
1 dB Comp. Input Power			+14		dBm

Notes: IP3 : RF Power = 0 dBm @ 200 MHz & 202 MHz , LO Power = +17 dBm @ 180 MHz
Non-hermetic

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA

PIN CONNECTIONS	
LO	4
RF	1
IF	2
GROUND	3

Electrical Schematics



Frequency Mixer

TUF-11AH

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=40MHz (dB)		
		@LO (dBm)		
		+14	+17	+20
460.0	500.0	12.40	10.85	9.82
520.0	560.0	11.17	9.57	8.78
580.0	620.0	11.11	9.41	8.60
640.0	680.0	10.78	9.12	8.29
700.0	740.0	9.88	8.42	7.73
760.0	800.0	9.67	8.26	7.62
820.0	860.0	9.18	7.95	7.38
880.0	920.0	8.72	7.70	7.23
940.0	980.0	8.26	7.30	6.87
1000.0	1040.0	8.09	7.18	6.80
1060.0	1100.0	7.78	6.97	6.60
1120.0	1160.0	7.91	7.05	6.70
1180.0	1220.0	8.27	7.23	6.85
1240.0	1280.0	8.76	7.51	7.02
1300.0	1340.0	9.18	7.69	7.06
1360.0	1400.0	9.29	7.62	6.97
1420.0	1460.0	9.12	7.60	6.94
1480.0	1520.0	9.06	7.53	6.84
1540.0	1580.0	9.06	7.77	7.05
1600.0	1640.0	8.73	7.58	6.97
1660.0	1700.0	8.81	7.65	7.08
1720.0	1760.0	8.64	7.60	7.12
1780.0	1820.0	8.51	7.51	7.05
1840.0	1880.0	8.55	7.54	7.13
1900.0	1940.0	8.49	7.52	7.15
1960.0	2000.0	8.52	7.50	7.09
2020.0	2060.0	8.53	7.60	7.14
2080.0	2120.0	8.62	7.74	7.33
2140.0	2180.0	8.65	7.74	7.32
2200.0	2240.0	8.87	8.00	7.59
2260.0	2300.0	9.02	8.23	7.78
2320.0	2360.0	9.17	8.42	7.91
2360.0	2400.0	9.33	8.65	8.18
2420.0	2460.0	9.55	8.85	8.38
2460.0	2500.0	9.78	9.21	8.80
2520.0	2560.0	9.91	9.39	9.00
2560.0	2600.0	10.27	9.80	9.48
2620.0	2660.0	10.47	9.98	9.72
2660.0	2700.0	10.95	10.48	10.25
2720.0	2760.0	11.28	10.78	10.55

RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)		
		@LO (dBm)		
		+14	+17	+20
460.0	500.0	16.16	19.42	24.74
520.0	560.0	16.88	21.92	26.03
580.0	620.0	16.21	20.33	24.57
640.0	680.0	16.13	20.57	24.57
700.0	740.0	17.69	21.47	22.51
760.0	800.0	17.43	20.11	21.37
820.0	860.0	18.21	19.97	21.32
880.0	920.0	18.04	19.26	20.43
940.0	980.0	18.50	19.45	20.71
1000.0	1040.0	19.14	19.80	20.72
1060.0	1100.0	19.47	20.52	21.39
1120.0	1160.0	23.57	24.43	24.58
1180.0	1220.0	23.26	27.35	27.41
1240.0	1280.0	21.01	27.61	26.34
1300.0	1340.0	19.47	23.20	23.92
1360.0	1400.0	19.71	22.44	22.97
1420.0	1460.0	19.69	22.30	22.55
1480.0	1520.0	20.21	23.15	24.38
1540.0	1580.0	19.98	21.65	23.20
1600.0	1640.0	20.79	21.29	22.12
1660.0	1700.0	20.31	20.42	21.50
1720.0	1760.0	20.75	20.44	21.21
1780.0	1820.0	20.97	20.39	21.09
1840.0	1880.0	20.57	20.33	21.15
1900.0	1940.0	20.65	20.36	20.72
1960.0	2000.0	19.43	19.53	20.00
2020.0	2060.0	19.95	19.94	21.06
2080.0	2120.0	19.98	20.12	20.76
2140.0	2180.0	20.40	20.87	21.06
2200.0	2240.0	20.35	22.11	22.05
2260.0	2300.0	19.95	22.00	23.35
2320.0	2360.0	20.22	22.44	25.14
2360.0	2400.0	20.35	22.60	25.53
2420.0	2460.0	21.01	22.95	26.52
2460.0	2500.0	21.86	22.70	25.42
2520.0	2560.0	23.82	23.59	24.96
2560.0	2600.0	25.06	24.78	25.82
2620.0	2660.0	25.16	25.62	27.11
2660.0	2700.0	26.05	27.07	28.01
2720.0	2760.0	26.21	28.06	29.65

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+14dBm (dB)		
		@LO (dBm)		
		+14	+17	+20
460.0	500.0	-1.19	-0.63	-0.25
520.0	560.0	-0.61	-0.07	0.05
580.0	620.0	-0.53	0.05	0.15
640.0	680.0	-0.29	0.22	0.32
700.0	740.0	0.54	0.77	0.73
760.0	800.0	0.73	0.88	0.84
820.0	860.0	1.20	1.07	0.96
880.0	920.0	1.45	1.23	1.09
940.0	980.0	1.67	1.38	1.22
1000.0	1040.0	1.65	1.23	1.07
1060.0	1100.0	1.56	1.01	0.87
1120.0	1160.0	1.34	0.71	0.56
1180.0	1220.0	1.17	0.70	0.57
1240.0	1280.0	1.14	0.96	0.80
1300.0	1340.0	0.98	1.06	0.94
1360.0	1400.0	1.14	1.29	1.15
1420.0	1460.0	1.17	1.29	1.19
1480.0	1520.0	1.30	1.37	1.24
1540.0	1580.0	1.20	1.11	1.08
1600.0	1640.0	1.55	1.26	1.15
1660.0	1700.0	1.38	1.11	1.02
1720.0	1760.0	1.47	1.17	0.99
1780.0	1820.0	1.42	1.15	1.02
1840.0	1880.0	1.41	1.15	0.99
1900.0	1940.0	1.32	1.04	0.92
1960.0	2000.0	1.37	0.98	0.89
2020.0	2060.0	1.28	0.82	0.74
2080.0	2120.0	1.25	0.78	0.64
2140.0	2180.0	1.17	0.77	0.60
2200.0	2240.0	1.12	0.68	0.53
2260.0	2300.0	1.21	0.66	0.56
2320.0	2360.0	1.10	0.53	0.46
2360.0	2400.0	1.14	0.55	0.43
2420.0	2460.0	1.09	0.47	0.34
2460.0	2500.0	1.03	0.44	0.29
2520.0	2560.0	0.96	0.37	0.21
2560.0	2600.0	0.96	0.34	0.18
2620.0	2660.0	0.95	0.34	0.16
2660.0	2700.0	0.88	0.35	0.16
2720.0	2760.0	0.86	0.32	0.17

Frequency Mixer

TUF-11AH

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1650MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1389.9MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1910.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+17			+17			+17
1590.0	60.0	10.43	10.1	1400.0	8.69	1690.1	220.0	10.33
1510.0	140.0	9.81	50.1	1440.0	7.50	1650.1	260.0	10.04
1430.0	220.0	9.43	90.1	1480.0	7.32	1610.1	300.0	9.68
1350.0	300.0	9.13	130.1	1520.0	7.33	1570.1	340.0	9.46
1270.0	380.0	8.52	170.1	1560.0	7.40	1530.1	380.0	9.23
1190.0	460.0	8.32	210.1	1600.0	7.56	1490.1	420.0	8.89
1110.0	540.0	8.35	250.1	1640.0	7.69	1450.1	460.0	8.81
1030.0	620.0	8.03	290.1	1680.0	7.74	1410.1	500.0	8.83
950.0	700.0	7.58	330.1	1720.0	7.80	1370.1	540.0	8.92
870.0	780.0	7.16	370.1	1760.0	7.85	1330.1	580.0	8.94
790.0	860.0	6.79	410.1	1800.0	7.96	1290.1	620.0	9.06
710.0	940.0	6.66	450.1	1840.0	8.05	1250.1	660.0	9.10
630.0	1020.0	6.80	490.1	1880.0	8.13	1210.1	700.0	8.94
550.0	1100.0	7.28	530.1	1920.0	8.13	1170.1	740.0	8.79
470.0	1180.0	7.27	570.1	1960.0	8.07	1130.1	780.0	8.55
390.0	1260.0	7.40	610.1	2000.0	8.00	1090.1	820.0	8.21
310.0	1340.0	7.44	650.1	2040.0	7.87	1050.1	860.0	7.89
230.0	1420.0	7.29	690.1	2080.0	7.73	1010.1	900.0	7.42
150.0	1500.0	7.35	730.1	2120.0	7.56	970.1	940.0	7.08
70.0	1580.0	7.62	770.1	2160.0	7.35	930.1	980.0	6.85
10.0	1660.0	8.70	810.1	2200.0	7.18	890.1	1020.0	6.65
90.0	1740.0	7.41	850.1	2240.0	7.05	850.1	1060.0	6.56
170.0	1820.0	7.51	890.1	2280.0	6.98	810.1	1100.0	6.50
250.0	1900.0	7.60	930.1	2320.0	6.95	770.1	1140.0	6.56
330.0	1980.0	7.74	970.1	2360.0	6.96	730.1	1180.0	6.62
410.0	2060.0	7.80	1010.1	2400.0	7.00	690.1	1220.0	6.70
490.0	2140.0	7.66	1050.1	2440.0	7.15	650.1	1260.0	6.82
570.0	2220.0	7.34	1090.1	2480.0	7.27	610.1	1300.0	6.96
650.0	2300.0	7.17	1130.1	2520.0	7.42	570.1	1340.0	7.08
730.0	2380.0	6.96	1170.1	2560.0	7.59	510.1	1400.0	7.24
810.0	2460.0	6.82	1210.1	2600.0	7.71	470.1	1440.0	7.18
890.0	2540.0	6.83	1250.1	2640.0	7.92	410.1	1500.0	7.11
970.0	2620.0	6.95	1290.1	2680.0	8.13	370.1	1540.0	7.06
1050.0	2700.0	7.15	1330.1	2720.0	8.34	310.1	1600.0	7.07
1130.0	2780.0	7.38	1370.1	2760.0	8.65	270.1	1640.0	7.05
1230.0	2880.0	7.78	1410.1	2800.0	8.84	210.1	1700.0	7.06
1310.0	2960.0	8.24	1450.1	2840.0	9.09	170.1	1740.0	7.08
1410.0	3060.0	8.91	1510.1	2900.0	9.42	110.1	1800.0	7.24
1490.0	3140.0	9.45	1550.1	2940.0	9.82	70.1	1840.0	7.43
1590.0	3240.0	10.28	1610.1	3000.0	10.35	10.1	1900.0	9.19

Frequency Mixer

TUF-11AH

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+14	+17	+20	+14	+17	+20
500.0	45.03	45.27	45.61	26.17	25.87	25.47
560.0	44.65	44.78	45.32	25.60	25.04	24.70
620.0	44.88	45.23	46.21	25.07	24.31	24.02
680.0	44.88	45.71	46.87	24.66	24.05	23.68
740.0	45.67	46.47	47.56	24.34	23.67	23.30
800.0	47.17	47.52	47.38	23.86	23.36	22.93
860.0	49.26	49.39	49.36	23.32	22.74	22.60
920.0	49.55	49.61	49.71	22.90	22.48	22.27
980.0	50.59	50.07	49.74	22.89	22.53	22.18
1040.0	52.49	52.23	52.41	22.81	22.38	22.06
1100.0	60.02	64.83	69.57	22.62	22.25	21.89
1160.0	58.92	52.84	50.19	22.47	22.24	21.92
1220.0	46.24	44.21	43.16	22.24	22.12	21.89
1280.0	42.60	42.60	42.93	21.85	21.75	21.60
1340.0	39.64	40.54	41.93	21.90	21.74	21.67
1400.0	37.73	39.74	41.95	21.15	21.38	21.74
1460.0	41.86	42.73	46.88	21.22	21.49	21.89
1520.0	44.94	43.99	46.85	21.89	22.34	22.41
1580.0	44.46	43.87	44.72	22.95	23.54	23.36
1640.0	42.54	42.70	43.60	23.86	24.84	24.36
1700.0	40.34	40.85	42.46	24.82	26.25	25.41
1760.0	37.91	38.53	40.11	26.00	27.40	26.53
1820.0	36.32	37.10	38.68	27.22	28.51	27.80
1880.0	34.42	35.27	36.70	28.86	29.91	28.77
1940.0	33.26	34.00	35.31	30.72	31.21	29.87
2000.0	32.38	33.03	34.27	32.44	33.06	31.18
2060.0	31.32	31.99	32.93	34.07	34.34	32.05
2120.0	30.54	31.43	32.28	35.64	35.05	32.69
2180.0	29.87	31.13	32.28	37.77	36.71	33.47
2240.0	28.95	30.12	31.47	38.91	39.12	35.14
2300.0	28.65	30.03	31.40	36.95	41.86	37.51
2360.0	28.17	29.74	31.27	35.01	40.02	39.92
2400.0	27.96	29.61	31.25	34.21	37.94	39.58
2460.0	27.62	29.50	31.26	34.29	36.22	37.78
2500.0	27.31	29.25	30.88	34.51	35.68	36.75
2560.0	26.94	28.99	30.62	35.21	35.75	36.61
2600.0	26.81	28.77	30.24	35.42	35.61	36.55
2660.0	27.17	29.26	30.69	36.17	35.81	36.88
2700.0	27.20	29.25	30.64	36.72	36.19	37.30
2760.0	27.36	29.44	30.91	38.28	37.11	38.53

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+14	+17	+20
460.0	490.0	25.19	24.71	24.31
520.0	550.0	24.02	23.84	23.57
580.0	610.0	23.44	23.46	23.34
640.0	670.0	22.54	22.39	22.18
700.0	730.0	22.43	22.35	22.24
760.0	790.0	22.75	22.49	22.36
820.0	850.0	23.52	23.38	23.44
880.0	910.0	24.52	24.32	24.38
940.0	970.0	26.22	26.18	26.00
1000.0	1030.0	28.73	28.75	28.78
1060.0	1090.0	33.08	34.05	34.28
1120.0	1150.0	39.14	44.58	43.59
1180.0	1210.0	31.86	32.52	32.78
1240.0	1270.0	27.94	29.31	29.98
1300.0	1330.0	27.31	29.01	30.13
1360.0	1390.0	28.38	29.83	31.20
1420.0	1450.0	27.38	28.62	30.43
1480.0	1510.0	27.56	28.06	29.68
1540.0	1570.0	27.90	27.63	28.61
1600.0	1630.0	28.28	27.59	27.99
1660.0	1690.0	28.22	27.52	27.49
1720.0	1750.0	28.06	27.41	27.06
1780.0	1810.0	27.74	27.43	26.93
1840.0	1870.0	27.59	27.50	27.23
1900.0	1930.0	27.65	27.58	27.47
1960.0	1990.0	27.80	27.65	27.65
2020.0	2050.0	27.99	28.08	28.21
2080.0	2110.0	28.29	28.66	28.84
2140.0	2170.0	28.54	29.09	29.48
2200.0	2230.0	28.58	29.17	29.66
2260.0	2290.0	28.10	28.51	28.97
2320.0	2350.0	27.01	27.33	27.67
2360.0	2390.0	26.16	26.52	26.91
2420.0	2450.0	25.08	25.64	26.35
2460.0	2490.0	24.54	25.25	26.08
2520.0	2550.0	24.43	25.37	26.48
2560.0	2590.0	24.68	25.69	26.96
2620.0	2650.0	25.79	26.90	28.28
2660.0	2690.0	26.81	27.98	29.37
2720.0	2750.0	28.50	30.34	31.86

Frequency Mixer

TUF-11AH

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=1900MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+14	+17	+20		+14	+17	+20		+14	+17	+20
460.0	500.0	6.03	5.23	4.75	500.0	1.75	1.48	1.88	10.0	2.03	2.00	2.02
520.0	560.0	4.68	4.04	3.70	560.0	1.84	1.49	1.82	50.0	1.41	1.33	1.33
580.0	620.0	4.06	3.45	3.16	620.0	1.93	1.48	1.78	90.0	1.43	1.29	1.26
640.0	680.0	3.40	2.89	2.65	680.0	2.10	1.53	1.73	130.0	1.42	1.28	1.25
700.0	740.0	2.82	2.40	2.20	740.0	2.17	1.53	1.68	170.0	1.46	1.33	1.29
760.0	800.0	2.53	2.12	1.92	800.0	2.36	1.58	1.65	210.0	1.46	1.32	1.28
820.0	860.0	2.21	1.85	1.67	860.0	2.48	1.62	1.61	250.0	1.48	1.36	1.32
880.0	920.0	2.05	1.74	1.56	920.0	2.60	1.66	1.57	290.0	1.50	1.37	1.32
940.0	980.0	1.94	1.66	1.50	980.0	2.74	1.70	1.53	330.0	1.50	1.38	1.33
1000.0	1040.0	1.83	1.57	1.45	1040.0	2.80	1.70	1.47	370.0	1.54	1.40	1.36
1060.0	1100.0	1.76	1.53	1.43	1100.0	2.88	1.72	1.43	410.0	1.54	1.40	1.36
1120.0	1160.0	1.65	1.42	1.34	1160.0	2.89	1.70	1.37	450.0	1.55	1.43	1.39
1180.0	1220.0	1.67	1.38	1.27	1220.0	2.97	1.71	1.31	490.0	1.55	1.42	1.38
1240.0	1280.0	1.91	1.59	1.44	1280.0	2.86	1.68	1.26	530.0	1.54	1.42	1.39
1300.0	1340.0	2.23	1.86	1.66	1340.0	2.91	1.67	1.21	570.0	1.54	1.42	1.39
1360.0	1400.0	2.39	1.96	1.75	1400.0	2.81	1.64	1.17	610.0	1.51	1.40	1.37
1420.0	1460.0	2.46	2.04	1.79	1460.0	2.66	1.58	1.11	650.0	1.51	1.40	1.38
1480.0	1520.0	2.53	2.10	1.84	1520.0	2.72	1.58	1.07	690.0	1.47	1.37	1.35
1540.0	1580.0	2.51	2.14	1.88	1580.0	2.53	1.52	1.03	730.0	1.44	1.35	1.35
1600.0	1640.0	2.46	2.14	1.91	1640.0	2.47	1.48	1.02	770.0	1.39	1.31	1.33
1660.0	1700.0	2.35	2.04	1.84	1700.0	2.40	1.45	1.07	810.0	1.33	1.27	1.32
1720.0	1760.0	2.26	1.96	1.79	1760.0	2.24	1.39	1.12	830.0	1.30	1.24	1.29
1780.0	1820.0	2.09	1.83	1.69	1820.0	2.18	1.36	1.18	870.0	1.23	1.20	1.29
1840.0	1880.0	1.97	1.69	1.58	1880.0	2.08	1.34	1.23	890.0	1.20	1.21	1.32
1900.0	1940.0	1.85	1.58	1.48	1940.0	1.95	1.31	1.29	930.0	1.15	1.22	1.36
1960.0	2000.0	1.70	1.44	1.34	2000.0	1.92	1.31	1.34	950.0	1.07	1.31	1.32
2020.0	2060.0	1.57	1.35	1.27	2060.0	1.77	1.27	1.38	990.0	1.10	1.30	1.48
2080.0	2120.0	1.43	1.25	1.25	2120.0	1.67	1.26	1.42	1010.0	1.11	1.32	1.50
2140.0	2180.0	1.32	1.18	1.26	2180.0	1.59	1.24	1.47	1050.0	1.19	1.44	1.64
2200.0	2240.0	1.23	1.20	1.34	2240.0	1.47	1.24	1.51	1070.0	1.27	1.53	1.74
2260.0	2300.0	1.16	1.28	1.44	2300.0	1.42	1.25	1.55	1110.0	1.39	1.67	1.90
2320.0	2360.0	1.20	1.41	1.60	2360.0	1.34	1.26	1.60	1130.0	1.43	1.72	1.95
2360.0	2400.0	1.30	1.54	1.75	2400.0	1.30	1.27	1.62	1170.0	1.60	1.91	2.15
2420.0	2460.0	1.45	1.73	1.95	2460.0	1.23	1.29	1.68	1190.0	1.72	2.06	2.32
2460.0	2500.0	1.61	1.90	2.13	2500.0	1.19	1.30	1.68	1230.0	1.91	2.29	2.56
2520.0	2560.0	1.83	2.16	2.43	2560.0	1.13	1.33	1.74	1250.0	2.02	2.39	2.67
2560.0	2600.0	2.04	2.39	2.68	2600.0	1.09	1.34	1.74	1290.0	2.28	2.69	2.97
2620.0	2660.0	2.34	2.73	3.09	2660.0	1.03	1.37	1.79	1310.0	2.41	2.84	3.14
2660.0	2700.0	2.61	2.99	3.35	2700.0	1.02	1.38	1.78	1350.0	2.69	3.14	3.45
2720.0	2760.0	3.00	3.44	3.81	2760.0	1.07	1.42	1.83	1370.0	2.88	3.35	3.66

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+0	15	14	35	38	30	34	39	44	59
1	-	20	+0	36	32	38	48	64	44	50	38	55
2	59	53	38	57	44	56	48	67	61	50	48	53
3	>90	71	69	76	53	73	65	79	62	>81	67	64
4	>90	>81	80	>81	72	>81	73	>81	74	>81	80	74
5	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
6	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
7	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
8	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
9	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
10	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 1650 MHz; -1.00 dBm.
LO IN: 1690 MHz; +17.00 dBm
IF OUT: 40 MHz; -8.87 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	12	26	29	49	55	53	47	55	52	73
1	-	20	+0	37	31	43	56	85	62	55	56	74
2	40	44	29	49	33	53	42	62	63	61	55	62
3	73	48	45	58	35	55	50	60	61	77	79	62
4	>90	73	56	56	44	60	51	55	54	72	71	68
5	>90	79	71	68	72	65	51	76	79	86	65	87
6	>90	76	81	80	68	65	51	62	62	66	63	77
7	>90	74	81	>91	81	89	78	69	60	80	81	78
8	>90	84	79	84	>91	86	74	77	61	70	71	79
9	>90	90	84	81	88	>91	87	87	77	73	62	88
10	>90	>91	84	87	88	>91	>91	>91	83	>91	71	80
	RF CAL	0	1	2	3	4	5	6	7	8	9	10


LO HARMONICS ORDER

Test conditions: RF IN: 1650 MHz; 9.00 dBm.
LO IN: 1690 MHz; +17.00 dBm
IF OUT: 40 MHz; 1.08 dBm


- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

Typical Performance Curves


Conversion Loss @ IF=40MHz




Conversion Loss vs. LO @ RF=1650MHz




Conversion Loss vs. IF @ RF=1650MHz




Conversion Loss vs. IF @ RF=1389.9MHz




Conversion Loss vs. IF @ RF=1910.1MHz



IP3 Input




Compression @ RF IN=+14dBm




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+0	15	14	35	38	30	34	39	44	59
1	-	20	+0	36	32	38	48	64	44	50	38	55
2	59	53	38	57	44	56	48	67	61	50	48	53
3	>90	71	69	76	53	73	65	79	62	>81	67	64
4	>90	>81	80	>81	72	>81	73	>81	74	>81	80	74
5	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
6	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
7	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
8	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
9	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
10	>90	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81	>81
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions: RF IN: 1650 MHz; -1.00 dBm.
LO IN: 1690 MHz; +17.00 dBm
IF OUT: 40 MHz; -8.87 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	12	26	29	49	55	53	47	55	52	73
1	-	20	+0	37	31	43	56	85	62	55	56	74
2	40	44	29	49	33	53	42	62	63	61	55	62
3	73	48	45	58	35	55	50	60	61	77	79	62
4	>90	73	56	56	44	60	51	55	54	72	71	68
5	>90	79	71	68	72	65	51	76	79	86	65	87
6	>90	76	81	80	68	65	51	62	62	66	63	77
7	>90	74	81	>91	81	89	78	69	60	80	81	78
8	>90	84	79	84	>91	86	74	77	61	70	71	79
9	>90	90	84	81	88	>91	87	87	77	73	62	88
10	>90	>91	84	87	88	>91	>91	>91	83	>91	71	80
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions: RF IN: 1650 MHz; 9.00 dBm.
LO IN: 1690 MHz; +17.00 dBm
IF OUT: 40 MHz; 1.08 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS




REV. X3
TUF-11AH
08/11/2010
Page 3 of 3

B02

B13

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
B02	.480 (12.19)	.500 (12.70)	.240 (6.10)	.255 (6.48)	.210 (5.33)	.230 (5.84)	.16 (4.06)	.100 (2.54)	.14 (3.56)	.20 (5.08)	.020 (.51)	1.9
B13			.390 (9.91)	.405 (10.29)								2.3

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D