

NON-CATALOG

Surface Mount Voltage Variable Equalizer

VAEQ-1000-75+

75 Ω

50 to 1000 MHz

The Big Deal

- Adjustable attenuation slope
- IP3 +48 dBm typical
- Minimal deviation from linear loss, ± 0.6 dB



CASE STYLE: HE1354

Product Overview

The VAEQ-1000-75+ is a 75 Ω Voltage Variable Equalizer built into a shielded case (size of .394"x.394"x.150"). This model offers excellent performance over a wide frequency range of 50 to 1000 MHz with the variable slope providing great flexibility in a small package.

The VAEQ-1000-75+ is often used to compensate RF chain gain flatness or cable loss versus frequency.

Key Features

Feature	Advantages
Low power consumption: • Supply voltage +5V_{DC} at max 16mA • Control voltage 0-10V at max 20mA	Allows for use in applications with power constraints.
Adjustable attenuation slope (Control voltage of 0V to 10V)	Allows adjusting the slope to compensate for the precise losses encountered.
High linearity (IP3 +48 dBm typ.)	Low distortion enabling improved system performance.
Minimal deviation from linear loss over frequency range: ± 0.6 dB	Provides low signal distortion over the passband.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount Voltage Variable Equalizer

VAEQ-1000-75+

75Ω

50 to 1000 MHz

Features

- Wide bandwidth
- Low insertion loss
- Low deviation from linear loss, ± 0.6 dB typ.
- High IP3 +48 dBm typ.
- Shielded case
- Aqueous washable

Applications

- CATV
- Cable loss compensation
- Instrumentation



CASE STYLE: HE1354

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C, $V_+ = 5V_{DC}$ unless otherwise noted


Parameter	Condition	Min.	Typ.	Max.	Units
Frequency Range		50		1000	MHz
Insertion Loss	50 MHz, Control Voltage, 0 - 10V 1000 MHz, Control Voltage, 0 - 10V		14.6 - 1.5 5.3 - 3.0		dB
Deviation from Linear Loss	50 - 1000 MHz, Control Voltage 0 - 10V		± 0.6		dB
IP3	50 - 1000 MHz, Control Voltage, 2.5 - 10V	+35	+48		dBm
0.2 dB Compression	50 - 1000 MHz, Control Voltage, 0 - 10V		+30		dBm
Input Return Loss	50 - 1000 MHz, Control Voltage, 0 - 10V		15.0		dB
Output Return Loss	50 - 1000 MHz, Control Voltage, 0 - 10V		12.5		dB
Supply Voltage (V_+)	50 - 1000 MHz, Control Voltage, 0 - 10V		5.0		V
Supply Current	50 - 1000 MHz, Control Voltage, 8.6V 50 - 1000 MHz, Control Voltage, 0V		0 8	16	mA
Control Current	50 - 1000 MHz, Control Voltage, 10V 50 - 1000 MHz, Control Voltage, 2.5V		15 0	20	mA

Maximum Ratings

Parameter	Ratings
Operating Temperature	0°C to 85°C
Storage Temperature	-55°C to 100°C
Input Power	+23dBm
Control voltage	12V
Supply Voltage (V_+)	7V

Permanent damage may occur if any of these limits are exceeded.

Simplified Functional Diagram



Pad Connections

Function	Pin Number
RF IN	1
RF OUT	6
V CONTROL	3
V_+	4
GROUND	2,5

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
M171222
VAEQ-1000-75+
EDR-11439MP
RAV
181128
Page 2 of 5

VAEQ-1000-75+

TOP SIDE

6 5 4

1 2 3

INDEX

SIDE VIEW

C

BOTTOM SIDE

A B C D E F G H J K

Suggested Layout

METALLIZATION

SOLDER RESIST

L TYP. M TYP.

A	B	C	D	E	F	G	H	J	K	L	M	wt.
.394	.394	.150	.122	.075	.098	.038	.026	.051	.038	.046	.434	grams
10.01	10.01	3.81	3.10	1.90	2.49	0.97	0.66	1.29	0.97	1.17	11.02	0.7

Figure 1: Typical Package Dimensions

Dimensions shown:

- Package Width: $.030'' \pm .002''$ [0.76 ± .05] LINE WIDTH 4 PL.
- Package Height: $.080''$ [2.0] TYP.
- Pin Pitch: $.080''$ [2.0] TYP.
- Pin Width: $.020''$ [0.51] PTH TYP×20.
- Pin Diameter: $.030'' \pm .002''$ [0.76 ± .05] LINE WIDTH 4 PL.
- Package Outline (dashed line)
- PIN 1

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Function	Pin Number
RF IN	1
RF OUT	6
V CONTROL	3
V+	4
GROUND	2,5

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Technical specifications and performance data contained in this specification document are based on Mini-Circuits's applicable established test performance criteria and measure test instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit [Mini-Circuits' website at www.minicircuits.com/MC/Store/terms](http://www.minicircuits.com/MC/Store/terms).

NON-CATALOG

Typical Performance Data

VAEQ-1000-75+

Frequency (MHz)	Insertion Loss (dB)		Input Return Loss (dB)		Output Return Loss (dB)		Deviation from Linear Loss (dB)		Insertion Phase (deg)		Input IP3 (dBm)	
	Vcontrol 0V	2.7V	Vcontrol 0V	2.7V	Vcontrol 0V	2.7V	Vcontrol 0V	2.7V	Vcontrol 0V	2.7V	Vcontrol 0V	2.7V
50	14.58	14.47	23.84	23.86	23.15	24.74	1.31	1.24	20.22	19.83	46.14	50.99
100	13.78	13.69	24.74	24.70	23.33	24.70	1.01	0.96	14.35	13.90	53.35	50.17
150	13.03	12.96	24.32	24.21	22.70	23.31	0.75	0.72	12.27	11.77	54.98	50.63
200	12.20	12.16	24.83	24.70	21.70	21.82	0.42	0.42	10.05	9.54	56.27	52.16
250	11.38	11.36	23.01	22.98	20.31	19.97	0.10	0.11	7.01	6.54	54.28	52.06
300	10.57	10.56	22.25	22.27	18.96	18.50	0.21	0.20	3.09	2.68	56.76	53.11
350	9.83	9.84	20.28	20.27	17.34	16.83	0.45	0.43	1.62	1.98	56.08	54.12
400	9.13	9.13	19.04	19.00	15.67	15.22	0.66	0.63	6.94	7.23	55.47	54.47
450	8.52	8.54	17.16	17.17	14.51	14.10	0.76	0.73	12.75	12.97	53.63	53.41
500	7.96	7.98	15.68	15.72	13.05	12.71	0.83	0.80	18.96	19.10	54.32	54.63
550	7.49	7.51	14.28	14.31	12.04	11.77	0.80	0.78	25.45	25.52	53.63	52.45
600	7.04	7.06	12.95	12.94	10.81	10.61	0.75	0.73	32.00	32.01	52.69	53.29
650	6.70	6.72	11.86	11.85	9.88	9.72	0.59	0.58	38.90	38.87	53.62	52.55
700	6.33	6.34	10.61	10.62	8.96	8.84	0.47	0.46	45.64	45.56	52.38	52.19
750	6.12	6.12	9.83	9.83	8.14	8.05	0.18	0.18	52.69	52.58	53.19	52.00
800	5.81	5.81	8.76	8.75	7.45	7.40	0.01	0.00	59.62	59.50	52.10	51.29
850	5.70	5.70	8.10	8.10	6.74	6.70	0.40	0.39	66.56	66.43	51.37	52.40
900	5.44	5.44	7.24	7.24	6.17	6.15	0.64	0.61	73.52	73.38	51.24	51.19
1000	5.22	5.22	6.05	6.04	5.08	5.08	1.42	1.38	86.98	86.82	50.29	50.30


Frequency (MHz)	Insertion Loss (dB)		Input Return Loss (dB)		Output Return Loss (dB)		Deviation from Linear Loss (dB)		Insertion Phase (deg)		Input IP3 (dBm)	
	Vcontrol 6V	10V	Vcontrol 6V	10V	Vcontrol 6V	10V	Vcontrol 6V	10V	Vcontrol 6V	10V	Vcontrol 6V	10V
50	4.06	1.48	12.72	22.56	11.34	22.18	0.04	0.27	2.17	0.25	45.69	47.15
100	4.00	1.44	12.90	22.19	11.58	22.42	0.02	0.14	9.35	6.69	49.74	51.69
150	3.99	1.45	13.12	20.87	11.72	21.19	0.05	0.07	15.53	12.13	52.59	54.84
200	3.96	1.47	13.40	19.68	11.76	19.49	0.06	0.00	21.42	17.40	52.35	57.91
250	3.95	1.51	13.67	18.25	12.06	18.27	0.08	0.04	27.18	22.49	55.08	58.79
300	3.90	1.55	13.92	17.18	12.08	16.85	0.07	0.08	32.91	27.71	55.82	57.66
350	3.87	1.64	14.41	16.23	12.36	15.85	0.08	0.08	38.52	32.64	54.72	55.52
400	3.80	1.70	14.62	15.35	12.53	14.64	0.05	0.10	44.12	37.79	53.69	56.13
450	3.73	1.81	15.31	14.83	12.93	14.15	0.02	0.08	49.48	42.52	52.46	52.91
500	3.64	1.90	15.42	14.03	13.16	13.26	0.03	0.08	54.93	47.26	54.31	54.43
550	3.56	2.02	16.22	13.86	13.35	12.82	0.08	0.04	60.16	51.71	53.33	52.33
600	3.43	2.09	15.96	13.11	13.51	12.16	0.17	0.05	65.34	55.73	54.39	54.04
650	3.37	2.23	16.50	13.20	13.31	11.73	0.19	0.00	70.51	59.89	53.68	52.62
700	3.26	2.29	15.75	12.63	13.24	11.45	0.26	0.03	75.63	63.32	51.15	51.49
750	3.28	2.46	15.74	12.95	12.57	11.11	0.21	0.06	80.59	67.45	54.43	53.90
800	3.25	2.50	14.54	12.57	12.02	11.04	0.19	0.02	85.53	70.91	52.92	52.63
850	3.36	2.62	14.07	12.84	11.06	10.69	0.05	0.05	90.40	75.18	54.23	54.00
900	3.42	2.63	13.12	12.56	10.33	10.53	0.05	0.03	95.89	79.34	52.96	52.13
1000	4.00	3.04	11.91	12.42	8.81	9.85	0.70	0.22	107.25	88.90	53.31	52.57

Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




**VAEQ-1000-75+
INSERTION LOSS Vs. FREQUENCY
OVER CONTROL VOLTAGES**




**VAEQ-1000-75+
INPUT RETURN LOSS Vs. FREQUENCY
OVER CONTROL VOLTAGES**




**VAEQ-1000-75+
OUTPUT RETURN LOSS Vs. FREQUENCY
OVER CONTROL VOLTAGES**




**VAEQ-1000-75+
PHASE UNBALANCE Vs. FREQUENCY
OVER CONTROL VOLTAGES**



**VAEQ-1000-75+
DEVIATION FROM LINEAR LOSS Vs. FREQUENCY
OVER CONTROL VOLTAGES**



**VAEQ-1000-75+
IP3 Vs. FREQUENCY
OVER CONTROL VOLTAGES**



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Voltage Variable Equalizer, 75Ω

VAEQ-1000-75+

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB) Vcontrol		Input Return Loss (dB) Vcontrol		Output Return Loss (dB) Vcontrol		Deviation from Linear Loss (dB) Vcontrol		Insertion Phase (deg) Vcontrol		Input IP3 (dBm) Vcontrol	
	0V		0V		0V		0V		0V		0V	
	2.7V		2.7V		2.7V		2.7V		2.7V		2.7V	
50	14.58	14.47	23.84	23.86	23.15	24.74	-1.31	-1.24	20.22	19.83	46.14	50.99
75	14.15	14.04	24.46	24.46	23.37	24.91	-1.12	-1.06	16.16	15.77	49.75	50.58
100	13.78	13.69	24.74	24.70	23.33	24.70	-1.01	-0.96	14.35	13.90	53.35	50.17
125	13.42	13.33	24.38	24.30	22.89	23.90	-0.89	-0.85	13.24	12.75	54.17	50.40
150	13.03	12.96	24.32	24.21	22.70	23.31	-0.75	-0.72	12.27	11.77	54.98	50.63
175	12.62	12.56	24.86	24.71	22.52	22.86	-0.59	-0.57	11.26	10.75	55.63	51.40
200	12.20	12.16	24.83	24.70	21.70	21.82	-0.42	-0.42	10.05	9.54	56.27	52.16
225	11.80	11.76	23.80	23.72	20.75	20.62	-0.26	-0.26	8.63	8.13	55.28	52.11
250	11.38	11.36	23.01	22.98	20.31	19.97	-0.10	-0.11	7.01	6.54	54.28	52.06
275	10.97	10.95	22.80	22.82	19.91	19.47	0.06	0.05	5.17	4.74	55.52	52.59
300	10.57	10.56	22.25	22.27	18.96	18.50	0.21	0.20	3.09	2.68	56.76	53.11
325	10.20	10.19	21.11	21.13	18.00	17.50	0.34	0.32	0.78	0.39	56.42	53.62
350	9.83	9.84	20.28	20.27	17.34	16.83	0.45	0.43	-1.62	-1.98	56.08	54.12
375	9.47	9.48	19.83	19.80	16.57	16.09	0.57	0.54	-4.16	-4.48	55.78	54.30
400	9.13	9.13	19.04	19.00	15.67	15.22	0.66	0.63	-6.94	-7.23	55.47	54.47
425	8.82	8.84	17.92	17.90	15.02	14.59	0.71	0.68	-9.84	-10.09	54.55	53.94
450	8.52	8.54	17.16	17.17	14.51	14.10	0.76	0.73	-12.75	-12.97	53.63	53.41
475	8.23	8.24	16.56	16.60	13.77	13.39	0.81	0.78	-15.80	-15.97	53.98	54.02
500	7.96	7.98	15.68	15.72	13.05	12.71	0.83	0.80	-18.96	-19.10	54.32	54.63
525	7.72	7.74	14.80	14.84	12.58	12.27	0.82	0.79	-22.19	-22.29	53.98	53.54
550	7.49	7.51	14.28	14.31	12.04	11.77	0.80	0.78	-25.45	-25.52	53.63	52.45
575	7.26	7.28	13.76	13.77	11.34	11.11	0.78	0.75	-28.70	-28.74	53.16	52.87
600	7.04	7.06	12.95	12.94	10.81	10.61	0.75	0.73	-32.00	-32.01	52.69	53.29
625	6.85	6.87	12.26	12.25	10.42	10.24	0.69	0.67	-35.49	-35.48	53.16	52.92
650	6.70	6.72	11.86	11.85	9.88	9.72	0.59	0.58	-38.90	-38.87	53.62	52.55
675	6.53	6.54	11.30	11.31	9.32	9.19	0.52	0.51	-42.16	-42.09	53.00	52.37
700	6.33	6.34	10.61	10.62	8.96	8.84	0.47	0.46	-45.64	-45.56	52.38	52.19
725	6.20	6.21	10.13	10.14	8.61	8.51	0.34	0.34	-49.31	-49.22	52.79	52.10
750	6.12	6.12	9.83	9.83	8.14	8.05	0.18	0.18	-52.69	-52.58	53.19	52.00
775	5.97	5.97	9.31	9.30	7.75	7.68	0.08	0.08	-55.96	-55.86	52.65	51.65
800	5.81	5.81	8.76	8.75	7.45	7.40	-0.01	0.00	-59.62	-59.50	52.10	51.29
825	5.74	5.74	8.41	8.40	7.09	7.04	-0.19	-0.17	-63.35	-63.23	51.74	51.85
850	5.70	5.70	8.10	8.10	6.74	6.70	-0.40	-0.39	-66.56	-66.43	51.37	52.40
875	5.57	5.57	7.64	7.63	6.47	6.44	-0.52	-0.50	-69.74	-69.60	51.31	51.80
900	5.44	5.44	7.24	7.24	6.17	6.15	-0.64	-0.61	-73.52	-73.38	51.24	51.19
930	5.43	5.43	6.93	6.92	5.78	5.76	-0.93	-0.90	-77.68	-77.55	-	-
950	5.39	5.38	6.67	6.66	5.60	5.59	-1.09	-1.06	-80.04	-79.90	52.30	51.09
975	5.27	5.26	6.29	6.28	5.39	5.39	-1.22	-1.19	-83.46	-83.32	51.30	50.70
1000	5.22	5.22	6.05	6.04	5.08	5.08	-1.42	-1.38	-86.98	-86.82	50.29	50.30

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Voltage Variable Equalizer, 75Ω

VAEQ-1000-75+

Typical Performance Data

Frequency (MHz)	Insertion Loss		Input Return Loss		Output Return Loss		Deviation from Linear Loss		Insertion Phase		Input IP3	
	(dB) Vcontrol		(dB) Vcontrol		(dB) Vcontrol		(dB) Vcontrol		(deg) Vcontrol		(dBm) Vcontrol	
	6V	10V	6V	10V	6V	10V	6V	10V	6V	10V	6V	10V
50	4.06	1.48	12.72	22.56	11.34	22.18	-0.04	-0.27	-2.17	-0.25	45.69	47.15
75	4.02	1.45	12.85	22.63	11.52	22.66	-0.02	-0.20	-6.00	-3.74	47.72	49.42
100	4.00	1.44	12.90	22.19	11.58	22.42	-0.02	-0.14	-9.35	-6.69	49.74	51.69
125	4.01	1.44	12.93	21.45	11.61	21.78	-0.05	-0.10	-12.50	-9.46	51.17	53.27
150	3.99	1.45	13.12	20.87	11.72	21.19	-0.05	-0.07	-15.53	-12.13	52.59	54.84
175	3.96	1.45	13.36	20.44	11.79	20.48	-0.04	-0.03	-18.49	-14.81	52.47	56.38
200	3.96	1.47	13.40	19.68	11.76	19.49	-0.06	0.00	-21.42	-17.40	52.35	57.91
225	3.96	1.49	13.42	18.78	11.86	18.70	-0.08	0.02	-24.32	-19.93	53.72	58.35
250	3.95	1.51	13.67	18.25	12.06	18.27	-0.08	0.04	-27.18	-22.49	55.08	58.79
275	3.91	1.53	13.90	17.87	12.10	17.67	-0.07	0.06	-30.00	-25.11	55.45	58.23
300	3.90	1.55	13.92	17.18	12.08	16.85	-0.07	0.08	-32.91	-27.71	55.82	57.66
325	3.90	1.60	14.06	16.51	12.22	16.27	-0.09	0.08	-35.77	-30.20	55.27	56.59
350	3.87	1.64	14.41	16.23	12.36	15.85	-0.08	0.08	-38.52	-32.64	54.72	55.52
375	3.82	1.67	14.61	15.95	12.38	15.21	-0.05	0.10	-41.29	-35.17	54.21	55.83
400	3.80	1.70	14.62	15.35	12.53	14.64	-0.05	0.10	-44.12	-37.79	53.69	56.13
425	3.78	1.77	14.89	14.91	12.82	14.43	-0.05	0.08	-46.84	-40.27	53.08	54.52
450	3.73	1.81	15.31	14.83	12.93	14.15	-0.02	0.08	-49.48	-42.52	52.46	52.91
475	3.68	1.85	15.41	14.56	12.93	13.59	0.01	0.09	-52.22	-44.79	53.39	53.67
500	3.64	1.90	15.42	14.03	13.16	13.26	0.03	0.08	-54.93	-47.26	54.31	54.43
525	3.60	1.96	15.82	13.81	13.41	13.18	0.06	0.06	-57.56	-49.67	53.82	53.38
550	3.56	2.02	16.22	13.86	13.35	12.82	0.08	0.04	-60.16	-51.71	53.33	52.33
575	3.50	2.06	16.09	13.56	13.30	12.32	0.12	0.04	-62.71	-53.61	53.86	53.19
600	3.43	2.09	15.96	13.11	13.51	12.16	0.17	0.05	-65.34	-55.73	54.39	54.04
625	3.39	2.15	16.27	13.06	13.57	12.09	0.18	0.04	-68.00	-57.92	54.04	53.33
650	3.37	2.23	16.50	13.20	13.31	11.73	0.19	0.00	-70.51	-59.89	53.68	52.62
675	3.31	2.26	16.08	12.90	13.19	11.45	0.23	0.01	-72.96	-61.62	52.42	52.06
700	3.26	2.29	15.75	12.63	13.24	11.45	0.26	0.03	-75.63	-63.32	51.15	51.49
725	3.26	2.37	15.84	12.78	13.01	11.37	0.24	-0.01	-78.27	-65.28	52.79	52.70
750	3.28	2.46	15.74	12.95	12.57	11.11	0.21	-0.06	-80.59	-67.45	54.43	53.90
775	3.26	2.48	15.07	12.71	12.30	11.04	0.21	-0.04	-82.92	-69.33	53.68	53.27
800	3.25	2.50	14.54	12.57	12.02	11.04	0.19	-0.02	-85.53	-70.91	52.92	52.63
825	3.30	2.56	14.39	12.77	11.51	10.86	0.13	-0.03	-88.09	-72.77	53.58	53.32
850	3.36	2.62	14.07	12.84	11.06	10.69	0.05	-0.05	-90.40	-75.18	54.23	54.00
875	3.37	2.61	13.47	12.60	10.75	10.67	0.02	0.00	-92.90	-77.51	53.60	53.07
900	3.42	2.63	13.12	12.56	10.33	10.53	-0.05	0.03	-95.89	-79.34	52.96	52.13
930	3.59	2.74	12.91	12.71	9.78	10.25	-0.24	-0.04	-99.27	-81.74	-	-
950	3.69	2.81	12.62	12.63	9.55	10.19	-0.36	-0.07	-101.35	-83.88	54.40	53.31
975	3.80	2.89	12.15	12.42	9.26	10.13	-0.49	-0.11	-104.30	-86.69	53.86	52.94
1000	4.00	3.04	11.91	12.42	8.81	9.85	-0.70	-0.22	-107.25	-88.90	53.31	52.57

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




Voltage Variable Equalizer, 75Ω


VAEQ-1000-75+

Typical Performance Curves


INSERTION LOSS
Vs.FREQUENCY OVER CONTROL VOLTAGES




INPUT RETURN LOSS
Vs.FREQUENCY OVER CONTROL VOLTAGES




OUTPUT RETURN LOSS
Vs.FREQUENCY OVER CONTROL VOLTAGES




PHASE UNBALANCE
Vs.FREQUENCY OVER CONTROL VOLTAGES



DEVIATION FROM LINEAR LOSS
Vs.FREQUENCY OVER CONTROL VOLTAGES



IP3
Vs.FREQUENCY OVER CONTROL VOLTAGES



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




Case Style

HE

HE1354

Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HE1354	.394 (10.01)	.394 (10.01)	.150 (3.81)	.122 (3.10)	.075 (1.90)	.098 (2.49)	.038 (0.97)	.026 (0.66)	.051 (1.29)	.038 (0.97)	.046 (1.17)	.434 (11.02)	0.7

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F37



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
24	16	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200
				500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M124493	NEW RELEASE (FROM RAVON)	09/09	EM	YB
OR	R77678	NEW RELEASE (FROM RAVON)	09/09	EM	YB

SUGGESTED MOUNTING CONFIGURATION
FOR HE1354 CASE STYLE, qg PIN CONNECTION, 75 OHM

**NOTE:**

1. TRACE WIDTH IS SHOWN FOR R04350B WITH DIELECTRIC THICKNESS $.030'' \pm .002''$. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

EM (RAVON)

16 SEP 09

TOLERANCES ON:

CHECKED

HH (RAVON)

21 SEP 09

2 PL DECIMALS ± .005

APPROVED

YB (RAVON)

21 SEP 09

ANGLES ±

FRACTIONS ±

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
 Brooklyn NY 11235

PL, qg, HE1354, TB-549+, 75 OHM

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-315


REV:
OR

FILE: 98PL315


SCALE: 5:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-549+



Schematic Diagram

Notes:

1. BNC Female connectors.
2. PCB Material: Rogers R04350B or equivalent,
Dielectric constant=3.48, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	0° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215