

Surface Mount

Voltage Variable Equalizer

VAEQ-1220-75+

75 Ω

50 to 1220 MHz

The Big Deal

- Adjustable attenuation slope
- IP3 +50 dBm typical
- Minimal deviation from linear loss, ± 0.5 dB



CASE STYLE: HE1354

Product Overview

The VAEQ-1220-75+ is a 75 Ω Voltage Variable Equalizer built into a shielded case (size of 394"x.394"x.150", 10 x 10 x 3.8 mm). This model offers excellent performance over a wide frequency range of 50 to 1220 MHz with the variable slope providing great flexibility in a small 10 mm package.

The VAEQ-1220-75+ is often used to compensate RF chain gain flatness or cable loss versus frequency.

Key Features

Feature	Advantages
Low power consumption: • Supply voltage +5V_{DC} at max 16mA • Control voltage 0-7V at max 20mA	Allows for use in applications with power constraints.
Adjustable attenuation slope (Control voltage of 0V to 7V)	Allows adjusting the slope to compensate for the precise losses encountered.
High linearity (IP3 +50 dBm typ.)	Low distortion enabling improved system performance.
Minimal deviation from linear loss over frequency range: ± 0.5 dB	Provides low signal distortion over the passband.



Features

- Wide bandwidth
- Low insertion loss
- Low deviation from linear loss, ± 0.5 dB typ.
- High IP3 +50 dBm typ.
- Shielded case
- Aqueous washable

Applications

- Cable loss compensation
- Instrumentation
- DOCSIS 3.1



CASE STYLE: HE1354

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C, $V_+ = 5V_{DC}$ unless otherwise noted

Parameter	Condition	Min.	Typ.	Max.	Units
Frequency Range		50		1220	MHz
Insertion Loss	50 MHz, Control Voltage, 0 - 7V 1220 MHz, Control Voltage, 0 - 7V		15 - 1.7 4.7 - 3.3		dB
Deviation from Linear Loss	Control Voltage 0 - 7V		± 0.5		dB
IP3	Control Voltage, 2.5 - 7V	+42	+50		dBm
1 dB Compression	Control Voltage, 0 - 7V		+30		dBm
Input Return Loss	Control Voltage, 0 - 7V		13		dB
Output Return Loss	Control Voltage, 0 - 7V		11.5		dB
Supply Voltage (V+)	Control Voltage, 0 - 7V	3.5	5	5.5	V
Supply Current	Control Voltage 7V, Control Voltage 0V,		0 10	16	mA
Control Current	Control Voltage 7V Control Voltage 2.5V		12 0	20	mA

Maximum Ratings

Parameter	Ratings
Operating Temperature	0°C to 85°C
Storage Temperature	-55°C to 100°C
Input Power	+23 dBm
Control voltage	11 V
Supply Voltage (V+)	7 V

Permanent damage may occur if any of these limits are exceeded.

Simplified Functional Diagram**Pad Connections**

Function	Pin Number
RF IN	1
RF OUT	6
V CONTROL	3
V+	4
GROUND	2,5

VAEQ-1220-75+







Page 3 of 5

@ $V_{\text{Control}}=0\text{V}$ & $V_{\text{Control}}=2.5\text{V}$

Frequency (MHz)	Insertion Loss (dB)		Input Return Loss (dB)		Output Return Loss (dB)		Deviation from Linear Loss (dB)		Insertion Phase (deg)		Input IP3 (dBm)	
	V_{control} 0V	2.5V	V_{control} 0V	2.5V	V_{control} 0V	2.5V	V_{control} 0V	2.5V	V_{control} 0V	2.5V	V_{control} 0V	2.5V
50	14.97	14.76	24.08	24.10	21.91	24.23	0.93	0.84	18.62	17.84	47.40	48.28
100	14.32	14.15	24.53	24.53	21.25	23.03	0.73	0.66	10.22	9.50	60.34	53.63
150	13.78	13.63	24.08	24.06	20.66	21.64	0.62	0.58	6.52	5.74	55.68	54.01
200	13.18	13.06	23.10	23.06	19.65	20.03	0.47	0.44	3.31	2.51	57.62	54.88
300	11.90	11.83	20.92	20.87	17.22	16.97	0.08	0.09	4.28	5.04	58.28	55.49
400	10.64	10.61	18.50	18.45	14.91	14.46	0.29	0.26	14.06	14.72	58.50	56.06
450	10.06	10.04	17.22	17.19	13.78	13.33	0.43	0.39	19.72	20.32	50.58	49.73
500	9.50	9.49	16.21	16.18	12.80	12.35	0.54	0.50	25.76	26.27	60.53	57.72
550	8.99	8.99	15.06	15.04	11.90	11.48	0.61	0.57	32.19	32.63	48.79	48.49
600	8.52	8.53	14.09	14.07	11.03	10.65	0.64	0.59	38.84	39.21	57.13	56.17
700	7.70	7.72	12.15	12.14	9.46	9.16	0.57	0.53	52.82	53.01	55.44	54.88
800	7.01	7.03	10.39	10.38	8.11	7.92	0.37	0.35	67.27	67.31	58.24	57.12
900	6.40	6.41	8.87	8.86	6.95	6.84	0.10	0.10	81.98	81.95	57.49	55.26
950	6.10	6.11	8.24	8.23	6.45	6.36	0.05	0.04	89.89	89.85	50.51	49.85
1000	5.78	5.78	7.57	7.56	6.09	6.03	0.17	0.15	97.44	97.36	55.94	53.49
1100	5.23	5.24	6.69	6.68	5.48	5.46	0.51	0.48	114.11	114.00	58.18	55.65
1150	4.94	4.94	6.30	6.30	5.31	5.30	0.66	0.62	122.37	122.27	50.19	48.90
1200	4.85	4.85	6.12	6.12	5.30	5.30	1.01	0.97	132.09	132.01	54.10	53.63
1220	4.73	4.74	6.02	6.01	5.28	5.29	1.07	1.02	135.30	135.22	49.70	48.51

@ $V_{\text{Control}}=5\text{V}$ & $V_{\text{Control}}=7\text{V}$

Frequency (MHz)	Insertion Loss (dB)		Input Return Loss (dB)		Output Return Loss (dB)		Deviation from Linear Loss (dB)		Insertion Phase (deg)		Input IP3 (dBm)	
	V_{control} 5.2V	7V	V_{control} 5.2V	7V	V_{control} 5.2V	7V	V_{control} 5.2V	7V	V_{control} 5.2V	7V	V_{control} 5V	7V
50	4.45	1.68	12.45	26.93	14.38	25.98	0.04	0.28	4.15	4.48	48.97	47.63
100	4.41	1.64	12.55	26.07	14.47	25.32	0.00	0.16	10.59	11.69	51.66	51.67
150	4.40	1.66	12.67	23.74	14.64	23.01	0.00	0.08	16.54	18.35	53.40	58.60
200	4.41	1.69	12.66	21.42	14.55	20.73	0.00	0.02	22.37	24.83	52.99	55.18
300	4.41	1.77	12.69	18.13	14.23	17.09	0.00	0.07	33.85	37.59	53.80	54.06
400	4.41	1.90	12.67	15.73	13.76	14.66	0.01	0.12	45.25	50.18	53.53	53.09
450	4.43	1.99	12.64	14.68	13.44	13.60	0.02	0.12	50.93	56.46	50.97	48.66
500	4.42	2.08	12.73	14.04	13.23	12.84	0.02	0.13	56.61	62.63	54.41	51.91
550	4.42	2.19	12.66	13.28	12.95	12.15	0.02	0.11	62.31	68.79	49.35	48.31
600	4.42	2.32	12.83	12.86	12.61	11.52	0.02	0.07	67.93	74.76	54.25	51.00
700	4.40	2.58	12.78	12.02	11.95	10.55	0.01	0.01	79.31	86.37	53.65	51.32
800	4.37	2.84	12.46	11.45	11.08	9.85	0.04	0.09	90.83	97.36	54.11	53.17
900	4.34	3.04	11.78	11.18	9.98	9.26	0.06	0.11	102.62	107.82	54.10	56.38
950	4.35	3.10	11.42	11.20	9.34	8.94	0.06	0.09	108.88	113.31	49.23	51.89
1000	4.35	3.14	10.74	11.00	8.78	8.69	0.06	0.03	114.71	118.35	53.04	55.90
1100	4.47	3.30	9.66	10.86	7.49	7.82	0.06	0.01	126.52	128.84	56.51	54.28
1150	4.46	3.33	8.95	10.42	6.90	7.34	0.06	0.04	131.47	133.03	48.45	53.41
1200	4.52	3.39	8.32	9.87	6.50	6.99	0.11	0.08	137.12	137.71	53.79	51.76
1220	4.43	3.30	8.00	9.49	6.36	6.86	0.02	0.20	138.75	138.82	48.81	50.74



Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Voltage Variable Equalizer, 75Ω

VAEQ-1220-75+

Typical Performance Data @ V+=5V

Frequency (MHz)	Insertion Loss (dB) Vcontrol		Input Return Loss (dB) Vcontrol		Output Return Loss (dB) Vcontrol		Deviation from Linear Loss (dB) Vcontrol		Insertion Phase (deg) Vcontrol		Frequency (MHz)	Input IP3 (dBm) Vcontrol	
	0V	2.5V	0V	2.5V	0V	2.5V	0V	2.5V	0V	2.5V		0V	2.5V
10	20.09	19.72	20.26	20.33	32.73	29.77	-	-	60.06	58.54	10	43.10	40.29
30	15.68	15.45	23.04	23.06	22.83	24.96	-	-	28.74	27.79	30	50.16	52.30
50	14.97	14.76	24.08	24.10	21.91	24.23	-0.93	-0.84	18.62	17.84	50	47.40	48.28
70	14.66	14.47	24.48	24.49	21.61	23.80	-0.80	-0.72	13.96	13.23	80	51.21	55.57
90	14.43	14.25	24.57	24.58	21.36	23.30	-0.75	-0.68	11.23	10.52	100	60.34	53.63
110	14.22	14.05	24.46	24.46	21.14	22.75	-0.71	-0.65	9.35	8.61	150	55.68	54.01
130	14.00	13.84	24.29	24.28	20.92	22.19	-0.67	-0.62	7.85	7.09	200	57.62	54.88
150	13.78	13.63	24.08	24.06	20.66	21.64	-0.62	-0.58	6.52	5.74	300	58.28	55.49
170	13.54	13.41	23.76	23.73	20.32	21.03	-0.57	-0.53	5.24	4.46	400	58.50	56.06
200	13.18	13.06	23.10	23.06	19.65	20.03	-0.47	-0.44	3.31	2.51	450	50.58	49.73
220	12.93	12.82	22.64	22.59	19.18	19.37	-0.40	-0.38	1.95	1.16	500	60.53	57.72
240	12.68	12.58	22.23	22.17	18.72	18.75	-0.32	-0.31	0.52	-0.28	550	48.79	48.49
260	12.42	12.33	21.87	21.81	18.24	18.15	-0.24	-0.24	-0.98	-1.77	600	57.13	56.17
300	11.90	11.83	20.92	20.87	17.22	16.97	-0.08	-0.09	-4.28	-5.04	700	55.44	54.88
320	11.64	11.58	20.35	20.30	16.71	16.41	0.00	-0.01	-6.07	-6.81	800	58.24	57.12
340	11.39	11.34	19.83	19.78	16.25	15.89	0.08	0.06	-7.95	-8.68	900	57.49	55.26
360	11.14	11.09	19.38	19.33	15.81	15.40	0.15	0.13	-9.90	-10.60	950	50.51	49.85
380	10.89	10.85	18.96	18.91	15.37	14.94	0.22	0.19	-11.92	-12.60	1000	55.94	53.49
400	10.64	10.61	18.50	18.45	14.91	14.46	0.29	0.26	-14.06	-14.72	1100	58.18	55.65
420	10.40	10.38	17.98	17.94	14.44	13.99	0.35	0.32	-16.29	-16.92	1150	50.19	48.90
450	10.06	10.04	17.22	17.19	13.78	13.33	0.43	0.39	-19.72	-20.32	1200	54.10	53.63
500	9.50	9.49	16.21	16.18	12.80	12.35	0.54	0.50	-25.76	-26.27	1220	49.70	48.51
550	8.99	8.99	15.06	15.04	11.90	11.48	0.61	0.57	-32.19	-32.63	1300	53.06	50.98
600	8.52	8.53	14.09	14.07	11.03	10.65	0.64	0.59	-38.84	-39.21	1400	54.02	50.37
650	8.08	8.09	13.11	13.10	10.16	9.82	0.64	0.60	-45.83	-46.11			
700	7.70	7.72	12.15	12.14	9.46	9.16	0.57	0.53	-52.82	-53.01			
750	7.32	7.33	11.34	11.33	8.76	8.52	0.51	0.48	-60.19	-60.32			
770	7.20	7.22	10.92	10.92	8.50	8.28	0.45	0.42	-63.09	-63.21			
800	7.01	7.03	10.39	10.38	8.11	7.92	0.37	0.35	-67.27	-67.31			
820	6.87	6.88	10.11	10.10	7.86	7.68	0.34	0.32	-70.19	-70.22			
840	6.73	6.74	9.84	9.84	7.62	7.45	0.30	0.29	-73.33	-73.37			
860	6.63	6.65	9.53	9.53	7.40	7.25	0.22	0.21	-76.43	-76.41			
880	6.53	6.54	9.19	9.18	7.18	7.05	0.14	0.14	-79.22	-79.23			
900	6.40	6.41	8.87	8.86	6.95	6.84	0.10	0.10	-81.98	-81.95			
920	6.25	6.26	8.59	8.57	6.73	6.63	0.07	0.07	-85.01	-84.98			
950	6.10	6.11	8.24	8.23	6.45	6.36	-0.05	-0.04	-89.89	-89.85			
970	5.99	6.00	7.99	7.98	6.31	6.24	-0.12	-0.11	-92.84	-92.76			
990	5.85	5.85	7.71	7.70	6.17	6.10	-0.15	-0.14	-95.82	-95.75			
1000	5.78	5.78	7.57	7.56	6.09	6.03	-0.17	-0.15	-97.44	-97.36			
1020	5.67	5.68	7.32	7.31	5.93	5.87	-0.24	-0.22	-100.68	-100.58			
1040	5.58	5.58	7.13	7.11	5.77	5.72	-0.33	-0.30	-103.86	-103.78			
1060	5.46	5.47	6.98	6.97	5.64	5.61	-0.39	-0.36	-107.01	-106.90			
1100	5.23	5.24	6.69	6.68	5.48	5.46	-0.51	-0.48	-114.11	-114.00			
1120	5.15	5.16	6.50	6.48	5.42	5.40	-0.61	-0.57	-117.25	-117.17			
1140	5.01	5.02	6.35	6.34	5.34	5.33	-0.64	-0.61	-120.52	-120.41			
1150	4.94	4.94	6.30	6.30	5.31	5.30	-0.66	-0.62	-122.37	-122.27			
1180	4.83	4.84	6.20	6.19	5.29	5.29	-0.82	-0.78	-128.57	-128.46			
1200	4.85	4.85	6.12	6.12	5.30	5.30	-1.01	-0.97	-132.09	-132.01			
1220	4.73	4.74	6.02	6.01	5.28	5.29	-1.07	-1.02	-135.30	-135.22			
1250	4.53	4.54	5.90	5.90	5.33	5.34	-	-	-141.55	-141.44			
1300	4.60	4.62	5.94	5.94	5.58	5.60	-	-	-151.43	-151.30			
1400	4.71	4.74	6.16	6.16	6.26	6.31	-	-	-172.24	-172.04			

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Voltage Variable Equalizer, 75Ω

VAEQ-1220-75+

Typical Performance Data @ V+=5V

Frequency (MHz)	Insertion Loss (dB) Vcontrol		Input Return Loss (dB) Vcontrol		Output Return Loss (dB) Vcontrol		Deviation from Linear Loss (dB) Vcontrol		Insertion Phase (deg) Vcontrol		Frequency (MHz)	Input IP3 (dBm) Vcontrol	
	5.2V	7V	5.2V	7V	5.2V	7V	5.2V	7V	5.2V	7V		5V	7V
10	4.80	2.10	11.94	20.73	13.41	18.61	-	-	3.73	4.91	10	38.24	41.46
30	4.51	1.74	12.32	25.48	14.20	24.11	-	-	-1.09	-1.00	30	44.50	48.58
50	4.45	1.68	12.45	26.93	14.38	25.98	-0.04	0.00	-4.15	-4.48	50	48.97	47.63
70	4.42	1.65	12.51	27.12	14.45	26.35	-0.02	0.00	-6.83	-7.48	80	49.59	50.52
90	4.41	1.64	12.53	26.51	14.46	25.78	0.00	0.00	-9.36	-10.32	100	51.66	51.67
110	4.41	1.64	12.56	25.58	14.49	24.82	0.00	0.00	-11.81	-13.04	150	53.40	58.60
130	4.41	1.65	12.62	24.62	14.56	23.87	0.00	0.00	-14.19	-15.72	200	52.99	55.18
150	4.40	1.66	12.67	23.74	14.64	23.01	0.00	0.00	-16.54	-18.35	300	53.80	54.06
170	4.40	1.67	12.68	22.84	14.65	22.15	0.00	0.00	-18.88	-20.95	400	53.53	53.09
200	4.41	1.69	12.66	21.42	14.55	20.73	0.00	0.00	-22.37	-24.83	450	50.97	48.66
220	4.41	1.70	12.67	20.56	14.47	19.81	0.00	0.00	-24.69	-27.40	500	54.41	51.91
240	4.41	1.72	12.71	19.87	14.41	19.01	0.00	0.00	-26.97	-29.96	550	49.35	48.31
260	4.41	1.74	12.75	19.32	14.37	18.32	0.00	0.00	-29.25	-32.50	600	54.25	51.00
300	4.41	1.77	12.69	18.13	14.23	17.09	0.00	0.00	-33.85	-37.59	700	53.65	51.32
320	4.41	1.80	12.64	17.48	14.13	16.51	-0.01	0.00	-36.15	-40.13	800	54.11	53.17
340	4.42	1.82	12.65	16.93	14.04	15.98	-0.01	0.00	-38.43	-42.66	900	54.10	56.38
360	4.42	1.85	12.68	16.51	13.97	15.52	-0.01	0.00	-40.67	-45.16	950	49.23	51.89
380	4.41	1.87	12.70	16.13	13.88	15.09	-0.01	0.00	-42.95	-47.66	1000	53.04	55.90
400	4.41	1.90	12.67	15.73	13.76	14.66	-0.01	0.00	-45.25	-50.18	1100	56.51	54.28
420	4.42	1.93	12.62	15.27	13.62	14.21	-0.01	0.00	-47.55	-52.72	1150	48.45	53.41
450	4.43	1.99	12.64	14.68	13.44	13.60	-0.02	0.00	-50.93	-56.46	1200	53.79	51.76
500	4.42	2.08	12.73	14.04	13.23	12.84	-0.02	0.00	-56.61	-62.63	1220	48.81	50.74
550	4.42	2.19	12.66	13.28	12.95	12.15	-0.02	0.00	-62.31	-68.79	1300	50.84	50.02
600	4.42	2.32	12.83	12.86	12.61	11.52	-0.02	0.00	-67.93	-74.76	1400	50.81	49.59
650	4.41	2.43	12.72	12.36	12.22	10.91	0.00	0.00	-73.71	-80.74			
700	4.40	2.58	12.78	12.02	11.95	10.55	0.01	0.00	-79.31	-86.37			
750	4.38	2.70	12.66	11.77	11.55	10.18	0.03	0.00	-85.20	-92.12			
770	4.38	2.77	12.53	11.58	11.38	10.05	0.02	0.00	-87.49	-94.30			
800	4.37	2.84	12.46	11.45	11.08	9.85	0.04	0.00	-90.83	-97.36			
820	4.35	2.87	12.45	11.46	10.87	9.72	0.06	0.00	-93.20	-99.51			
840	4.34	2.90	12.37	11.45	10.66	9.60	0.07	0.00	-95.71	-101.79			
860	4.35	2.97	12.19	11.37	10.46	9.49	0.05	0.00	-98.15	-103.98			
880	4.36	3.02	11.97	11.26	10.23	9.39	0.05	0.00	-100.38	-105.92			
900	4.34	3.04	11.78	11.18	9.98	9.26	0.06	0.00	-102.62	-107.82			
920	4.32	3.04	11.64	11.16	9.71	9.12	0.09	0.00	-105.05	-109.94			
950	4.35	3.10	11.42	11.20	9.34	8.94	0.06	0.00	-108.88	-113.31			
970	4.37	3.14	11.20	11.16	9.15	8.86	0.04	0.00	-111.15	-115.26			
990	4.35	3.14	10.89	11.05	8.91	8.76	0.05	0.00	-113.50	-117.27			
1000	4.35	3.14	10.74	11.00	8.78	8.69	0.06	0.00	-114.71	-118.35			
1020	4.38	3.17	10.49	10.91	8.51	8.52	0.03	0.00	-117.18	-120.53			
1040	4.41	3.22	10.29	10.90	8.22	8.34	0.00	0.00	-119.47	-122.55			
1060	4.43	3.24	10.12	10.93	7.95	8.15	-0.02	0.00	-121.70	-124.53			
1100	4.47	3.30	9.66	10.86	7.49	7.82	-0.06	0.00	-126.52	-128.84			
1120	4.50	3.35	9.33	10.67	7.26	7.65	-0.10	0.00	-128.46	-130.54			
1140	4.48	3.35	9.06	10.49	7.01	7.44	-0.07	0.00	-130.37	-132.12			
1150	4.46	3.33	8.95	10.42	6.90	7.34	-0.06	0.00	-131.47	-133.03			
1180	4.46	3.34	8.60	10.15	6.64	7.10	-0.06	0.00	-135.20	-136.17			
1200	4.52	3.39	8.32	9.87	6.50	6.99	-0.11	0.00	-137.12	-137.71			
1220	4.43	3.30	8.00	9.49	6.36	6.86	-0.02	0.00	-138.75	-138.82			
1250	4.22	3.04	7.57	8.89	6.25	6.77	-	-	-142.62	-141.87			
1300	4.20	2.89	7.17	8.37	6.39	6.98	-	-	-149.14	-147.72			
1400	4.19	2.63	6.70	7.98	6.91	7.42	-	-	-163.98	-161.71			

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




Voltage Variable Equalizer, 75 Ω


Typical Performance Curves @ $V_+ = 5V$

VAEQ-1220-75+


INSERTION LOSS
Vs.FREQUENCY OVER CONTROL VOLTAGES




INPUT RETURN LOSS
Vs.FREQUENCY OVER CONTROL VOLTAGES




OUTPUT RETURN LOSS
Vs.FREQUENCY OVER CONTROL VOLTAGES




PHASE UNBALANCE
Vs.FREQUENCY OVER CONTROL VOLTAGES



DEVIATION FROM LINEAR LOSS
Vs.FREQUENCY OVER CONTROL VOLTAGES



IP3
Vs.FREQUENCY OVER CONTROL VOLTAGES




Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HE1354	.394 (10.01)	.394 (10.01)	.150 (3.81)	.122 (3.10)	.075 (1.90)	.098 (2.49)	.038 (0.97)	.026 (0.66)	.051 (1.29)	.038 (0.97)	.046 (1.17)	.434 (11.02)	0.7

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Tape & Reel Packaging TR-F37



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
24	16	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200
				500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M124493	NEW RELEASE (FROM RAVON)	09/09	EM	YB
OR	R77678	NEW RELEASE (FROM RAVON)	09/09	EM	YB

SUGGESTED MOUNTING CONFIGURATION
FOR HE1354 CASE STYLE, qg PIN CONNECTION, 75 OHM

**NOTE:**

1. TRACE WIDTH IS SHOWN FOR R04350B WITH DIELECTRIC THICKNESS $.030'' \pm .002''$. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

EM (RAVON)

16 SEP 09

TOLERANCES ON:

CHECKED

HH (RAVON)

21 SEP 09

2 PL DECIMALS ± .005

APPROVED

YB (RAVON)

21 SEP 09

ANGLES ±

FRACTIONS ±

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
 Brooklyn NY 11235

PL, qg, HE1354, TB-549+, 75 OHM

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-315


REV:
OR

FILE: 98PL315


SCALE: 5:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-549+



Schematic Diagram

Notes:

1. BNC Female connectors.
2. PCB Material: Rogers R04350B or equivalent,
Dielectric constant=3.48, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	0° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215