

# Coaxial High Pass Filter

## VHF-145+

50Ω

140 to 1150 MHz



CASE STYLE: FF704

### The Big Deal

- Low Insertion Loss (2.0 dB max.)
- Good close-in rejection
- Versatile small size, coaxial, 1.43" length

### Product Overview

The VHF-145+ High Pass Filter is constructed using internal LTCC High Pass Filter structure to achieve repeatable performance. Covering 140-1150 MHz, these filters offer a wide bandwidth. For a high pass filter, that is versatile for many upconverter applications. Built using Mini-Circuits proven unibody construction which integrates the RF connectors with the case body, the VHF-145+ takes very little space and meets rugged field test lab system environment.

### Key Features

| Feature                                 | Advantages  |
|---|---|
| Wideband                                | Covers VHF and UHF bands, and is ideal for up conversion applications.  |
| Compact Versatile Case<br>(1.43"x0.41") | Enables use in a variety of applications including space constrained connectorized systems.<br>Connectors: SMA Female (1), SMA Male (1) |
| Rugged Unibody Construction             | Mini-Circuits Unibody construction allows survivability in critical applications including militarized or industrial systems.           |

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Coaxial High Pass Filter


50Ω 140 to 1150 MHz

## Maximum Ratings

|                       |                 |
|-----------------------|-----------------|
| Operating Temperature | -55°C to 100°C  |
| Storage Temperature   | -55°C to 100°C  |
| RF Power Input*       | 7W max. at 25°C |

\* Passband rating, derate linearly to 3W at 100°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

## Outline Drawing



## Outline Dimensions (inch/mm)

| B     | D     | E    | wt    |
|-------|-------|------|-------|
| .410  | 1.43  | .312 | grams |
| 10.41 | 36.32 | 7.92 | 10.0  |

## Features

- rugged unibody construction, small size
- 7 sections
- temperature stable
- excellent power handling, 7W
- low cost

## Applications

- sub-harmonic rejection
- transmitters/receivers
- lab use

VHF-145+



Generic photo used for illustration purposes only

CASE STYLE: FF704

| Connectors | Model    |
|------------|----------|
| SMA        | VHF-145+ |


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


## Electrical Specifications at 25°C

| Parameter | F#             | Frequency (MHz) | Min.     | Typ. | Max. | Unit |
|-----------|----------------|-----------------|----------|------|------|------|
| Stop Band | Rejection Loss | DC-F1           | DC-80    | 20   |      | dB   |
|           |                | DC-F2           | DC-115   | 15   |      | dB   |
|           | Freq. Cut-Off  | F3              | 132      | 3.0  |      | dB   |
|           | VSWR           | DC-F2           | DC-115   | 20   |      | :1   |
| Pass Band | Insertion Loss | F5-F6           | 155-1050 |      | 1.5  | dB   |
|           |                | F4-F7           | 140-1150 |      | 3.0  | dB   |
|           | VSWR           | F5-F7           | 155-1150 | 1.5  |      | :1   |

## Typical Frequency Response





## Electrical Schematic



## Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 0.30            | 63.96               | 434.30    |
| 100.00          | 20.05               | 23.49     |
| 110.00          | 19.50               | 13.60     |
| 124.00          | 8.68                | 3.42      |
| 133.00          | 2.45                | 1.20      |
| 141.00          | 1.39                | 1.14      |
| 145.00          | 1.17                | 1.19      |
| 148.00          | 1.06                | 1.20      |
| 152.00          | 0.94                | 1.19      |
| 156.00          | 0.84                | 1.16      |
| 160.00          | 0.77                | 1.14      |
| 600.00          | 0.39                | 1.20      |
| 1120.00         | 1.23                | 2.03      |
| 1150.00         | 1.38                | 2.18      |
| 1200.00         | 1.71                | 2.50      |



## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

REV. A  
M151107  
VHF-145+  
ED-13423A/3  
AD/AM/CP  
160701  
Page 2 of 2

# Coaxial High Pass Filter

## VHF-145+



### Typical Performance Data

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | RETURN<br>LOSS<br>(dB) |
|--------------------|---------------------------|------------------------|
| 0.3                | 63.96                     | 0.04                   |
| 1.0                | 53.29                     | 0.00                   |
| 10.0               | 33.38                     | 0.00                   |
| 40.0               | 23.59                     | 0.06                   |
| 70.0               | 28.65                     | 0.20                   |
| 100.0              | 20.05                     | 0.74                   |
| 110.0              | 19.50                     | 1.28                   |
| 115.0              | 22.35                     | 1.80                   |
| 120.0              | 15.57                     | 2.98                   |
| 125.0              | 7.42                      | 6.11                   |
| 130.0              | 3.50                      | 13.18                  |
| 131.0              | 3.08                      | 15.29                  |
| 132.0              | 2.73                      | 17.75                  |
| 140.0              | 1.46                      | 24.91                  |
| 141.0              | 1.39                      | 23.61                  |
| 142.0              | 1.33                      | 22.70                  |
| 143.0              | 1.27                      | 22.06                  |
| 144.0              | 1.22                      | 21.60                  |
| 145.0              | 1.17                      | 21.29                  |
| 146.0              | 1.13                      | 21.09                  |
| 147.0              | 1.09                      | 20.98                  |
| 148.0              | 1.06                      | 20.94                  |
| 149.0              | 1.02                      | 20.97                  |
| 150.0              | 0.99                      | 21.06                  |
| 151.0              | 0.96                      | 21.19                  |
| 152.0              | 0.94                      | 21.36                  |
| 153.0              | 0.91                      | 21.57                  |
| 154.0              | 0.89                      | 21.82                  |
| 155.0              | 0.86                      | 22.08                  |
| 156.0              | 0.84                      | 22.37                  |
| 157.0              | 0.82                      | 22.69                  |
| 158.0              | 0.80                      | 23.04                  |
| 159.0              | 0.79                      | 23.40                  |
| 160.0              | 0.77                      | 23.78                  |
| 180.0              | 0.56                      | 26.62                  |
| 200.0              | 0.48                      | 21.52                  |
| 400.0              | 0.37                      | 18.85                  |
| 600.0              | 0.39                      | 20.64                  |
| 800.0              | 0.49                      | 18.09                  |
| 1000.0             | 0.80                      | 12.73                  |
| 1110.0             | 1.18                      | 9.66                   |
| 1120.0             | 1.23                      | 9.39                   |
| 1130.0             | 1.28                      | 9.12                   |
| 1140.0             | 1.33                      | 8.86                   |
| 1150.0             | 1.38                      | 8.61                   |
| 1160.0             | 1.44                      | 8.35                   |
| 1170.0             | 1.50                      | 8.10                   |
| 1180.0             | 1.56                      | 7.85                   |
| 1190.0             | 1.63                      | 7.61                   |
| 1200.0             | 1.71                      | 7.37                   |

# Coaxial High Pass Filter

## Typical Performance Curves

VHF-145+



**Mini-Circuits®**  
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)




IF/RF MICROWAVE COMPONENTS

[minicircuits.com](http://minicircuits.com)

REV. X1  
VHF-145+  
5/17/2011  
Page 1 of 1

### Outline Dimensions



| CASE #. | A  | B               | C  | D               | E              | WT GRAMS |
|---------|----|-----------------|----|-----------------|----------------|----------|
| FF704   | -- | .410<br>(10.41) | -- | 1.43<br>(36.32) | .312<br>(7.92) | 10.0     |

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

#### Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition  | Reference/Spec                       |
|----------------------------|--|--------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment   | Individual Model Data Sheet          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment  | Individual Model Data Sheet          |
| Barometric Pressure        | 100,000 Feet   | MIL-STD-202, Method 105, Condition D |
| Humidity                   | 90% RH, 65°C<br>Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103              |
| Thermal Shock              | -65° to 125°C, 5 cycles  | MIL-STD-202, Method 107, Condition B |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)    | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock           | 100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)                          | MIL-STD-202, Method 213, Condition I |