

Engineering Development Model

Voltage Controlled Oscillator

UOS-EDR5476/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : CZ682

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	1544		1700	MHz
Tuning Voltage	0.5		7	V
Power Output		+1		dBm
Phase Noise				
at 1 kHz offset		-78		dBc/Hz
at 10 KHz offset		-103		dBc/Hz
at 100 KHz offset		-126		dBc/Hz
at 1000 kHz offset		-145		dBc/Hz
Pulling at 12 dBr PK-PK all phases		5.5		MHz
Pushing at Vcc=5V±0.25V		1.1		MHz/V
Tuning Sensitivity		29 - 55		MHz/V
Harmonic Suppression		-33	-30	dBc
3 dB Modulation Bandwidth		6600		kHz
Supply Voltage		5.7		V
Supply Current			30	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+7.7V
Absolute Tuning Voltage (Vtune)	+9V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	1
GROUND	2,4,6,7,8

Voltage Controlled Oscillator

UOS-EDR5476/2






Typical Performance Data

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ OFFSET (KHz)	PHASE NOISE (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C	F2	F3	F4			
0.3	61.28	1495.8	1488.9	1483.4	0.81	-0.24	-0.93	-40.9	-31.7	-39.7	-0.30	1	-78
0.5	53.47	1508.7	1502.3	1497.0	0.93	-0.05	-0.71	-44.7	-31.3	-39.6	-0.26	10	-103
0.8	48.16	1520.7	1514.3	1509.2	1.02	0.08	-0.46	-44.3	-32.1	-40.2	-0.24	100	-126
1.0	45.10	1531.9	1525.6	1520.5	1.12	0.24	-0.26	-46.6	-32.3	-40.4	-0.22	1000	-145
1.3	42.38	1542.5	1536.2	1531.2	1.15	0.39	-0.04	-44.7	-31.6	-40.2	-0.21		
1.5	40.26	1552.4	1546.3	1541.4	1.17	0.50	0.09	-49.6	-31.8	-39.5	-0.20		
1.8	38.12	1561.8	1555.8	1551.0	1.25	0.63	0.19	-51.3	-31.7	-38.3	-0.20		
2.0	36.79	1571.1	1565.0	1560.1	1.37	0.75	0.37	-50.8	-32.3	-37.2	-0.20		
2.3	35.84	1580.1	1574.0	1569.0	1.45	0.90	0.52	-48.3	-32.2	-36.3	-0.20		
2.5	34.96	1588.9	1582.7	1577.6	1.57	1.04	0.69	-44.6	-32.3	-35.7	-0.21		
2.8	33.84	1597.4	1591.2	1586.1	1.65	1.20	0.88	-44.4	-31.9	-35.4	-0.21		
3.0	33.10	1605.8	1599.4	1594.3	1.72	1.33	1.05	-44.5	-32.2	-35.2	-0.21		
3.3	32.48	1614.1	1607.6	1602.4	1.83	1.48	1.20	-44.1	-32.4	-35.2	-0.22		
3.5	32.16	1622.3	1615.6	1610.4	1.95	1.64	1.36	-46.1	-33.0	-35.7	-0.22		
3.8	31.85	1630.3	1623.6	1618.3	2.10	1.80	1.49	-45.1	-33.1	-36.1	-0.23		
4.0	31.24	1638.1	1631.4	1626.1	2.24	1.97	1.62	-44.1	-33.2	-36.1	-0.24		
4.3	30.73	1645.8	1639.1	1633.7	2.38	2.10	1.76	-44.4	-33.0	-36.6	-0.25		
4.5	30.38	1653.4	1646.7	1641.3	2.49	2.21	1.90	-44.7	-33.0	-36.7	-0.26		
4.8	30.27	1661.2	1654.2	1648.8	2.59	2.33	2.05	-43.8	-33.4	-37.2	-0.27		
5.0	30.50	1668.8	1661.8	1656.3	2.72	2.47	2.13	-43.2	-33.4	-37.1	-0.28		
5.3	29.98	1676.3	1669.3	1663.8	2.83	2.61	2.20	-44.6	-33.6	-38.1	-0.29		
5.5	29.76	1683.8	1676.8	1671.3	2.94	2.72	2.33	-44.5	-33.9	-37.5	-0.30		
5.8	29.70	1691.3	1684.2	1678.7	3.04	2.81	2.43	-44.0	-33.5	-38.3	-0.32		
6.0	29.67	1698.8	1691.6	1686.0	3.12	2.89	2.52	-44.1	-33.8	-38.0	-0.34		
6.3	29.75	1706.4	1699.1	1693.4	3.24	2.95	2.62	-43.9	-33.8	-38.0	-0.36		
6.5	30.19	1714.0	1706.6	1700.8	3.36	3.06	2.69	-43.0	-33.7	-38.6	-0.37		
6.8	30.02	1721.6	1714.1	1708.3	3.44	3.18	2.77	-42.6	-33.9	-38.4	-0.39		
7.0	29.92	1729.2	1721.6	1715.7	3.51	3.25	2.87	-42.5	-34.3	-38.7	-0.41		


Voltage Controlled Oscillator

UOS-EDR5476/2


Typical Performance Data




Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$



CASE #	A	B	C	D	E	F	G	H	J	K
CZ682	.375 (9.52)	.375 (9.52)	.131 (3.33)	.188 (4.77)	.035 (0.89)	.033 (0.84)	.154 (3.91)	.050 (1.27)	.425 (10.80)	.183 (4.65)

CASE #	L	M	N	P	Q	WT. GRAM
CZ682	.060 (1.52)	.425 (10.80)	.028 (0.71)	.154 (3.91)	.060 (1.52)	.60

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .010$

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate
For RoHS-5 Case Styles: Tin-Lead plate.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F60



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
24	16	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200
				500
				1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M76040	NEW RELEASE (FROM RAVON)	03/01	DK	HH
A	M82575	UPDATED DRAWING	08/08/02	GF	MM
B	M101142	ADDED NOTE 2 & TB-128 TO DESCRIPTION	10/10/05	MMG	MM
C	M102713	ADDED "...WITH SMOBC"	01/12/06	GF	IL

SUGGESTED MOUNTING CONFIGURATION FOR CZ682 CASE STYLE, "my" PIN CONNECTION



- NOTE: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS $0.030'' \pm 0.002''$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

DK (RAV)

03/22/01

TOLERANCES ON:

CHECKED

DE (RAV)

03/27/01

2 PL DECIMALS $\pm$

APPROVED

HH (RAV)

03/27/01

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$
 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, my, CZ682, MOS, TB-128

 SIZE
A

 CODE IDENT
15542

 DRAWING NO:
98-PL-023


 REV:
C

FILE: 98PL023


SCALE: 5:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-28



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®