

# Coaxial High Pass Filter

## VHFG-1100+

50Ω 1400 to 3900 MHz



Generic photo used for illustration purposes only  
CASE STYLE: FF704

### The Big Deal

- Excellent power handling, 4W
- Temperature stable
- Rugged unibody construction
- Good rejection, 51 dB typical

### Product Overview

VHFG-1100+ is a 50Ω high pass filter built in rugged unibody construction. Covering 1400-3900 MHz bandwidth, these units offer good matching within the passband and good rejection in stopband. VHFG-1100+ offer low insertion loss, and excellent power handling capability. It handles up to 4W RF input power and provides a wide operating temperature range from -55°C to 125°C.

### Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application.
4W Power handling	Supports a range of system power requirements.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# High Pass Filter

## VHFG-1100+

50Ω 1400 to 3900 MHz



Generic photo used for illustration purposes only  
CASE STYLE: FF704

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Features

- Temperature stable
- Excellent power handling, 4W
- Connectorized package
- Rugged unibody construction

### Electrical Specifications at 25°C


Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection Loss	DC-F1	DC - 530	38	51	-	dB
		DC-F2	DC - 700	20	30	-	dB
	Freq. Cut-Off	F3*	1050	-	3.0	-	dB
Pass Band	Insertion Loss	F4-F7	1400 - 3900	-	1.6	2.5	dB
		F5-F6	1500 - 3200	-	1.2	2.0	dB
	Return Loss	F4-F6	1400 - 3200	-	13	-	dB

In Applications where DC voltage is present at either input or output ports, DC blocks are required.  
\* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

### Applications

- Transmitters / Receivers
- Global positioning system(GPS)
- Satellite broadcast applications

### Functional Schematic



### Maximum Ratings





Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	4W max. @25°C

\*Passband rating, derate linearly to 0.8W at 125°C ambient  
Permanent damage may occur if any of these limits are exceeded.

### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	87.33	0.17
100	72.06	0.24
250	62.55	0.33
530	53.11	0.50
700	32.01	0.67
710	31.05	0.68
750	27.33	0.75
810	22.01	0.89
900	14.33	1.40
970	8.70	2.60
1040	4.21	6.26
1050	3.75	7.18
1100	2.19	14.59
1400	1.07	14.10
1500	0.89	17.10
2000	0.63	18.20
2500	0.53	19.23
3000	0.46	28.87
3200	0.52	19.10
3900	1.18	8.54

### Typical Frequency Response



### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

## Outline Drawing



## Outline Dimensions ( inch )

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10

Note: Please refer to case style drawing for details

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



*Typical Performance Data*

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	72.92	66.62	67.67	0.17	0.22	0.27	0.18	0.24	0.28
50	66.58	69.57	63.96	0.18	0.24	0.29	0.19	0.25	0.30
100	65.36	69.06	67.36	0.20	0.27	0.32	0.22	0.29	0.33
150	63.21	63.64	63.95	0.22	0.29	0.34	0.26	0.33	0.37
200	60.35	60.98	60.78	0.25	0.31	0.38	0.27	0.34	0.40
250	59.08	59.05	58.41	0.26	0.33	0.40	0.28	0.36	0.42
300	57.49	57.46	57.39	0.28	0.35	0.43	0.31	0.38	0.46
350	56.91	56.96	57.04	0.29	0.37	0.46	0.33	0.41	0.49
400	57.38	57.41	57.50	0.30	0.39	0.48	0.33	0.42	0.51
450	60.59	62.22	62.23	0.32	0.41	0.52	0.35	0.45	0.54
500	64.16	61.62	59.17	0.34	0.44	0.55	0.38	0.48	0.58
530	54.89	53.67	52.18	0.36	0.46	0.57	0.39	0.50	0.60
600	42.95	42.24	41.36	0.40	0.52	0.64	0.44	0.57	0.67
650	36.91	36.32	35.54	0.45	0.58	0.70	0.48	0.62	0.73
700	31.68	31.14	30.40	0.49	0.64	0.78	0.53	0.69	0.80
750	26.91	26.38	25.65	0.56	0.72	0.88	0.60	0.78	0.92
800	22.37	21.84	21.11	0.64	0.83	1.03	0.70	0.90	1.08
850	17.98	17.45	16.72	0.81	1.04	1.30	0.86	1.11	1.36
900	13.68	13.15	12.44	1.13	1.44	1.81	1.20	1.52	1.90
940	10.35	9.85	9.21	1.65	2.07	2.62	1.73	2.17	2.75
1000	5.81	5.48	5.11	3.48	4.28	5.36	3.61	4.45	5.62
1050	3.08	3.01	2.95	7.16	8.56	10.41	7.45	8.96	11.07
1100	1.70	1.82	1.97	14.70	16.97	19.27	15.95	19.06	23.07
1150	1.24	1.44	1.64	21.31	19.76	18.18	24.29	21.08	18.81
1200	1.14	1.33	1.52	15.38	14.94	14.58	15.54	14.93	14.52
1250	1.11	1.28	1.43	13.15	13.24	13.40	13.10	13.09	13.23
1300	1.06	1.21	1.34	12.56	12.91	13.37	12.42	12.68	13.10
1350	0.97	1.11	1.22	12.84	13.36	14.05	12.64	13.09	13.71
1400	0.88	1.00	1.11	13.69	14.38	15.31	13.45	14.05	14.86
1450	0.78	0.91	1.01	15.08	15.93	17.15	14.68	15.44	16.44
1500	0.69	0.81	0.92	16.92	17.98	19.60	16.41	17.36	18.62
1550	0.62	0.74	0.85	19.38	20.76	23.01	18.62	19.77	21.29
1600	0.55	0.68	0.79	22.79	24.76	28.30	21.55	23.02	24.81
1650	0.51	0.64	0.75	27.95	30.92	35.65	24.89	26.39	27.56
1700	0.48	0.61	0.72	34.21	33.36	30.54	27.72	27.80	26.95
1750	0.46	0.58	0.69	30.07	27.58	25.54	27.15	25.98	24.65
1800	0.44	0.57	0.68	25.33	23.84	22.61	24.27	23.26	22.30
1850	0.44	0.57	0.67	22.39	21.44	20.69	22.04	21.32	20.68
1900	0.43	0.56	0.66	20.57	19.91	19.44	20.31	19.80	19.42
1950	0.43	0.56	0.66	19.25	18.77	18.50	19.20	18.83	18.64
2000	0.43	0.55	0.65	18.36	18.01	17.88	18.35	18.09	18.04
2100	0.42	0.54	0.64	17.27	17.11	17.18	17.36	17.26	17.44
2200	0.41	0.53	0.62	16.89	16.90	17.13	16.96	17.03	17.39
2300	0.39	0.51	0.60	17.02	17.18	17.56	17.13	17.35	17.89
2400	0.37	0.49	0.57	17.62	17.88	18.43	17.75	18.12	18.87
2500	0.34	0.46	0.54	18.77	19.09	19.88	18.86	19.35	20.39
2600	0.31	0.43	0.52	20.51	20.88	21.91	20.72	21.35	22.85
2700	0.29	0.41	0.51	23.19	23.66	24.95	23.47	24.43	26.92
2800	0.26	0.39	0.49	27.42	27.91	28.48	28.56	30.59	36.87
2900	0.25	0.38	0.49	32.04	30.49	27.65	41.22	46.39	33.72
3000	0.25	0.39	0.50	27.24	25.68	23.44	29.56	28.02	25.12
3100	0.26	0.40	0.52	22.22	21.33	19.94	23.00	22.21	20.69
3200	0.29	0.44	0.55	18.84	18.25	17.33	19.25	18.71	17.73
3300	0.34	0.48	0.61	16.35	15.90	15.26	16.56	16.15	15.48
3400	0.40	0.54	0.67	14.33	14.00	13.52	14.57	14.26	13.77
3500	0.47	0.63	0.75	12.73	12.46	12.11	12.86	12.61	12.27
3700	0.66	0.83	0.96	10.22	10.02	9.85	10.35	10.15	9.98
3800	0.78	0.96	1.08	9.28	9.09	8.98	9.35	9.17	9.06
3850	0.84	1.02	1.15	8.79	8.62	8.53	8.93	8.76	8.67
3900	0.91	1.09	1.22	8.40	8.24	8.17	8.52	8.36	8.29

\* Temperature test data was based on the underlying chip








## Typical Performance Data

FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-55°C	@+25°C	@+125°C
1000	1.34	1.38	1.41
1050	1.49	1.48	1.44
1100	1.37	1.31	1.24
1150	1.11	1.05	0.99
1200	0.86	0.82	0.79
1250	0.74	0.71	0.69
1300	0.63	0.62	0.61
1350	0.56	0.55	0.55
1400	0.51	0.50	0.50
1450	0.47	0.47	0.46
1500	0.44	0.43	0.43
1550	0.41	0.41	0.40
1600	0.38	0.38	0.38
1650	0.36	0.36	0.35
1700	0.34	0.33	0.33
1750	0.32	0.31	0.31
1800	0.30	0.29	0.29
1850	0.28	0.28	0.28
1900	0.27	0.26	0.26
2000	0.24	0.24	0.24
2100	0.22	0.22	0.22
2200	0.20	0.20	0.20
2300	0.19	0.19	0.19
2400	0.18	0.18	0.18
2500	0.17	0.17	0.17
2600	0.16	0.16	0.16
2700	0.15	0.15	0.16
2800	0.15	0.15	0.15
2900	0.15	0.15	0.15
3000	0.14	0.14	0.14
3100	0.14	0.14	0.14
3200	0.13	0.13	0.14
3300	0.13	0.13	0.13
3400	0.13	0.13	0.13
3500	0.12	0.12	0.13
3600	0.12	0.12	0.12
3700	0.12	0.12	0.12
3800	0.11	0.11	0.11
3900	0.11	0.11	0.11
3950	0.11	0.11	0.11
4000	0.11	0.11	0.11

\* Temperature test data was based on the underlying chip

## Typical Performance Curves




\* Temperature test data was based on the underlying chip

# Case Style

# FF

## FF704

### Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

#### Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.

**Mini-Circuits**<sup>®</sup>  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Thermal Shock	-55° to 125°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, Except +125°C