

Ultra-Reliable High Pass Filter

50Ω 2300 to 5500 MHz

VHP-19



Generic photo used for illustration purposes only

CASE STYLE: FF704

Connectors	Model
SMA	VHP-19

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	10W at 25°C

* Passband rating, derate linearly to 0.4x Pmax at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.


Features

- rugged unibody construction, small size
- pass band insertion loss 1.0 dB typ.
- excellent power handling, 10W
- low cost

Applications

- sub-harmonic rejection of VCO
- transmitters/receivers
- lab use

Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0


Electrical Specifications (T_{AMB}=25°C)

STOP BAND (MHz)	f _{co} , MHz Nom. (loss 3 dB)	PASSBAND (MHz)	VSWR (:1)	
			Stopband	Passband
(loss > 40 dB)	(loss > 20 dB)	Typ.	Typ.	Typ.
DC-1450	1650	1995	18	1.3

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1.00	93.02	492.89
500.00	48.24	95.45
1000.00	42.60	69.61
1250.00	44.03	60.92
1450.00	44.29	50.18
1650.00	23.60	32.72
1995.00	2.37	1.97
2300.00	1.00	1.40
5500.00	0.50	1.31
9000.00	3.79	5.70



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
M151107
VHP-19
ED10545B/6
WZ/AD/CP/AM
200522

Coaxial High Pass Filter (Ultra Reliable)

VHP-19

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	92.34	93.02	92.90	0.01	0.04	0.05	0.00	0.04	0.05
50	67.17	67.77	67.68	0.07	0.10	0.12	0.05	0.10	0.10
100	61.69	61.93	61.85	0.10	0.13	0.15	0.08	0.13	0.14
350	51.23	51.19	51.35	0.16	0.21	0.23	0.13	0.20	0.21
800	44.23	44.22	44.30	0.20	0.27	0.33	0.17	0.26	0.30
1060	42.55	42.60	42.70	0.22	0.30	0.38	0.19	0.30	0.35
1300	46.78	47.51	48.44	0.23	0.34	0.44	0.23	0.35	0.42
1380	58.50	56.64	53.27	0.25	0.37	0.47	0.24	0.37	0.45
1415	51.02	48.14	45.74	0.25	0.38	0.49	0.25	0.38	0.47
1440	45.53	43.54	41.76	0.27	0.39	0.50	0.25	0.39	0.48
1450	43.81	42.01	40.39	0.26	0.39	0.51	0.26	0.39	0.49
1475	40.16	38.70	37.35	0.27	0.40	0.52	0.27	0.41	0.51
1515	35.45	34.27	33.15	0.30	0.43	0.56	0.29	0.43	0.54
1565	30.63	29.63	28.66	0.32	0.46	0.60	0.32	0.48	0.60
1625	25.58	24.66	23.79	0.37	0.53	0.69	0.38	0.56	0.70
1650	23.61	22.71	21.87	0.40	0.58	0.74	0.41	0.60	0.75
1690	20.55	19.67	18.85	0.47	0.66	0.86	0.49	0.70	0.87
1755	15.75	14.90	14.11	0.68	0.94	1.20	0.71	0.99	1.24
1830	10.43	9.64	8.94	1.27	1.71	2.17	1.33	1.79	2.26
1910	5.42	4.91	4.50	3.17	4.11	5.11	3.31	4.30	5.35
1995	2.13	2.09	2.09	8.96	10.90	12.91	9.42	11.58	13.93
2100	1.02	1.21	1.37	22.21	21.50	20.33	32.62	26.40	22.86
2300	0.76	0.92	1.06	16.26	16.85	17.14	16.84	17.57	17.87
2500	0.58	0.73	0.86	19.25	19.90	20.40	21.16	21.88	22.08
3000	0.48	0.62	0.75	16.33	16.84	17.23	16.42	16.87	17.27
3500	0.37	0.53	0.66	18.55	18.45	18.08	17.94	18.10	18.27
4000	0.29	0.45	0.60	21.08	20.32	19.75	20.60	20.25	20.08
4500	0.25	0.42	0.58	21.48	21.82	22.11	22.04	22.85	22.86
5000	0.24	0.41	0.61	21.24	22.80	25.96	23.03	25.17	26.84
5500	0.30	0.48	0.74	16.76	17.31	17.92	17.75	18.14	18.36
6000	0.45	0.67	0.90	12.65	12.37	12.25	12.99	12.61	12.24
6360	0.62	0.91	1.18	10.42	9.87	9.55	10.58	10.01	9.55
7000	1.14	1.51	1.80	7.16	6.86	6.71	7.28	7.03	6.79
7500	1.89	2.14	2.34	5.04	5.18	5.34	5.36	5.38	5.45
8290	2.83	3.02	3.22	3.41	3.70	3.89	3.42	3.81	4.06
9000	3.21	3.78	3.82	2.98	3.21	3.22	3.04	3.72	3.48
10000	3.52	3.68	3.87	2.75	3.01	3.38	3.05	3.08	3.47
11000	3.19	3.54	3.78	3.08	3.34	3.68	3.03	3.27	3.45
11630	2.89	3.49	3.97	3.51	3.62	3.86	3.46	3.51	3.50
12000	3.02	3.59	4.13	3.47	3.75	4.10	3.49	3.65	3.71
14000	0.74	1.15	1.49	11.36	11.74	12.84	11.59	11.70	12.16

REV. X1

VHP-19

081221

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




Patent Pending

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I