

Coaxial Low Pass Filter

VLFG-3400+

50Ω DC to 3400 MHz



Generic photo used for illustration purposes only

CASE STYLE: FF704

The Big Deal

- Excellent power handling, 4.5W
- Temperature stable
- Rugged unibody construction
- Good rejection, 40 dB typical

Product Overview

VLFG-3400+ is a 50Ω low pass filter built in rugged unibody construction. Covering DC-3400 MHz bandwidth, these units offer good matching within the passband and good rejection in stopband. VLFG-3400+ offer low insertion loss, and excellent power handling capability. It handles up to 4.5W RF input power and provides a wide operating temperature range from -55°C to 125°C.

Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application.
4.5W Power handling	Supports a range of system power requirements.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Low Pass Filter

50Ω

DC to 3400 MHz

VLFG-3400+



Features

- Low loss, 1.4dB typ.
- High rejection 40dB typ.
- Excellent power handling, 4.5W
- Temperature stable
- Connectorized package
- Rugged unibody construction

Generic photo used for illustration purposes only
CASE STYLE: FF704

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Applications


- Military radar applications
- Test and measurement
- Telecommunications and broadband wireless applications

Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	DC - 3400	—	1.4	dB
	Freq. Cut-Off	F2*	3800	—	3.0	dB
	Return Loss	DC-F1	DC - 3400	—	16	dB
Stop Band	Rejection Loss	F3-F4	4700 - 5000	20	35	dB
		F4-F5	5000 - 8500	30	40	dB
		F5-F6	8500 - 15000	—	25	dB

In Application where DC voltage is present at either input or output port, DC blocks are required.
* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

Functional Schematic



Maximum Ratings





Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	4.5W max. @25°C

*Passband rating, derate linearly to 1W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	0.04	44.51
100	0.09	37.65
300	0.17	34.68
500	0.22	35.23
1000	0.33	28.69
1500	0.46	20.76
2000	0.62	17.31
3400	1.37	22.76
3800	3.36	9.51
4040	10.10	2.96
4240	20.42	1.62
4380	30.36	1.32
4700	44.69	1.04
5000	51.22	0.91
7000	48.11	0.53
8500	40.93	0.45
9000	39.47	0.44
10000	36.90	0.42
12000	32.78	0.45
15000	30.86	1.12

Typical Frequency Response



Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch mm)

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	0.08	0.09	0.10	44.86	47.55	45.10	42.47	45.30	43.35
100	0.11	0.13	0.15	42.51	40.09	38.47	40.80	39.09	37.64
200	0.13	0.16	0.19	38.42	37.88	37.30	36.49	36.00	35.52
250	0.14	0.17	0.21	37.17	37.43	37.27	35.06	34.96	34.62
300	0.14	0.18	0.22	36.86	37.40	37.57	33.96	33.95	33.71
350	0.15	0.19	0.24	36.81	37.46	37.88	33.20	33.15	32.88
400	0.16	0.20	0.25	37.04	37.75	38.38	32.43	32.22	31.94
500	0.17	0.22	0.27	36.76	38.66	39.99	30.97	30.76	30.48
550	0.18	0.23	0.28	36.15	38.91	41.19	30.16	30.00	29.77
600	0.18	0.24	0.30	35.88	39.32	42.73	29.50	29.35	29.15
650	0.19	0.25	0.31	35.56	39.22	44.44	28.73	28.62	28.46
700	0.19	0.25	0.32	35.10	38.77	45.31	28.17	28.05	27.93
750	0.20	0.26	0.33	34.57	37.95	44.39	27.51	27.40	27.28
1000	0.23	0.30	0.38	29.91	31.61	33.62	24.80	24.69	24.61
1500	0.30	0.40	0.50	22.44	22.96	23.44	20.70	20.57	20.44
2000	0.40	0.52	0.65	18.56	18.85	19.00	18.34	18.23	17.99
2500	0.51	0.65	0.81	18.01	18.21	18.36	18.31	18.32	18.34
3000	0.63	0.82	1.03	23.27	23.79	24.95	22.95	23.34	24.51
3400	0.87	1.13	1.44	35.50	34.54	30.87	27.87	25.86	23.54
3800	1.72	2.27	3.04	15.76	14.11	12.56	14.00	12.58	11.28
3900	2.38	3.20	4.39	11.38	9.96	8.65	10.55	9.37	8.39
4000	3.61	4.90	6.75	7.65	6.55	5.64	7.64	6.81	6.26
4100	5.77	7.72	10.39	4.78	4.13	3.69	5.45	5.05	4.94
4200	9.16	11.81	15.25	2.91	2.67	2.59	4.05	4.00	4.12
4300	13.76	17.02	21.15	1.87	1.88	1.98	3.19	3.31	3.49
4400	19.40	23.24	28.12	1.32	1.45	1.62	2.59	2.77	2.94
4500	25.98	30.57	36.66	1.01	1.18	1.37	2.11	2.29	2.45
4600	33.79	39.75	48.02	0.82	1.00	1.19	1.72	1.89	2.04
4700	43.87	52.30	52.04	0.69	0.87	1.05	1.40	1.57	1.71
4800	56.73	52.84	50.57	0.58	0.76	0.93	1.15	1.31	1.45
4900	53.86	52.14	52.31	0.50	0.67	0.83	0.95	1.11	1.24
5000	54.32	54.63	56.35	0.44	0.60	0.75	0.80	0.95	1.08
5100	58.25	59.79	61.55	0.38	0.54	0.68	0.69	0.83	0.96
5200	64.45	63.09	60.08	0.33	0.48	0.62	0.59	0.73	0.86
5300	61.18	58.58	56.48	0.29	0.44	0.57	0.52	0.65	0.79
5400	56.77	55.33	54.22	0.26	0.40	0.52	0.46	0.59	0.72
5500	54.25	53.61	53.05	0.22	0.36	0.48	0.41	0.54	0.67
5600	52.96	52.74	52.48	0.20	0.33	0.45	0.37	0.50	0.63
5700	52.45	52.40	52.29	0.17	0.31	0.42	0.33	0.47	0.61
5800	52.18	52.31	52.61	0.15	0.28	0.39	0.30	0.44	0.58
5900	52.14	52.45	52.87	0.13	0.26	0.37	0.28	0.42	0.56
6000	52.26	52.82	53.32	0.11	0.25	0.35	0.26	0.40	0.55
6100	52.61	53.37	54.52	0.10	0.23	0.33	0.24	0.38	0.54
6200	53.57	54.98	56.15	0.08	0.22	0.32	0.22	0.37	0.54
6300	55.20	55.35	56.24	0.07	0.21	0.31	0.21	0.37	0.54
6400	55.48	56.80	57.81	0.06	0.20	0.30	0.20	0.36	0.54
6500	56.81	57.97	58.83	0.05	0.19	0.30	0.20	0.36	0.55
6600	57.69	60.49	65.11	0.04	0.18	0.29	0.18	0.35	0.55
6700	58.98	59.49	65.04	0.03	0.17	0.29	0.18	0.35	0.56
6800	62.87	62.90	65.22	0.03	0.17	0.29	0.18	0.36	0.57
7000	62.19	64.93	65.43	0.02	0.17	0.30	0.17	0.35	0.58
8000	50.87	50.68	49.45	0.02	0.21	0.44	0.14	0.36	0.65
8500	46.23	47.78	45.87	0.04	0.25	0.54	0.12	0.34	0.62
9000	42.40	42.44	41.94	0.07	0.31	0.67	0.10	0.32	0.59
10000	39.34	39.08	40.05	0.14	0.40	0.82	0.01	0.18	0.37
11000	35.96	35.95	36.40	0.17	0.47	0.82	0.09	0.11	0.24
12000	32.53	32.47	29.71	0.20	0.44	0.75	0.13	0.09	0.39
13000	28.96	29.26	29.46	0.09	0.27	0.42	0.22	0.01	0.26
14000	29.76	29.61	29.47	0.02	0.20	0.42	0.27	0.01	0.38
15000	29.08	29.38	29.65	0.09	0.18	0.57	0.34	0.02	0.43






* Temperature test data was based on the underlying chip

Typical Performance Data

FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-55°C	@+25°C	@+125°C
10	0.15	0.18	0.19
50	0.16	0.17	0.18
80	0.16	0.17	0.17
100	0.16	0.17	0.17
150	0.16	0.16	0.17
200	0.16	0.16	0.17
300	0.16	0.16	0.17
400	0.16	0.16	0.17
500	0.16	0.16	0.17
600	0.16	0.16	0.17
700	0.16	0.16	0.17
800	0.16	0.16	0.17
900	0.16	0.17	0.17
1000	0.17	0.17	0.17
1100	0.17	0.17	0.17
1200	0.17	0.17	0.18
1300	0.17	0.17	0.18
1400	0.17	0.18	0.18
1500	0.18	0.18	0.18
1600	0.18	0.18	0.19
1700	0.18	0.19	0.19
1800	0.19	0.19	0.20
1900	0.19	0.19	0.20
2000	0.20	0.20	0.20
2100	0.20	0.20	0.21
2200	0.21	0.21	0.22
2300	0.21	0.22	0.22
2400	0.22	0.22	0.23
2500	0.23	0.23	0.24
2600	0.24	0.24	0.25
2700	0.25	0.25	0.26
2800	0.26	0.27	0.28
2900	0.27	0.28	0.29
3000	0.29	0.29	0.31
3100	0.31	0.32	0.33
3200	0.33	0.34	0.36
3250	0.34	0.35	0.37
3300	0.35	0.37	0.39
3310	0.36	0.37	0.39
3350	0.37	0.38	0.40
3400	0.38	0.40	0.42


* Temperature test data was based on the underlying chip

Typical Performance Curves



* Temperature test data was based on the underlying chip

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Thermal Shock	-55° to 125°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, Except +125°C