

Coaxial High Pass Filter

NON-CATALOG

VHF-1200

50Ω 1220 to 4600 MHz



Maximum Ratings

Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input*	7W max.

* Passband rating, derate linearly to 3W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Features

- rugged unibody construction, small size
- 7 sections
- temperature stable
- excellent power handling, 7W
- low cost

CASE STYLE: FF704


Connectors	Model
SMA	VHF-1200

Price: Contact Sales Dept.

Applications

- sub-harmonic rejection
- transmitters/receivers
- lab use

Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0


Electrical Specifications (T_{AMB}=25°C)

STOP BAND (MHz)		f _{co} , MHz	PASSBAND (MHz)		VSWR (:1)		NO. OF SECTIONS
Min.		Nom.	(loss < 1.3 dB)	(loss < 2 dB)	Typ.	Frequency (MHz)	
(loss > 40 dB)	(loss > 20 dB)	(loss 3 dB) Typ.	Max.	Typ.	Stopband	1.5:1	
750	910	1180	1380-4000	1220-4600	20:1	1300-3200	7

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	104.60	1737.18
500	77.89	124.09
750	49.00	56.04
910	29.02	32.18
1050	13.46	12.18
1130	5.97	4.39
1180	3.08	2.29
1220	1.98	1.62
1300	1.24	1.39
1380	0.97	1.39
3200	0.46	1.43
4000	1.04	2.29
4600	1.72	3.14
7000	4.66	7.56



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. H
M151777
VHF-1200
EDR-6713/2
RVN/AD/AM
150717
Page 1 of 1

Coaxial High Pass Filter

VHF-1200

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	117.74	104.60	114.38	0.00	0.01	0.00	0.00	0.01	0.00
50	72.98	59.82	69.64	0.01	0.00	0.00	0.01	0.00	0.01
100	88.13	70.14	70.06	0.00	0.00	0.02	0.01	0.00	0.01
300	71.68	70.35	69.76	0.01	0.06	0.07	0.01	0.02	0.02
510	78.27	80.18	98.65	0.08	0.13	0.16	0.07	0.11	0.14
690	58.53	57.55	56.78	0.17	0.25	0.30	0.15	0.24	0.27
750	49.71	49.00	48.30	0.22	0.31	0.35	0.19	0.28	0.32
780	45.65	44.95	44.42	0.25	0.34	0.40	0.22	0.30	0.34
825	39.85	39.23	38.67	0.31	0.42	0.47	0.27	0.35	0.40
865	34.91	34.30	33.72	0.34	0.46	0.53	0.30	0.40	0.45
905	30.24	29.62	29.04	0.41	0.53	0.64	0.36	0.45	0.55
910	29.65	29.02	28.45	0.41	0.54	0.65	0.38	0.48	0.57
940	26.17	25.59	24.99	0.51	0.64	0.76	0.40	0.55	0.63
995	20.02	19.45	18.84	0.74	0.90	1.09	0.62	0.77	0.92
1040	15.05	14.53	13.96	1.04	1.29	1.55	0.83	1.05	1.24
1090	9.83	9.40	8.92	1.85	2.28	2.73	1.54	1.88	2.22
1150	4.76	4.57	4.39	4.49	5.40	6.25	3.80	4.44	5.07
1180	3.10	3.08	3.06	6.94	8.13	9.22	5.85	6.65	7.37
1190	2.73	2.73	2.73	7.95	9.26	10.37	6.66	7.48	8.21
1200	2.36	2.40	2.44	9.00	10.37	11.51	7.48	8.31	9.02
1210	2.07	2.16	2.22	10.12	11.50	12.66	8.37	9.19	9.88
1220	1.87	1.98	2.06	11.16	12.55	13.67	9.23	9.98	10.63
1280	1.18	1.35	1.46	15.20	15.73	16.25	13.02	13.44	13.94
1300	1.07	1.24	1.37	15.36	15.73	16.16	13.69	14.07	14.56
1320	1.00	1.15	1.26	15.32	15.63	16.01	14.12	14.49	15.03
1340	0.92	1.08	1.20	15.28	15.58	15.95	14.51	14.97	15.52
1380	0.83	0.97	1.07	15.46	15.77	16.11	15.32	15.87	16.48
1410	0.76	0.90	1.02	15.96	16.27	16.54	16.03	16.66	17.22
1590	0.53	0.66	0.75	18.33	18.31	18.14	19.23	19.56	19.76
2000	0.39	0.51	0.59	17.22	17.22	17.33	17.13	17.11	17.21
2500	0.23	0.34	0.44	23.78	25.05	26.81	23.17	23.31	23.34
3200	0.32	0.46	0.57	14.88	15.01	14.72	14.66	14.69	14.35
3500	0.48	0.63	0.75	11.51	11.60	11.60	11.52	11.44	11.37
4000	0.88	1.04	1.17	8.07	8.15	8.25	8.03	8.04	8.05
4300	1.19	1.37	1.51	6.76	6.79	6.86	6.73	6.71	6.69
4600	1.49	1.72	1.91	5.81	5.73	5.78	5.76	5.67	5.64
5000	1.91	2.21	2.41	4.82	4.69	4.72	4.75	4.67	4.64
5500	2.57	2.82	3.05	3.71	3.79	3.88	3.65	3.74	3.82
6000	3.24	3.45	3.65	2.96	3.13	3.30	2.93	3.08	3.24
6500	3.92	4.03	4.23	2.43	2.67	2.86	2.38	2.62	2.81
7000	4.38	4.66	4.96	2.19	2.31	2.39	2.11	2.26	2.40
7500	4.94	5.44	5.96	1.94	1.96	1.94	1.84	1.88	1.96
8030	8.43	9.66	7.36	2.12	4.13	7.33	1.32	1.78	2.81
9000	11.16	12.58	10.85	0.99	1.58	2.58	1.89	2.94	4.70

REV. X1

VHF-1200

080723

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Coaxial High Pass Filter


Typical Performance Curves

VHF-1200


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X1
VHF-1200
080723
Page 1 of 1

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .04$; 3Pl. $\pm .030$

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I