

High Pass Filter

50Ω 3400 to 9900 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	7W max. at 25°C

*Passband rating, derate linearly to 3W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Features

- Rugged uni-body construction, small size
- 5 sections
- Temperature stable
- Excellent power handling, 7W
- Low cost

Application

- Sub-harmonic rejection and DC blocking
- Transmitters/Receivers
- Lab use

VHF-3100+




CASE STYLE: FF704

Connectors	Model
SMA	VHF-3100+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10


High Pass Filter Electrical Specifications (T_{AMB} = 25°C)

STOPBAND (MHz)		fco, MHz	PASSBAND (MHz)		VSWR		NO. OF SECTIONS
(Loss>30dB)	(Loss>20dB)	Nom.	(Loss<1.5dB)	(Loss<2dB)	Typ.	Frequency	
Typ. DC-F1	Min. DC-F2	Typ. F3	Max. F4-F5	Max.	Stopband	(MHz)	
					1.5:1		
DC-2500	DC-2450	3100	3500-9500	3400-9900	20:1	3100-10500	5

Typical Frequency Response




Electrical schematic




Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	54.69	1737.18
800	32.70	124.09
1810	54.43	64.35
2450	42.98	29.46
2500	36.08	27.59
2700	17.52	16.56
2920	6.49	5.25
3100	2.20	1.89
3400	0.91	1.19
3500	0.83	1.25
5000	0.48	1.16
7000	0.52	1.29
9000	0.87	1.21
9500	0.68	1.24
9900	0.74	1.29
10500	1.04	1.49
11000	2.20	2.45

VHF-3100+
INSERTION LOSS



VHF-3100+
VSWR



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial High Pass Filter

VHF-3100+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	54.49	54.84	55.25	0.00	0.01	0.01	0.01	0.00	0.02
70	51.88	51.71	51.45	0.01	0.00	0.01	0.01	0.01	0.02
80	50.81	50.55	50.29	0.02	0.01	0.01	0.01	0.01	0.02
100	48.81	48.63	48.33	0.02	0.01	0.02	0.00	0.01	0.02
200	42.94	42.74	42.50	0.03	0.01	0.02	0.00	0.02	0.05
300	39.42	39.34	39.23	0.04	0.02	0.03	0.01	0.04	0.07
400	37.11	37.05	36.98	0.04	0.03	0.04	0.03	0.07	0.09
500	35.39	35.39	35.34	0.05	0.03	0.05	0.04	0.09	0.12
600	34.12	34.14	34.13	0.05	0.04	0.06	0.08	0.13	0.17
700	33.19	33.24	33.29	0.05	0.05	0.08	0.10	0.16	0.20
800	32.58	32.60	32.67	0.04	0.06	0.10	0.13	0.20	0.24
900	32.15	32.21	32.30	0.05	0.07	0.11	0.15	0.23	0.27
1000	31.96	32.04	32.17	0.04	0.08	0.13	0.19	0.27	0.31
1100	31.98	32.13	32.29	0.04	0.09	0.14	0.21	0.30	0.34
1200	32.30	32.47	32.66	0.04	0.11	0.15	0.23	0.32	0.36
1300	32.94	33.14	33.37	0.04	0.12	0.16	0.25	0.35	0.39
1400	34.00	34.24	34.49	0.02	0.14	0.18	0.27	0.37	0.41
1500	35.69	35.96	36.26	0.01	0.16	0.20	0.27	0.38	0.43
1600	38.27	38.67	39.07	0.02	0.17	0.22	0.27	0.39	0.43
1700	42.79	43.58	44.22	0.00	0.19	0.23	0.29	0.40	0.46
1800	54.64	56.06	56.44	0.03	0.21	0.28	0.29	0.41	0.47
1810	56.65	57.37	56.33	0.02	0.22	0.27	0.29	0.41	0.47
1900	46.02	45.08	44.22	0.04	0.24	0.29	0.29	0.41	0.49
2000	38.90	38.58	38.21	0.07	0.27	0.31	0.28	0.42	0.49
2100	35.20	35.13	34.92	0.09	0.31	0.35	0.30	0.43	0.52
2200	33.13	33.19	33.11	0.11	0.34	0.39	0.32	0.46	0.57
2300	32.40	32.56	32.63	0.14	0.39	0.46	0.33	0.49	0.61
2400	33.28	33.74	34.07	0.18	0.44	0.52	0.36	0.54	0.67
2450	34.91	35.62	36.21	0.20	0.46	0.56	0.37	0.56	0.70
2500	38.13	39.26	40.03	0.21	0.49	0.59	0.40	0.60	0.75
2600	37.30	34.83	32.96	0.28	0.58	0.72	0.49	0.70	0.88
2700	25.35	24.19	23.16	0.38	0.72	0.92	0.60	0.84	1.04
2800	17.97	17.21	16.46	0.58	0.98	1.25	0.82	1.11	1.35
2920	11.29	10.78	10.18	1.13	1.70	2.16	1.42	1.83	2.21
3000	7.72	7.36	6.94	1.97	2.71	3.35	2.24	2.81	3.33
3100	4.31	4.19	4.03	4.04	5.10	6.01	4.25	5.12	5.86
3400	0.78	1.07	1.24	27.77	31.72	28.63	22.80	24.25	24.08
3500	0.63	0.92	1.08	25.10	26.04	30.80	24.54	26.30	32.28
4000	0.42	0.69	0.86	17.65	19.64	21.71	19.01	21.23	22.78
4500	0.27	0.58	0.77	24.69	27.79	29.97	26.59	33.35	32.05
5000	0.24	0.56	0.75	20.06	23.49	33.24	20.59	24.88	34.76
5500	0.18	0.56	0.79	25.16	21.28	22.19	26.02	21.20	21.06
6000	0.21	0.60	0.84	18.20	18.54	20.23	18.84	18.76	19.56
6500	0.23	0.65	0.93	16.73	16.90	18.21	17.36	16.82	18.49
7000	0.27	0.71	1.07	15.32	16.52	16.40	15.70	16.28	16.66
7500	0.32	0.74	1.01	19.13	19.92	18.11	20.52	20.73	18.38
8000	0.17	0.64	0.96	35.28	28.03	20.77	32.30	27.09	20.10
8500	0.18	0.71	1.01	30.45	32.49	24.76	37.87	59.18	30.40
9000	0.64	1.13	1.36	23.11	21.14	21.96	33.90	32.90	31.50
9500	0.20	0.76	1.12	22.84	21.35	23.37	24.92	21.91	24.28
9900	0.26	0.88	1.31	19.71	16.09	16.77	18.67	15.65	15.68
10000	0.31	0.94	1.37	16.87	15.03	15.95	16.53	14.66	14.36
10500	0.42	0.98	1.43	12.29	13.56	14.57	12.57	13.05	13.82
11000	0.55	1.26	1.79	12.76	12.50	13.49	15.29	16.02	17.77

REV. X2

VHF-3100+

110927

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Coaxial High Pass Filter


Typical Performance Curves

VHF-3100+


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X2
VHF-3100+
110927
Page 1 of 1

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I