

Ultra-Reliable Low Pass Filter

50Ω DC to 5400 MHz

VLP-64

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	19W max. at 25°C

* Passband rating, derate linearly to 0.4xPmax at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Features

- rugged unibody construction
- low insertion loss passband, less than 1 dB typ.
- excellent power handling, 19W
- low cost

Applications

- harmonic rejection
- transmitters/receivers
- lab use




Generic photo used for illustration purposes only

CASE STYLE: FF704

Connectors	Model
SMA	VLP-64

Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0


Electrical Specifications (T_{AMB}=25°C)

PASSBAND (MHz) (loss < 1 dB)	f _{co} , MHz Nom. (loss 3 dB)	STOP BAND (MHz) (loss > 20 dB)	fr20 dB Typ.	VSWR (:1) Passband Typ.
DC-5400	6410	9000	18000	1.1

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50.00	0.09	1.02
1000.00	0.16	1.04
2000.00	0.26	1.10
3000.00	0.38	1.19
4000.00	0.45	1.02
5400.00	0.73	1.11
6410.00	3.76	3.91
7000.00	9.80	11.81
9000.00	26.39	33.93
12000.00	37.61	49.56
15000.00	30.54	69.04
18000.00	27.29	55.01



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.C
M151107
VLP-64
ED-10545B/5
WZ/AD/CP/AM
200522

Coaxial Low Pass Filter (Ultra Reliable)

VLP-64

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.06	0.07	0.08	38.99	36.99	35.70	39.03	37.03	35.59
100	0.06	0.07	0.09	38.03	36.31	35.15	38.55	36.39	34.85
1000	0.14	0.21	0.26	27.72	28.90	30.01	29.51	31.09	32.81
2000	0.19	0.30	0.40	29.68	28.36	28.67	29.72	28.34	28.30
2500	0.24	0.37	0.49	21.23	21.15	21.31	21.60	21.24	21.06
3000	0.30	0.45	0.59	18.07	18.32	18.06	18.04	18.26	17.97
3500	0.34	0.51	0.67	18.48	18.34	17.82	18.01	17.98	17.76
4000	0.35	0.53	0.71	21.24	21.74	21.91	20.53	21.07	21.60
4500	0.36	0.58	0.76	29.81	35.30	36.27	28.51	32.37	34.53
5000	0.43	0.66	0.89	26.21	24.59	23.78	24.94	23.50	23.09
5400	0.54	0.78	1.03	21.75	23.59	24.39	20.80	22.13	22.68
5810	0.67	0.99	1.31	24.54	20.44	18.87	23.09	19.73	18.10
6300	2.27	2.84	3.44	6.22	6.02	5.95	6.22	5.93	5.70
6410	3.12	3.74	4.42	4.60	4.59	4.60	4.61	4.51	4.40
6520	4.09	4.76	5.53	3.40	3.46	3.52	3.49	3.45	3.42
6970	9.00	9.87	10.87	1.27	1.42	1.52	1.23	1.35	1.43
7460	14.08	15.01	15.74	0.61	0.84	1.00	0.67	0.80	0.93
8040	19.42	20.00	20.47	0.39	0.72	1.02	0.41	0.61	0.73
8690	24.36	25.09	25.83	0.32	0.69	1.13	0.31	0.51	0.66
9000	26.73	27.68	28.58	0.29	0.68	1.17	0.26	0.47	0.64
9250	29.04	30.04	30.93	0.25	0.66	1.17	0.23	0.44	0.66
9500	32.02	32.91	33.71	0.22	0.63	1.16	0.17	0.46	0.77
9930	40.71	42.31	43.79	0.25	0.62	1.06	0.15	0.42	0.71
10200	42.96	41.60	39.92	0.26	0.58	0.94	0.14	0.44	0.80
10400	33.55	33.11	32.36	0.30	0.60	0.92	0.23	0.55	0.92
10590	26.55	26.56	26.35	0.52	0.81	1.12	0.44	0.77	1.19
11000	25.15	25.82	27.35	0.40	0.73	0.95	0.40	0.68	0.97
11500	36.16	36.62	37.74	0.03	0.43	0.77	0.13	0.39	0.66
11700	41.04	41.42	42.60	0.02	0.40	0.81	0.08	0.36	0.63
12000	52.18	52.29	52.70	0.02	0.36	0.76	0.13	0.39	0.65
12200	49.72	49.17	48.04	0.06	0.37	0.80	0.02	0.34	0.62
12500	42.26	42.07	41.61	0.04	0.32	0.72	0.02	0.31	0.61
13000	36.79	37.11	37.12	0.01	0.33	0.69	0.02	0.26	0.50
14000	32.44	32.86	33.02	0.01	0.41	0.77	0.03	0.20	0.37
15000	30.68	30.71	30.56	0.09	0.42	0.94	0.01	0.26	0.47
16000	29.18	29.56	29.56	0.12	0.48	1.23	0.04	0.27	0.56
17000	29.97	30.12	30.61	0.07	0.56	1.55	0.00	0.33	0.69
18000	26.83	28.92	30.58	0.44	0.97	1.40	0.13	0.49	0.96
19000	21.69	17.46	16.80	1.42	2.59	2.59	1.07	2.90	3.09
20000	7.23	6.10	5.85	3.99	7.17	13.56	2.33	4.10	6.01

REV. X1

VLP-64

071002

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I