

High Pass Filter

VHF-440+

50Ω 500 to 2500 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input* 7W max. at 25°C

*Passband rating, derate linearly to 3W at 100°C ambient.

Permanent damage may occur if any of these limits are exceeded.

Features

- Rugged uni-body construction, small size
- 7 sections
- Temperature stable
- Excellent power handling, 7W
- Low cost

Applications

- Military
- Sub-harmonic rejection and DC blocking
- Transmitters/Receivers
- Lab use




CASE STYLE: FF704

Connectors	Model
SMA	VHF-440+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch mm)

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10


High Pass Filter Electrical Specifications (T_{AMB} = 25°C)

STOPBAND (MHz) Min.	f _{co} , MHz Nom.	PASSBAND (MHz)		VSWR Typ. Frequency (MHz) Stopband 1.5:1	NO. OF SECTIONS
		(Loss>40dB)	(Loss>20dB)		
230	350	440	600-1700	500-2500	7

typical frequency response





electrical schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	84.17	1737.18
100	80.55	579.06
230	47.11	75.53
350	28.57	18.11
385	13.96	8.77
410	6.58	3.72
440	2.73	1.67
450	2.30	1.54
500	1.41	1.34
510	1.30	1.29
600	0.80	1.12
800	0.54	1.29
1000	0.38	1.10
1500	0.48	1.53
1700	0.69	1.84
2500	1.99	3.54
4000	4.24	6.01



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial High Pass Filter

VHF-440+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
40	89.74	99.08	90.54	0.03	0.01	0.03	0.00	0.01	0.01
45	84.58	93.43	79.33	0.02	0.00	0.02	0.00	0.00	0.01
46	92.73	73.73	89.07	0.02	0.01	0.02	0.00	0.00	0.01
47	86.67	90.74	81.67	0.01	0.01	0.02	0.00	0.00	0.01
48	79.23	79.49	85.14	0.02	0.01	0.02	0.00	0.01	0.01
49	80.48	82.12	77.30	0.02	0.01	0.02	0.00	0.00	0.01
50	85.67	83.08	80.05	0.02	0.01	0.02	0.00	0.01	0.02
55	83.05	78.01	80.19	0.02	0.01	0.02	0.00	0.01	0.02
56	81.66	80.69	99.90	0.02	0.01	0.02	0.00	0.01	0.02
57	87.74	83.44	87.28	0.02	0.01	0.03	0.00	0.01	0.02
58	95.01	82.31	91.27	0.02	0.01	0.03	0.00	0.01	0.02
59	85.68	94.79	84.72	0.02	0.01	0.03	0.01	0.01	0.02
60	89.36	87.26	94.02	0.02	0.01	0.03	0.00	0.01	0.02
65	92.66	92.50	85.05	0.02	0.01	0.03	0.00	0.01	0.02
70	89.72	85.83	95.42	0.02	0.02	0.03	0.00	0.01	0.02
75	97.19	87.17	85.56	0.02	0.02	0.03	0.00	0.02	0.03
76	87.12	85.16	88.20	0.02	0.02	0.03	0.00	0.01	0.03
77	85.88	88.07	90.97	0.02	0.02	0.03	0.00	0.02	0.03
78	94.48	90.34	82.41	0.02	0.02	0.03	0.00	0.02	0.03
79	87.39	86.91	88.99	0.02	0.02	0.03	0.00	0.02	0.03
81	86.32	83.46	88.25	0.02	0.02	0.03	0.00	0.02	0.03
85	82.23	87.13	82.25	0.02	0.02	0.03	0.00	0.02	0.03
90	97.33	84.13	85.81	0.02	0.02	0.04	0.00	0.03	0.04
95	85.26	80.04	91.20	0.03	0.03	0.04	0.00	0.03	0.04
100	81.98	88.05	89.37	0.03	0.03	0.05	0.01	0.03	0.05
150	68.65	69.38	67.78	0.08	0.09	0.12	0.05	0.08	0.10
200	52.70	52.41	52.25	0.16	0.19	0.22	0.13	0.17	0.21
230	46.63	46.51	46.28	0.24	0.26	0.31	0.18	0.24	0.29
300	42.33	42.81	43.30	0.53	0.60	0.68	0.46	0.54	0.62
350	26.87	26.05	25.16	1.08	1.25	1.44	0.89	1.06	1.23
400	7.85	7.56	7.26	4.55	5.40	6.49	3.60	4.22	4.96
440	2.21	2.38	2.55	23.56	24.72	23.60	14.12	14.48	14.65
500	1.18	1.31	1.44	17.38	17.96	18.52	17.87	18.88	19.99
600	0.67	0.79	0.89	23.25	22.34	20.88	24.34	23.17	21.62
700	0.55	0.64	0.72	17.63	17.84	17.22	17.50	17.71	16.99
800	0.45	0.53	0.60	18.12	18.64	18.43	17.82	18.42	18.17
900	0.37	0.44	0.50	21.51	22.38	22.95	21.02	21.79	22.34
1000	0.29	0.37	0.43	31.50	32.42	33.89	28.08	27.96	29.40
1100	0.26	0.34	0.41	30.68	29.54	25.99	27.76	26.87	25.15
1200	0.28	0.35	0.42	20.52	20.98	19.68	20.29	20.69	19.66
1300	0.31	0.39	0.46	16.78	16.84	16.06	16.83	16.88	16.16
1400	0.38	0.46	0.54	14.03	14.17	13.73	14.16	14.31	13.89
1500	0.47	0.55	0.63	12.27	12.23	12.01	12.44	12.42	12.19
1600	0.57	0.65	0.72	10.68	10.76	10.68	10.84	10.93	10.87
1700	0.70	0.79	0.85	9.58	9.58	9.59	9.74	9.75	9.76
1800	0.85	0.93	0.97	8.47	8.60	8.70	8.60	8.76	8.85
1900	0.98	1.07	1.10	7.67	7.77	7.91	7.81	7.91	8.04
2000	1.17	1.24	1.26	6.90	7.06	7.22	7.02	7.19	7.34
2100	1.32	1.40	1.42	6.34	6.44	6.59	6.44	6.57	6.71
2200	1.51	1.60	1.62	5.82	5.91	6.05	5.89	6.03	6.16
2300	1.65	1.77	1.80	5.45	5.46	5.56	5.50	5.55	5.65
2400	1.83	1.95	1.97	5.03	5.04	5.13	5.04	5.13	5.22
2500	1.98	2.14	2.19	4.74	4.69	4.75	4.71	4.76	4.83

REV. X1

VHF-440+

090402

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Coaxial High Pass Filter


Typical Performance Curves

VHF-440+


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X1
VHF-440+
090402
Page 1 of 1




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I